

# Piccolo MCU CAN Module Operation Using the On-Chip Zero-Pin Oscillator

Mark Labbato

## ABSTRACT

CAN protocol imposes rather stringent requirements on its timing source, which are generally met by the provision of an external quartz crystal/oscillator. The TMS320C2803x/TMS320F2806x series of microcontrollers have an on-chip zero-pin oscillator that needs no external components. This application report describes how to use the CAN module with this oscillator to operate at the maximum bit rate and bus length without the added cost of an external clock source. The experimental setup was tested over the entire operating temperature range of the device.

Project collateral and source code discussed in this application report can be downloaded from the following URL: <http://www.ti.com/lit/zip/sprabi7>.

## Contents

1	Introduction .....	1
2	Experiment .....	1
3	Implementation .....	2
4	References .....	3

## 1 Introduction

The CAN module on the Piccolo™ series of devices can operate at up to 1 Mbps. Such high bit-rates across the maximum demand a precision clock source. Accuracy needs to be maintained regardless of the thermal conditions in order to comply with timing requirements imposed by the CAN protocol. Without compensation, the internal oscillator's drift across temperature could negatively impact CAN communication. One solution is to use an external clock source, which adds to overall system cost and complexity. This document explains how to implement CAN protocol using the internal oscillator with compensation for the frequency drift due to temperature. The oscillator compensation method is provided in the header files and a description of the function can be found in the *Oscillator Compensation Guide (SPRAB84)*.

## 2 Experiment

Using the Oscillator Compensation function provided in the header files, the CAN module was able to transmit across a 40 meter cable at full 1 Mbps speed, across the entire temperature range of the device. This was done by connecting two TMS320F2803x devices with a 40 meter cable. The receiving node waits in a loop that uses the compensation function and acknowledges any valid transmission across the bus. The transmitting node sends a message at 1 Mbps. The transmitter toggles GPIO0 with every successful transmission. The transmitter also polls the temperature sensor and then uses the Oscillator Compensation function with every transmission.

Once the system is running, the transmitter is raised to 125°C while the receiver is lowered to -40°C. The transmitter continues to transmit successfully, even while the transmitter and the receiver are on opposite ends of the operating temperatures outlined in the spec. While still running, the transmitter is dropped to -40°C while the receiver is raised to room temperature. Proper communication is observed across the operating temperature range of the device, if the oscillator compensation function is used.

Piccolo is a trademark of Texas Instruments.  
All other trademarks are the property of their respective owners.

### 3 Implementation

The ADC temperature sensor should be sampled at a rate that fulfills the needs of the application in which it is used. If the temperature of the system changes slowly, the compensation function can be called once every few minutes. However, if the ambient temperature fluctuates rapidly, the oscillator may have to be calibrated more frequently. This can be done by having a CPU timer generate an interrupt that does the calibration, or by just placing the necessary code into the main application loop.

The following is the main loop of the provided `CAN_Osc_Comp.c` file:

```
while(1)
{
    /****** Application code goes here******/

    // Sample temperature sensor. Note: the end application
    // will be responsible for deciding how and when to sample
    // the temperature sensor so that the value can be
    // passed to the compensation function

    //Force start of conversion on SOC0 and SOC1
    AdcRegs.ADCSOCFRCl.all = 0x03;

    //Wait for end of conversion.
    while(AdcRegs.ADCINTFLG.bit.ADCINT1 == 0){} //Wait for ADCINT1
    AdcRegs.ADCINTFLGCLR.bit.ADCINT1 = 1;      //Clear ADCINT1

    //Get temp sensor sample result from SOC1
    temp = AdcResult.ADCRESULT1;

    //Use temp sensor measurement to perform oscillator
    // compensation even as temperature changes.
    Osc1Comp(temp);
}
```

Based on the conditions of this experiment, it was necessary to sample the temperature sensor as often as possible. In order to do so, the ADC must be commanded to begin a conversion.

```
AdcRegs.ADCSOCFRCl.all = 0x03;
```

This is done on both SOC0 and SOC1 in order to get an accurate reading.

After the conversion is triggered, the device waits until an end of conversion interrupt is generated, signaling that there is a valid sample in the ADC result registers. The interrupt bit was also reset so that it could be used again in the next iteration of the loop.

```
while(AdcRegs.ADCINTFLG.bit.ADCINT1 == 0){}

AdcRegs.ADCINTFLGCLR.bit.ADCINT1 = 1;      //Clear ADCINT1
```

Since the result of the temperature sensor sampling is stored in the ADC result register, the value can be saved as the current temperature or *temp*.

```
temp = AdcResult.ADCRESULT1;
```

Once the temp is saved, it can be passed to the oscillator compensation function.

```
Osc1Comp(temp);
```

This function uses the new temperature reading to adjust the fine trim value of the oscillator. Because of the application, this function was called in each iteration of the loop in order to keep the temperature as accurate as possible.

#### 4 References

- *Oscillator Compensation Guide* ([SPRAB84](#))
- *Controller Area Network* by Konrad Etschberger. IXXAT Press, 2001.
- *A Comprehensible Guide To Controller Area Network* by Wilfried Voss. Copperhill Technologies, 2005.

## IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

### Products

Audio	<a href="http://www.ti.com/audio">www.ti.com/audio</a>
Amplifiers	<a href="http://amplifier.ti.com">amplifier.ti.com</a>
Data Converters	<a href="http://dataconverter.ti.com">dataconverter.ti.com</a>
DLP® Products	<a href="http://www.dlp.com">www.dlp.com</a>
DSP	<a href="http://dsp.ti.com">dsp.ti.com</a>
Clocks and Timers	<a href="http://www.ti.com/clocks">www.ti.com/clocks</a>
Interface	<a href="http://interface.ti.com">interface.ti.com</a>
Logic	<a href="http://logic.ti.com">logic.ti.com</a>
Power Mgmt	<a href="http://power.ti.com">power.ti.com</a>
Microcontrollers	<a href="http://microcontroller.ti.com">microcontroller.ti.com</a>
RFID	<a href="http://www.ti-rfid.com">www.ti-rfid.com</a>
RF/IF and ZigBee® Solutions	<a href="http://www.ti.com/lprf">www.ti.com/lprf</a>

### Applications

Communications and Telecom	<a href="http://www.ti.com/communications">www.ti.com/communications</a>
Computers and Peripherals	<a href="http://www.ti.com/computers">www.ti.com/computers</a>
Consumer Electronics	<a href="http://www.ti.com/consumer-apps">www.ti.com/consumer-apps</a>
Energy and Lighting	<a href="http://www.ti.com/energy">www.ti.com/energy</a>
Industrial	<a href="http://www.ti.com/industrial">www.ti.com/industrial</a>
Medical	<a href="http://www.ti.com/medical">www.ti.com/medical</a>
Security	<a href="http://www.ti.com/security">www.ti.com/security</a>
Space, Avionics and Defense	<a href="http://www.ti.com/space-avionics-defense">www.ti.com/space-avionics-defense</a>
Transportation and Automotive	<a href="http://www.ti.com/automotive">www.ti.com/automotive</a>
Video and Imaging	<a href="http://www.ti.com/video">www.ti.com/video</a>
Wireless	<a href="http://www.ti.com/wireless-apps">www.ti.com/wireless-apps</a>

TI E2E Community Home Page

[e2e.ti.com](http://e2e.ti.com)

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2011, Texas Instruments Incorporated