


NOTES:

- 1. MATERIAL: LEADER TECH FLEX-TECH NPB SLOT LOK PRO.
- 2. INSIDE HEIGHT: .500" ; OUTSIDE HEIGHT: .515"
- 3. PULL TABS INCLUDED ON THE COVER.
- 4. THREE MOUSE HOLES DESIGNATED IN DESIGN ON BOTTOM SIDE.
- 5. FENCE DIMENSIONS DESIGNATED AT CENTERLINE.
- 6. SINGLE CABITY SHIELD FRAME WITH 1 WELD.
- 7. STANDARD DIMPLE SPACING: .400"
- 8. LOCATOR PINS TO BE STANDARD .040 X .060 LG



LEADER TECH P/N: SL-11101

UNLESS OTHERWISE SPECIFIED  DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS +/- .01 3 PL DECIMALS +/- .005 ANGLES ° FRACTIONS ⁄	SIGNATURES	DATE	TEXAS INSTRUMENTS	
	JV SMITH	01-05-12	RF SHIELD DRAWING	
	J SETON	01-05-12	TSW3085 REV D	
			SIZE	DWG NO
			SCALE	SHEET 1 OF 1