


NOTES: UNLESS OTHERWISE SPECIFIED:

© COPYRIGHT 2014 TEXAS INSTRUMENTS
UNPUBLISHED, ALL RIGHTS RESERVED

DWG NO GREEN LED HEATSINK SUBASSEMBLY		SHEET 1	1
REVISIONS			
REV	DESCRIPTION	DATE	BY
A	INITIAL DRAWING RELEASE	8/31/17	JCC
B	BOM AND BALLOONS UPDATE	10/10/17	JCC



ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
1	P33-EVM_GRN_LED_FAN	30x30x10mm 5VDC Fan (Sunon Fans)	1
2	P33-EVM-FAN-SHROUD	FAN SHROUD	1
3	91294A536	M3x35mm BLACK FHSCS (McMaster-Carr)	2
4	P33-EVM-GREEN-ADAPTOR	Green LED Mounting Plate	1
5	91294A003	M2x5mm Black Steel FHSCS (McMaster-Carr)	2
6	08346	Finger Guard 30mm Metal (Qualtek)	1
7	90710A030	M3x0.5 SS Thin HN (McMaster-Carr)	2
8	3-1212206U_GreenLED	3-1212206U (Cool Innovations)	1
9	120MM-1M-0.5MM-5590H - 33.4x28.0mm	120MM-1M-0.5MM-5590H (3M)	1
10	120MM-1M-0.5MM-5590H-31.1x31.1x0.5mm	120MM-1M-0.5MM-5590H (3M)	1

UNLESS OTHERWISE SPECIFIED

- DIMENSIONS ARE IN MILLIMETERS
- TOLERANCES: ANGLES $\pm 1^\circ$
2 PLACE DECIMALS ± 0.25
1 PLACE DECIMALS ± 0.50
- DIMENSIONAL LIMITS APPLY BEFORE PROCESSES
- INTERPRET DIMENSIONS IN ACCORDANCE WITH ASME Y14.5M-1994
- REMOVE ALL BURRS AND SHARP EDGES
- PARENTHETICAL INFO FOR REF ONLY

DWN Justin Chambliss	DATE 9/1/2017
Engr Justin Chambliss	8/31/2017
CQE/QA	
CM	
Apprvd	



P33 EVM KIT GREEN LED HEATSINK
SUBASSEMBLY

SIZE B	DWG NO Green LED Heatsink SubAssembly	REV B
SCALE 1:2		SHEET 1 OF 1



NEXT ASSY	USED ON
APPLICATION	