

## TAPE AND REEL INFORMATION



\*All dimensions are nominal

| Device         | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|----------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| DAC8311IDCKR   | SC70         | DCK             | 6    | 3000 | 180.0              | 8.4                | 2.2     | 2.5     | 1.2     | 4.0     | 8.0    | Q3            |
| DAC8311IDCKRG4 | SC70         | DCK             | 6    | 3000 | 180.0              | 8.4                | 2.2     | 2.5     | 1.2     | 4.0     | 8.0    | Q3            |
| DAC8311IDCKT   | SC70         | DCK             | 6    | 250  | 180.0              | 8.4                | 2.2     | 2.5     | 1.2     | 4.0     | 8.0    | Q3            |
| DAC8411IDCKR   | SC70         | DCK             | 6    | 3000 | 180.0              | 8.4                | 2.2     | 2.5     | 1.2     | 4.0     | 8.0    | Q3            |
| DAC8411IDCKT   | SC70         | DCK             | 6    | 250  | 180.0              | 8.4                | 2.2     | 2.5     | 1.2     | 4.0     | 8.0    | Q3            |

## TAPE AND REEL BOX DIMENSIONS



\*All dimensions are nominal

| Device         | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|----------------|--------------|-----------------|------|------|-------------|------------|-------------|
| DAC8311IDCKR   | SC70         | DCK             | 6    | 3000 | 200.0       | 183.0      | 25.0        |
| DAC8311IDCKRG4 | SC70         | DCK             | 6    | 3000 | 200.0       | 183.0      | 25.0        |
| DAC8311IDCKT   | SC70         | DCK             | 6    | 250  | 200.0       | 183.0      | 25.0        |
| DAC8411IDCKR   | SC70         | DCK             | 6    | 3000 | 200.0       | 183.0      | 25.0        |
| DAC8411IDCKT   | SC70         | DCK             | 6    | 250  | 200.0       | 183.0      | 25.0        |