

## TAPE AND REEL INFORMATION



\*All dimensions are nominal

| Device           | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|------------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| LMC6482AIMX/NOPB | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| LMC6482AIMX/NOPB | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.5     | 5.4     | 2.0     | 8.0     | 12.0   | Q1            |
| LMC6482IMMX/NOPB | VSSOP        | DGK             | 8    | 3500 | 330.0              | 12.4               | 5.3     | 3.4     | 1.4     | 8.0     | 12.0   | Q1            |
| LMC6482IMMX/NOPB | VSSOP        | DGK             | 8    | 3500 | 330.0              | 12.4               | 5.3     | 3.4     | 1.4     | 8.0     | 12.0   | Q1            |
| LMC6482IMX/NOPB  | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| LMC6484AIMX/NOPB | SOIC         | D               | 14   | 2500 | 330.0              | 16.4               | 6.5     | 9.35    | 2.3     | 8.0     | 16.0   | Q1            |
| LMC6484AIMX/NOPB | SOIC         | D               | 14   | 2500 | 330.0              | 16.4               | 6.5     | 9.0     | 2.1     | 8.0     | 16.0   | Q1            |
| LMC6484IMX/NOPB  | SOIC         | D               | 14   | 2500 | 330.0              | 16.4               | 6.5     | 9.0     | 2.1     | 8.0     | 16.0   | Q1            |

## TAPE AND REEL BOX DIMENSIONS



\*All dimensions are nominal

| Device           | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|------------------|--------------|-----------------|------|------|-------------|------------|-------------|
| LMC6482AIMX/NOPB | SOIC         | D               | 8    | 2500 | 353.0       | 353.0      | 32.0        |
| LMC6482AIMX/NOPB | SOIC         | D               | 8    | 2500 | 367.0       | 367.0      | 35.0        |
| LMC6482IMMX/NOPB | VSSOP        | DGK             | 8    | 3500 | 367.0       | 367.0      | 35.0        |
| LMC6482IMMX/NOPB | VSSOP        | DGK             | 8    | 3500 | 353.0       | 353.0      | 32.0        |
| LMC6482IMX/NOPB  | SOIC         | D               | 8    | 2500 | 353.0       | 353.0      | 32.0        |
| LMC6484AIMX/NOPB | SOIC         | D               | 14   | 2500 | 367.0       | 367.0      | 35.0        |
| LMC6484AIMX/NOPB | SOIC         | D               | 14   | 2500 | 353.0       | 353.0      | 32.0        |
| LMC6484IMX/NOPB  | SOIC         | D               | 14   | 2500 | 353.0       | 353.0      | 32.0        |

**TUBE**


\*All dimensions are nominal

| Device             | Package Name | Package Type | Pins | SPQ | L (mm) | W (mm) | T (μm) | B (mm) |
|--------------------|--------------|--------------|------|-----|--------|--------|--------|--------|
| LMC6482AIN/NOPB    | P            | PDIP         | 8    | 40  | 506    | 13.97  | 11230  | 4.32   |
| LMC6482AIN/NOPB    | P            | PDIP         | 8    | 40  | 502    | 14     | 11938  | 4.32   |
| LMC6482AIN/NOPB.A  | P            | PDIP         | 8    | 40  | 506    | 13.97  | 11230  | 4.32   |
| LMC6482AIN/NOPB.A  | P            | PDIP         | 8    | 40  | 502    | 14     | 11938  | 4.32   |
| LMC6482AIN/NOPB.B  | P            | PDIP         | 8    | 40  | 502    | 14     | 11938  | 4.32   |
| LMC6482AIN/NOPB.B  | P            | PDIP         | 8    | 40  | 506    | 13.97  | 11230  | 4.32   |
| LMC6482IN/NOPB     | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| LMC6482IN/NOPB.A   | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| LMC6482IN/NOPBG4   | P            | PDIP         | 8    | 40  | 506    | 13.97  | 11230  | 4.32   |
| LMC6482IN/NOPBG4.A | P            | PDIP         | 8    | 40  | 506    | 13.97  | 11230  | 4.32   |
| LMC6484AIN/NOPB    | N            | PDIP         | 14   | 25  | 502    | 14     | 11938  | 4.32   |
| LMC6484AIN/NOPB.A  | N            | PDIP         | 14   | 25  | 502    | 14     | 11938  | 4.32   |
| LMC6484IN/NOPB     | N            | PDIP         | 14   | 25  | 502    | 14     | 11938  | 4.32   |
| LMC6484IN/NOPB.A   | N            | PDIP         | 14   | 25  | 502    | 14     | 11938  | 4.32   |