

## TAPE AND REEL INFORMATION



\*All dimensions are nominal

| Device       | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|--------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| OPA182IDBVR  | SOT-23       | DBV             | 5    | 3000 | 178.0              | 9.0                | 3.3     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| OPA182IDBVT  | SOT-23       | DBV             | 5    | 250  | 178.0              | 9.0                | 3.3     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| OPA182IDR    | SOIC         | D               | 8    | 3000 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| OPA182IDT    | SOIC         | D               | 8    | 250  | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| OPA2182IDGKR | VSSOP        | DGK             | 8    | 2500 | 330.0              | 12.4               | 5.25    | 3.35    | 1.25    | 8.0     | 12.0   | Q1            |
| OPA2182IDGKT | VSSOP        | DGK             | 8    | 250  | 330.0              | 12.4               | 5.25    | 3.35    | 1.25    | 8.0     | 12.0   | Q1            |
| OPA2182IDR   | SOIC         | D               | 8    | 2500 | 330.0              | 12.8               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| OPA4182IDR   | SOIC         | D               | 14   | 3000 | 330.0              | 16.4               | 6.5     | 9.5     | 2.3     | 8.0     | 16.0   | Q1            |
| OPA4182IDT   | SOIC         | D               | 14   | 250  | 330.0              | 16.4               | 6.5     | 9.5     | 2.3     | 8.0     | 16.0   | Q1            |

## TAPE AND REEL BOX DIMENSIONS



\*All dimensions are nominal

| Device       | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|--------------|--------------|-----------------|------|------|-------------|------------|-------------|
| OPA182IDBVR  | SOT-23       | DBV             | 5    | 3000 | 190.0       | 190.0      | 30.0        |
| OPA182IDBVT  | SOT-23       | DBV             | 5    | 250  | 190.0       | 190.0      | 30.0        |
| OPA182IDR    | SOIC         | D               | 8    | 3000 | 366.0       | 364.0      | 50.0        |
| OPA182IDT    | SOIC         | D               | 8    | 250  | 366.0       | 364.0      | 50.0        |
| OPA2182IDGKR | VSSOP        | DGK             | 8    | 2500 | 366.0       | 364.0      | 50.0        |
| OPA2182IDGKT | VSSOP        | DGK             | 8    | 250  | 366.0       | 364.0      | 50.0        |
| OPA2182IDR   | SOIC         | D               | 8    | 2500 | 366.0       | 364.0      | 50.0        |
| OPA4182IDR   | SOIC         | D               | 14   | 3000 | 366.0       | 364.0      | 50.0        |
| OPA4182IDT   | SOIC         | D               | 14   | 250  | 366.0       | 364.0      | 50.0        |

## TUBE



\*All dimensions are nominal

| Device      | Package Name | Package Type | Pins | SPQ | L (mm) | W (mm) | T (μm) | B (mm) |
|-------------|--------------|--------------|------|-----|--------|--------|--------|--------|
| OPA2182ID   | D            | SOIC         | 8    | 75  | 509    | 7.9    | 3800   | 2.81   |
| OPA2182ID.B | D            | SOIC         | 8    | 75  | 509    | 7.9    | 3800   | 2.81   |