

## TAPE AND REEL INFORMATION



\*All dimensions are nominal

| Device         | Package Type     | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|----------------|------------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| TPS74901DRCR   | VSON             | DRC             | 10   | 3000 | 330.0              | 12.4               | 3.3     | 3.3     | 1.1     | 8.0     | 12.0   | Q2            |
| TPS74901DRCRG4 | VSON             | DRC             | 10   | 3000 | 330.0              | 12.4               | 3.3     | 3.3     | 1.1     | 8.0     | 12.0   | Q2            |
| TPS74901DRCRM3 | VSON             | DRC             | 10   | 3000 | 330.0              | 12.4               | 3.3     | 3.3     | 1.1     | 8.0     | 12.0   | Q2            |
| TPS74901DRCT   | VSON             | DRC             | 10   | 250  | 180.0              | 12.4               | 3.3     | 3.3     | 1.1     | 8.0     | 12.0   | Q2            |
| TPS74901KTWR   | DDPAK/<br>TO-263 | KTW             | 7    | 500  | 330.0              | 24.4               | 10.6    | 15.8    | 4.9     | 16.0    | 24.0   | Q2            |
| TPS74901RGWR   | VQFN             | RGW             | 20   | 3000 | 330.0              | 12.4               | 5.3     | 5.3     | 1.1     | 8.0     | 12.0   | Q2            |
| TPS74901RGWRM3 | VQFN             | RGW             | 20   | 3000 | 330.0              | 12.4               | 5.3     | 5.3     | 1.1     | 8.0     | 12.0   | Q2            |
| TPS74901RGWT   | VQFN             | RGW             | 20   | 250  | 180.0              | 12.4               | 5.3     | 5.3     | 1.1     | 8.0     | 12.0   | Q2            |

## TAPE AND REEL BOX DIMENSIONS



\*All dimensions are nominal

| Device         | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|----------------|--------------|-----------------|------|------|-------------|------------|-------------|
| TPS74901DRCR   | VSON         | DRC             | 10   | 3000 | 367.0       | 367.0      | 35.0        |
| TPS74901DRCRG4 | VSON         | DRC             | 10   | 3000 | 367.0       | 367.0      | 35.0        |
| TPS74901DRCRM3 | VSON         | DRC             | 10   | 3000 | 367.0       | 367.0      | 35.0        |
| TPS74901DRCT   | VSON         | DRC             | 10   | 250  | 210.0       | 185.0      | 35.0        |
| TPS74901KTWR   | DDPAK/TO-263 | KTW             | 7    | 500  | 356.0       | 356.0      | 45.0        |
| TPS74901RGWR   | VQFN         | RGW             | 20   | 3000 | 367.0       | 367.0      | 35.0        |
| TPS74901RGWRM3 | VQFN         | RGW             | 20   | 3000 | 367.0       | 367.0      | 35.0        |
| TPS74901RGWT   | VQFN         | RGW             | 20   | 250  | 210.0       | 185.0      | 35.0        |