

## NOTES:

1. PCB VENDOR MUST BE UL QUALIFIED
2. BOARD MUST BE IDENTIFIED WITH APPROPRIATE VENDOR UL IDENTIFICATION MARK, DATE CODE
3. PCB MATERIAL UL FLAMMABILITY RATING( 94V-0 MINIMUM)
4. ALL DIMENSION TOLERANCE AS BELOW UNLESS OTHERWISE SPECIFIED.
5. PCB LAYERS : 2 LAYERS
6. PCB THICKNESS : 1.0 mm+/-0.1 mm
7. TRACE WIDTHS TO BE FINISHED SIZES+/-1MIL
8. TOP SIDE SILKSCREEN : WHITE  
BOTTOM SIDE SILKSCREEN: WHITE
9. SOLDER MASK : RED , BOTH SIDES
10. MATERIAL : HF FR4 TG: 150 CELSIUS
11. PLATING : OSP 0.2-0.6um[8-24uinch] )
12. PCB Outline Dimension Tol: ROUTING : +/- 0.13mm



