



LIMITS UNLESS OTHERWISE NOTED				
1-6	±0.05	300-1000	±0.5	
6-30	±0.05	1000-2000	±1.0	
30-100	±0.1	2000-	±2.0	
100-300	±0.2	ANGLE	±0.5°	

GP-04-003F3 Rev.A