

INSTRUMENTS

TEXAS

CC5241 P2 1.1

TPVDD	TP10
TPGND	TP17
TP34	TP10
TP32	TP12
TP50	TP14
TP5	
TP3	
TP0	
TP11	




A1


X1


FL1

X2

U1










L1: TOP CONDUCTOR - COPPER 0.035 MM

* DIELECTRIC - FR-4 0.8 MM

L2: BOTTOM CONDUCTOR - COPPER 0.035 MM

DESIGN CROSS SECTION CHART

TOTAL THICKNESS 0.87 MM



DRILL CHART: TOP to BOTTOM			
ALL UNITS ARE IN MILLIMETERS			
FIGURE	SIZE	PLATED	QTY
⊙	0.2	PLATED	62
.	0.5	PLATED	14