采用 MicroSiP™ 封装并具有集成电感器的 TPSM82903 3A 3V 至 17V，高效率和低 I_Q 降压转换器模块

1 特性

- 在宽占空比和负载范围内可实现高效率
  - I_Q：4μA（典型值）
  - 62mΩ 高侧和 22mΩ 低侧 $R_{DS(ON)}$
- 3mm × 2.8mm × 1.6mm MicroSiP™ 封装
- 高达 3A 的持续输出电流
- 整个温度范围（-40°C 至 125°C）内的反馈电压精度达 ±0.9%
- 可配置的输出电压选项：
  - V_{FB} 外部分压器：0.6V 至 5.5V
  - V_{SET} 内部分压器：16 个电压选项（0.4V 至 5.5V）
- 带 100% 模式的 DCS-Control 拓扑
- 通过 MODE/S-CONF 引脚实现灵活性
  - 2.5MHz 或 1.0MHz 开关频率
  - 具有动态模式更改选项的强制 PWM 或自动 (PFM) 省电模式
  - 自动效率增强 (AEE)
  - 输出放电开/关
- 高度灵活且易于使用
  - 针对单层布线的引脚排列进行了优化
  - 精密使能输入
  - 电源正常状态输出
  - 可调软启动和跟踪
- 无需外部自举电容器
- 使用 TPSM82903 并借助 WEBENCH® Power Designer 创建定制设计方案

2 应用

- 数据中心和企业级计算
- 有线网络
- 无线基础设施
- 工厂自动化和控制
- 测试和测量



简化版原理图

3 说明

TPSM82903 是一款高效、小巧、灵活且易用的同步降压直流/直流转换器 MicroSiP 封装模块。2.5MHz 或 1.0MHz 的可选开关频率支持使用小型元件，并提供快速瞬态响应。该器件利用 DCS-Control 拓扑支持 ± 1% 的高 V_{OUT} 精度。3V 至 17V 的宽输入电压范围支持各种标称输入，例如 12V 电源轨、单节或多节锂离子电池、5V 或 3.3V 电源轨。

TPSM82903 可在轻负载时自动进入省电模式（如果选择了自动 PFM/PWM）以保持高效率。此外，为了在非常小的负载下提供高效率，该器件具有 4μA 的低典型静态电流。AEE（如果启用）可在 V_{IN}、V_{OUT} 和负载电流范围内提供高效率。该器件包含一个 MODE/Smart-CONF 输入，用来设置内部/外部分压器、开关频率、输出电压放电和自动省电模式或强制 PWM 操作。

该器件采用小型 11 引脚 MicroSiP 封装，尺寸为 3.0mm × 2.8mm × 1.6mm，带有集成 1μH 电感器。

封装信息

器件型号	封装(1)	封装尺寸（标称值）
TPSM82903	SIS (uSiP, 11)	3.00mm × 2.80mm

(1) 如需了解所有可用封装，请参阅数据表末尾的可订购产品附录。



效率与输出电流间的关系（频率为 2.5MHz 时 V_O 为 1.2V，自动 PFM/PWM）

本文档旨在为方便起见，提供有关 TI 产品中文版本的信息，以确认产品的概要。有关适用的官方英文版本的最新信息，请访问 www.ti.com，其内容始终优先。TI 不保证翻译的准确性和有效性。在实际设计之前，请务必参考最新版本的英文版本。

Table of Contents

1 特性.....1
2 应用.....1
3 说明.....1
4 Revision History.....2
5 Pin Configuration and Functions.....3
6 Specifications.....4
6.1 Absolute Maximum Ratings.....4
6.2 ESD Ratings.....4
6.3 Recommended Operating Conditions.....4
6.4 Thermal Information.....5
6.5 Electrical Characteristics.....5
6.6 Typical Characteristics.....7
7 Detailed Description.....8
7.1 Overview.....8
7.2 Functional Block Diagram.....8
7.3 Feature Description.....9
7.4 Device Functional Modes.....14
8 Application and Implementation.....17
8.1 Application Information.....17
8.2 Typical Application with Adjustable Output Voltage.....17
8.3 Typical Application with Setable V_O Using VSET.....29
8.4 Power Supply Recommendations.....32
8.5 Layout.....32
9 Device and Documentation Support.....35
9.1 Device Support.....35
9.2 接收文档更新通知.....35
9.3 支持资源.....35
9.4 Trademarks.....35
9.5 Electrostatic Discharge Caution.....35
9.6 术语表.....35
10 Mechanical, Packaging, and Orderable Information.....36

4 Revision History

注：以前版本的页码可能与当前版本的页码不同

Changes from Revision A (October 2022) to Revision B (November 2022)	Page
• 将状态从“预告信息”更改为“量产数据”	1

Changes from Revision * (February 2022) to Revision A (October 2022)	Page
• 通篇更新了商标信息	1
• Added Peak reflow case temperature	4
• Added Maximum number of reflows allowed	4
• Added Mil-STD-883D, Method 2002.3, 1 msec, 1/2 sine, mounted	4
• Added Mil-STD-883D, Method 2007.2, 20 to 2000 Hz	4
• Updated 图 8-4 “SW” pin to “VOUT” pin to reflect accurate pin name	19

Copyright © 2022 Texas Instruments Incorporated

5 Pin Configuration and Functions



图 5-1. 11-Pin SIS MicroSiP™ Package (Top View, Device Pins Face Down)

表 5-1. Pin Functions

Pin		I/O	Description
Name	Number		
VIN	1, 2	I	Power supply input pin. Ensure the input capacitor is connected as close as possible between the VIN and GND pins.
EN	3	I	Enable input pin. Connect to logic low to disable the device. Pull high to enable the device. Do not leave this pin unconnected.
MODE/ S-CONF	4	I	Device mode selection (auto PFM/PWM or forced PWM operation) and SmartConfig™ application. Connect high, low, or to a resistor to configure the device according to 表 7-2. Do not leave this pin unconnected.
SS/TR	5	I	Soft start/tracking pin. An external capacitor connected from this pin to GND defines the rise time for the internal reference voltage. The pin can also be used as an input for tracking and sequencing. The pin can be left floating for the fastest ramp-up time.
PG	6	O	Open-drain power-good output. High = V_{OUT} is ready. Low = V_{OUT} is below nominal regulation. This pin requires a pullup resistor.
FB/VSET	7	I	Depends on device configuration (see 节 7.3.1) • FB: Voltage feedback input. Connect a resistive output voltage divider to this pin. • VSET: Output voltage setting pin. Connect a resistor to GND to choose the output voltage according to 表 7-3.
SW/NC	8	NC	Switch pin of the converter. Do not connect, leave floating.
VOUT	9, 10	O	Output voltage pin. Connect directly to the positive pin of the output capacitor.
GND	11	—	Ground pin. It must be connected directly to the common ground plane. It must be soldered to achieve appropriate power dissipation and mechanical reliability.

Copyright © 2022 Texas Instruments Incorporated

6 Specifications

6.1 Absolute Maximum Ratings

over operating temperature range (unless otherwise noted)(1)

		MIN	MAX	UNIT
Voltage(2)	VIN	–0.3	18	V
	EN, PG	–0.3	18	
	MODE/S-CONF	–0.3	18	
	FB/VSET, SS/TR, VOUT	–0.3	6	
T_J	Junction temperature	–55	125	°C
	Peak reflow case temperature		260	°C
	Maximum number of reflows allowed		3	
Mechanical shock	Mil-STD-883D, Method 2002.3, 1 msec, 1/2 sine, mounted		1500	G
Mechanical vibration	Mil-STD-883D, Method 2007.2, 20 to 2000 Hz		20	G
T_{stg}	Storage temperature	–55	125	°C

(1) Operation outside the Absolute Maximum Ratings may cause permanent device damage. Absolute Maximum Ratings do not imply functional operation of the device at these or any other conditions beyond those listed under Recommended Operating Conditions. If used outside the Recommended Operating Conditions but within the Absolute Maximum Ratings, the device may not be fully functional, and this may affect device reliability, functionality, performance, and shorten the device lifetime.
(2) All voltage values are with respect to network ground terminal.

6.2 ESD Ratings

			VALUE	UNIT
$V_{(ESD)}$	Electrostatic discharge	Human body model (HBM), per ANSI/ESDA/JEDEC JS-001, all pins(1)	±2000	V
		Charged device model (CDM), per ANSI/ESDA/JEDEC JS-002, all pins(2)	±500	

(1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.
(2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

6.3 Recommended Operating Conditions

Over operating junction temperature range (unless otherwise noted)

		MIN	NOM	MAX	UNIT
V_I	Input voltage range	3.0		17	V
V_O	Output voltage range	0.4		5.5	V
C_I	Effective input capacitance	3	10		µF
C_O	Effective output capacitance (2.5MHz selection)	10	22	100 (1)	µF
C_O	Effective output capacitance (1.0MHz selection)	6	22	50 (1)	µF
I_{OUT}	Output current	0		3	A
I_{SINK_PG}	Sink current at PG-Pin			1	mA
T_J	Junction temperature (2)	-40		125	°C

(1) This is for capacitors directly at the output of the device. More capacitance is allowed if there is a series resistance associated to the capacitor.
(2) Operating lifetime is derated at junction temperatures greater than 125°C.

Copyright © 2022 Texas Instruments Incorporated

6.4 Thermal Information

THERMAL METRIC[1]		TPSM8290x uSIP11-Pin		UNIT
		JEDEC PCB	TPSM8290xEVM-188	
$R_{\theta JA}$	Junction-to-ambient thermal resistance	58.2	48.7	°C/W
$R_{\theta JC(top)}$	Junction-to-case (top) thermal resistance	34.5		°C/W
$R_{\theta JB}$	Junction-to-board thermal resistance	26.9		°C/W
Ψ_{JT}	Junction-to-top characterization parameter	0.3	0.8	°C/W
Ψ_{JB}	Junction-to-board characterization parameter	26.6	27.8	°C/W
$R_{\theta JC(bot)}$	Junction-to-case (bottom) thermal resistance	26.0		°C/W

(1) For more information about traditional and new thermal metrics, see the Semiconductor and IC Package Thermal Metrics application report.

6.5 Electrical Characteristics

V_I = 3 V to 17 V, T_J = -40°C to +125°C, Typical values at V_I = 12.0 V and T_A = 25°C,unless otherwise noted

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
SUPPLY						
I_{Q_PSM}	Operating Quiescent Current (Power Save Mode)	Iout = 0 mA, device not switching		4		µA
I_{Q_PWM}	Operating Quiescent Current (PWM Mode)	VIN=12 V, VOUT=1.2 V; Iout = 0 mA, device switching		8		mA
I_{SD}	Shutdown current into VIN pin	EN = 0 V		0.27	3.5	µA
V_{UVLO}	Under Voltage Lock-Out	V_{IN} rising	2.85	2.925	3.0	V
	Under Voltage Lock-Out	V_{IN} falling	2.7	2.775	2.85	V
V_{UVLO_HYS}	Under Voltage Lock-Out Hysteresis	Hysteresis		150		mV
CONTROL & INTERFACE						
I_{LKG}	EN Input leakage current	EN = 12 V		10	300	nA
V_{IH_MODE}	High-Level Input Voltage at MODE/S-CONF-Pin		1.0			V
T_{SD}	Thermal Shutdown Threshold	T_J rising		170		°C
	Thermal Shutdown Hysteresis	Hysteresis		20		
V_{IH}	High-level input voltage at EN-Pin		0.97	1.0	1.03	V
V_{IL}	Low-level input voltage at EN-Pin		0.87	0.9	0.93	V
R_{EN_PD}	Smart-Enable Internal Pulldown Resistor	EN = LOW		0.5		MΩ
V_{PG}	Power good threshold	V_{FB} rising, referenced to V_{FB} nominal	93.5%	96%	99%	
		V_{FB} falling, referenced to V_{FB} nominal	88.5%	93%	96%	
		Hysteresis	1.5%	3.5%	6%	
V_{PG_OL}	Low-level output voltage at PG pin	I_{SINK} = 1 mA			0.4	V
I_{PG_LKG}	Input leakage current into PG pin	V_{PG} = 5 V		15	550	nA
t_{PG_DLY}	Power good delay time	V_{FB} falling		32		µs
R_{SET}	S-CONF/VSET Resistor Tolerance		-4		+4	%
C_{SET}	Maximum Capacitance connected to S-CONF/VSET Pins				30	pF
POWER SWITCHES						
I_{LKG_SW}	Leakage current into SW-Pin	V_{SW} = V_{OS} = 5.5 V		2	7	µA
R_{DS_ON}	High-side FET on resistance	V_{IN} > 4 V, I_{SW} = 500 mA		62	111	mΩ
	Low-side FET on resistance	V_{IN} > 4 V, I_{SW} = 500 mA		22	40	

Copyright © 2022 Texas Instruments Incorporated

6.5 Electrical Characteristics (continued)

V_I = 3 V to 17 V, T_J = -40°C to +125°C, Typical values at V_I = 12.0 V and T_A = 25°C,unless otherwise noted

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
I_{LIM}	High-side FET current limit		4.1	4.9	5.8	A
	Low-side FET current limit		3.8	4.3	4.7	A
I_{LIM_SINK}	Low-side FET sink current limit		1.3	1.7	2.5	A
f_{SW}	Switching frequency	2.5-MHz selection		2.5		MHz
$T_{ON(MIN)}$	Minimum On-time			50		ns
f_{SW}	Switching frequency	1.0-MHz selection		1.0		MHz
D	Dutycycle				1	
R_{PD}	Dropout resistance	100% mode, V_{IN} > 4 V		100		mΩ
OUTPUT						
V_{O_Reg1}	Output Voltage Regulation	VSET Configuration selected. T_J = 25°C.	-0.9%		+0.9%	
V_{O_Reg2}	Output Voltage Regulation	VSET Configuration selected. 0 °C< T_J < 85°C	-1.1%		+1.1%	
V_{O_Reg3}	Output Voltage Regulation	VSET Configuration selected. -40°C < T_J < 125°C	-1.25%		+1.25%	
V_{FB}	Feedback Regulation Voltage	Adjustable Configuration selected		0.6		V
V_{FB_Reg1}	Feedback Voltage Regulation	FB-Option selected. T_J = 25°C.	-0.6%		+0.6%	
V_{FB_Reg2}	Feedback Voltage Regulation	FB-Option selected. 0°C < T_J < 85°C.	-0.65%		+0.65%	
V_{FB_Reg3}	Feedback Voltage Regulation	FB-Option selected. -40°C < T_J < 125°C	-0.9%		+0.9%	
I_{FB}	Input leakage current into FB pin	Adjustable configuration, VFB = 0.6 V		1	70	nA
T_{delay}	Start-up delay time	I_O = 0 mA, time from EN=HIGH until start switching, Adjustable Configuration selected		600	1400	µs
	Start-up delay time	I_O = 0 mA, time from EN=HIGH until start switching, VSET Configuration selected. The typical value is based on the first option of VSET configuration.		650	1850	µs
T_{SS}	Soft-Start time	I_O = 0 mA after T_{delay}, from 1st switching pulse until target V_O; TR/SS-Pin = OPEN		150	200	µs
I_{SS}	SS/TR source current		2.3	2.5	2.7	µA
$V_{FB}/V_{SS/TR}$	Tracking Gain, Adjustable Configuration			0.75		
$V_{FB}/V_{SS/TR}$	Tracking Gain tolerance			±8		mV
R_{DISCH}	Active Discharge Resistance	Discharge = ON - Option Selected, EN = LOW,		7.5	20	Ω

Copyright © 2022 Texas Instruments Incorporated

6.6 Typical Characteristics



图 6-1. Typical Quiescent Current vs V_{IN}



图 6-2. Maximum Quiescent Current vs Temperature



图 6-3. Typical Shutdown Current



图 6-4. Output Voltage Accuracy – VFEB Selected

Copyright © 2022 Texas Instruments Incorporated

7 Detailed Description

7.1 Overview

The TPSM82903 synchronous step-down converter MicroSiP package module is based on DCS-Control (Direct Control with Seamless Transition into power save mode). DCS-Control is an advanced regulation topology that combines the advantages of hysteretic, voltage mode, and current mode control. This control loop takes information about output voltage changes and feeds it directly to a fast comparator stage. The control loop sets the switching frequency, which is constant for steady-state operating conditions, and provides immediate response to dynamic load changes. To get accurate DC load regulation, a voltage feedback loop is used. The internally compensated regulation network achieves fast and stable operation with small external components and low-ESR capacitors.

7.2 Functional Block Diagram



Copyright © 2022 Texas Instruments Incorporated

7.3 Feature Description

7.3.1 Mode Selection and Device Configuration (MODE/S-CONF)

With MODE/S-CONF (SmartConfig application), this device features an input with two functions. It can be used to customize the device behavior in two ways:

- Select the device mode (FPWM or auto PFM/PWM with AEE operation) traditionally with a HIGH- or LOW-level.
- Select the device configuration (switching frequency, internal/external feedback, output discharge, and PFM/PWM mode) by connecting a single resistor to the MODE/S-CONF pin.

The device interprets this pin during the start-up sequence after the internal OTP readout and before it starts switching in soft start. If the device reads a HIGH- or LOW-level, the dynamic mode change is active and PFM/PWM mode can be changed during operation. If the device reads a resistor value, there is no further interpretation during operation and device mode or other configurations cannot be changed afterward.

备注

The MODE/S-CONF pin must not be left floating. Connect the pin high, low, or to a resistor to configure the device according to 表 7-2.



图 7-1. Interpretation of S-CONF and VSET Flow

CAUTION

For each operating mode and switching frequency, the following V_{OUT} range is recommended:

表 7-1. Recommended V_{OUT} Ranges with Respect to MODE and F_{SW}

Mode	F_{SW} (MHz)	V_{OUT}
Auto PFM/PWM	1 MHz	0.4 V < V_{OUT} < 2.0 V
Forced PWM	1 MHz	0.4 V < V_{OUT} < 2.0 V
Auto PFM/PWM with AEE	2.5 MHz	0.4 V < V_{OUT}< 5.5 V
Forced PWM	2.5 MHz	2.0 V < V_{OUT} < 5.5 V

Failure to follow the recommended V_{OUT} ranges causes the device to malfunction.

Copyright © 2022 Texas Instruments Incorporated

表 7-2. SmartConfig™ Application Setting Table

#	Level Or Resistor Value [Ω] (1)	FB/VSET-Pin	F_{SW} (MHz)	Output Discharge	Mode (Auto or Forced PWM)	Dynamic Mode Change
	Setting Options by Level					
1	GND	external FB	2.5	yes	Auto PFM/PWM with AEE	active
2	HIGH (>V_{IH_MODE})	external FB	2.5	yes	Forced PWM	
	Setting Options by Resistor					
3	7.15 k	external FB	2.5	no	Auto PFM/PWM with AEE	not active
4	8.87 k	external FB	2.5	no	Forced PWM	
5	11.0 k	external FB	1	yes	Auto PFM/PWM	
6	13.7 k	external FB	1	yes	Forced PWM	
7	16.9 k	external FB	1	no	Auto PFM/PWM	
8	21.0 k	external FB	1	no	Forced PWM	
9	26.1 k	VSET	2.5	yes	Auto PFM/PWM with AEE	
10	32.4 k	VSET	2.5	yes	Forced PWM	
11	40.2 k	VSET	2.5	no	Auto PFM/PWM with AEE	
12	49.9 k	VSET	2.5	no	Forced PWM	
13	61.9 k	VSET	1	yes	Auto PFM/PWM	
14	76.8 k	VSET	1	yes	Forced PWM	
15	95.3 k	VSET	1	no	Auto PFM/PWM	
16	118 k	VSET	1	no	Forced PWM	

(1) E96 Resistor Series, 1% Accuracy, Temperature Coefficient better or equal than ±200 ppm/°C

7.3.2 Adjustable V_O Operation (External Voltage Divider)

The TPSM82903 can be programmed by the MODE/S-CONF pin to either classical configuration where the FB/VSET pin is used as the feedback pin, sensing V_O through an external resistive divider. The TPSM82903 can also be programmed to 16 different fixed output voltages. These are set through an external resistor between the FB/VSET pin and GND. In this configuration, V_O is directly sensed at the VOS internal terminal connection of the device.

If the device is configured to operate in classical adjustable V_O operation, the FB/VSET pin is used as the feedback pin and needs to sense V_O through an external divider network. 图 7-2 shows the typical schematic for this configuration.



图 7-2. Adjustable V_O Operation Schematic

Copyright © 2022 Texas Instruments Incorporated

7.3.3 Setable V_O Operation (VSET and Internal Voltage Divider)

If the device is configured to VSET operation, V_O is sensed only through the internal VOS connection by an internal resistor divider. The target V_O is programmed by an external resistor connected between the VSET pin and GND. 图 7-3 shows the typical schematic for this configuration.



图 7-3. Setable V_O Operation Schematic

表 7-3. VSET Selection Table

#	Resistor Value [Ω]	Target V_O [V]
1	GND	1.2
2	4.64 k	0.4
3	5.76 k	0.6
4	7.15 k	0.8
5	8.87 k	1.0
6	11.0 k	1.1
7	13.7 k	1.3
8	16.9 k	1.35
9	21.0 k	1.8
10	26.1 k	1.9
11	40.2 k	2.5
12	61.9 k	3.8
13	76.8 k	5.0
14	95.3 k	5.1
15	118.0 k	5.5
16	249.00 k or larger/Open	3.3

7.3.4 Soft Start/Tracking (SS/TR)

With the SS/TR pin, it is possible to adjust the soft-start behavior and track an external voltage. See 节 8.2.2.4 for operation details.

The internal soft-start circuitry controls the output voltage slope during start-up. This avoids excessive inrush current and makes sure there is a controlled output voltage rise time. It also prevents unwanted voltage drops from high impedance power sources or batteries. When EN is set high to start operation, the device starts switching after a delay, then the internal reference, and hence V_O, rises with a slope controlled by an external capacitor connected to the SS/TR pin.

Leaving the SS/TR pin unconnected provides the fastest start-up, limited internally (the pin must not be pulled LOW externally).

Copyright © 2022 Texas Instruments Incorporated

If the device is set to shut down (EN = GND), undervoltage lockout, or thermal shutdown, an internal resistor pulls the SS/TR pin down to ensure a proper low level. Returning from those states causes a new start-up sequence as set by the SS/TR connection.

A voltage supplied to SS/TR can be used to track a primary voltage. The output voltage follows this voltage up and down in forced PWM mode. In PFM mode, the output voltage decreases based on the load current.

7.3.5 Smart Enable with Precise Threshold

The voltage applied at the enable pin of the TPSM82903 is compared to a fixed threshold rising voltage, allowing the user to drive the pin by a slowly changing voltage and enables the use of an external RC network to achieve a power-up delay.

The precise enable input allows the user to program the undervoltage lockout by adding a resistor divider to the input of the enable pin.

The enable input threshold for a falling edge is lower than the rising edge threshold. The TPSM82903 starts operation when the rising threshold is exceeded. For proper operation, the EN pin must be terminated and must not be left floating. Pulling the EN pin low forces the device into shutdown. In this mode, the internal high-side and low-side MOSFETs are turned off and the entire internal control circuitry is switched off.

An internal resistor pulls the EN pin to GND when the device is disabled and avoids floating the pin after the device is enabled, the pulldown is removed. This prevents an uncontrolled start-up of the device in case the EN pin cannot be driven to a low level safely. With EN low, the device is in shutdown mode. The device is turned on with EN set to a high level. The pulldown control circuit disconnects the pulldown resistor on the EN pin after the internal control logic and the reference have been powered up. With EN set to a low level, the device enters shutdown mode and the pulldown resistor is activated again.

7.3.6 Power Good (PG)

The TPSM82903 has a built-in power-good (PG) feature to indicate whether the output voltage has reached its target and the device is ready. The PG signal can be used for start-up sequencing of multiple rails. The PG pin is an open-drain output that requires a pullup resistor to any voltage up to the recommended input voltage level. PG is low when the device is turned off due to EN, UVLO (undervoltage lockout), or thermal shutdown. V_{IN} must remain present for the PG pin to stay low.

If the power-good output is not used, it is recommended to tie to GND or leave it open.

表 7-4. Power Good Indicator Functional Table

Logic Signals				PG Status
V_I	EN Pin	Thermal Shutdown	V_O	
V_I > UVLO	HIGH	No	V_O on target	**High Impedance**
			V_O < target	**LOW**
		Yes	x	**LOW**
	LOW	x	x	**LOW**
1.8 V< V_I < UVLO	x	x	x	**LOW**
V_I < 1.8 V	x	x	x	**Undefined**

7.3.7 Undervoltage Lockout (UVLO)

If the input voltage drops, the undervoltage lockout prevents mis-operation of the device by switching off both the power FETs. The device is fully operational for voltages above the rising UVLO threshold and turns off if the input voltage trips below the threshold for a falling supply voltage.

7.3.8 Current Limit And Short Circuit Protection

The TPSM82903 is protected against overload and short circuit events. If the inductor current exceeds the high-side FET current limit (I_{LIMH}), the high-side switch is turned off and the low-side switch is turned on to ramp down the inductor current. The high-side FET turns on again only if the current in the low-side FET has decreased below the low-side FET current limit threshold.

Copyright © 2022 Texas Instruments Incorporated

Due to internal propagation delay, the actual current can exceed the static current limit during that time. The dynamic current limit is given as 方程式 1:

$$I_{peak(typ)} = I_{LIMH} + \frac{V_L}{L} \times t_{PD} \quad (1)$$

where

- I_{LIMH} is the static high-side FET current limit as specified in the *Electrical Characteristics*.
- L is the effective inductance at the peak current (approximately 0.9 µH).
- V_L is the voltage across the inductor (V_{IN} – V_{OUT}).
- t_{PD} is the internal propagation delay of typically 50 ns.

The current limit can exceed static values, especially if the input voltage is high and very small inductances are used. The dynamic high-side switch peak current can be calculated as follows:

$$I_{peak(typ)} = I_{LIMH} + \frac{VIN - VOUT}{L} \times 50ns \quad (2)$$

7.3.9 Thermal Shutdown

The junction temperature, T_J, of the device is monitored by an internal temperature sensor. If T_J rises and exceeds the thermal shutdown threshold, T_{SD}, the device shuts down. Both the high-side and low-side power FETs are turned off and PG goes low. When T_J decreases below the hysteresis, the converter resumes normal operation, beginning with soft start. During a PFM skip pause, the thermal shutdown feature is not active. A shutdown or re-start is only triggered during a switching cycle. See 节 7.4.3.

Copyright © 2022 Texas Instruments Incorporated

7.4 Device Functional Modes

7.4.1 Pulse Width Modulation (PWM) Operation

The TPSM82903 has two operating modes: forced PWM mode discussed in this section and PWM/PFM as discussed in 节 7.4.3.

With the MODE/S-CONF pin configured for PWM mode, the TPSM82903 operates with pulse width modulation in continuous conduction mode (CCM) with a nominal switching frequency of 2.5 MHz/1.0 MHz. The frequency variation in PWM is controlled and depends on V_{IN}, V_{OUT}, and the inductance. The on time in forced PWM mode is given by 方程式 3:

$$TON = \frac{V_{OUT}}{V_{IN}} \times \frac{1}{f_{sw}} \tag{3}$$

7.4.2 AEE (Automatic Efficiency Enhancement)

When the MODE/S-CONF pin is configured for AEE mode, the TPSM82903 provides the highest efficiency over the entire input voltage and output voltage range by automatically adjusting the switching frequency of the converter. This is achieved by setting the predictive off time of the converter. The efficiency of a switched mode converter is determined by the power losses during the conversion. The efficiency decreases if V_{OUT} decreases, V_{IN} increases as shown in 方程式 4, or both. In order to keep the efficiency high over the entire duty cycle range (V_{OUT}/V_{IN} ratio), the switching frequency is adjusted while maintaining the ripple current.

$$F_{sw}(MHz) = 10 \times V_{OUT} \times \frac{V_{IN} - V_{OUT}}{V_{IN}^{\ 2}} \tag{4}$$

The AEE function in the TPSM82903 adjusts the on time (TON) in power save mode, depending on the input voltage and the output voltage to maintain highest efficiency. The on time in steady-state operation can be estimated as using 方程式 5:

$$TON = 100 \times \frac{VIN}{VIN - VOUT}[ns] \tag{5}$$

方程式 6 shows the relationship among the inductor ripple current, switching frequency, and duty cycle.

$$\Delta I_L = V_{OUT} \times (\frac{1-D}{L \times f_{SW}}) = V_{OUT} \times (\frac{1-(\frac{V_{OUT}}{V_{IN}})}{L \times f_{SW}}) \tag{6}$$

Efficiency increases by decreasing switching losses and preserving high efficiency for varying duty cycles, while the ripple current amplitude remains low enough to deliver the full output current without reaching current limit. The AEE feature provides an efficiency enhancement for various duty cycles, especially for lower V_{OUT} values where fixed frequency converters suffer from a significant efficiency drop. Furthermore, this feature compensates for the very small duty cycles of high V_{IN} to low V_{OUT} conversion, which limits the control range in other topologies.

7.4.3 Power Save Mode Operation (Auto PFM/PWM)

When the MODE/S-CONF pin is configured for power save mode (auto PFM/PWM), the device operates in PWM mode as long the output current is higher than half of the ripple current of the inductor. To maintain high efficiency at light loads, the device enters power save mode at the boundary to discontinuous conduction mode (DCM). This happens if the output current becomes smaller than half of the ripple current of the inductor. The power save mode is entered seamlessly when the load current decreases. This makes sure there is a high efficiency in light load operation. The device remains in power save mode as long as the inductor current is discontinuous.

Copyright © 2022 Texas Instruments Incorporated

In power save mode, the switching frequency decreases linearly with the load current maintaining high efficiency. The transition in and out of power save mode is seamless in both directions.

In addition to adjusting the switching, the TPSM82903 adjusts the on time (TON) in power save mode, depending on the input voltage and the output voltage to maintain the highest efficiency using the AEE function when 2.5 MHz is selected as described in 节 7.4.2.

In power save mode, the TON time can be estimated using 方程式 3 for 1 MHz and 方程式 5 for 2.5 MHz (given the AEE is enabled for 2.5 MHz).

For very small output voltages, an absolute minimum on time of about 50 ns is kept to limit switching losses. The operating frequency is thereby reduced from its nominal value, which keeps efficiency high. Using TON, the typical peak inductor current in power save mode is approximated by 方程式 7:

$$ILPSM_{(peak)} = \frac{(VIN - VOUT)}{L} \times TON \tag{7}$$

There is a minimum off time that limits the duty cycle of the TPSM82903. When V_{IN} decreases to typically 15% above V_{OUT}, the TPSM82903 does not enter power save mode, regardless of the load current. The device maintains output regulation in PWM mode.

The output voltage ripple in power save mode is given by 方程式 8:

$$\Delta V = \frac{L \times VIN^2}{200 \times C}\left(\frac{1}{VIN - VOUT} + \frac{1}{VOUT}\right) \tag{8}$$

where

- L is the effective inductance (approximately 0.9 μF).
- C is the output effective capacitance.

7.4.4 100% Duty-Cycle Operation

The duty cycle of the buck converter operating in PWM mode is given as D = V_{OUT}/V_{IN}. The duty cycle increases as the input voltage comes close to the output voltage and the off time gets smaller. When the minimum off time of typically 80 ns is reached, the TPSM82903 scales down its switching frequency while it approaches 100% mode. In 100% mode, the device keeps the high-side switch on continuously. The high-side switch stays turned on as long as the output voltage is below the internal set point. This allows the conversion of small input to output voltage differences (for example, getting longest operation time of battery-powered applications). In 100% duty cycle mode, the low-side FET is switched off.

The minimum input voltage to maintain output voltage regulation, depending on the load current and the output voltage level, can be calculated as:

$$VIN_{(min)} = VOUT + IOUT\left(R_{DS(on)} + R_L\right) \tag{9}$$

where

- I_{OUT} is the output current.
- $R_{DS(on)}$ is the on-state resistance of the high-side FET.
- R_L is the DC resistance of the inductor used (approximately 40 mΩ).

7.4.5 Output Discharge Function

The purpose of the discharge function is to ensure a defined down-ramp of the output voltage when the device is being disabled but also to keep the output voltage close to 0 V when the device is off. The output discharge feature is only active after the TPSM82903 has been enabled at least once since the supply voltage was applied. The internal discharge resistor is connected to the VOS pin. The discharge function is enabled as soon

Copyright © 2022 Texas Instruments Incorporated

as the device is disabled, in thermal shutdown, or in undervoltage lockout. The minimum supply voltage required for the discharge function to remain active typically is 2 V.

7.4.6 Starting into a Pre-Biased Load

The TPSM82903 is capable of starting into a pre-biased output. The device only starts switching when the internal soft-start ramp is equal or higher than the feedback voltage. If the voltage at the feedback pin is biased to a higher voltage than the nominal value, the TPSM82903 does not start switching unless the voltage at the feedback pin drops to the target.

Copyright © 2022 Texas Instruments Incorporated

8 Application and Implementation

备注

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI’s customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

8.1 Application Information

The TPSM82903 device is highly efficient, small, and flexible synchronous step-down DC-DC converter MicroSiP package module that is easy to use. A wide input voltage range of 3 V to 17 V supports a wide variety of inputs like 12-V supply rails, single-cell or multi-cell Li-Ion, and 5-V or 3.3-V rails.

8.2 Typical Application with Adjustable Output Voltage



图 8-1. Typical Application Circuit

8.2.1 Design Requirements

表 8-1. List of Components

Reference	Description	Manufacturer
IC	17 V, 3-A Step-Down Converter	TPSM8290x series; Texas Instruments
CIN	10 µF, 25 V, Ceramic, 0805	C3216X7R1E106M160AE, TDK
COUT	22 µF, 16 V, Ceramic, 0805	C2012X7S1A226M125AC, TDK
CSS	Depends on soft start time; see 节 8.2.2.3.3.	16 V, Ceramic, X7R
R1	Depending on V_{OUT}; see 节 8.2.2.2.	Standard 1% metal film
R2	Depending on V_{OUT}; see 节 8.2.2.2.	Standard 1% metal film
R3	Depending on device setting, see 节 7.3.1.	Standard 1% metal film

8.2.2 Detailed Design Procedure

8.2.2.1 Custom Design With WEBENCH® Tools

Click here to create a custom design using the TPSM82903 device with the WEBENCH® Power Designer.

1. Start by entering the input voltage (V_{IN}), output voltage (V_{OUT}), and output current (I_{OUT}) requirements.
2. Optimize the design for key parameters such as efficiency, footprint, and cost using the optimizer dial.
3. Compare the generated design with other possible solutions from Texas Instruments.

The WEBENCH Power Designer provides a customized schematic along with a list of materials with real-time pricing and component availability.

Copyright © 2022 Texas Instruments Incorporated

In most cases, these actions are available:

- Run electrical simulations to see important waveforms and circuit performance
- Run thermal simulations to understand board thermal performance
- Export customized schematic and layout into popular CAD formats
- Print PDF reports for the design, and share the design with colleagues

Get more information about WEBENCH tools at www.ti.com/WEBENCH.

8.2.2.2 Programming the Output Voltage

The output voltage of the TPSM82903 is adjustable. It can be programmed for output voltages from 0.6 V to 5.5 V using a resistor divider from V_{OUT} to GND. The voltage at the FB pin is regulated to 600 mV. The value of the output voltage is set by the selection of the resistor divider from 方程式 10. It is recommended to choose resistor values that allow a current of at least 2 μA, meaning the value of R2 must not exceed 400 kΩ. Lower resistor values are recommended for highest accuracy and most robust design.

$$R1 = R2 \times \left(\frac{VOUT}{VFB} - 1 \right) \tag{10}$$

With typical VFB = 0.6 V, 1-MHz switching frequency is not recommended for V_{OUT} > 1.8 V.

表 8-2. Setting the Output Voltage

Nominal Output Voltage	R1	R2	Exact Output Voltage
0.75 V	24.9 kΩ	100 kΩ	0.749 V
1.2 V	100 kΩ	100 kΩ	1.2 V
1.5 V	150 kΩ	100 kΩ	1.5 V
1.8 V	200 kΩ	100 kΩ	1.8 V
2.0 V	49.9 kΩ	21.5 kΩ	1.992 V
2.5 V	100 kΩ	31.6 kΩ	2.498 V
3.0 V	100 kΩ	24.9 kΩ	3.009 V
3.3 V	113 kΩ	24.9 kΩ	3.322 V
5.0 V	182 kΩ	24.9 kΩ	4.985 V

8.2.2.3 Capacitor Selection

8.2.2.3.1 Output Capacitor

The recommended value for the output capacitor is 22 μF. Output capacitance above 100 μF needs to have a ESR of ≥ 10 mΩ for stable operation. The architecture of the TPSM82903 allows the use of tiny ceramic output capacitors with low equivalent series resistance (ESR). These capacitors provide low output voltage ripple and are recommended. To keep its low resistance up to high frequencies and to get narrow capacitance variation with temperature, use X7R or X5R dielectric. Using a higher value has advantages like smaller voltage ripple and a tighter DC output accuracy in power save mode (see the *Optimizing the TPS62130/40/50/60 Output Filter* application report).

In power save mode, the output voltage ripple depends on the output capacitance, its ESR, ESL, and the peak inductor current. Using ceramic capacitors provides small ESR, ESL, and low ripple. The output capacitor needs to be as close as possible to the device.

For large output voltages, the DC bias effect of ceramic capacitors is large and the effective capacitance must be observed.

8.2.2.3.2 Input Capacitor

For most applications, 10 μF nominal is sufficient and is recommended, though a larger value reduces input current ripple further. The input capacitor buffers the input voltage for transient events and also decouples the

Copyright © 2022 Texas Instruments Incorporated

converter from the supply. A low-ESR multilayer ceramic capacitor (MLCC) is recommended for best filtering and must be placed between VIN and GND as close as possible to those pins.

表 8-3. List of Capacitors

Type (1)	Nominal Capacitance [µF]	Voltage Rating [V]	Size	Manufacturer
C3216X7R1E106K160AB	10	25	0805	TDK
C2012X7S1A226M125AC	22	10	0805	TDK

(1) Lower of I_{RMS} at 40°C rise or I_{SAT} at 30% drop

8.2.2.3.3 Soft-Start Capacitor

A capacitor connected between SS/TR pin and GND allows a user-programmable start-up slope of the output voltage.



图 8-2. Soft-Start Operation Simplified Schematic

An internal constant current source is provided to charge the external capacitance. The capacitor required for a given soft-start ramp time is given by:

$$C_{SS} = T_{SS} \times \frac{I_{SS}}{V_{REF}} \tag{11}$$

where

- C_{SS} is the capacitance required at the SS/TR pin.
- T_{SS} is the desired soft-start ramp time.
- I_{SS} is the SS/TR source current, see the *Electrical Characteristics*.
- V_{REF} is the feedback regulation voltage divided by tracking gain (V_{FB}/0.75), see the *Electrical Characteristics*.

The fastest achievable typical ramp time is 150 µs even if the external C_{ss} capacitance is lower than 680 pF or the pin is open.

8.2.2.4 Tracking Function

If a tracking function is desired, the SS/TR pin can be used for this purpose by connecting it to an external tracking voltage. The output voltage tracks that voltage with the typical gain and offset as specified in the *Electrical Characteristics*.



图 8-3. Tracking Operation Simplified Schematic

$$V_{FB} = 0.75 \times V_{SS/TR} \quad (12)$$

When the SS/TR pin voltage is above 0.8 V, the internal voltage is clamped and the device goes to normal regulation. This works for rising and falling tracking voltages with the same behavior, as long as the input voltage is inside the recommended operating conditions. For decreasing SS/TR pin voltage in PFM mode, the device does not sink current from the output. The resulting decrease of the output voltage can therefore be slower than the SS/TR pin voltage if the load is light. When driving the SS/TR pin with an external voltage, do not exceed the voltage rating of the SS/TR pin, which is 6 V. The SS/TR pin is internally connected with a resistor to GND when EN = 0.

If the input voltage drops below undervoltage lockout, the output voltage goes to zero, independent of the tracking voltage. 图 8-4 shows how to connect devices to get ratiometric and simultaneous sequencing by using the tracking function.



图 8-4. Schematic for Ratiometric and Simultaneous Start-Up

The resistive divider of R7 and R8 can be used to change the ramp rate of VOUT2 to be faster, slower, or the same as VOUT1.

A sequential start-up is achieved by connecting the PG pin of VOUT of device 1 to the EN pin of device 2. PG requires a pullup resistor. Ratiometric start-up sequence happens if both supplies are sharing the same soft-start

Copyright © 2022 Texas Instruments Incorporated

capacitor. 方程式 11 gives the soft-start time, though the SS/TR current has to be doubled. Details about these and other tracking and sequencing circuits are found in *Sequencing and Tracking With the TPS621-Family and TPS821-Family* application report.

备注

If the voltage at the FB pin is below its typical value of 0.6 V, the output voltage accuracy can have a wider tolerance than specified. The current of 2.5 µA out of the SS/TR pin also has an influence on the tracking function, especially for high resistive external voltage dividers on the SS/TR pin.

Copyright © 2022 Texas Instruments Incorporated

8.2.3 Application Curves



Auto PFM/PWM F_{sw} = 1 MHz

图 8-5. Efficiency vs Output Current V_{OUT} = 1.2 V



Auto PFM/PWM F_{sw} = 2.5 MHz

图 8-6. Efficiency vs Output Current V_{OUT} = 1.2 V



FPWM F_{sw} = 1 MHz

图 8-7. Efficiency vs Output Current V_{OUT} = 1.2 V



Auto PFM/PWM F_{sw} = 1 MHz

图 8-8. Efficiency vs Output Current V_{OUT} = 1.8 V



Auto PFM/PWM F_{sw} = 2.5 MHz

图 8-9. Efficiency vs Output Current V_{OUT} = 1.8 V



FPWM F_{sw} = 1 MHz

图 8-10. Efficiency vs Output Current V_{OUT} = 1.8 V

Copyright © 2022 Texas Instruments Incorporated



Auto PFM/PWM F_{sw} = 2.5 MHz

图 8-11. Efficiency vs Output Current V_{OUT} = 3.3 V



FPWM F_{sw} = 2.5 MHz

图 8-12. Efficiency vs Output Current V_{OUT} = 3.3 V



Auto PFM/PWM F_{sw} = 2.5 MHz

图 8-13. Efficiency vs Output Current V_{OUT} = 5.5 V



FPWM F_{sw} = 2.5 MHz

图 8-14. Efficiency vs Output Current V_{OUT} = 5.5 V



Auto PFM/PWM F_{sw} = 1 MHz

图 8-15. Switching Frequency vs Input Voltage V_{OUT} = 1.2 V



Auto PFM/PWM F_{sw} = 2.5 MHz

图 8-16. Switching Frequency vs Input Voltage V_{OUT} = 1.2 V

Copyright © 2022 Texas Instruments Incorporated



FPWM F_{sw} = 1 MHz

图 8-17. Switching Frequency vs Input Voltage V_{OUT} = 1.2 V



Auto PFM/PWM F_{sw} = 1 MHz

图 8-18. Switching Frequency vs Input Voltage V_{OUT} = 1.8 V



Auto PFM/PWM F_{sw} = 2.5 MHz

图 8-19. Switching Frequency vs Input Voltage V_{OUT} = 1.8 V



FPWM F_{sw} = 1 MHz

图 8-20. Switching Frequency vs Input Voltage V_{OUT} = 1.8 V



Auto PFM/PWM F_{sw} = 2.5 MHz

图 8-21. Switching Frequency vs Input Voltage V_{OUT} = 3.3 V



FPWM F_{sw} = 2.5 MHz

图 8-22. Switching Frequency vs Input Voltage V_{OUT} = 3.3 V

Copyright © 2022 Texas Instruments Incorporated



Auto PFM/PWM F_{sw} = 2.5 MHz

图 8-23. Switching Frequency vs Input Voltage V_{OUT} = 5.5 V



FPWM F_{sw} = 2.5 MHz

图 8-24. Switching Frequency vs Input Voltage V_{OUT} = 5.5 V



FPWM F_{sw} = 1 MHz

图 8-25. Output Voltage vs Output Current V_{OUT} = 1.8 V



V_{IN} = 12 V 1-MHz FPWM I_O = 0 mA
V_{OUT} = 1.2 V T_A = 25°C

图 8-26. Start-Up Timing



V_{IN} = 12 V 1-MHz Auto PFM/PWM I_O = 1 A
V_{OUT} = 1.8 V T_A = 25°C

图 8-27. Start-Up Timing



V_{IN} = 12 V 2.5-MHz FPWM I_O = 1 A
V_{OUT} = 5 V T_A = 25°C

图 8-28. Start-Up Timing

Copyright © 2022 Texas Instruments Incorporated



V_{IN} = 12 V　2.5-MHz PFM/PWM　I_O = 1 A
V_{OUT} = 5 V　T_A = 25°C

图 8-29. Start-Up Timing



V_{IN} = 12 V　1-MHz Auto PFM/PWM　I_O = 3 A
V_{OUT} = 1.2 V　T_A = 25°C

图 8-30. Output Voltage Ripple



V_{IN} = 12 V　1-MHz Auto PFM/PWM　I_O = 0.1 A
V_{OUT} = 1.2 V　T_A = 25°C

图 8-31. Output Voltage Ripple



V_{IN} = 12 V　2.5-MHz Auto PFM/PWM　I_O = 3 A
V_{OUT} = 1.2 V　T_A = 25°C

图 8-32. Output Voltage Ripple



V_{IN} = 12 V　2.5-MHz Auto PFM/PWM　I_O = 0.1 A
V_{OUT} = 1.2 V　T_A = 25°C

图 8-33. Output Voltage Ripple



V_{IN} = 12 V　2.5-MHz Auto PFM/PWM　I_O = 1 A
V_{OUT} = 3.3 V　T_A = 25°C

图 8-34. Output Voltage Ripple

Copyright © 2022 Texas Instruments Incorporated



V_{IN} = 12 V　2.5-MHz FPWM　I_O = 0.1 A
V_{OUT} = 3.3 V　T_A = 25°C

图 8-35. Output Voltage Ripple



V_{IN} = 12 V　2.5-MHz FPWM　I_O = 1 A
V_{OUT} = 5.0 V　T_A = 25°C

图 8-36. Output Voltage Ripple



V_{IN} = 12 V　2.5-MHz Auto PFM/PWM
V_{OUT} = 5.0 V　I_O = 1 A　T_A = 25°C

图 8-37. Output Voltage Ripple



V_{IN} = 12 V　1-MHz Auto PFM/PWM　I_O = 0.1 A to 1 A
V_{OUT} = 1.2 V　T_A = 25°C

图 8-38. PSM-to-PWM Transition



V_{IN} = 12 V　1-MHz Auto PFM/PWM　I_O = 5 mA to 1 A to 5 mA
V_{OUT} = 1.2 V　T_A = 25°C

图 8-39. Load Transient Response



V_{IN} = 12 V　1-MHz Auto PFM/PWM　I_O = 5 mA to 1 A
V_{OUT} = 1.2 V　T_A = 25°C

图 8-40. Load Transient Response – Rising Edge

Copyright © 2022 Texas Instruments Incorporated



V_{IN} = 12 V　1-MHz Auto PFM/PWM　I_O = 1 A to 5 mA
V_{OUT} = 1.2 V　T_A = 25°C

图 8-41. Load Transient Response – Falling Edge



V_{IN} = 12 V　I_O = 5 mA to 2 A to 5 mA
V_{OUT} = 3.3 V　2.5-MHz Auto PFM/PWM　T_A = 25°C

图 8-42. Load Transient Response



V_{IN} = 12 V　I_O = 5 mA to 2 A to 5 mA
V_{OUT} = 3.3 V　2.5-MHz FPWM　T_A = 25°C

图 8-43. Load Transient Response



V_{IN} = 12 V　Output Discharge = Yes
V_{OUT} = 1.2 V　T_A = 25°C

图 8-44. Output Discharge Function – Enabled



Auto PFM/PWM　F_{sw} = 2.5 MHz

图 8-45. Thermal Derating V_{OUT} = 1.2 V



Auto PFM/PWM　F_{sw} = 2.5 MHz

图 8-46. Thermal Derating V_{OUT} = 3.3 V

Copyright © 2022 Texas Instruments Incorporated

8.3 Typical Application with Setable V_O Using VSET



图 8-47. Typical Application Circuit (VSET)

8.3.1 Design Requirements

VSET allows the user to set the output voltage using only one resistor to ground on the FB/VSET pin. 表 7-3 shows the 16 available options.

8.3.2 Detailed Design Procedure

The VSET option needs to be selected using the MODE/S-CONF pin. After the device is configured to VSET operation, V_O is sensed only through the VOS pin by an internal resistor divider. The target V_O is programmed by an external resistor R2 connected between FB/VSET and GND.

Copyright © 2022 Texas Instruments Incorporated

8.3.3 Application Curves



V_{IN} = 12 V　1-MHz Auto　I_O = 1 A
V_{OUT} = 0.4 V　PFM/PWM　T_A = 25°C

图 8-48. Output Voltage Ripple



V_{IN} = 12 V　1-MHz Auto　I_O = 100 mA
V_{OUT} = 0.4 V　PFM/PWM　T_A = 25°C

图 8-49. Output Voltage Ripple



V_{IN} = 12 V　1-MHz FPWM　I_O = 1 A
V_{OUT} = 0.4 V　T_A = 25°C

图 8-50. Output Voltage Ripple



V_{IN} = 12 V　1-MHz FPWM　I_O = 100 mA
V_{OUT} = 0.4 V　T_A = 25°C

图 8-51. Output Voltage Ripple



V_{IN} = 3 V – 17 V　Temp = – 40°C to 150°C

图 8-52. Output Voltage Accuracy – VSET Selected



Auto PFM/PWM　F_{sw} = 1 MHz

图 8-53. Efficiency vs Output Current V_{OUT} = 0.4 V

Copyright © 2022 Texas Instruments Incorporated



Auto PFM/PWM F_{sw} = 2.5 MHz

图 8-54. Efficiency vs Output Current V_{OUT} = 0.4 V



FPWM F_{sw} = 1 MHz

图 8-55. Efficiency vs Output Current V_{OUT} = 0.4 V



Auto PFM/PWM F_{sw} = 1 MHz

图 8-56. Switching Frequency vs Input Voltage V_{OUT} = 0.4 V



Auto PFM/PWM F_{sw} = 2.5 MHz

图 8-57. Switching Frequency vs Input Voltage V_{OUT} = 0.4 V



FPWM F_{sw} = 1 MHz

图 8-58. Switching Frequency vs Input Voltage V_{OUT} = 0.4 V



Auto PFM/PWM F_{sw} = 1 MHz

图 8-59. Output Voltage vs Output Current V_{OUT} = 1.2 V

Copyright © 2022 Texas Instruments Incorporated



Auto PFM/PWM F_{sw} = 2.5 MHz

图 8-60. Output Voltage vs Output Current
V_{OUT} = 5.5 V

8.4 Power Supply Recommendations

The power supply to the TPSM82903 must have a current rating according to the supply voltage, output voltage, and output current of the TPSM82903.

8.5 Layout

8.5.1 Layout Guidelines

A proper layout is critical for the operation of a switched mode power supply, even more at high switching frequencies. Therefore, the PCB layout of the TPSM82903 demands careful attention to ensure operation and to get the performance specified. A poor layout can lead to issues like poor regulation (both line and load), stability and accuracy weaknesses, increased EMI radiation, bad thermal performance, and noise sensitivity.

- See 图 8-61 for the recommended layout of the TPSM82903, which is designed for common external ground connections. TI recommends placing all components as close as possible to the package pins. The input and output capacitors placement specifically, must be closest to the VIN, VOUT, and GND pins of the TPSM82903.
- Provide low capacitive paths (with respect to all other nodes) for traces with high dv/dt. Therefore, the input and output capacitance must be placed as close as possible to the IC pins and parallel wiring over long distances as well as narrow traces must be avoided. Loops which conduct an alternating current must outline an area as small as possible, as this area is proportional to the energy radiated.
- Sensitive nodes like FB needs to be connected with short wires and not nearby high dv/dt signals. As it carries information about the output voltage, it must be connected as close as possible to the actual output voltage (at the output capacitor). The capacitor on the SS/TR pin as well as the FB resistors, R1 and R2, must be kept close to the module and connect directly to those pins and the system ground plane. The same applies to VSET resistor if VSET is used to scale the output voltage.
- The package uses the pins for power dissipation. Thermal vias on the VIN, VOUT, and GND pins help to spread the heat through the PCB.
- In case of the EN, and MODE/S-CONF need to be tied to the input supply voltage at V_{IN}, the connection must be made directly at the input capacitor as indicated in the schematics.
- The SW/NC pin must not be connected to any other traces. For best practice, this pin must be left floating. If the pin is soldered to PCB copper, the pour needs to be: as small as possible, no inner layer connections, no vias, electrically floating, and limited to the pin area as possible.
- Refer to 图 8-61 for an example of component placement, routing and thermal design. The recommended layout is implemented on the EVM and shown in its user's guide.

Copyright © 2022 Texas Instruments Incorporated

8.5.2 Layout Example



图 8-61. Layout

8.5.2.1 Thermal Considerations

Implementation of power converter modules with low-profile and fine-pitch such as MircoSiP packages typically requires special attention to power dissipation and thermal rise. Many system-dependent issues such as thermal coupling, airflow, added heat sinks and convection surfaces, and the presence of other heat-generating components affect the power-dissipation limits of a given component.

The TPSM82903 is designed for a maximum operating junction temperature (T_J) of 125°C. Therefore, the maximum output power is limited by the power losses that can be dissipated over the actual thermal resistance, given by the package and the surrounding PCB structures. If the thermal resistance of the package is given, the size of the surrounding copper area and a proper thermal connection of the module can reduce the thermal resistance. To get an improved thermal behavior, TI recommends to follow the following guidelines:

- Use a multi-layer PCB boards (at least four layers, with 1-oz or more copper).
- Use thermal vias on the GND pin to connect the GND top layer with the GND inner and bottom layers. This helps dissipate the heat across layers.
- Generate as large a GND plane as allowable on the top and bottom layers, especially right near the package. The exposed thermal pad of the device sits right at the middle of the package. This is ideal for thermal dissipation. To take advantage of that, TI recommends the ground plan to cross through the package to allow maximum ground plan connection with the exposed pad. See 图 8-61 how the north ground pour is connecting with the south ground pour as it crosses through the exposed pad of the package.
- Use thermal vias on the VIN and VOUT pins (as close as possible to the pin) and around input and output capacitors to connect the VIN and VOUT top layer with the inner and bottom layers. This helps dissipate the heat across layers as well as decreases the resistance drop on these traces.
- Use wide and short traces for the main current paths to reduce the parasitic inductance and resistance and helps on thermal dissipation.
- Introduce airflow in the system if possible.
- Refer to 图 8-61 for an example of component placement, routing and thermal design.

For more details on how to use the thermal parameters, see the *Thermal Characteristics of Linear and Logic Packages Using JEDEC PCB Designs* and *Semiconductor and IC Package Thermal Metrics* application reports.

If short circuit or overload conditions are present, the device is protected by limiting internal power dissipation.

The device is qualified for long term qualification with a 125°C junction temperature.

Copyright © 2022 Texas Instruments Incorporated

9 Device and Documentation Support

9.1 Device Support

9.1.1 第三方产品免责声明

TI 发布的与第三方产品或服务有关的信息，不能构成与此类产品或服务或保修的适用性有关的认可，不能构成此类产品或服务单独或与任何 TI 产品或服务一起的表示或认可。

9.1.2 Development Support

9.1.2.1 Custom Design With WEBENCH® Tools

Click here to create a custom design using the TPSM82903 device with the WEBENCH® Power Designer.

1. Start by entering the input voltage (V_{IN}), output voltage (V_{OUT}), and output current (I_{OUT}) requirements.
2. Optimize the design for key parameters such as efficiency, footprint, and cost using the optimizer dial.
3. Compare the generated design with other possible solutions from Texas Instruments.

The WEBENCH Power Designer provides a customized schematic along with a list of materials with real-time pricing and component availability.

In most cases, these actions are available:

- Run electrical simulations to see important waveforms and circuit performance
- Run thermal simulations to understand board thermal performance
- Export customized schematic and layout into popular CAD formats
- Print PDF reports for the design, and share the design with colleagues

Get more information about WEBENCH tools at www.ti.com/WEBENCH.

9.2 接收文档更新通知

要接收文档更新通知，请导航至 ti.com 上的器件产品文件夹。点击 *订阅更新* 进行注册，即可每周接收产品信息更改摘要。有关更改的详细信息，请查看任何已修订文档中包含的修订历史记录。

9.3 支持资源

TI E2E™ 支持论坛是工程师的重要参考资料，可直接从专家获得快速、经过验证的解答和设计帮助。搜索现有解答或提出自己的问题可获得所需的快速设计帮助。

链接的内容由各个贡献者“按原样”提供。这些内容并不构成 TI 技术规范，并且不一定反映 TI 的观点；请参阅 TI 的《使用条款》。

9.4 Trademarks

MicroSiP™, SmartConfig™, and TI E2E™ are trademarks of Texas Instruments.
WEBENCH® is a registered trademark of Texas Instruments.
所有商标均为其各自所有者的财产。

9.5 Electrostatic Discharge Caution

This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

9.6 术语表

TI 术语表	本术语表列出并解释了术语、首字母缩略词和定义。

10 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

Copyright © 2022 Texas Instruments Incorporated

PACKAGING INFORMATION

Orderable part number	Status (1)	Material type (2)	Package | Pins	Package qty | Carrier	RoHS (3)	Lead finish/ Ball material (4)	MSL rating/ Peak reflow (5)	Op temp (°C)	Part marking (6)
TPSM82903SISR	Active	Production	uSiP (SIS) | 11	3000 | LARGE T&R	-			-40 to 125	TM2903
TPSM82903SISR.A	Active	Production	uSiP (SIS) | 11	3000 | LARGE T&R	-	Call TI	Call TI	-40 to 125	TM2903

(1) **Status:** For more details on status, see our product life cycle.

(2) **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

(3) **RoHS values:** Yes, No, RoHS Exempt. See the TI RoHS Statement for additional information and value definition.

(4) **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

(5) **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

(6) **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

SIS0011A

PACKAGE OUTLINE

MicroSiP™ - 1.6 mm max height

MICRO SYSTEM IN PACKAGE



MicroSiP is a trademark of Texas Instruments

NOTES:

1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. Pick and place nozzle ∅ 1.3 mm or smaller recommended.
4. The package thermal pad must be soldered to the printed circuit board for thermal and mechanical performance.



LAND PATTERN EXAMPLE
SOLDER MASK DEFINED
SCALE:25X

SOLDER MASK DETAIL

4226726/B 07/2021

NOTES: (continued)

5. This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature number SLUA271 (www.ti.com/lit/slua271).

6. Vias are optional depending on application, refer to device data sheet. If any vias are implemented, refer to their locations shown on this view. It is recommended that vias under paste be filled, plugged or tented



SOLDER PASTE EXAMPLE
BASED ON 0.125 mm THICK STENCIL

EXPOSED PAD
80% PRINTED SOLDER COVERAGE BY AREA
SCALE:25X

4226726/B 07/2021

NOTES: (continued)

7. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.

重要通知和免责声明

TI“按原样”提供技术和可靠性数据（包括数据表）、设计资源（包括参考设计）、应用或其他设计建议、网络工具、安全信息和其他资源，不保证没有瑕疵且不做出任何明示或暗示的担保，包括但不限于对适销性、与某特定用途的适用性或不侵犯任何第三方知识产权的暗示担保。

这些资源可供使用 TI 产品进行设计的熟练开发人员使用。您将自行承担以下全部责任：(1) 针对您的应用选择合适的 TI 产品，(2) 设计、验证并测试您的应用，(3) 确保您的应用满足相应标准以及任何其他安全、安保法规或其他要求。

这些资源如有变更，恕不另行通知。TI 授权您仅可将这些资源用于研发本资源所述的 TI 产品的相关应用。严禁以其他方式对这些资源进行复制或展示。您无权使用任何其他 TI 知识产权或任何第三方知识产权。对于因您对这些资源的使用而对 TI 及其代表造成的任何索赔、损害、成本、损失和债务，您将全额赔偿，TI 对此概不负责。

TI 提供的产品受 TI 销售条款)、TI 通用质量指南 或 ti.com 上其他适用条款或 TI 产品随附的其他适用条款的约束。TI 提供这些资源并不会扩展或以其他方式更改 TI 针对 TI 产品发布的适用的担保或担保免责声明。 除非德州仪器 (TI) 明确将某产品指定为定制产品或客户特定产品，否则其产品均为按确定价格收入目录的标准通用器件。

TI 反对并拒绝您可能提出的任何其他或不同的条款。

版权所有 © 2026，德州仪器 (TI) 公司

最后更新日期：2025 年 10 月