


FMI

FM2

P3

A1



C257

R256

L303

C303

L302

L311

C302

C312

L301

R371

C371

C361

R361

R351

X2



C391

C392

C311

C301

C281

X1



C271

C261

C5

C4


C3

C411

C421

C431

U1



C251

C221

R221

R181

R191

C211

C1


J

FCC ID: ZAT2545EM  
IC: 451H-2545EM

FM3





**TEXAS  
INSTRUMENTS**  
CC2545EM 1.1




FM4

FM2

P2





P1





FM3


Max. 3.8V

























FCC ID: ZAT2545EM  
IC: 451H-2545EM



**TEXAS  
INSTRUMENTS**  
CC2545EM 1.1

CE



Max. E .x 8V

