



Linsenkopfschrauben

mit TX-Antrieb



dk	4	5	6	8	10	12
k	1,6	2,0	2,4	3,1	3,8	4,6
a	0,8	0,9	1,0	1,4	1,6	2,0
★	TX 6	TX 8	TX 10	TX 20	TX 25	TX 30
Länge / Ø	M2	M2,5	M3	M4	M5	M6