



TAPE AND REEL INFORMATION


*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
M0C1103QDDFRQ1	SOT-23-THIN	DDF	8	3000	180.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
M0C1103QDGS20RQ1	VSSOP	DGS	20	5000	330.0	16.4	5.4	5.4	1.45	8.0	16.0	Q1
M0C1103QDSGRQ1	WSO	DSG	8	3000	180.0	8.4	2.3	2.3	1.15	4.0	8.0	Q2
M0C1103QDYRQ1	SOT-23-THIN	DYY	16	3000	330.0	12.4	4.8	3.6	1.6	8.0	12.0	Q3
M0C1103QRUKRQ1	WQFN	RUK	20	3000	330.0	12.4	3.3	3.3	1.1	8.0	12.0	Q2
M0C1104QDDFRQ1	SOT-23-THIN	DDF	8	3000	180.0	8.4	3.2	3.2	1.4	4.0	8.0	Q3
M0C1104QDGS20RQ1	VSSOP	DGS	20	5000	330.0	16.4	5.4	5.4	1.45	8.0	16.0	Q1
M0C1104QDSGRQ1	WSO	DSG	8	3000	180.0	8.4	2.3	2.3	1.15	4.0	8.0	Q2
M0C1104QDYRQ1	SOT-23-THIN	DYY	16	3000	330.0	12.4	4.8	3.6	1.6	8.0	12.0	Q3
M0C1104QRUKRQ1	WQFN	RUK	20	3000	330.0	12.4	3.3	3.3	1.1	8.0	12.0	Q2

TAPE AND REEL BOX DIMENSIONS



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
M0C1103QDDFRQ1	SOT-23-THIN	DDF	8	3000	210.0	185.0	35.0
M0C1103QDGS20RQ1	VSSOP	DGS	20	5000	353.0	353.0	32.0
M0C1103QDSGRQ1	WSON	DSG	8	3000	210.0	185.0	35.0
M0C1103QDYRQ1	SOT-23-THIN	DYY	16	3000	336.6	336.6	31.8
M0C1103QRUKRQ1	WQFN	RUK	20	3000	367.0	367.0	35.0
M0C1104QDDFRQ1	SOT-23-THIN	DDF	8	3000	210.0	185.0	35.0
M0C1104QDGS20RQ1	VSSOP	DGS	20	5000	353.0	353.0	32.0
M0C1104QDSGRQ1	WSON	DSG	8	3000	210.0	185.0	35.0
M0C1104QDYRQ1	SOT-23-THIN	DYY	16	3000	336.6	336.6	31.8
M0C1104QRUKRQ1	WQFN	RUK	20	3000	367.0	367.0	35.0