

PMP40381 REV A Bill of Materials

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
C1, C19, C20	3		870025374005	Würth Electronics Inc.	CAP ALUM POLY 330UF 20% 16V T/H	Radial, Can
C2, C3	2	47uF	C3216X5R1E476M160AC	TDK	CAP, CERM, 47 µF, 25 V, +/- 20%, X5R, 1206_190	1206_190
C4	1	470pF	06035A471JAT2A	AVX	CAP, CERM, 470 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
C5	1	330pF	GRM31A5C2J331JW01D	MuRata	CAP, CERM, 330 pF, 630 V, +/- 5%, C0G/NP0, 1206	1206
C6, C7, C12, C13	4	1uF	GCM188R71C105KA64D	MuRata	CAP, CERM, 1 µF, 16 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0603	0603
C8	1		860020373010	Würth Electronics Inc.	CAP, AL, 220 µF, 16 V, +/- 20%, TH	Radial, Can
C9, C11, C17, C18	4		860021378014	Würth Electronics Inc.	CAP ALUM 33UF 20% 400V RADIAL	Radial, Can
C10	1		860020474013	Würth Electronics Inc.	CAP, AL, 330 µF, 25 V, +/- 20%, TH	Radial, Can
C14	1	0.1uF	06033C104KAT2A	AVX	CAP, CERM, 0.1 µF, 25 V, +/- 10%, X7R, 0603	0603
C15, C22	2	100pF	06035A101JAT2A	AVX	CAP, CERM, 100 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
C16	1		RNU1E221MDNASQPX	Nichicon	CAP ALUM POLY 220UF 20% 25V T/H	Radial, Can
C21	1	33uF	UVR1E220MDD6TP	Nichicon	CAP, AL, 33 µF, 25 V, +/- 20%, TH	D5xL11mm
C23	1	0.033uF	06035C333JAT2A	AVX	CAP, CERM, 0.033 µF, 50 V, +/- 5%, X7R, 0603	0603
C25	1	0.1uF	06035C104KAT2A	AVX	CAP, CERM, 0.1 µF, 50 V, +/- 10%, X7R, 0603	0603
C26	1	10uF	C1608X5R1A106M080AC	TDK	CAP, CERM, 10 µF, 10 V, +/- 20%, X5R, 0603	0603
C27, C28, C30, C32, C33	5	0.1uF	06033D104KAT2A	AVX	CAP, CERM, 0.1 µF, 25 V, +/- 10%, X5R, 0603	0603
C29	1	1uF	C0603C105K3RACTU	Kemet	CAP, CERM, 1 µF, 25 V, +/- 10%, X7R, 0603	0603
C31	1	2200pF	DE1E3RA472MA4BP01F	MuRata	CAP, CERM, 4700 pF, 500 V, +/- 20%, E, Disc 10x8mm	Disc 10x8mm
C35	1	470pF	06031C471JAT2A	AVX	CAP, CERM, 470 pF, 100 V, +/- 5%, X7R, 0603	0603
D1, D5	2	60V	B160S1F	Diodes	Diode, Schottky, 60 V, 1 A, SOD-123	SOD-123
D2	1	200V	BAS20HT1G	ON Semiconductor	Diode, Switching, 200 V, 0.2 A, AEC-Q101, SOD-323	SOD-323
D3	1	800V	MB8S-TP	Micro Commercial Component	Diode, Switching-Bridge, 800 V, 0.5 A, TO269AA	TO269AA
D4	1	60V	B160-13-F	Diodes Inc.	Diode, Schottky, 60 V, 1 A, SMA	SMA
D6	1	150V	SK215ATR	SMC Diode Solutions	Diode, Schottky, 150 V, 2 A, SMA	SMA
D13	1	1000V	RS1M-13-F	Diodes Inc.	Diode, P-N, 1000 V, 1 A, SMA	SMA
F1	1		36911000000	Littelfuse	Fuse, 1 A, 300VAC/VDC, TH	8x8.5x4mm
L1	1	220uH	7447462221	Würth Elektronik	Inductor, Unshielded Drum Core, Ferrite, 220 µH, 0.5 A, 0.96 ohm, TH	D6 x 8.5mm
L2	1		XFL3010-153MEB	Coilcraft	Power inductor, shielded, 20% tol, SMT, RoHS, halogen-f	
L4	1		7447462010	Würth Electronics Inc.	FIXED IND 1UH 8.5A 15 MOHM TH	Radial
Q2	1		STD4NK80Z-1	STMicroelectronics	MOSFET N-CH 800V 3A IPAK	
R1, R11, R22, R25	4	1.00Meg	CRCW12061M00FKEA	Vishay-Dale	RES, 1.00 M, 1%, 0.25 W, 1206	1206
R2, R15, R23, R28	4	200k	CRCW1206200KJNEA	Vishay-Dale	RES, 200 k, 5%, 0.25 W, 1206	1206
R3, R7, R9	3	3.00k	ERJ-6ENF3001V	Panasonic	RES, 3.00 k, 1%, 0.125 W, AEC-Q200 Grade 0, 0805	0805
R4	1	1.50Meg	CRCW06031M50FKEA	Vishay-Dale	RES, 1.50 M, 1%, 0.1 W, 0603	0603
R5	1	10.0k	CRCW080510K0FKEA	Vishay-Dale	RES, 10.0 k, 1%, 0.125 W, 0805	0805
R6	1	150	CRCW1206150RJNEA	Vishay-Dale	RES, 150, 5%, 0.25 W, 1206	1206
R8	1	330k	CRCW1206330KJNEA	Vishay-Dale	RES, 330 k, 5%, 0.25 W, 1206	1206
R13	1	106k	RT0805BRD07106KL	Yageo America	RES, 106 k, 1%, 0.125 W, 0805	0805
R14	1	36.0k	RG1608P-363-B-T5	Susumu Co Ltd	RES, 36.0 k, 1%, 0.1 W, 0603	0603

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
R16	1	10k	CRCW060310K0JNEA	Vishay-Dale	RES, 10 k, 5%, 0.1 W, 0603	0603
R17, R20	2	4.70	ERJ-6RQF4R7V	Panasonic	RES, 4.70, 1%, 0.125 W, 0805	0805
R18	1	560	CRCW0603560RJNEA	Vishay-Dale	RES, 560, 5%, 0.1 W, 0603	0603
R19	1	51.0k	RC0603FR-0751KL	Yageo America	RES, 51.0 k, 1%, 0.1 W, 0603	0603
R21	1	110k	CRCW0603110KFKEA	Vishay-Dale	RES, 110 k, 1%, 0.1 W, 0603	0603
R24, R34, R35	3	10	CRCW080510R0JNEA	Vishay-Dale	RES, 10, 5%, 0.125 W, 0805	0805
R27	1	1.50k	RC0603FR-071K5L	Yageo America	RES, 1.50 k, 1%, 0.1 W, 0603	0603
R30, R31, R33, R41	4	10.0k	RC0603FR-0710KL	Yageo America	RES, 10.0 k, 1%, 0.1 W, 0603	0603
R37	1	20.0	CRCW060320R0FKEA	Vishay-Dale	RES, 20.0, 1%, 0.1 W, 0603	0603
R42	1	470	RC0603FR-07470RL	Yageo America	RES, 470, 1%, 0.1 W, 0603	0603
R43	1	56.0K	RC0603FR-0756KL	Yageo America	RES, 56.0k, 1%, 0.1 W, 0603	0603
T1	1		750343920	Würth Electronics Inc.	Transformer, Flyback	Würth Elektronik
U1, U7	2		TLV76050DBZR	Texas Instruments	100mA, 30V Wide-VIN, Fixed-Output Linear-Voltage Regulator	DBZ
U2	1		TPS70950DRVR	Texas Instruments	150-mA, 30-V, Ultra-Low IQ, Wide Input Low-Dropout Regulator with Reverse Current Protection, DRV0006A (WSON-6)	DRV0006A
U3	1		TPS560430XFDBVR	Texas Instruments	4V to 36 V 0.6 A Synchronous Step-Down Converter, DBV0006A (SOT-23-6)	DBV0006A
U4	1		LTV-817S	Lite-On	Optocoupler, 5 kV, 50-600% CTR, SMT	DIP-4 SMT
U5	1		TL431AIDBZT	Texas Instruments	Adjustable Precision Shunt Regulator, 34 ppm / degC, 100 mA, -40 to 85 degC, 3-pin SOT-23 (DBZ), Green (RoHS & no Sb/Br)	DBZ0003A
U6	1		UCC28600D	Texas Instruments	Quasi-Resonant Flyback Green-Mode Controller with Current Control, 99 % Duty Cycle, -40 to +105 degC, 8-pin SOIC (D), Green (RoHS & no Sb/Br)	D0008A
C24	0	2200pF	DE1E3RA222MA4BP01F	MuRata	CAP, CERM, 2200 pF, 500 V, +/- 20%, E, Disc 10x8mm	Disc 10x8mm
C34, C36, C37	0	470pF	06031C471JAT2A	AVX	CAP, CERM, 470 pF, 100 V, +/- 5%, X7R, 0603	0603
Q1	0	40 V	MMBT3904LT1G	ON Semiconductor	Transistor, NPN, 40 V, 0.2 A, SOT-23	SOT-23
R10	0	330k	CRCW1206330KJNEA	Vishay-Dale	RES, 330 k, 5%, 0.25 W, 1206	1206
R12, R29	0	1.10k	CRCW12061K10FKEA	Vishay-Dale	RES, 1.10 k, 1%, 0.25 W, 1206	1206
R26, R32, R44	0	10.0k	RC0603FR-0710KL	Yageo America	RES, 10.0 k, 1%, 0.1 W, 0603	0603
R36, R38, R39	0	20.0	CRCW060320R0FKEA	Vishay-Dale	RES, 20.0, 1%, 0.1 W, 0603	0603
TP1	0		5005	Keystone	Test Point, Compact, Red, TH	Red Compact Testpoint
TP2	0		5006	Keystone	Test Point, Compact, Black, TH	Black Compact Testpoint
RV1	0	560V	Used in BOM report	Used in BOM report	Varistor, xxxVAC, xxVDC, xxJ, [Diameter], [Package]	Used in PnP output and some BOM reports

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>), [evaluation modules](#), and [samples](http://www.ti.com/sc/docs/sampterm.htm) (<http://www.ti.com/sc/docs/sampterm.htm>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2018, Texas Instruments Incorporated