## TUSB1046EVM-008 HSDC008-002 Revised: Monday, May 22, 2017 Revision: E1

## Bill Of Mat Page1

Item Quantity Reference Part Manufacturer Manufacturer Part No Description

1	12 C1,C2,C3,C4,	220nF	60201	TDK Corporation	C0603X5R1A224K	CAP CER 0.22UF 10V X5R 0201
<del></del>	C9,C10,C11,C12,C13,C14,	220111	0201	TER COLDOLATION	COODS/GREATER	CAF CER 0.2201 10 V ASR 0201
<del></del>	C15,C16					
2	0 C5,C6, C7, C8	DNI - 220nF		TDK Corporation	C0603X5R1A224K	CAP CER 0.22UF 10V X5R 0201
3	3 C17,C24,C25	10uF		Samsung	CL21B106KOQNNNE	CAP CER 10UF 16V X7R 0805
4	0 C34,C35	DNI - 10uF		Samsung	CL21B106KOQNNNE	CAP CER 10UF 16V X7R 0805
5	3 C18,C19,C20	1uF			GRM033R60J105MEA2D	CAP CER 1UF 6.3V X5R 0201
6	10 C21,C22,C23,C27,C28,C29,	0.1uF	c0201	Murata Electronics No	GRM033R61A104ME15D	CAP CER 0.1UF 10V X5R 0201
1	C32,C33, C30,C31					
7	1 C26	22uF	805	Taiyo Yuden	JMK212BJ226KG-T	CAP CER 22UF 6.3V X5R 0805
8	0 C36	DNI - 22uF	805	Taiyo Yuden	JMK212BJ226KG-T	CAP CER 22UF 6.3V X5R 0805
9	1 D1	SCHOTTKY	diode smb	NXP Semiconductors	PMEG3050EP,115	DIODE SCHOTTKY 30V 5A SOD128
10	5 D2,D3,D4,D5	Green		Lite-On Inc	LTST-C170KGKT	LED GREEN CLEAR 0805 SMD
11	0 D6	DNI - Green		Lite-On Inc	LTST-C170KGKT	LED GREEN CLEAR 0805 SMD
	0,00	DIVI GICCII	icuooos	Samtec Inc	HTSW-104-07-G-S	ELD GREEN CLEAR GOOD SIND
1				Samtee me	1113W 104 07 0 3	
l	JMP1,JMP2,JMP3,JMP4,JMP5,JMP6,	l				
12	10 JMP7,JMP8,JMP9,JMP11	4 Pin-T Berg Jumper	berg2x3tee	6	UTCW 405 07 0 C	4 Positions Header Connector Through Hole
13	2 JMP10,JMP12	5Pin-T Berg Jumper	berg2x5tee		HTSW-105-07-G-S	5 Positions Header Connector Through Hole
14	5 J1,J2,J3,J4	CON02	HDR_THVT_1x2_100_M		HTSW-102-07-G-S	2 Positions Header Connector Through Hole
15	0 16	DNI - CON02	HDR_THVT_1x2_100_M		HTSW-102-07-G-S	2 Positions Header Connector Through Hole
16	1 J5	DC_PWR_JACK	pj-202ah		PJ-202AH	CONN PWR JACK 2X5.5MM KINKED PIN
17	1 L1	1uH	IND_NR3015	Taiyo Yuden	NR3015T1R0N	FIXED IND 1UH 2.1A 36 MOHM SMD
18	0 L2	DNI - 1uH	IND_NR3015	Taiyo Yuden	NR3015T1R0N	FIXED IND 1UH 2.1A 36 MOHM SMD
19	4 M1,M2,M3,M4	#4-40 1/2	mprt-shcs-00001-0000	MSC	05664057	screws
20	4 M5,M6,M7,M8	#4-40 1in	mprt-stan-00001-0000		534-2031	Standoff
21	1 P1	Wurth 632712000021	t_632_712_000_b6_b7		632712000021	CONN PLUG USB TYPE C SMD
22	1 P2	JAE DX07S024JJ2	-C SMRT DX07S024JJ2		DX07S024JJ2R1300	CONN RCPT USB3.1 TYPEC SMD R/A
23	2 R1,R2	* 0 Ohm		Yageo	RC0402JR-070RL	RES SMD 0.00HM JUMPER 1/16W 0402
24	17 R3,R4,R5,R6,R7,R8,R9,R10,	1K		Vishay Dale	CRCW04021K00FKED	RES SMD 1K OHM 1% 1/16W 0402
24		ır	10402	Visitay Date	CNCW04021R001RED	RES SIVID IN ORIVI 176 I/ 16W 0402
$\vdash$	R19,R20,R24,R25,R26,R29,					
	R30,R33,R35					
25	9 R11,R12,R13,R14,R15,R16,	100K	r0402	Yageo	RC0402FR-07100KL	RES SMD 100K OHM 1% 1/16W 0402
	R17,R18,R42					
26	12 R21,R23,R27,R28,R31,R32,	20K	r0402	Vishay Dale	CRCW040220K0FKED-	RES SMD 20K OHM 1% 1/5W 0402
	R34,R37,R49,R50,R58,R57					
27	1 R39	178K	r0402	Panasonic Electronic C	ERJ-2RKF1783X	RES SMD 178K OHM 1% 1/10W 0402
28	0 R36,R55	DNI - 178K	r0402	Panasonic Electronic C	ERJ-2RKF1783X	RES SMD 178K OHM 1% 1/10W 0402
29	1 R40	0 Ohm	r1206	Vishay Dale	CRCW12060000Z0EA-	RES SMD 0.0 OHM JUMPER 1/4W 1206
30	0 R56	DNI - 0 Ohm	r1206	Vishay Dale	CRCW12060000Z0EA-	RES SMD 0.0 OHM JUMPER 1/4W 1206
23	2 R41	330 Ohm		Yageo	RC0603FR-07330RL	RES SMD 330 OHM 1% 1/10W 0603
23	0 R52	DNI - 330 Ohm		Yageo	RC0603FR-07330RL	RES SMD 330 OHM 1% 1/10W 0603
24	4 R43,R44,R51	0		Panasonic Electronic C		RES SMD 0.00HM JUMPER 1/10W 0402
24	0 R38	DNI - 0	r0402	Panasonic Electronic C		RES SMD 0.00HM JUMPER 1/10W 0402
25	2 R45,R74	200		Panasonic Electronic C	ERJ-2RKF2000X	RES SMD 200 OHM 1% 1/10W 0402
26	2 R46,R75	1.5K	r0402	Panasonic Electronic C		RES SMD 1.5K OHM 1% 1/10W 0402
27	2 R47,R60	3.9K	r0402	Panasonic Electronic C		RES SMD 3.9K OHM 1% 1/10W 0402
28	2 R48,R59	6.2K	r0402	Panasonic Electronic C		RES SMD 6.2K OHM 5% 1/10W 0402
28	7 R70,R71,R72,R69, R53, R54, R66	0 0		Panasonic Electronic C		RES SMD 0.00HM JUMPER 1/20W 0201
						·
30	0 R61,R62,R63,R64,R65	DNI - 0		Panasonic Electronic C		RES SMD 0.00HM JUMPER 1/20W 0201
31	3 R67,R68,R73	75		Yageo	RC0603JR-0775RL	RES SMD 75 OHM 5% 1/10W 0603
32	0 R22	DNI - 39.2K		Yageo	RC0402FR-0739K2L	RES SMD 39.2K OHM 1% 1/16W 0402
33	1 SW1	8-POS 50-MIL SMT	W_SMVT_SPST_TDA08		TDA08H0SB1	SWITCH SLIDE DIP SPST 25MA 24V
34	1 U1	TUSB1046	VOOD_C14861_QFN-40		TUSB1046	USB Type-C DP ALT Mode, 10 Gbps Linear Redriver Crosspoint Switch
35	1 U2	TPS62082DSGT		Texas Instruments	TPS62082DSGT	1.2A High Efficient Step Down Converter in 2x2mm SON Package. 3.3 Vout (Min)
36	1 U3	TPD6S300		Texas Instruments	TPD6S300RUKR	USB Type-C™ Port Protector: Short-to-VBUS Overvoltage and IEC ESD Protection
37	2 U4,U5	TPD4E02B04		Texas Instruments	TPD4E02B04DQAR	4-Channel ESD Protection Diode for USB Type-C and HDMI 2.0
	2 U6,U7	DNI TUSB212	rgy_s-pvqfn-n14	Texas Instruments	TUSB212RWB	USB 2.0 High Speed Signal Conditioner
38					TRESCAGARGE	lander to the control of the control
39	0 U8	DNI - TPS62082	dsg	Texas Instruments	TPS62082DSGT	1.2A High Efficient Step Down Converter in 2x2mm SON Package. 3.3 Vout (Min)
		DNI - TPS62082 White Sticker TUSB1046EVM-008		Texas Instruments 3M ANY	THT-14-423-10 HSDC008-003	1.2A High Efficient Step Down Converter in 2x2mm SUN Package. 3.3 Yout (Min) Sticker Text: TUSB1046EVM-008 HSDC008-002 Rev A TUSB1046EVM-008 PCB Board

## IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ('TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products <a href="http://www.ti.com/sc/docs/stdterms.htm">http://www.ti.com/sc/docs/stdterms.htm</a>), evaluation modules, and samples (<a href="http://www.ti.com/sc/docs/sampterms.htm">http://www.ti.com/sc/docs/sampterms.htm</a>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2018, Texas Instruments Incorporated