

# PMP8362\_REVA BOM

COUNT	RefDes	Value	Description	Size	Part Number	MFR
1	C1	0.068uF	Capacitor, Film, 275VAC, 20%	0.689 x 0.217 inch	ECQU2A683ML	Panasonic
1	C15	0.01uF	Capacitor, Ceramic, 50V, X7R, 10%	0603	STD	STD
1	C17	100pF	Capacitor, Ceramic, 50V, C0G, 10%	0603	STD	STD
1	C2	22uF	CAP ALUM 22UF 400V 20% RADIAL	16 x 25 mm	UVR2G220MHD	Nichicon
2	C3, C12	1uF	Capacitor, Ceramic, 25V, X7R, 10%	0603	STD	STD
1	C4	330uF	CAP ALUM 330UF 25V 20% RADIAL	0.315 inch	EKY-250ELL331MH15D	United Chemicon
4	C5, C8, C13, C16	0.1uF	Capacitor, Ceramic, 50V, X7R, 10%	0603	STD	STD
1	C6	180uF	CAP Polymer 180UF 16V 20% RADIAL	0.315 inch	RL81C181MDN1KX	Nichicon
2	C7, C14	33uF	Capacitor, Alum Electrolytic, 35V, -40 to +85C, ±20%	6.3x11 mm	STD	STD
1	C9	220pF	CAP CER 220PF 250VAC X1Y2 RAD	7.00 Dia mm	CS70-B2GA221KYNS	TDK
1	D1	SMAJ120A	Diode, Transient Voltage Suppressor, 120V	SMA	SMAJ120A	Bourns
2	D2, D5	B3100	Diode, Schottky, 3-A, 100-V		B3100	
1	D3	RH06-T	Diode, Bridge, 0.5-A, 600-V	MiniDIP	RH06-T	Diodes
1	D4	MRA4007	Diode, Rectifier, 1A, 1000V, SMA	SMA	STD	STD
1	D6	1N4148	Diode, Switching, 100-V, 200-mA, 225-mW,	SOD-123	1N4148W-7-F	Diodes Inc.
1	D7	MMSZ5248BT	Diode, Zener, xx-mA, yy-V	SOD123	MMSZ5248BT	On Semi
1	D8	BAT54WX	DIODE SCHOTTKY 30V SOD-523	SOD-523	BAT54WX	Micro Commercial Co
1	F1	2A	STD	0.335 inch	37213150001	STD
3	FB1, FB2, FB3		Bead, SMD Ferrite, 26ohms @ 100MHz, 10mohm DC, 6A	0603	BLM18KG260TN1D	Murata
1	J2	C-640901	Header, 5 pin Mate-N-Lock	0.300x1.300 inch	C-640901	Tyco
1	J3	1-1123723-4	Connector, 4 pin Vertical, 3.96mm pitch	8.5mm x 15.78mm	1-1123723-4	Tyco
1	L1	54PR515-146	Inductor, AC-Line Common Mode Choke	0.539 x 0.606 inch	54PR515-146	Vitec
1	Q1	SPP03N60C3	MOSFET N-CH 650V 3.2A TO-220AB	TO-220	SPP03N60C3	Infineon
2	R1, R2	1MEG	Resistor, 1/4 watt, 5%	1206	STD	STD
1	R10	10k	Resistor, Chip, 1/16W, 1%	0603	STD	STD
1	R100	1k	Resistor, 1/4 watt, 5%	1206	STD	STD
1	R11	54.9k	Resistor, Chip, 1/16W, 1%	0603	STD	STD
2	R12, R13	75k	Resistor, Chip, 1/16W, 1%	0603	STD	STD
1	R14	4.99k	Resistor, Chip, 1/16W, 1%	0603	STD	STD
1	R15	20k	Resistor, Chip, 1/16W, 1%	0603	STD	STD
1	R16	100k	Resistor, Chip, 1/16W, 1%	0603	STD	STD
1	R22	200	Resistor, Chip, 1/16W, 1%	0603	STD	STD
1	R3	30	Resistor, 1/4 watt, 5%	1206	STD	STD
2	R4, R6	10	Resistor, Chip, 1/16W, 1%	0603	STD	STD
1	R5	187k	Resistor, Chip, 1/16W, 1%	0603	STD	STD
1	R8	1k	Resistor, Chip, 1/16W, 1%	0603	STD	STD
1	R9	2k	Resistor, Chip, 1/16W, 1%	0603	STD	STD
4	SC1, SC2, SC3, SC4		Through Hole for Screw #4 plated		STD	STD
1	T2	250 µH	Transformer, Flyback, 2 Prim, 1 Sec	1.000 x 0.670	G124039LF	GCI
2	TP2, TP5	5000	Test Point, Red, Thru Hole Color Keyed	0.100 x 0.100 inch	5000	Keystone
1	TP4	5001	Test Point, Black, Thru Hole Color Keyed	0.100 x 0.100 inch	5001	Keystone
1	U2	UCC28610D	IC, Quasi-Resonant Flyback Green-Mode Controller	SO8	UCC28610D	TI
1	U3	FOD817A	IC, Optocoupler, 5300-V, 80-160% CTR	DIP-4	FOD817A	Fairchild
1	U4	TL431DBZ	IC, Precision Adjustable Shunt Regulator	SOT23-3	TL431DBZ	TI

## IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46C and to discontinue any product or service per JESD48B. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have **not** been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components which meet ISO/TS16949 requirements, mainly for automotive use. Components which have not been so designated are neither designed nor intended for automotive use; and TI will not be responsible for any failure of such components to meet such requirements.

### Products

Audio	<a href="http://www.ti.com/audio">www.ti.com/audio</a>
Amplifiers	<a href="http://amplifier.ti.com">amplifier.ti.com</a>
Data Converters	<a href="http://dataconverter.ti.com">dataconverter.ti.com</a>
DLP® Products	<a href="http://www.dlp.com">www.dlp.com</a>
DSP	<a href="http://dsp.ti.com">dsp.ti.com</a>
Clocks and Timers	<a href="http://www.ti.com/clocks">www.ti.com/clocks</a>
Interface	<a href="http://interface.ti.com">interface.ti.com</a>
Logic	<a href="http://logic.ti.com">logic.ti.com</a>
Power Mgmt	<a href="http://power.ti.com">power.ti.com</a>
Microcontrollers	<a href="http://microcontroller.ti.com">microcontroller.ti.com</a>
RFID	<a href="http://www.ti-rfid.com">www.ti-rfid.com</a>
OMAP Mobile Processors	<a href="http://www.ti.com/omap">www.ti.com/omap</a>
Wireless Connectivity	<a href="http://www.ti.com/wirelessconnectivity">www.ti.com/wirelessconnectivity</a>

### Applications

Automotive and Transportation	<a href="http://www.ti.com/automotive">www.ti.com/automotive</a>
Communications and Telecom	<a href="http://www.ti.com/communications">www.ti.com/communications</a>
Computers and Peripherals	<a href="http://www.ti.com/computers">www.ti.com/computers</a>
Consumer Electronics	<a href="http://www.ti.com/consumer-apps">www.ti.com/consumer-apps</a>
Energy and Lighting	<a href="http://www.ti.com/energy">www.ti.com/energy</a>
Industrial	<a href="http://www.ti.com/industrial">www.ti.com/industrial</a>
Medical	<a href="http://www.ti.com/medical">www.ti.com/medical</a>
Security	<a href="http://www.ti.com/security">www.ti.com/security</a>
Space, Avionics and Defense	<a href="http://www.ti.com/space-avionics-defense">www.ti.com/space-avionics-defense</a>
Video and Imaging	<a href="http://www.ti.com/video">www.ti.com/video</a>

**TI E2E Community** [e2e.ti.com](http://e2e.ti.com)