

DS90CP04

2.5 Gbps LVDS 4 x 4 Crosspoint Switch



Literature Number: SNLA152

Application Brief

2.5 Gbps LVDS 4 x 4 Crosspoint Switch

Application Brief 117

Lee Sledjeski

The unique architecture, diminutive size and flow through pinout of the DS90CP04 (Figure 1) make it an ideal building block for today's high performance systems. This 4 x 4 crosspoint switch easily expands to build larger or uniquely shaped switch arrays. Digital control pins give the designer direct access to common building block functionality. Low power LVDS (Low Voltage Differential Signal) design and an efficient, low profile 6 mm square LLP (Leaded Leadless Package), allow the CP04 to be placed into the tightest board designs. Each CP04 is guaranteed to operate at datarates to 2.5 Gbps. Clock distribution applications will support output clock rates up to 1.5 GHz.

Programming The Switch

The DS90CP04 can be programmed in two ways, via external control pins (Mode = 1), or

through a serial link (Mode = 0). The digital control pins provide immediate access to commonly used switch configurations:

1. Broadcast (1:4)
2. Buffer/Repeater (4:4)
3. Redundancy (Dual 1:2)

For applications where multiple CP04s will be utilized as larger switch arrays, or when flexible hardware configurations are required, a serial programming link is provided. This link enables the designer to daisy-chain multiple CP04s together and reprogram individual ICs based on an address determined by IC placement in the serial stream. For array applications, row and column links can simplify the programming model and ease board routing constraints.




Figure 1: DS90CP04 Block Diagram and Pinout

Highly Adaptable I/Os

Designers are often faced with various signaling issues between subsystems or even adjacent ICs. At the forefront is signal interface of signal translation. This problem isn't limited to low speed TTL signals. High-speed differential lines can also require special conditioning or translation.

The CP04 allows for an extended input




Figure 2: I/O Voltage Levels




Figure 3: 2.5 Gbps Eye Diagram

common mode range, easily translating from other widely used high-speed technologies like CML (Current Mode Logic) or LVPECL (Low Voltage Positive ECL) to LVDS. The chart shown in *Figure 2* highlights typical voltage swings generated by various high-speed I/O technologies.

Performance Measurements

For high-speed data communications, just being able to detect various I/O standards isn't enough. The CP04 is tuned to produce low jitter LVDS outputs for a wide range of the input signal conditions. Running at the maximum specified data rate of 2.5 Gbps a PRBS datastream (shown in *Figure 3*) will have 35 ps pp of total jitter. The CP04 AC response is flat across the entire common mode range with input voltage swings of as low as 100 mV. Whether it's being used to switch clock and data in a CDR application or for simple distribution, the CP04 delivers low skew (40 ps typical, 100 ps maximum, see *Figure 4*) performance for all possible datapaths.




Figure 4: Channel to Channel Skew

LVDS Specialty Function Selection Guide

Part Number	Description	Data Rate	Jitter (ps)
DS92CK16	1 to 6 LVDS Clock Distribution	DC to 125 MHz	--
DS90LV110	1 to 10 LVDS Clock Distribution	DC to 400 MHz	2.8 _{RMS}
DS90LV110	1 to 10 LVDS Data Distribution	DC to 800 Mbps	145
DS90CP04	4 x 4 Digital Crosspoint Switch (Data)	DC to 2.5 Gbps	35
DS90CP04	4 x 4 Digital Crosspoint Switch (Clock)	DC to 1.25 GHz	2.5 _{RMS}
DS90CP22	2 x 2 Digital Crosspoint Switch	DC to 800 Mbps	75
DS90LV001	1-Bit LVDS Repeater	DC to 800 Mbps	100
DS92001	1-Bit BLVDS Backplane Driver (27Ω)	DC to 400 Mbps	--

National Semiconductor
2900 Semiconductor Dr.
PO Box 58090
Santa Clara, CA 95052
1-800-272-9959

Visit our Web site at:
www.national.com

For more information,
send email to:
newfeedback@nsc.com

Additional Information

www.national.com/pf/DS/DS90CP04.html
lvds.national.com

Visit **The National Edge**, our online technical journal for an archive of Application Briefs and other interesting information.
edge.national.com

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products

Audio	www.ti.com/audio
Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DLP® Products	www.dlp.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
OMAP Mobile Processors	www.ti.com/omap
Wireless Connectivity	www.ti.com/wirelessconnectivity

Applications

Communications and Telecom	www.ti.com/communications
Computers and Peripherals	www.ti.com/computers
Consumer Electronics	www.ti.com/consumer-apps
Energy and Lighting	www.ti.com/energy
Industrial	www.ti.com/industrial
Medical	www.ti.com/medical
Security	www.ti.com/security
Space, Avionics and Defense	www.ti.com/space-avionics-defense
Transportation and Automotive	www.ti.com/automotive
Video and Imaging	www.ti.com/video

TI E2E Community Home Page

e2e.ti.com

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2011, Texas Instruments Incorporated