Variant: 001

Generated: 5/12/2016 9:39:22 AM

TID #: TIDA-00314

ISE4022 REV E2 Bill of Materials



Item #	Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
1	!PCB1	1		ISE4022	Any	Printed Circuit Board	
2	C1	1	1000pF	C1210C102KGRACTU	Kemet	CAP, CERM, 1000pF, 2000V, +/-10%, X7R, 1210	1210
3	C2	1	0.01uF	GCM155R71H103KA55D	MuRata	CAP, CERM, 0.01uF, 50V, +/-10%, C0G/NP0, 0402	0402
4	C3	1	2.2uF	GRM188R71A225KE15D	MuRata	CAP, CERM, 2.2 µF, 10 V, +/- 10%, X7R, 0603	0603
5	C4	1	2.2uF	GRM188R71A225KE15D	MuRata	CAP, CERM, 2.2uF, 10V, +/-10%, X7R, 0603	0603
6	C5, C8	2	18pF	GRM1885C2A180JA01D	MuRata	CAP, CERM, 18pF, 100V, +/-5%, C0G/NP0, 0603	0603
7	C6, C7	2	10pF	500R07S100JV4T	Johanson Technology	CAP, CERM, 10 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
8	C9, C13	2	0.22uF	GRM155R71C224KA12D	MuRata	CAP, CERM, 0.22 µF, 16 V, +/- 10%, X7R, 0402	0402
9	C10	1	0.47uF	C0603C474K8RACTU	Kemet	CAP, CERM, 0.47uF, 10V, +/-10%, X7R, 0603	0603
10	C11	1	2200pF	C1005X7R1H222K	TDK	CAP, CERM, 2200 pF, 50 V, +/- 10%, X7R, 0402	0402
11	C12	1	4.7uF	GRM21BR71A475KA73L	MuRata	CAP, CERM, 4.7 μF, 10 V, +/- 10%, X7R, 0805	0805
12	C14, C17, C21, C34	4	10uF	C1608X5R1A106M	TDK	CAP, CERM, 10 μF, 10 V, +/- 20%, X5R, 0603	0603
13	C15	1	1uF	C1608X7R1C105K	TDK	CAP, CERM, 1uF, 16V, +/-10%, X7R, 0603	0603
14	C16, C35	2	0.1uF	GRM155R71C104KA88D	MuRata	CAP, CERM, 0.1uF, 16V, +/-10%, X7R, 0402	0402
15	C18, C22, C24, C26	4	1uF	C1608X7R1C105K	TDK	CAP, CERM, 1 μF, 16 V, +/- 10%, X7R, 0603	0603
16	C19, C27, C29, C38, C39	5	0.1uF	GRM155R71C104KA88D	MuRata	CAP, CERM, 0.1 μF, 16 V, +/- 10%, X7R, 0402	0402
17	C25, C31	2	100pF	06035A101FAT2A	AVX Corporation	CAP CER 100PF 50V 1% NP0 0603	0603
18	C28, C30	2	120pF	GRM1885C2A121JA01D	MuRata	CAP, CERM, 120 pF, 100 V, +/- 5%, C0G/NP0, 0603	0603
19	C32	1	0.1uF	C1005X7R1H104K050BB	TDK	CAP, CERM, 0.1 µF, 50 V, +/- 10%, X7R, 0402	0402
20	C36	1	3.3uF	C1005X5R1A335K050BC	TDK	CAP, CERM, 3.3 µF, 10 V, +/- 10%, X5R, 0402	0402
21	C37	1	0.1uF	C3216X7R2E104K	TDK	CAP, CERM, 0.1uF, 250V, +/-10%, X7R, 1206	1206
22	D1	1	6V	SMBJ6.0CA	Littelfuse	Diode, TVS, Bi, 6 V, 600 W, SMB	SMB
23	D2	1	Orange	SML-P12DTT86	Rohm	LED, Orange, SMD	Orange LED
24	J1	1		651-305-142-821	Wurth Elektronik eiSos	MINI USB 2.0 SMT TYPE AB 5 CONTACTS R/A, SMD	9.2x9.9x4 mm
25	J2	1		LPPB061NFSC-RC	Sullins Connector Solutions	Receptacle, 1.27mm, 6x1, Gold, SMT	Receptacle, 1.27mm, 6x1, SMT
26	L1, L3, L4	3	330 ohm	BLM18SG331TN1D	MuRata	1.5A Ferrite Bead, 330 ohm @ 100MHz, SMD	0603
27	L2	1		SRF2012-300Y	Bourns	Inductor, Wirewound, Ferrite, , 0.45 A, 0.2 ohm, SMD	SMD, 2.05x1.25mm
28	L5	1	3.3uH	NLCV32T-3R3M-PFR	TDK	Inductor, Wirewound, Ferrite, 3.3uH, 1A, 0.16 ohm, SMD	3.2x2.2x2.5mm
29	L6, L7	2	1000 ohm	74279266	Wurth Elektronik eiSos	Ferrite Bead, 1000 ohm @ 100 MHz, 0.2 A, 0603	0603
30	R1	1	0	CRCW08050000Z0EA	Vishay-Dale	RES, 0, 5%, 0.125 W, 0805	0805
31	R2, R5, R8, R15, R18	5	0	CRCW04020000Z0ED	Vishay-Dale	RES, 0 ohm, 5%, 0.063W, 0402	0402
32	R6, R7	2	4.99k	CRCW04024K99FKED	Vishay-Dale	RES, 4.99k ohm, 1%, 0.063W, 0402	0402
33	R9, R12	2	27.4	CRCW040227R4FKED	Vishay-Dale	RES, 27.4, 1%, 0.063 W, 0402	0402
34	R10	1	499	CRCW0402499RFKED	Vishay-Dale	RES, 499, 1%, 0.063 W, 0402	0402
35	R11	1	1.40k	CRCW04021K40FKED	Vishay-Dale	RES, 1.40 k, 1%, 0.063 W, 0402	0402
36	R13	1	1M	RC0402JR-071ML	Yageo	RES,1M ohm, 5%, 0.063W, 0402	0402
37	R14	1	47.5k	CRCW040247K5FKED	Vishay-Dale	RES, 47.5 k, 1%, 0.063 W, 0402	0402
38	R19	1	768k	CRCW0402768KFKED	Vishay-Dale	RES, 768k ohm, 1%, 0.063W, 0402	0402
39	R20	1	15.0k	CRCW040215K0FKED	Vishay-Dale	RES, 15.0 k, 1%, 0.063 W, 0402	0402
40	R21	1	13k	CRCW040213K0JNED	Vishay-Dale	RES, 13k ohm, 5%, 0.063W, 0402	0402
41	S1	1		B3U-1000P	Omron Electronic Components	SWITCH TACTILE SPST-NO 0.05A 12V	3x1.6x2.5mm
42	U1	1		LP5907MFX-3.3/NOPB	Texas Instruments	ULTRA LOW-NOISE, 250-mA LINEAR REGULATOR FOR RF AND ANALOG CIRCUITS REQUIRES NO BYPASS CAPACITOR, DBV0005A	DBV0005A
43	U2	1		TPD2E2U06DRL	Texas Instruments	DUAL CHANNEL HIGH SPEED ESD PROTECTION DEVICE, DRL0005A	DRL0005A
44	U3	1		MSP430F5528IRGC	Texas Instruments	Mixed Signal MicroController, RGC0064B	RGC0064B
45	U4, U5	2		TPD1E10B06DPYR	Texas Instruments	ESD in 0402 Package with 10 pF Capacitance and 6 V Breakdown, 1 Channel, -40 to +125 degC, 2-pin X2SON (DPY), Green (RoHS & no Sb/Br)	DPY0002A
46	U6	1		DRV2605LDGS	Texas Instruments	Haptic Driver for LRA and ERM With Built-In Library and Smart Loop Architecture, DGS0010A	DGS0010A
47	U7	1		LDC1614RGH	Texas Instruments	Multi-Channel 12/28-Bit Inductance to Digital Converter with I2C, RGH0016A	RGH0016A
48	U8	1		TS5A12301EYFP	Texas Instruments	IEC LEVEL 4 ESD-PROTECTED 0.75-O SPDT ANALOG SWITCH WITH 1.8-V COMPATIBLE INPUT LOGIC, YFP0006AAAA	YFP0006AAAA
49	U9	1		DRV2667RGPR	Texas Instruments	Piezo Haptic Driver with Boost, Digital Front End, and Internal Waveform Memory, RGP0020D	RGP0020D
50	U10	1		HDC1010YPAR	Texas Instruments	Low Power, High Accuracy Digital Humidity Sensor with Temperature Sensor, YPA0008AGAE	YPA0008AGAE
51	Y1	1		ABM8-24.000MHZ-B2-T	Abracon Corportation	Crystal, 24.000MHz, 18pF, SMD	3.2x0.8x2.5mm
52	C20, C33	0	100uF	C3216X5R1A107M160AC	TDK	CAP, CERM, 100 μF, 10 V, +/- 20%, X5R, 1206_190	1206_190
		_			N/A	Fiducial mark. There is nothing to buy or mount.	Fiducial
53	FID1, FID2, FID3	0		N/A	IV/A	Fiducial mark. There is nothing to buy of mount.	i iuuciai

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ('TI") reference designs are solely intended to assist designers ("Designer(s)") who are developing systems that incorporate TI products. TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design.

Tl's provision of reference designs and any other technical, applications or design advice, quality characterization, reliability data or other information or services does not expand or otherwise alter Tl's applicable published warranties or warranty disclaimers for Tl products, and no additional obligations or liabilities arise from Tl providing such reference designs or other items.

TI reserves the right to make corrections, enhancements, improvements and other changes to its reference designs and other items.

Designer understands and agrees that Designer remains responsible for using its independent analysis, evaluation and judgment in designing Designer's systems and products, and has full and exclusive responsibility to assure the safety of its products and compliance of its products (and of all TI products used in or for such Designer's products) with all applicable regulations, laws and other applicable requirements. Designer represents that, with respect to its applications, it has all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. Designer agrees that prior to using or distributing any systems that include TI products, Designer will thoroughly test such systems and the functionality of such TI products as used in such systems. Designer may not use any TI products in life-critical medical equipment unless authorized officers of the parties have executed a special contract specifically governing such use. Life-critical medical equipment is medical equipment where failure of such equipment would cause serious bodily injury or death (e.g., life support, pacemakers, defibrillators, heart pumps, neurostimulators, and implantables). Such equipment includes, without limitation, all medical devices identified by the U.S. Food and Drug Administration as Class III devices and equivalent classifications outside the U.S.

Designers are authorized to use, copy and modify any individual TI reference design only in connection with the development of end products that include the TI product(s) identified in that reference design. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of the reference design or other items described above may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS AND OTHER ITEMS DESCRIBED ABOVE ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY DESIGNERS AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS AS DESCRIBED IN A TI REFERENCE DESIGN OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

Tl's standard terms of sale for semiconductor products (http://www.ti.com/sc/docs/stdterms.htm) apply to the sale of packaged integrated circuit products. Additional terms may apply to the use or sale of other types of TI products and services.

Designer will fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of Designer's non-compliance with the terms and provisions of this Notice.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2016, Texas Instruments Incorporated