Variant: 001

Generated: 10/28/2016 6:29:22 PM

TID #: TIDA-00913

TIDA-00913 REV E1 Bill of Materials



Item #	Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
1	C1	1	220uF	EKYB101ELL221MK25S	Chemi-Con	CAP, AL, 220 µF, 100 V, +/- 20%, 0.039 ohm, TH	D12.5xL25mm
2	C2, C5, C6, C7,	12	3.3uF	C3216X7S2A335M160AB	TDK	CAP, CERM, 3.3 µF, 100 V, +/- 20%, X7S, 1206_190	1206_190
	C10, C11, C12,						
	C21, C22, C23,						
	C42, C45						
3	C3, C8, C19	3	2.2uF	C1005X5R1A225K050BC	TDK	CAP, CERM, 2.2 μF, 10 V, +/- 10%, X5R, 0402	0402
	C4, C9, C20	3	0.1uF	C3216C0G2A104J160AC	TDK	CAP, CERM, 0.1 µF, 100 V, +/- 5%, C0G/NP0, 1206_190	1206_190
	C13, C14, C24,	7	0.1uF	GCM155R71C104KA55D	MuRata	CAP, CERM, 0.1 μF, 16 V, +/- 10%, X7R, 0402	0402
	C47, C50, C54,						
	C59						
	C15, C16, C17,	6	47pF	GRM1555C1E470JA01D	MuRata	CAP, CERM, 47 pF, 25 V, +/- 5%, C0G/NP0, 0402	0402
	C18, C25, C26						
7	C27, C32	2	0.1uF	GRM155R71A104KA01D	MuRata	CAP, CERM, 0.1 μF, 10 V, +/- 10%, X7R, 0402	0402
	C28, C29, C30,	8	2200pF	885012206036	Wurth Elektronik	CAP, CERM, 2200 pF, 16 V, +/- 10%, X7R, 0603	0603
	C31, C33, C34,						
	C35, C36						
9	C37	1	0.01uF	GRM155R61C103KA01D	MuRata	CAP, CERM, 0.01 µF, 16 V, +/- 10%, X5R, 0402	0402
	C38	1	3300pF	GRM188R72A332KA01D	MuRata	CAP, CERM, 3300 pF, 100 V, +/- 10%, X7R, 0603	0603
11	C39	1	0.01uF	GRM216R71H103KA01D	MuRata	CAP, CERM, 0.01 μF, 50 V, +/- 10%, X7R, 0805	0805
	C40	1	100uF	C3216X5R1A107M160AC	TDK	CAP, CERM, 100 μF, 10 V, +/- 20%, X5R, 1206_190	1206_190
13	C41	1	0.1uF	C1005X7R1E104M050BB	TDK	CAP, CERM, 0.1 µF, 25 V, +/- 20%, X7R, 0402	0402
14	C43, C44	2	0.1uF	GRM188R72A104KA35D	MuRata	CAP, CERM, 0.1 μF, 100 V, +/- 10%, X7R, 0603	0603
15	C46	1	1uF	GRM188R71A105KA61D	MuRata	CAP, CERM, 1 µF, 10 V, +/- 10%, X7R, 0603	0603
16	C48	1	1uF	GCM155C71A105KE38D	MuRata	CAP, CERM, 1 µF, 10 V, +/- 10%, X7S, AEC-Q200 Grade 1, 0402	0402
17	C49	1	100uF	GRM31CR60J107ME39L	MuRata	CAP, CERM, 100 µF, 6.3 V, +/- 20%, X5R, 1206	1206
18	C51, C55, C57,	4	0.033uF	GRM155R71A333KA01D	MuRata	CAP, CERM, 0.033 μF, 10 V, +/- 10%, X7R, 0402	0402
	C60	_					
19	C53, C58, C61,	5	0.1uF	GRM188R71C104KA01D	MuRata	CAP, CERM, 0.1 μF, 16 V, +/- 10%, X7R, 0603	0603
	C62, C64		701/	100700070 115	NN/D 0 : 1 :	D: 1- 0-1-44 - 70 V 0 07 A 00D 500	000 500
	D1, D2, D3, D4	4	70V	1PS79SB70,115	NXP Semiconductor	Diode, Schottky, 70 V, 0.07 A, SOD-523	SOD-523
	D5, D6	2	Green	150060GS75000	Wurth Elektronik	LED, Green, SMD	LED_0603
	H1 J1, J2	1		691352510002	Wurth Elektronik	TERM BLOCK PLUG 2POS 5.08MM	10v0 December
23 24	J3	2		SSW-110-23-F-D OSTTC032162	Samtec	Connector, Receptacle, 100mil, 10x2, Gold plated, TH Terminal Block, 3x1, 5.08 mm, Tin, TH	10x2 Receptacle Terminal Block, 3x1,
24	13	'		05110032162	On-Shore Technology	Terminal block, 3x1, 5.08 mm, 1m, 1m	5.08 mm, TH
25	J4	1		OSTTC022162	On-Shore Technology	Terminal Block, 2-pole, 200mil, TH	THD, 2-Leads, Body
20				0011002102	Chiefe realmology	7	10.16x7.6mm. Pitch
							5.08mm
26	J5, J6	2		PEC02SAAN	Sullins Connector Solutions	Header, 100mil, 2x1, Tin, TH	Header, 2 PIN,
_0	, 00	_				,,,,	100mil, Tin
27	L1	1	470uH	7447709471	Wurth Elektronik	Inductor, Shielded Drum Core, Ferrite, 470 µH, 1.4 A, 0.56 ohm, SMD	SMD
	L2	1	33uH	NLFV25T-330K-PF	TDK	Inductor, Shielded, Ferrite, 33 µH, 0.085 A, 1.4 ohm, SMD	2.5x1.8x2mm
29	L3	1	300 ohm	74279272	Wurth Elektronik	Ferrite Bead, 300 ohm @ 100 MHz, 0.2 A, 0402	0402
30	LBL1	1		THT-14-423-10	Brady	Thermal Transfer Printable Labels, 0.650" W x 0.200" H - 10,000 per roll	PCB Label 0.650"H x
					,		0.200"W
31	R1, R2, R54	3	0	MCR03EZPJ000	Rohm	RES, 0, 5%, 0.1 W, 0603	0603
	R3, R4, R9, R22,	17	0	CRCW04020000Z0ED	Vishay-Dale	RES, 0, 5%, 0.063 W, 0402	0402
	R46, R47, R49,						
	R57, R58, R60,						
	R63, R64, R68,						
	R71, R72, R75,						
	R76						

Item #	Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
33	R5, R6, R7, R8, R10, R11	6	20.0	CRCW040220R0FKED	Vishay-Dale	RES, 20.0, 1%, 0.063 W, 0402	0402
34	R12, R13, R14, R15, R16, R17, R18, R19, R20	9	20	CRCW040220R0JNED	Vishay-Dale	RES, 20, 5%, 0.063 W, 0402	0402
35	R21, R24, R25, R26, R27, R28, R29, R30, R31, R32, R33, R34, R35, R36, R37, R38	16	10k	CRCW040210K0JNED	Vishay-Dale	RES, 10 k, 5%, 0.063 W, 0402	0402
36	R39	1	1.2k	CRCW04021K20JNED	Vishay-Dale	RES, 1.2 k, 5%, 0.063 W, 0402	0402
37	R40	1	470k	CRCW0402470KJNED	Vishay-Dale	RES, 470 k, 5%, 0.063 W, 0402	0402
38	R41, R48	2	10.0k	CRCW040210K0FKED	Vishay-Dale	RES, 10.0 k, 1%, 0.063 W, 0402	0402
39	R42	1	510k	RC0603FR-07510KL	Yageo America	RES, 510 k, 1%, 0.1 W, 0603	0603
40	R43	1	100k	CRCW0603100KJNEA	Vishay-Dale	RES, 100 k, 5%, 0.1 W, 0603	0603
41	R44	1	3.24k	CRCW04023K24FKED	Vishay-Dale	RES, 3.24 k, 1%, 0.063 W, 0402	0402
42	R45	1	20k	CRCW040220K0JNED	Vishay-Dale	RES, 20 k, 5%, 0.063 W, 0402	0402
43	R50	1	820	CRCW0402820RJNED	Vishay-Dale	RES, 820, 5%, 0.063 W, 0402	0402
44	R55, R61, R69	3	0.005	CRE2512-FZ-R005E-3	Bourns	RES, 0.005, 1%, 3 W, AEC-Q200 Grade 0, 2512	2512
45	R56, R62, R66, R70	4	100k	CRCW0402100KFKED	Vishay-Dale	RES, 100 k, 1%, 0.063 W, 0402	0402
46	R59, R65, R67, R74	4	4.22k	CRCW04024K22FKED	Vishay-Dale	RES, 4.22 k, 1%, 0.063 W, 0402	0402
47	TP1, TP2	2		5001	Keystone	Test Point, Miniature, Black, TH	Black Miniature Testpoint
48	U1, U2, U3	3		LMG5200MOFT	Texas Instruments	100V GaN Half Bridge Power Module, MOF0009A	MOF0009A
49	U4	1		SN74AVC8T245RHLR	Texas Instruments	8-BIT DUAL-SUPPLY BUS TRANSCEIVER WITH CONFIGURABLE VOLTAGE TRANSLATION AND 3-STATE OUTPUTS, RHL0024A	RHL0024A
50	U5	1		LM5018MRX/NOPB	Texas Instruments	100V, 300mA Constant On-Time Synchronous Buck Regulator, DDA0008B	DDA0008B
51	U6	1		TMP302BQDRLRQ1	Texas Instruments	Automotive Grade, Low-Power, Easy-to-Use, Temperature Switch in MicroPackage, DRL0006A	DRL0006A
52	U7	1		LP38691SD-3.3/NOPB	Texas Instruments	500mA Low Dropout CMOS Linear Regulators Stable with Ceramic Outpu Capacitors, 6-pin LLP, Pb-Free	
53	U8, U9, U11	3		INA240A1PW	Texas Instruments	Wide Common-Mode Range, Voltage Output, High or Low-Side Bi- Directional Zero-Drift Current Shunt Monitor, PW0008A	PW0008A
54	U10	1		REF3333AIDBZR	Texas Instruments	30 ppm / degC Drift, 3.9 uA Voltage Reference, -40 to 125 degC, 3-pin SOT-23 (DBZ), Green (RoHS & no Sb/Br)	DBZ0003A
55	C52, C56, C63	0	1500pF	C0402H152J3GAC7867	Kemet	CAP, CERM, 1500 pF, 25 V, +/- 5%, C0G/NP0, 0402	0402
56	FID1, FID2, FID3	0		N/A	N/A	Fiducial mark. There is nothing to buy or mount.	Fiducial
57	R23, R51, R52, R73	0	0	CRCW04020000Z0ED	Vishay-Dale	RES, 0, 5%, 0.063 W, 0402	0402
58	R53	0	0	MCR03EZPJ000	Rohm	RES, 0, 5%, 0.1 W, 0603	0603

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ('TI") reference designs are solely intended to assist designers ("Designer(s)") who are developing systems that incorporate TI products. TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design.

Tl's provision of reference designs and any other technical, applications or design advice, quality characterization, reliability data or other information or services does not expand or otherwise alter Tl's applicable published warranties or warranty disclaimers for Tl products, and no additional obligations or liabilities arise from Tl providing such reference designs or other items.

TI reserves the right to make corrections, enhancements, improvements and other changes to its reference designs and other items.

Designer understands and agrees that Designer remains responsible for using its independent analysis, evaluation and judgment in designing Designer's systems and products, and has full and exclusive responsibility to assure the safety of its products and compliance of its products (and of all TI products used in or for such Designer's products) with all applicable regulations, laws and other applicable requirements. Designer represents that, with respect to its applications, it has all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. Designer agrees that prior to using or distributing any systems that include TI products, Designer will thoroughly test such systems and the functionality of such TI products as used in such systems. Designer may not use any TI products in life-critical medical equipment unless authorized officers of the parties have executed a special contract specifically governing such use. Life-critical medical equipment is medical equipment where failure of such equipment would cause serious bodily injury or death (e.g., life support, pacemakers, defibrillators, heart pumps, neurostimulators, and implantables). Such equipment includes, without limitation, all medical devices identified by the U.S. Food and Drug Administration as Class III devices and equivalent classifications outside the U.S.

Designers are authorized to use, copy and modify any individual TI reference design only in connection with the development of end products that include the TI product(s) identified in that reference design. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of the reference design or other items described above may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS AND OTHER ITEMS DESCRIBED ABOVE ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY DESIGNERS AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS AS DESCRIBED IN A TI REFERENCE DESIGN OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

Tl's standard terms of sale for semiconductor products (http://www.ti.com/sc/docs/stdterms.htm) apply to the sale of packaged integrated circuit products. Additional terms may apply to the use or sale of other types of TI products and services.

Designer will fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of Designer's non-compliance with the terms and provisions of this Notice.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2016, Texas Instruments Incorporated