Fitted	Description	Decisester	DestNumber	Occapitor	Manufaaturee	Dealars Deference	Mahua
Fitted	Description	Designator	Partivumber	Quantity	Manufacturer	Packagekererence	Value
Fitted	Printed Circuit Board	IPCB	TIDA_010254_mo dule	1	Any		
		C1, C13, C15, C23,					
	CAP, CERM, 10 uF,	C36, C37, C38, C39, C40, C44,	GRM188Z71A106				
Fitted	10 V, +/- 20%, X7R 0603	C56, C62, C72,	MA73D	17	MuRata	0603	10uF
		C119, C120, C128, C129					
	CAP, CERM, 10 pF,		GRM1555C1H1001				
Fitted	50 V, +/- 5%, COC/NR0_0402	C2, C100	A01D	2	MuRata	0402	10pF
	CAP, CERM, 1 uF,		0.00 100000 101105				
Fitted	6.3 V, +/- 20%,	C3, C78	MEA2D	2	MuRata	0201	1uF
	A3R, 0201	C4, C5, C7, C8,					
	CAP, CERM, 0.22	C10, C11, C12,	GRM155R71C224				
Fitted	uF, 16 V, +/- 10%, X7R 0402	C14, C16, C19, C21, C25, C26	KA12D	16	MuRata	0402	0.22uF
	X/IK, 0402	C28, C29, C101					
F141.4	CAP, CERM, 0.047		C1005X7R1H473K		TOW		0.017.5
Fitted	uF, 50 V, +/- 10%, X7R 0402	C6	05088	1	I DK	0402	0.047uF
	Chip Multilayer						
	Ceramic Canacitors for		CPM155PA1A225				
Fitted	General Purpose.	C9, C17, C20	ME01D	3	Murata	0402	2.2µF
	0402, 2.2uF, X5R,						
	15%, 20%, 10V CAP_CERM_1 uF						
Fitted	6.3 V,+/- 10%,	C18, C22, C35	GRM155R70J105K	3	MuRata	0402	1uF
	X7R, 0402 Chin Multilauar		A120				
	Ceramic						
Fitted	Capacitors for	C24 C27	GRM188C71C475	2	Murata	0603	4 7.uF
	General Purpose, 0402 4 705 YZS		KE21D	-			
	22%, 10%, 16V						
	CAP, CERM, 0.01		GRM155R71E103				
Fitted	uF, 25 V, +/- 10%, y7P, 0402	C30, C45	KA01D	2	MuRata	0402	0.01uF
	CAP, CERM, 0.1	1	GRM0330714104	1			
Fitted	uF, 10 V,+/- 10%,	C31, C34, C53	KE14D	3	MuRata	0201	0.1uF
	A /S, 0201 CAP, CERM. 4.7		0.0.00777				
Fitted	pF, 50 V, +/- 2%,	C32, C33	GJM1555C1H4R7 BB01D	2	MuRata	0402	4.7pF
	C0G/NP0, 0402						
Fitted	uF, 16 V, +/- 10%	C60, C66. C73	GRM188R71C474	3	MuRata	0603	0.47uF
	X7R, 0603		USSIN				
	unip Multilayer Ceramic						
F144 - 4	Capacitors for	014 070	GRM31CR70J226			100/	00 F
ricted	General Purpose,	C01, C/9	ME19K	2	wufata	1200	erth.
	1206, 22uF, X/R, 15% 20% 6 3V						
	CAP, CERM, 470		000415550114711				
Fitted	pF, 50 V, +/- 5%,	C67, C69, C74	A01D	3	MuRata	0402	470pF
	COG/NP0, 0402 CAP, CERM, 47 uF.						
Fitted	6.3 V, +/- 20%,	C68	GRM31CR60J476	1	MuRata	1206	47uF
	X5R, 1206		IVIE 19L				
	Yellow 588nm 2-						
Fitted	Pin Chip	D3	VLMY1500-G508	1	Vishay	0402	
	0402(1006Metric)						
F144 - 4	Header, 1.27mm,		GRPB122VWVN-		Sullins Connector	Header, 1.27mm,	
Fitted	12x2, Gold, TH	11	RC		Solutions	12x2, TH	
	100nH Shielded Multilaver						
Fitted	Inductor 4A	111514	LQM2MPZR10MJ		1. francis	0004 (2014)	0.1
Fitted	19mOhm Max	L 1, L5, L6	HL	3	Murata	0806 (2016)	0. TUH
	0806 (2016 Motein)						
	Ferrite Bead, 120						
Fitted	ohm @ 100 MHz,	L2, L3, L4, L7, L8	D	5	MuRata	0603	120 ohm
	1.9 A, 0603 470pH Shielded						
	Wirewound						
Fitted	Inductor 3A	L14, L15	DFE201210U-	2	Murata	0805 (2012)	0.47uH
	42mOnm Max 0805 (2012		R4/M=P2				
	Metric)						
Fitted	MOSFET, N-CH,	02.02	DEC12204/7.E		Diadas Inc.	COT 222	1000/
Fitted	323	02,05	B33123W-7-F	- í	biodes inc.	301-323	1007
	RES, 80.6 k, 1%,						
Fitted	0.063 W, AEC-	R1	CRCW040280K6F	1	Vishay-Dale	0402	80.6k
	0402		KED				
	RES, 40.2 k, 1%,						
Fitted	0.063 W, AEC- 0.200 Grade 0	R2	CRCW040240K2F	1	Vishay-Dale	0402	40.2k
	0402						
	Res Thick Film						
	0.5% 0.05W						
Fitted	±50ppm/*C	R4, R44, R49, R67, R75, R131 R165	ERJ-1RHD1002C	7	Panasonic	0201	10k
	Involded SMD						
	T/R						
Fitted	RES, 33.2, 1%,	R45, R46, R47, R49, R51, R03	CRCW020133R2F	6	Vishay-Dale	0201	33.2
	Res Thick Film	www.mai, K93	mul/			-	
	0402 47.5K Ohm						
Fitted	±100ppm/*C	R50	AL0402FR- 0747K5L	1	Yageo	0402	47.5k
	Molded SMD						
	Paper T/R	072 074 0435	CDCW02C4 400	I			
Fitted	ncs, 100 k, 1%, 0.05 W, 0201	R13, R14, R175, R177, R238, R244	CRUWU201100KF KED	6	Vishay-Dale	0201	100k
Fitted	RES, 1.00 k, 1%,	R86. R89	CRCW02011K00F	2	Vishay-Dale	0201	1.00k
	0.05 W, 0201		KED PC0402EP		,		
Fitted	0.063 W, 0402	R119, R121	0768K1L	2	Yageo America	0402	68.1k
Fitted	RES, 510, 1%, 0.1	R172, R179	ERJ-2RKF5100X	2	Panasonic	0402	510
	W, 0402 RES SMD 0 OUE4			· ·		-	
Fitted	JUMPER 1/20W	R173, R176	RC0201JR-070RL	2	Yageo	0201 (0603 Metric)	
	0201 Reg Thick Cites						
	0402 18K Ohm 1%						
Fitted	1/16W	R178. R180	CRCW040218K0F	,	Vishav	0402	18k
	±100ppm/°C Molded SMD		KEDC	ĺ	,	1	
	Paper T/R						
Fitted	IWRL64320GAMF	U1	IWRL64320GAMF	1	Texas	FOCSP102	
	FLASH - NOR				instruments		
	Memory IC 16Mb						
Fitted	(2M x 8) SPI -	U2	W25Q16IVUXIO	· ·	Winbond	USON8	
		1 · ·		I '			
	Quad I/O 133 MHz 6 re 9-116/041			1			
	Quad I/O 133 MHz 6 ns 8-USON (2x3)						
	Ouad I/O 133 MHz 6 ns 8-USON (2x3) 2.7-V to 6-V, 1-A /						
Fitted	Quad I/O 133 MHz 6 ns 8-USON (2x3) 2.7-V to 6-V, 1-A / 2-A Automotive Step-Down	1119 1120	TPSA2850100 P		Texas	\$07583	
Fitted	Quad I/O 133 MHz 6 ns 8-USON (2x3) 2.7-V to 6-V, 1-A / 2-A Automotive Step-Down Converter in	U19, U20	TPS628502DRLR	2	Texas Instruments	SOT583	
Fitted	Quad I/O 133 MHz 6 ns 8-USON (2x3) 2.7-V to 6-V, 1-A / 2-A Automotive Step-Down Converter in SOT583 Package	U 19, U20	TPS628502DRLR	2	Texas Instruments	SOT583	
Fitted	Quad I/O 133 MHz 6 ns 8-USON (2x3) 2.7-V to 6-V, 1-A / 2-A Automotive Step-Down Converter in SOT583 Package 40MHz±10ppm Constal #E 50	U 19, U20	TPS628502DRLR	2	Texas Instruments	SOT583	
Fitted	Quad I/O 133 MHz 6 ns 8-USON (2x3) 2.7-V to 6-V, 1-A / 2-A Automotive Step-Down Converter in SOT583 Package 40MHz ±10ppm Crystal 8pF 50 Ohms 4-SMD, No	U 19, U20 Y1	TPS628502DRLR FW4000044Q	2	Texas Instruments Diodes	SOT583 4-SMD- 2.0x1.6mm	
Fitted	Quad I/O 133 MHz 6 ns 8-USON (2x3) 2.7-V to 6-V, 1-A / 2-A Automotive Step-Down Converter in SOT583 Package 40MHz ±10ppm Crystal 8pF 50 Ohms 4-SMD, No Lead	U 19, U20 Y1	TPS628502DRLR FW4000044Q	2	Texas Instruments Diodes	SOT583 4-SMD- 2.0x1.6mm	
Fitted Fitted	Quad I/O 133 MHz 6 ns 8-USON (2x3) 2.7-V to 6-V, 1-A/ 2-A Automotive Step-Down Converter in SOT583 Package 40MHz ±10ppm Crystal 8pF 50 Ohms 4-SMD, No Lead Fiducial mark. There is nothing	U 19, U20 Y1 FID1, FID2, FID3,	TPS628502DRLR FW4000044Q	1	Texas Instruments Diodes N/A	SOT583 4-SMD- 2.0x1.6mm N/A	

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2023, Texas Instruments Incorporated