## PMP11155 REV C Bill of Materials



Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
PCB1	1		PMP11155PCB Rev. B	Any	Printed Circuit Board	
C1	1	0.33uF	B32672Z5334K	EPCOS Inc	CAP, Film, 0.33uF, 520V, +/-10%, TH	18x14.5x8.5mm
C2	1	470pF	C1608C0G2E471J	TDK	CAP, CERM, 470 pF, 250 V, +/- 5%, C0G/NP0, 0603	0603
C3	1	0.47uF	890334025039CS	Wurth Elektronik	CAP, Film, 0.47 µF, 310 V, +/- 10%, TH	18x8mm
C4	1	100uF	ECA-2AM101	Panasonic	CAP, AL, 100 μF, 100 V, +/- 20%, TH	D10xL16mm
C5	1	680uF	EKZE350ELL681MK20S	Chemi-Con	CAP, AL, 680 µF, 35 V, +/- 20%, 0.021 ohm, TH	D12.5xL20mm
C6, C7, C8, C9	4	10uF	GRM32ER71H106KA12L	MuRata	CAP, CERM, 10 µF, 50 V, +/- 10%, X7R, 1210	1210
C10	1	0.01uF	GRM155R71E103KA01D	MuRata	CAP, CERM, 0.01uF, 25V, +/-10%, X7R, 0402	0402
C11	1	22uF	ECA-1VM220	Panasonic	CAP, AL, 22 μF, 35 V, +/- 20%, TH	5.0mmx11mm
C12	1	0.01uF	GRM155R71E103KA01D	MuRata	CAP, CERM, 0.01 µF, 25 V, +/- 10%, X7R, 0402	0402
C13	1	2200pF	DE2E3KY222MA2BM01	MuRata	CAP, CERM, 2200pF, 250V, +/-20%, KY, Radial D8x5mm	Radial D8x5mm
C14	1	1000pF	C1005X7R1H102K	TDK	CAP, CERM, 1000pF, 50V, +/-10%, X7R, 0402	0402
C15, C18	2	10pF	GRM1555C1H100JA01D	MuRata	CAP, CERM, 10pF, 50V, +/-5%, C0G/NP0, 0402	0402
C16	1	100pF	GRM1555C1H101JA01D	MuRata	CAP, CERM, 100pF, 50V, +/-5%, C0G/NP0, 0402	0402
C17	1	0.1uF	C1005X7R1H104K050BB	TDK	CAP, CERM, 0.1uF, 50V, +/-10%, X7R, 0402	0402
C19	1	2.2uF	GRM188R6YA225KA12D	MuRata	CAP, CERM, 2.2 µF, 35 V, +/- 10%, X5R, 0603	0603
C20	1	4.7uF	GRM188R61E475KE11D	MuRata	CAP, CERM, 4.7 µF, 25 V, +/- 10%, X5R, 0603	0603
D1	1	1V	HD04-T	Diodes Inc.	Diode, Switching-Bridge, 400V, 0.8A, MiniDIP	MiniDIP
D2	1	100V	SMCJ100A	Littelfuse	Diode, TVS, Uni, 100 V, 1500 W, SMC	SMC
D3, D6	2	1.05V	MURA160T3G	ON Semiconductor	Diode, Ultrafast, 600V, 1A, SMA	SMA
D4	1	200V	SBR10200CTL-13	Diodes Inc.	Diode, Super Barrier Rectifier, 200 V, 5 A, DPAK	DPAK
D5, D11	2	100V	BAS316,115	NXP Semiconductor	Diode, Ultrafast, 100V, 0.25A, SOD-323	SOD-323
D7. D8	2	600V	CGRM4005-G	Comchip Technology	Diode, P-N. 600V. 1A. 3.9x1.7x1.8mm	3.9x1.7x1.8mm
D9	1	15V	MMSZ5245B-7-F	Diodes Inc.	Diode, Zener, 15 V. 500 mW, SOD-123	SOD-123
D10	1	12V	MMSZ5242B-7-F	Diodes Inc.	Diode, Zener, 12 V. 500 mW, SOD-123	SOD-123
D12	1	24V	MMSZ5252B-7-F	Diodes Inc.	Diode, Zener, 24 V, 500 mW, SOD-123	SOD-123
F1	1		0443003.DR	Littelfuse	Fuse, 3 A, 250 V, SMD	FUSE
	-					10.1x3.12x3.13mm
J1	1		770W-X2/10	Qualtek Electronics Corporation	AC Receptacle, 2,5A, R/A, TH	AC. Reception
					······································	14.5x15x22 mm
11.14	2	470uH	74477124	Wurth Elektronik	Inductor, Shielded Drum Core, Metal Composite, 470 uH, 0.64 A, 0.66	WF-PD-I
,	_				ohm. SMD	
12	1	1.3mH	UU9 8V-132LF	GCI Technologies	Coupled inductor 1.3 mH 0.7 A 0.5 ohm TH	Coupled inductor
	-			g		17.5x17x11mm
13	1	4 7uH	SD43-472MLB	Coilcraft	Inductor Ferrite 47 µH 2.9 A 0.094 ohm SMD	4 2x4 7mm
Q1	1	100 V	FZT493TA	Diodes Inc.	Transistor NPN 100 V 1 A AEC-Q101 SQT-223	SOT-223
Q2	1	600V	AOD7S60	AOS	MOSEET N-CH 600V 7A DPAK	DPAK
Q3	1	0.21	MMBT3904-7-F	Diodes Inc	Transistor NPN 40V 0.2A SOT-23	SOT-23
04	1	40 V	MMDT3946-7-F	Diodes Inc	Transistor, NPN/PNP Pair, 40 V, 0.2 A, SOT-363	SOT-363
R1 R5	2	100k	CRCW1206100K.INFA	Vishav-Dale	RES 100 k 5% 0.25 W 1206	1206
R2 R4	2	1.0	CRCW12061B00 INFA	Vishay-Dale	RES 1 0 5% 0 25 W 1206	1206
R3	1	1.00k	CRCW12061K00EKEA	Vishay-Dale	RES 1.00 k 1% 0.25 W 1206	1206
R6	1	51	CRCW120651R0 INFA	Vishay-Dale	RES 51 5% 0.25 W 1206	1206
R7 R12	2	10.0k		Vishay-Dale	RES 10.0 k 1% 0.1 W 0603	0603
R8	1	100k		Vishay-Dale	RES 100 k 1% 0.063 W 0402	0402
Rg	1	33		Vishay-Dale	RES 33 5% 0 125 W 0805	0805
R10	1	6.98k		Vishay-Dale	RES 6.98 k 1% 0.063 W 0402	0402
		0.001			1120, 0.00 K, 170, 0.000 W, 0402	0102

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
R11, R14	2	590k	CRCW1206590KFKEA	Vishay-Dale	RES, 590k ohm, 1%, 0.25W, 1206	1206
R13	1	100k	CRCW0402100KFKED	Vishay-Dale	RES, 100k ohm, 1%, 0.063W, 0402	0402
R15	1	0	CRCW04020000Z0ED	Vishay-Dale	RES, 0 ohm, 5%, 0.063W, 0402	0402
R16, R19	2	1.00k	CRCW04021K00FKED	Vishay-Dale	RES, 1.00k ohm, 1%, 0.063W, 0402	0402
R17	1	7.87k	CRCW04027K87FKED	Vishay-Dale	RES, 7.87 k, 1%, 0.063 W, 0402	0402
R18	1	0.82	CSR1206FTR820	Stackpole Electronics Inc	RES, 0.82, 1%, 0.5 W, 1206	1206
R20	1	10.0k	CRCW040210K0FKED	Vishay-Dale	RES, 10.0k ohm, 1%, 0.063W, 0402	0402
R21, R22	2	1.00k	CRCW06031K00FKEA	Vishay-Dale	RES, 1.00 k, 1%, 0.1 W, 0603	0603
R23	1	499k	CRCW0402499KFKED	Vishay-Dale	RES, 499k ohm, 1%, 0.063W, 0402	0402
R24	1	20.0k	CRCW040220K0FKED	Vishay-Dale	RES, 20.0k ohm, 1%, 0.063W, 0402	0402
R25	1	4.99k	CRCW04024K99FKED	Vishay-Dale	RES, 4.99k ohm, 1%, 0.063W, 0402	0402
R26	1	10.0k	CRCW040210K0FKED	Vishay-Dale	RES, 10.0 k, 1%, 0.063 W, 0402	0402
R27	1	57.6k	CRCW040257K6FKED	Vishay-Dale	RES, 57.6 k, 1%, 0.063 W, 0402	0402
R100	1	10.0k	ERJ-3EKF1002V	Panasonic	RES, 10.0 k, 1%, 0.1 W, 0603	0603
T1	1	580 uH	RLTI-1153	Renco Electronics	Transformer, 580 uH, TH	1000x1000mil
TP1	1	Red	5010	Keystone	Test Point, Multipurpose, Red, TH	Red Multipurpose
						Testpoint
TP2	1	Black	5011	Keystone	Test Point, Multipurpose, Black, TH	Black Multipurpose
						Testpoint
U1	1		UCC28050D	Texas Instruments	Transition Mode PFC Controller	D0008A
U2	1		VOS617A-7X001T	Vishay-Semiconductor	OptoCoupler, Phototransitor, 80-160%, SSOP-4	7x2.12x2.6mm
U3	1		TL431AIDBZ	Texas Instruments	PRECISION PROGRAMMABLE REFERENCE, DBZ0003A	DBZ0003A

## IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ('TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your noncompliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products <a href="http://www.ti.com/sc/docs/stdterms.htm">http://www.ti.com/sc/docs/stdterms.htm</a>), evaluation modules, and samples (<a href="http://www.ti.com/sc/docs/stdterms.htm">http://www.ti.com/sc/docs/stdterms.htm</a>), evaluation

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2017, Texas Instruments Incorporated