Texas Instruments

## **Bill of Materials**

TI DESIGNS

TIDA-00539

ltem	Qty	Reference	Value	Part Description	Manufacturer	Manufacturer Part Number
1	2	C1, C17	2200pF	CAP, CERM, 2200pF, 2000V, +/- 10%, X7R, 1812	TDK	C4532X7R3D222K
2	4	C2, C6, C34, C36	0.1uF	CAP, CERM, 0.1uF, 100V, +/-10%, X7R, 0805	Kemet	C0805C104K1RACTU
3	1	C3		CAP, CERM, 2.2uF, 100V, +/-10%, X7R, 1210	Taiyo Yuden	HMK325B7225KN-T
4	2	C4, C5	2.2uF	CAP, CERM, 2.2uF, 100V, +/-10%, X7R, 1210	Taiyo Yuden	HMK325B7225KN-T
5	1	C7	68uF	CAP, AL, 68uF, 25V, +/-20%, 0.36 ohm, SMD	Panasonic	EEE-FK1E680P
6	3	C8, C9, C10	10uF	CAP, CERM, 10uF, 25V, +/-20%, X5R, 1210	TDK	C3225X5R1E106K
7	3	C11, C22, C23	1uF	CAP, CERM, 1uF, 25V, +/-10%, X5R, 0805	AVX	08053D105KAT2A
8	1	C12	470pF	CAP, CERM, 470pF, 100V, +/-5%, X7R, 0603	AVX	06031C471JAT2A
9	1	C13	100pF	CAP, CERM, 100pF, 50V, +/-5%, C0G/NP0, 0603	TDK	C1608C0G1H101J
10	1	C14	22uF	CAP, AL, 22uF, 25V, +/-20%, 0.7 ohm, SMD	Panasonic	EEE-FK1E220R

Item	Qty	Reference	Value	Part Description	Manufacturer	Manufacturer Part Number
11	2	C15, C16	0.47uF	CAP, CERM, 0.47uF, 16V, +/-10%, X7R, 0603	Kemet	C0603C474K4RACTU
12	1	C18	0.01uF	CAP, CERM, 0.01uF, 50V, +/-5%, X7R, 0603	Kemet	C0603C103J5RACTU
13	1	C19	47pF	CAP, CERM, 47pF, 50V, +/-5%, C0G/NP0, 0603	AVX	06035A470JAT2A
14	1	C20	1uF	CAP, CERM, 1uF, 16V, +/-10%, X5R, 0603	Kemet	C0603C105K4PACTU
15	1	C21	0.047uF	CAP, CERM, 0.047 µF, 50 V, +/- 10%, X7R, 0603	MuRata	GRM188R71H473KA61D
16	1	C24	0.039uF	CAP, CERM, 0.039 µF, 25 V, +/- 10%, X7R, 0603	AVX	06033C393KAT2A
17	2	C25, C32	1000pF	CAP, CERM, 1000pF, 2000V, +/- 10%, X7R, 1210	Kemet	C1210C102KGRACTU
18	6	C26, C27, C28, C29, C37, C38	0.01uF	CAP, CERM, 0.01uF, 100V, +/- 10%, X7R, 0603	AVX	06031C103KAT2A
19	2	C30, C31	1000pF	CAP, CERM, 1000pF, 100V, +/- 10%, X7R, 0603	AVX	06031C102KAT2A
20	2	C33, C35	47uF	CAP, AL, 47uF, 63V, +/-20%, 0.65 ohm, SMD	Panasonic	EEE-FK1J470P
20	1	C39	2.2uF	CAP, CERM, 2.2 μF, 50 V, +/- 10%, X5R, 0805	ТDК	C2012X5R1H225K125AB
22	2	C40, C41	0.1uF	CAP, CERM, 0.1 μF, 50 V, +/- 10%, X7R, 0603	AVX	06035C104KAT2A
23	1	D1	200V	Diode, Ultrafast, 200V, 1A, SMA	ON Semiconductor	MURA120T3G
23	2	D2, D5	100V	Diode, Switching, 100V, 0.2A, SOD 123	ON Semiconductor	MMSD4148T1G

Item	Qty	Reference	Value	Part Description	Manufacturer	Manufacturer Part Number
25	1	D3	Yellow	LED, Yellow, SMD	OSRAM	LY E6SF-AABA-46-1-Z
26	3	D4, D6, D7	30V	Diode, Schottky, 30V, 0.2A, SOT- 23	Diodes Inc.	BAT54S-7-F
27	8	D8, D9, D10, D11, D12, D13, D14, D15	100V	Diode, Schottky, 100V, 3A, SMC	Diodes Inc.	B3100-13-F
28	1	D16		LED, Orange, SMD	OSRAM	LO E6SF-ABCB-24-1-Z
29	2	D17, D19	58V	Diode, TVS, Uni, 58V, 400W, SMA	Diodes Inc.	SMAJ58A
30	1	D18	Orange	LED, Orange, SMD	OSRAM	LO E6SF-ABCB-24-1-Z
31	1	D20		Diode, Schottky, 100V, 0.15A, SOD-123	Diodes Inc.	BAT46W-7-F
32	2	D21, D22	100V	Diode, Schottky, 100V, 0.15A, SOD-123	Diodes Inc.	BAT46W-7-F
33	4	H1, H2, H3, H4		Bumpon, Hemisphere, 0.375 X 0.235, Black	3M	SJ61A2
34	1	J1		Terminal Block, 6A, 3.5mm Pitch, 2 Pos, TH	On-Shore Technology	ED555/2DS
35	4	J2, J5, J7, J11		Header, 100mil, 2x1, Gold plated, TH	TE Connectivity	5-146261-1
36	2	J3, J4		RJ-45, Right Angle, No LED, tab up	AMP	1-406541-1
37	1	J6		Header, TH, 100mil, 4x1, Gold plated, 230 mil above insulator	Samtec	TSW-104-07-G-S
38	1	L1	3.3uH	Inductor, Shielded Drum Core, Ferrite, 3.3uH, 1.9A, 0.08 ohm,	Coilcraft	LPS4018-332MLB

ltem	Qty	Reference	Value	Part Description	Manufacturer	Manufacturer Part Number
39	1	L2	400nH	Inductor, Shielded, Composite, 400nH, 12.5A, 0.01 ohm, SMD	Coilcraft	XAL4020-401MEB
40	4	L3, L4, L5, L6	100 ohm	4A Ferrite Bead, 100 ohm @ 100MHz, SMD	MuRata	MPZ2012S101A
41	1	Q1	150V	MOSFET, N-CH, 150V, 4.6A, PQFN08A	Fairchild Semiconductor	FDMS86252
42	2	Q2, Q4	0.25V	Transistor, PNP, 40V, 0.2A, SOT- 23	Fairchild Semiconductor	MMBT3906
43	3	Q3, Q8, Q9	100V	MOSFET, N-CH, 100V, 26A, PowerPAK SO-8	Fairchild Semiconductor	FDMS86105
44	1	Q5	0.25V	Transistor, NPN, 140V, 0.6A, SOT- 23	ON Semiconductor	MMBT5550LT1G
45	2	Q6, Q7	100V	MOSFET, N-CH, 100V, 0.17A, SOT-23	Fairchild Semiconductor	BSS123
46	1	Q10	40V	MOSFET, N-CH, 40 V, 15 A, SON 5x6mm	Texas Instruments	CSD18504Q5A
47	1	R1	39k	RES, 39k ohm, 5%, 0.25W, 1206	Vishay-Dale	CRCW120639K0JNEA
48	1	R2	4.7	RES, 4.7 ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW06034R70JNEA
49	3	R3, R47, R54	10.0k	RES, 10.0 k, 1%, 0.1 W, 0603	Vishay-Dale	CRCW060310K0FKEA
50	1	R4	0.1	RES, 0.1, 1%, 2 W, 2512	Stackpole Electronics Inc	CSRN2512FKR100
50	1	R5	1.00k	RES, 1.00k ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW06031K00FKEA
52	1	R6	10	RES, 10 ohm, 5%, 1W, 2512	Panasonic	ERJ-1TYJ100U

Item	Qty	Reference	Value	Part Description	Manufacturer	Manufacturer Part Number
	1	R7	20.0	RES, 20.0 ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW060320R0FKEA
53						
	1	R8	20.0	RES, 20.0 ohm, 1%, 0.125W, 0805	Vishay-Dale	CRCW080520R0FKEA
54	2	R9, R12	121k	RES, 121k ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW0603121KFKEA
55	2	10, 112			vishay-Daic	
55	1	R10	2.61k	RES, 2.61k ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW06032K61FKEA
56						
	5	R11, R18, R19, R38, R39	10.0k	RES, 10.0k ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW060310K0FKEA
57						
- 0	1	R13	4.22k	RES, 4.22k ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW06034K22FKEA
58	1	R14	0	RES, 0 ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW06030000Z0EA
59			0		Vishay Daio	
	1	R15	7.50k	RES, 7.50k ohm, 1%, 0.1W, 0603	Panasonic	ERJ-3EKF7501V
60						
	1	R16	80.6k	RES, 80.6k ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW060380K6FKEA
61		<b>-</b>				
63	1	R17	3.83k	RES, 3.83k ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW06033K83FKEA
62	1	R20	61.9k	RES, 61.9k ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW060361K9FKEA
63			01.01		Violity Dalo	
05	5	R21, R40, R41, R48, R56	100k	RES, 100k ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW0603100KFKEA
64						
	1	R22	1.21Meg	RES, 1.21 M, 1%, 0.1 W, 0603	Vishay-Dale	CRCW06031M21FKEA
65						
66	1	R23	49.9k	RES, 49.9k ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW060349K9FKEA
66						

ltem	Qty	Reference	Value	Part Description	Manufacturer	Manufacturer Part Number
	1	R24	200k	RES, 200 k, 1%, 0.1 W, 0603	Vishay-Dale	CRCW0603200KFKEA
67	1	R25	6.81k	RES, 6.81 k, 1%, 0.1 W, 0603	Vishay-Dale	CRCW06036K81FKEA
69	1	R26	7.5k	RES, 7.5k ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW06037K50JNEA
70	1	R27	2.00k	RES, 2.00 k, 1%, 0.1 W, 0603	Vishay-Dale	CRCW06032K00FKEA
71	8	R28, R29, R30, R31, R32, R33, R34, R35	75.0	RES, 75.0 ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW060375R0FKEA
72	2	R36, R37	5.6k	RES, 5.6k ohm, 5%, 1W, 2512	Panasonic	ERJ-1TYJ562U
73	1	R42	30.1k	RES, 30.1k ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW060330K1FKEA
74	2	R44, R52	63.4	RES, 63.4 ohm, 1%, 0.125W, 0805	Vishay-Dale	CRCW080563R4FKEA
75	1	R45	8.87k	RES, 8.87k ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW06038K87FKEA
76	2	R46, R53	49.9k	RES, 49.9 k, 1%, 0.1 W, 0603	Vishay-Dale	CRCW060349K9FKEA
77	2	R49, R55	24.9k	RES, 24.9k ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW060324K9FKEA
78	1	R51	78.7k	RES, 78.7k ohm, 1%, 0.125W, 0805	Panasonic	ERJ-6ENF7872V
79	1	R57	12.1k	RES, 12.1 k, 1%, 0.1 W, 0603	Vishay-Dale	CRCW060312K1FKEA
80	1	R58	33.2k	RES, 33.2 k, 1%, 0.1 W, 0603	Vishay-Dale	CRCW060333K2FKEA

ltem	Qty	Reference	Value	Part Description	Manufacturer	Manufacturer Part Number
	1	R60	47.5k	RES, 47.5 k, 1%, 0.1 W, 0603	Vishay-Dale	CRCW060347K5FKEA
81						
	1	R61	1.43k	RES, 1.43 k, 1%, 0.1 W, 0603	Vishay-Dale	CRCW06031K43FKEA
82						
83	2	R62, R63	25.5k	RES, 25.5 k, 1%, 0.1 W, 0603	Vishay-Dale	CRCW060325K5FKEA
84	4	SH-J1, SH-J2, SH-J3, SH- J4	1x2	Shunt, 100mil, Gold plated, Black	3M	969102-0000-DA
85	1	T1	62uH	Transformer, 62uH, SMT	Pulse Engineering	PA4036NL
05	1	T2	1.2mH	Transformer, Gate Drive, 1.2mH,	Pulse Engineering	PA0184NLT
86				SMT		
87	1	Т3	350uH	TRANSFORMER/CMC MOD, GIGABIT POE+, SMT	Pulse Engineering	H6096NL
88	14	TP1, TP3, TP5, TP6, TP8, TP9, TP10, TP11, TP12,	SMT	Test Point, Miniature, SMT	Keystone	5015
89	6	TP12 TP14 TP15 TP17 TP2, TP4, TP7, TP16, TP18, TP19		Test Point, Miniature, SMT	Keystone	5019
90	2	U1, U7		Optocoupler, 3.75kV RMS, SMT	Fairchild Semiconductor	HMHA2801A
91	1	U2		PRECISION PROGRAMMABLE REFERENCE, DBV0005A	Texas Instruments	TL431AIDBV
92	2	U3, U4		IEEE 802.3at PoE High-Power PD Interface, DDA0008E	Texas Instruments	TPS2378DDA
93	2	U5, U8		Optocoupler, 5kV RMS, SMT	Fairchild Semiconductor	FOD817DS
95	1	U6		Advanced Active Clamp PWM Controller with Current Control, -40	Texas Instruments	UCC2897APW

Item	Qty	Reference	Value	Part Description	Manufacturer	Manufacturer
item	QLY	Reference	Value	Part Description	Walturacturer	Part Number TL7700CDGKR N/A 76308-204LF PPTC021LFBN-RC CRCW06030000Z0EA
	1	U9		SUPPLY-VOLTAGE	Texas Instruments	TL7700CDGKR
95				SUPERVISOR, DGK0008A		
	0	FID1, FID2, FID3		Fiducial mark. There is nothing to	N/A	N/A
96				buy or mount.		
	0	J8		Receptacle, 100mil, 4x1, TH	FCI	76308-204LF
97						
	0	J9, J10		Receptacle 100mil 2x1, Tin, TH	Sullins Connector Solution	PPTC021LFBN-RC
98						
	0	R43	0	RES, 0 ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW06030000Z0EA
99						
	0	R50	20.0k	RES, 20.0k ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW060320K0FKEA
100						
	0	R59	100	RES, 100, 1%, 0.1 W, 0603	Vishay-Dale	CRCW0603100RFKEA
101						

## **IMPORTANT NOTICE FOR TI REFERENCE DESIGNS**

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. **TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design.** TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have **not** been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2015, Texas Instruments Incorporated