

PMP11494 REV A Bill of Materials

Designator	Quantity	Value	PartNumber	Manufacturer	Description	Package
C1, C2, C3, C4,	8	2.2uF	GRM32ER72A225KA35L	MuRata	CAP, CERM, 2.2 µF, 100 V, +/- 10%, X7R, 1210	1210
C5, C6, C7, C8						
C9	1	220uF	EEV-FK1J221Q	Panasonic	CAP, AL, 220 µF, 63 V, 0.8Arms, 0.16 ohm, SMD	SMT Radial H13
C10, C18	2	0.1uF	C1608X7R1H104K	TDK	CAP, CERM, 0.1uF, 50V, +/-10%, X7R, 0603	0603
C11, C16	2	1000pF	C1608X7R1H102K	TDK	CAP, CERM, 1000 pF, 50 V, +/- 10%, X7R, 0603	0603
C12	1	120uF	35SVPF120M	Panasonic	CAP, Aluminum Polymer, 120 µF, 35 V, +/- 20%, 0.018 ohm, F12,	F12, SMD, 2-Leads,
					SMD, 2-Leads, Body 10.5x10.5mm, Height 12.7mm SMD	Body 10.5x10.5mm,
						Height 12.7mm
C13	1	10uF	C3225X7R1H106M250AC	TDK	CAP, CERM, 10 μF, 50 V, +/- 20%, X7R, 1210	1210
C14	1	4.7uF	GRM21BR71C475KA73L	MuRata	CAP, CERM, 4.7 µF, 16 V, +/- 10%, X7R, 0805	0805
C15, C21	2	1000pF	C1608C0G1H102J	TDK	CAP, CERM, 1000 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
C17	1	1uF	C1608X5R1C105K	TDK	CAP, CERM, 1 µF, 16 V, +/- 10%, X5R, 0603	0603
C19	1	0.47uF	GRM21BR72A474KA73L	MuRata	CAP, CERM, 0.47 µF, 100 V, +/- 10%, X7R, 0805	0805
C20	1	100pF	C1608C0G1H101J	TDK	CAP, CERM, 100 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
C22	1	4700pF	C1608C0G1E472J	TDK	CAP, CERM, 4700 pF, 25 V, +/- 5%, C0G/NP0, 0603	0603
J1, J4	2		ED555/2DS	On-Shore Tech	Terminal Block, 6A, 3.5mm Pitch, 2-Pos, TH	7.0x8.2x6.5mm
J2, J3	2		PEC02SAAN	Sullins	Header, 100mil, 2x1, Tin, TH	Header, 2 PIN,
,						100mil, Tin
L1	1	3.3uH	DR127-3R3-R	Coiltronics	Inductor, Shielded Drum Core, Ferrite, 3.3 µH, 10.5 A, 0.00567 ohm,	DR127
					SMD	
L2	1	15uH	SER2918H-153KL	Coilcraft	Inductor, Shielded E Core, Ferrite, 15 µH, 21.9 A, 0.0026 ohm, SMD	29.7x17.78x27.94mm
Q1, Q2	2	100V	CSD19534Q5A	Texas Instruments	MOSFET, N-CH, 100 V, 10 A, SON 5x6mm	SON 5x6mm
Q3	1	100V	CSD19532Q5B	Texas Instruments	MOSFET, N-CH, 100 V, 17 A, SON 5x6mm	SON 5x6mm
Q4	1		open	Texas Instruments	MOSFET, open, SON 5x6mm	SON 5x6mm
R1		2.00	CRCW25122R00FKEG	Vishay-Dale	RES, 2.00, 1%, 1 W, 2512	2512
R2	1	100k	CRCW0603100KFKEA	Vishay-Dale	RES, 100 k, 1%, 0.1 W, 0603	0603
R3, R4, R8	3	3.3	CRCW06033R30JNEA	Vishay-Dale	RES, 3.3, 5%, 0.1 W, 0603	0603
R5, R7, R12	3	10.0k	CRCW060310K0FKEA	Vishay-Dale	RES, 10.0 k, 1%, 0.1 W, 0603	0603
R6	1	1.00Meg	CRCW06031M00FKEA	Vishay-Dale	RES, 1.00 M, 1%, 0.1 W, 0603	0603
R9	1	22.6k	CRCW060322K6FKEA	Vishay-Dale	RES, 22.6 k, 1%, 0.1 W, 0603	0603
R10	1	2.70	ERJ-8RQF2R7V	Panasonic	RES, 2.70, 1%, 0.25 W, 1206	1206
R11, R14	2				RES, open, 0603	0603
R13	1	16.9k	CRCW060316K9FKEA	Vishay-Dale	RES, 16.9 k, 1%, 0.1 W, 0603	0603
R15	1	78.7k	CRCW060378K7FKEA	Vishay-Dale	RES, 78.7 k, 1%, 0.1 W, 0603	0603
R16	1	1.37k	CRCW06031K37FKEA	Vishay-Dale	RES, 1.37 k, 1%, 0.1 W, 0603	0603
R17	1	2.00k	CRCW06032K00FKEA	Vishay-Dale	RES, 2.00 k, 1%, 0.1 W, 0603	0603
R18	1	14.7k	CRCW060314K7FKEA	Vishay-Dale	RES, 14.7 k, 1%, 0.1 W, 0603	0603
R19	1	53.6k	CRCW060353K6FKEA	Vishay-Dale	RES, 53.6 k, 1%, 0.1 W, 0603	0603
R20	1	49.9	CRCW060349R9FKEA	Vishay-Dale	RES, 49.9, 1%, 0.1 W, 0603	0603
TP1, TP3, TP4,	6	Red	5000	Keystone	Test Point, Miniature, Red, TH	Red Miniature
TP5, TP6, TP8						Testpoint

Designator	Quantity	Value	PartNumber	Manufacturer	Description	Package
TP2, TP7	2	Black	5001	Keystone	Test Point, Miniature, Black, TH	Black Miniature
						Testpoint
U1	1		TPS40170RGYR	Texas Instruments	4.5-v to 60-v wide-input synchronous PWM buck controller,	RGY0020A
					RGY0020A	

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design. TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have *not* been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.