PMP30104 REV A Bill of Materials

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
C1	1	330pF	GRM188R71H331KA01D	MuRata	CAP, CERM, 330pF, 50V, +/-10%, X7R, 0603	0603
C2	1	0.22uF	GRM188R71E224KA88D	MuRata	CAP, CERM, 0.22uF, 25V, +/-10%, X7R, 0603	0603
C3, C13	2	1000pF	GRM188R71H102KA01D	MuRata	CAP, CERM, 1000pF, 50V, +/-10%, X7R, 0603	0603
C4	1	220uF	EEE-FC1E221P	Panasonic	CAP, AL, 220 µF, 25 V, +/- 20%, 0.15 ohm, SMD	SMT Radial G
C5	1	0.1uF	GRM188R71H104KA93D	MuRata	CAP, CERM, 0.1 µF, 50 V, +/- 10%, X7R, 0603	0603
C6, C7	2	10uF	C2012X5R1E106K125AB	TDK	CAP, CERM, 10 µF, 25 V, +/- 10%, X5R, 0805	0805
C8	1	1uF	GRM21BR71H105KA12L	MuRata	CAP, CERM, 1uF, 50V, +/-10%, X7R, 0805	0805
C9	1	100pF	06033C101KAT2A	AVX	CAP, CERM, 100pF, 25V, +/-10%, X7R, 0603	0603
C10	1	1uF	GRM188R71E105KA12D	MuRata	CAP, CERM, 1uF, 25V, +/-10%, X7R, 0603	0603
C11, C12	2	10uF	C3216X5R1H106K160AB	TDK	CAP, CERM, 10 µF, 50 V, +/- 10%, X5R, 1206	1206
C14	1	0.01uF	GRM188R71H103KA01D	MuRata	CAP, CERM, 0.01uF, 50V, +/-10%, X7R, 0603	0603
C15	1	0.1uF	GCM188R71H104KA57D	MuRata	CAP, CERM, 0.1uF, 50V, +/-10%, X7R, 0603	0603
C16	1	100uF	EEE-FK1E101XP	Panasonic	CAP, AL, 100 μF, 25 V, +/- 20%, 0.34 ohm, SMD	SMT Radial D8
Cm1, Cm2, Cm3,	•	2.2uF	GRM31CR72A225KA73K	MuRata	CAP, CERM, 2.2 µF, 100 V, +/- 10%, X7R, 1206_190	1206_190
Cm4, Cm5, Cm6,		2.201		Multata	$CAI, CEININ, 2.2 \mu i, 100 v, 47^{-10}, 700, 700, 1200 - 190$	1200_130
Cm7, Cm8, Cm9,						
Cm10, Cm11						
D1, D2	2	6.8V	MMSZ5235BS-7-F	Diodes Inc.	Diode, Zener, 6.8V, 200mW, SOD-323	SOD-323
D3, D4		BAS16-7-F	BAS16-7-F	Diodes Inc.	Diode, Ultrafast, 75V, 0.3A, SOT-23	SOT-23
D3, D4 Dm1, Dm2, Dm3,	6	STPS1150A	STPS1150A	STMicroelectronics	Diode, Schottky, 150 V, 1 A, SMA	SMA
Dm1, Dm2, Dm3, Dm4, Dm5, Dm6	0	STPSTIDUA	51P51150A	STWICTOElectronics	Didde, Scholiky, 150 V, 1 A, SMA	SIVIA
J1	1		ED555/2DS	On-Shore Technology	Terminal Block, 6A, 3.5mm Pitch, 2-Pos, TH	7.0x8.2x6.5mm
J2	1		691 101 710 002	Wurth Elektronik	Terminal Block, 5 mm, 2x1, Tin, TH	Terminal Block, 5 mm, 2x1, TH
L1	1	47uH	7447709470	Wurth Elektronik	Inductor, Shielded Drum Core, Ferrite, 47 µH, 3.8 A, 0.04593 ohm, SMD	SMD
Lm1, Lm2, Lm3, Lm4, Lm5, Lm6	6	1mH	74477730	Wurth Elektronik	Inductor, Shielded Drum Core, Metal Composite, 1 mH, 0.2 A, 3.27 ohm, SMD	SMD
Q1	1	MMBT2222A	MMBT2222A	Fairchild Semiconductor	Transistor, NPN, 40V, 0.15A, SOT-23	SOT-23
Q2	1	BSZ520N15NS3 G	BSZ520N15NS3 G	Infineon Technologies	MOSFET, N-CH, 150 V, 21 A, PG-TSDSON-8	PG-TSDSON-8
Q3	1	BSS138W-7-F	BSS138W-7-F	Diodes Inc.	MOSFET, N-CH, 50 V, 0.2 A, SOT-323	SOT-323
R1, R3	2	100k	CRCW0603100KFKEA	Vishay-Dale	RES, 100k ohm, 1%, 0.1W, 0603	0603
R2, R4	2	20.0k	CRCW060320K0FKEA	Vishay-Dale	RES, 20.0k ohm, 1%, 0.1W, 0603	0603
R5	1	3.92k	CRCW06033K92FKEA	Vishay-Dale	RES, 3.92k ohm, 1%, 0.1W, 0603	0603
R6, R8, R24	3	10.0k	CRCW060310K0FKEA	Vishay-Dale	RES, 10.0k ohm, 1%, 0.1W, 0603	0603
R7	1	261k	RC0603FR-07261KL	Yageo America	RES, 261 k, 1%, 0.1 W, 0603	0603
R9	1	4.64	CRCW06034R64FKEA	Vishay-Dale	RES, 4.64 ohm, 1%, 0.1W, 0603	0603
R10	1	49.9	CRCW060349R9FKEA	Vishay-Dale	RES, 49.9 ohm, 1%, 0.1W, 0603	0603
R11	1	2.21	RC0603FR-072R21L	Yageo America	RES, 2.21, 1%, 0.1 W, 0603	0603
R12, R20	2	1.00k	CRCW06031K00FKEA	Vishay-Dale	RES, 1.00k ohm, 1%, 0.1W, 0603, RES, 1.00 k, 1%, 0.1 W, 0603	0603
R13	1	0.025	CSRN2010FK25L0	Stackpole Electronics Inc	RES, 0.025 ohm, 1%, 1W, 2010	2010
R14	1	25.5k	RC0603FR-0725K5L	Yageo America	RES, 25.5 k, 1%, 0.1 W, 0603	0603
R15, R16, R17, R18	4	1.00Meg	RC1206FR-071ML	Yageo America	RES, 1.00 M, 1%, 0.25 W, 1206	1206

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
R21	1	1.50	RC0805FR-071R5L	Yageo America	RES, 1.50, 1%, 0.125 W, 0805	0805
R22	1	392k	RC0603FR-07392KL	Yageo America	RES, 392 k, 1%, 0.1 W, 0603	0603
R23	1	10.0	RC0805FR-0710RL	Yageo America	RES, 10.0, 1%, 0.125 W, 0805	0805
TP1, TP5, TP8	3	Red	5000	Keystone	Test Point, Miniature, Red, TH	Red Miniature
						Testpoint
TP2, TP4	2	Black	5001	Keystone	Test Point, Miniature, Black, TH	Black Miniature
						Testpoint
TP3	1	Orange	5003	Keystone	Test Point, Miniature, Orange, TH	Orange Miniature
						Testpoint
U1	1	TPS40210DGQR	TPS40210DGQR	Texas Instruments	4.5-V TO 52-V INPUT CURRENT MODE BOOST	DGQ0010D
					CONTROLLER, DGQ0010D	
U2	1	TLC272CD	TLC272CD	Texas Instruments	IC, Precision Dual Operational Amplifiers	SO8

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ('TI') reference designs are solely intended to assist designers ("Designer(s)") who are developing systems that incorporate TI products. TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design.

TI's provision of reference designs and any other technical, applications or design advice, quality characterization, reliability data or other information or services does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such reference designs or other items.

TI reserves the right to make corrections, enhancements, improvements and other changes to its reference designs and other items.

Designer understands and agrees that Designer remains responsible for using its independent analysis, evaluation and judgment in designing Designer's systems and products, and has full and exclusive responsibility to assure the safety of its products and compliance of its products (and of all TI products used in or for such Designer's products) with all applicable regulations, laws and other applicable requirements. Designer represents that, with respect to its applications, it has all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. Designer agrees that prior to using or distributing any systems that include TI products, Designer will thoroughly test such systems and the functionality of such TI products as used in such systems. Designer may not use any TI products in life-critical medical equipment unless authorized officers of the parties have executed a special contract specifically governing such use. Life-critical medical equipment is medical equipment where failure of such equipment would cause serious bodily injury or death (e.g., life support, pacemakers, defibrillators, heart pumps, neurostimulators, and implantables). Such equivalent classifications outside the U.S.

Designers are authorized to use, copy and modify any individual TI reference design only in connection with the development of end products that include the TI product(s) identified in that reference design. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of the reference design or other items described above may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS AND OTHER ITEMS DESCRIBED ABOVE ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY DESIGNERS AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS AS DESCRIBED IN A TI REFERENCE DESIGN OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

TI's standard terms of sale for semiconductor products (<u>http://www.ti.com/sc/docs/stdterms.htm</u>) apply to the sale of packaged integrated circuit products. Additional terms may apply to the use or sale of other types of TI products and services.

Designer will fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of Designer's noncompliance with the terms and provisions of this Notice.

> Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2016, Texas Instruments Incorporated