

TIDA-01348-BOM					
Item #	Designator	Comment	Description	Manufacturer	Quantity
2	C1	GCM188R71H104KA57D	CAP, CERM, 0.1 礮, 50 V, +/- 10%, X7R, 0603	MuRata	1
3	C2, C5	GRM21BR71H104KA01L	CAP, CERM, 0.1 礮F, 50 V, +/- 10%, X7R, 0805	MuRata	2
4	C3, C4	GRM31CR71H475KA12L	CAP, CERM, 4.7 礮, 50 V, +/- 10%, X7R, 1206	MuRata	2
5	C6	GCM188R71C105KA64D	CAP, CERM, 1 礮, 16 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0603	MuRata	1
6	C7, C9	GRM31CR71C106KAC7L	CAP, CERM, 10 礮, 16 V, +/- 10%, X7R, 1206	MuRata	2
7	C8	GRM32ER61C226KE20L	CAP, CERM, 22 礮F, 16 V, +/- 10%, X5R, 1210	MuRata	1
8	C10	GRM155R71C104JA88D	CAP, CERM, 0.1 礮F, 16 V, +/- 5%, X7R, 0402	MuRata	1
9	C11, C12, C14, C15, C17, C18, C19, C20, C23, C24	GRM188R72A103KA01D	CAP, CERM, 0.01 礮F, 100 V, +/- 10%, X7R, 0603	MuRata	10
10	C13, C16	GRM21BR71H105KA12L	CAP, CERM, 1 礮F, 50 V, +/- 10%, X7R, 0805	MuRata	2
11	C21, C22	GRM188R71C103KA01D	CAP, CERM, 0.01 礮, 16 V, +/- 10%, X7R, 0603	MuRata	2
12	C25, C27	GRM188R71H104KA93D	CAP, CERM, 0.1 礮F, 50 V, +/- 10%, X7R, 0603	MuRata	2
13	C26	GRM188R71E473KA01D	CAP, CERM, 0.047 礮F, 25 V, +/- 10%, X7R, 0603	MuRata	1
14	Cd1	GCM31MR71E105KA37L	CAP, CERM, 1 礮, 25 V, +/- 10%, X7R, AEC-Q200 Grade 1, 1206	MuRata	1
15	D1, D2, D3, D4, D5, D6, D7, D8, D9, D10, D11, D12, D13, D14, D15, D16, D17, D18, D19, D20, D21, D22, D23, D24	LR G6SP-CBEA-1-1	LED, Red, SMD	OSRAM	24
16	J1	TMM-103-01-T-S	Header, 2mm, 3x1, Tin, TH	Samtec	1
17	JEN, Jmode, Jreset	HTSW-103-07-G-S	Header, 100mil, 3x1, Gold, TH	Samtec	3
18	L1	MPI4040R3-4R7-R	Inductor, Shielded, 4.7 礮, 2.3 A, 0.092 ohm, SMD	Coiltronics	1
19	Lfilt1	LQH3NPN4R7NG0	Inductor, Wirewound, Ferrite, 4.7 礮H, 0.8 A, 0.26 ohm, SMD	MuRata	1
20	P1, P2, P3, P4, P5, P6, P7, P8	Header 3	Header, 3-Pin		8
21	P9, P10	Header 4X2	Header, 4-Pin, Dual row		2
22	R1, R2, R3, R4, R5, R9, R12, R14, R15, R16, R21, Rfb2	CRCW060310K0FKEA	RES, 10.0 k, 1%, 0.1 W, 0603	Vishay-Dale	12
23	R6, R8	CRCW06036K98FKEA	RES, 6.98 k, 1%, 0.1 W, 0603	Vishay-Dale	2
24	R7, R10	CRCW06039K76FKEA	RES, 9.76 k, 1%, 0.1 W, 0603	Vishay-Dale	2
25	R11, R13	RC0603JR-070RL	RES, 0, 5%, 0.1 W, 0603	Yageo America	2
26	R17, R27	CRCW06030000Z0EA	RES, 0, 5%, 0.1 W, 0603	Vishay-Dale	2
27	R18	3314J-x-yyyz	Potentiometer, 4mm Sq, 0.25W, 礮20%	Bourns	1
28	R19	CRCW060321K5FKEA	RES, 21.5 k, 1%, 0.1 W, 0603	Vishay-Dale	1
29	R20	CRCW06032K10FKEA	RES, 2.10 k, 1%, 0.1 W, 0603	Vishay-Dale	1
30	R22	CRCW0603475KFKEA	RES, 475 k, 1%, 0.1 W, 0603	Vishay-Dale	1
31	R23	CRCW060315K8FKEA	RES, 15.8 k, 1%, 0.1 W, 0603	Vishay-Dale	1
32	R24, R25, R26	CRCW060345K3FKEA	RES, 45.3 k, 1%, 0.1 W, 0603	Vishay-Dale	3
33	Rd1	CRCW06034R99FKEA	RES, 4.99, 1%, 0.1 W, 0603	Vishay-Dale	1
34	REN, Rmode, Rreset, Rsync1	CRCW0603100KFKEA	RES, 100 k, 1%, 0.1 W, 0603	Vishay-Dale	4
35	Rfb1	CRCW060366K5FKEA	RES, 66.5 k, 1%, 0.1 W, 0603	Vishay-Dale	1
36	SH-J1, SH-J2, SH-J3	969102-0000-DA	Shunt, 100mil, Gold plated, Black	3M	3
37	TP1	VIN_filt	Terminal, Turret, TH, Double	Keystone	1
38	TP2	VIN	Terminal, Turret, TH, Double	Keystone	1
39	TP3	VOUT	Terminal, Turret, TH, Double	Keystone	1
40	TP4	GND_filt	Terminal, Turret, TH, Double	Keystone	1

41	TP5, TP6	GND	Terminal, Turret, TH, Double	Keystone	2
42	TP7	SYNC	Test Point, Miniature, White, TH	Keystone	1
43	TP8	RESET	Test Point, Miniature, White, TH	Keystone	1
44	TP9	EN	Test Point, Miniature, White, TH	Keystone	1
45	U1	LM53601MQDSXRQ1	Synchronous Buck Regulator for 650mA Space Constraint Applications, DSX0010A	Texas Instruments	1
46	U2, U3	TPS92638QPWRQ1	Eight-Channel Linear LED Driver with PWM Dimming, PWP0020B	Texas Instruments	2
47	U4	TLC2274AQDRG4Q1	Advanced LinCMOS(TM) Rail-to-Rail Quad Operational Amplifier, 4.4 to 16 V, -40 to 125 degC, 14-pin SOIC (D0014A), Green (RoHS & no Sb/Br)	Texas Instruments	1

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>), [evaluation modules](#), and [samples](http://www.ti.com/sc/docs/sampterm.htm) (<http://www.ti.com/sc/docs/sampterm.htm>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2017, Texas Instruments Incorporated