

**PMP8978\_REVA BOM**

COUNT	RefDes	Value	Description	Size	Part Number	Mfr
1	C1	330uF	Capacitor, Aluminum, 420V, 20%	22 x 35 mm	EET-UQ2S331LA	Panasonic
1	C100	0.47uF	Capacitor, Ceramic, 16V, X7R, 10%	0603	STD	STD
2	C101, C102	47pF	Capacitor, Ceramic, 50V, C0G, 5%	0603	STD	STD
1	C12	220pF	Capacitor, Ceramic, 1kV, C0G	1808	Std	Std
1	C18	4700uF	CAP 4700UF 16V ELECT KY RAD	0.571 inch	EKY-160ELL472MLN3S	United Chemi-Con
9	C2, C3, C4, C5, C19, C23, C26, C28, C31	1uF	Capacitor, Ceramic, 16V, X7R, 10%	0603	C1608X7R1C105K	TDK
2	C20, C21	0.033uF	Capacitor, Film, TH, 400V	6.4x12.5mm	ECWF4333HL	Panasonic
1	C24	0.047uF	Capacitor, Ceramic, 50V, X7R, 10%	0603	C1608X7R1H473K	TDK
1	C25	1500pF	CAP, CERM DISC Y1, 250Vac, 20%	.500 X .310	ECKDNA152ME	Panasonic
4	C29, C30, C103, C104	0.01uF	Capacitor, Ceramic, 50V, X7R, 10%	0603	C1608X7R1H103K	TDK
3	C6, C22, C27	0.1uF	Capacitor, Ceramic, 50V, X7R, 10%	0603	C1608X7R1H104K	TDK
10	C7, C8, C9, C10, C11, C13, C14, C15, C16, C17	22uF	Capacitor, Ceramic, 16V, X5R, 15%	1210	STD	STD
2	D1, D3	MMSD914	Diode, Switching, 100-V, 200-mA, 225-mW	SOD-123	MMSD914T1	On Semi
4	D2, D4, D5, D8	BAV99	Diode, Dual Ultra Fast, Series, 200-mA, 70-V	SOT23	BAV99	Fairchild
1	D6	MBR0560	Diode, Schottky, 500-mA, 60-V	SOD123	MBR0560	STD
1	D7	5.1V	Diode, Zener, 5.1-V	SOT23	BZX84C5V1LT1	ON Semiconductor
1	HS1	529702 B 0 25 00	Heatsink, Vertical-mount With Solderable Pins	1.000 x 1.650 inch	529702 B 0 25 00	Aavid
2	J3, J4	33457	Lug, Solderless, #10 - #10-12 AWG, Copper/Tin, Uninsulated	0.375 x1.00 inch	33457	AMP
1	L1	30 uH	Inductor, 10±%	0.700 x 0.760 inch	PA3329NL	Pulse
1	L2	0.44uH	Inductor, SMT Power 20%	0.510 x 0.530 inch	SLC1480-441ML	Coilcraft
6	Q1, Q3, Q6, Q10, Q11, Q12	CSD18501Q5A	MOSFET N-CH 40V 8SON	SO-8	CSD18501Q5A	TI
2	Q2, Q5	IPP50R350CP	Trans, Nchan, 550V, 10A, 350 millohm	TO-220AB	IPP50R350CP	Infineon
2	Q4, Q8	MMBT2222A	Bipolar, NPN, 40V, 600mA	SOT23	MMBT2222ALT1	ON Semiconductor
2	Q7, Q9	MMBT2907	Bipolar, PNP, 60V, 600mA	SOT23	MMBT2907LT1	On Semiconductor
2	R1, R11	221k	Resistor, Chip, 1/16W, 1%	0603	Std	Std
5	R10, R101, R102, R103, R104	100	Resistor, Chip, 1/16W, 1%	0603	Std	Std
4	R105, R106, R107, R108	10	Resistor, 1W, 5%	2512	STD	STD
1	R12	2.94k	Resistor, Chip, 1/16W, 1%	0603	Std	Std
2	R14, R18	499k	Resistor, Chip, 1/16W, 1%	1206	Std	Std
1	R15	1k	Resistor, Chip, 1/16W, 1%	0603	Std	Std
3	R16, R109, R110	0	Resistor, Chip, 1/16W, 1%	0603	Std	Std
2	R17, R19	2k	Resistor, Chip, 1/16W, 1%	0603	Std	Std
4	R2, R13, R21, R22	100k	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R23	2.61k	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R24	17.8k	Resistor, Chip, 1/16W, 1%	0603	Std	Std
2	R3, R5	3	Resistor, Chip, 1/16W, 1%	0603	Std	Std
3	R4, R6, R20	10k	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R7	0.05	Resistor, 1W, 5%	2512	STD	STD
1	R8	20k	Resistor, Chip, 1/16W, 1%	0603	Std	Std
2	R9, R100	499	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	T1	56P3362	Transformer, Gate Drive	0.453 x 0.492 inch	56P3362	Vitec Electronics
1	T2	128 uH	Transformer, ±10%	1.700 x 2.100 inch	PA3321NL	Pulse
1	TP1		TEST POINT PC MULTI PURPOSE RED	0.125 x 0.125 inch	5010	Keystone
1	TP2		TEST POINT PC MULTI PURPOSE BLK	0.125 x 0.125 inch	5011	Keystone
3	TP3, TP5, TP6	5000	Test Point, Red, Thru Hole Color Keyed	0.100 x 0.100 inch	5000	Keystone
2	TP4, TP7	5001	Test Point, Black, Thru Hole Color Keyed	0.100 x 0.100 inch	5001	Keystone
2	U1, U4	UCC24610D	IC, SYNCHRONOUS RECTIFIER CONTROLLER	SO-8	UCC24610D	TI
1	U2	TPS71550DCK	IC, High Input Voltage, Micropower LDO, 5V	SOP-5 (DCK)	TPS71550DCKR	TI
1	U3	UCC25600D	IC, Resonant Mode Controller	SO-8	UCC25600D	TI
1	U5	TL331DBV	IC, COMPARATOR, DIFFERENTIAL, SINGLE	SOT_23_5 (DBV)	TL331DBV	TI
1	U6	H11A817A	IC, Optocoupler, 5300-V, 80-160% CTR	0.380 x 0.180 inch	H11A817A	Fairchild
1	U7	TL431AIDBZ	IC, Precision Adjustable Shunt Regulator	SOT23-3	TL431AIDBZ	TI

## IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have **not** been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

### Products

Audio	<a href="http://www.ti.com/audio">www.ti.com/audio</a>
Amplifiers	<a href="http://amplifier.ti.com">amplifier.ti.com</a>
Data Converters	<a href="http://dataconverter.ti.com">dataconverter.ti.com</a>
DLP® Products	<a href="http://www.dlp.com">www.dlp.com</a>
DSP	<a href="http://dsp.ti.com">dsp.ti.com</a>
Clocks and Timers	<a href="http://www.ti.com/clocks">www.ti.com/clocks</a>
Interface	<a href="http://interface.ti.com">interface.ti.com</a>
Logic	<a href="http://logic.ti.com">logic.ti.com</a>
Power Mgmt	<a href="http://power.ti.com">power.ti.com</a>
Microcontrollers	<a href="http://microcontroller.ti.com">microcontroller.ti.com</a>
RFID	<a href="http://www.ti-rfid.com">www.ti-rfid.com</a>
OMAP Applications Processors	<a href="http://www.ti.com/omap">www.ti.com/omap</a>
Wireless Connectivity	<a href="http://www.ti.com/wirelessconnectivity">www.ti.com/wirelessconnectivity</a>

### Applications

Automotive and Transportation	<a href="http://www.ti.com/automotive">www.ti.com/automotive</a>
Communications and Telecom	<a href="http://www.ti.com/communications">www.ti.com/communications</a>
Computers and Peripherals	<a href="http://www.ti.com/computers">www.ti.com/computers</a>
Consumer Electronics	<a href="http://www.ti.com/consumer-apps">www.ti.com/consumer-apps</a>
Energy and Lighting	<a href="http://www.ti.com/energy">www.ti.com/energy</a>
Industrial	<a href="http://www.ti.com/industrial">www.ti.com/industrial</a>
Medical	<a href="http://www.ti.com/medical">www.ti.com/medical</a>
Security	<a href="http://www.ti.com/security">www.ti.com/security</a>
Space, Avionics and Defense	<a href="http://www.ti.com/space-avionics-defense">www.ti.com/space-avionics-defense</a>
Video and Imaging	<a href="http://www.ti.com/video">www.ti.com/video</a>

### TI E2E Community

[e2e.ti.com](http://e2e.ti.com)