

| TSW3070 RevC BOM | | | | | | | DNI = DO NOT INSTALL | |
|------------------|-----|---|---------------------|-----------------------------|--------------------|-----------------------|--------------------------|-------------|
| Item | Qty | Part Reference | Value | PCB Footprint | Mfr_Name | Mfr_Part_Number | Note | TI Supplied |
| 1 | 7 | C1 C2 C5 C8 C56 C79 C124 | .01uF | 0603 | Panasonic | ECJ-1V81C103K | | |
| 2 | 1 | C3 | 0.15uF | 0402 | AVX | 04026D154KAT2A | | |
| 3 | 8 | C4 C29 C48 C127 C135 C136 C140 C141 | 1000pF | 0402 | Panasonic | ECJ-0EB1E102K | | |
| 4 | 47 | C6 C7 C9-C15 C17 C18 C20 C23-C25 C27 C33 C38-C47 C50-C52 C57 C61 C66 C94-C96 C100 C103 C105 C107 C130 C131 C149 C156 C160 C166 C168 | .1uF | 0402 | Panasonic | ECJ-0EB1C104K | | |
| 5 | 13 | C16 C21 C32 C53 C54 C80 C93 C97 C101 C102 C104 C106 C126 | 10uF | tant_a | Kemet | T494A106M016AS | | |
| 6 | 1 | C22 | 560pF | 0402 | Panasonic | ECJ-0EB1H561K | | |
| 7 | 1 | C31 | 100pF | 0402 | Panasonic | ECJ-0EB1E101K | | |
| 8 | 4 | C34 C78 C91 C125 | 1uF | 0603 | Panasonic | ECJ-1V41E105M | | |
| 9 | 1 | C35 | .47uF | 0603 | Murata | GRM188R71C474KA88D | | |
| 10 | 1 | C36 | 22uF | TANT_A | KEMET | T494A226M010AT | | |
| 11 | 1 | C37 | 2.2uF | 1206 | muRata | GRM31MR71C225KA35L | | |
| 12 | 6 | C49 C90 C92 C99 C128 C129 | .01uF | 0402 | Panasonic | ECJ-0EB1E103K | | |
| 13 | 1 | C58 | 4.7uF | tant_a | AVX | TAJA475K020R | | |
| 14 | 2 | C59 C60 | 47pF | 0603 | Panasonic | ECJ-1VC1H470J | | |
| 15 | 1 | C62 | 100uF | tant_c | AVX | TPSC1070M010R0075 | | |
| 16 | 1 | C63 | 1uF | tant_a | AVX | T494A105M016AT | | |
| 17 | 1 | C64 | 4.7uF | tant_b | AVX | T494B475M010AT | | |
| 18 | 9 | C67 C68 C81 C123 C153 C157 C162 C165 C169 | 47uF | tant_b | Kemet | T494B476M010AS | | |
| 19 | 4 | C132 C134 C137 C139 | 5pF | 0603 | AVX | 06031A5R0BAT2A | | |
| 20 | 2 | C133 C138 | 16pF | 0603 | JOHANSON TECH | 251R14S160GV4T | | |
| 21 | 0 | C142-C145 | 15pF | 0402 | Panasonic | ECD-G0E150J_DNI | DNI | |
| 22 | 7 | C148 C154 C161 C163 C167 C170 C349 | 10uF | 1206 | Panasonic | ECJ-3YB1C106K | | |
| 23 | 4 | C155 C158 C159 C164 | 10uF | 1206 | Panasonic | ECJ-3YB1C106K | LOW ESR | |
| 24 | 1 | C171 | .015uF | 0402 | Panasonic | ECJ-0EB1C153K | | |
| 25 | 4 | D1-D3 D18 | Green | LED_0805 | Panasonic | LNJ306G5UUX | | |
| 26 | 1 | D20 | 20V, 1A | MCC_SOD123 | On Semi | MBR120LSFT1G | | |
| 27 | 16 | FB1-FB4 FB7 FB10 FB11 FB13-FB16 FB23-FB27 | 68 OHM @ 100MHz | 1206 | Panasonic | EXC-ML32A680U | | |
| 28 | 2 | J1 J3 | SMA_PCB_THVT | SMA_THVT_312x312 | Johnson Components | 142-0701-201 | | |
| 29 | 7 | J6-J11 J16 | SMA_END_JACK_RND | SMA_SMEL_218x247_096 | Johnson Components | 142-0761-801 | | |
| 30 | 1 | J12 | CONN JACK PWR | CON_RAPC722_JACK_THVT_3 | Switchcraft | RAPC722 | | |
| 31 | 1 | J13 | USB_B_S_F_B_TH | CON_THRT_USB_B_F | SAMTEC | USB-B-S-F-B-TH | | |
| 32 | 1 | J24 | BANANA_JACK_RED | CON_THVT_BANANA_JACK_250DIA | SPC Technology | 845-R | | |
| 33 | 1 | J25 | BANANA_JACK_BLK | CON_THVT_BANANA_JACK_250DIA | SPC Technology | 845-B | | |
| 34 | 1 | J5 | ASP-122952-01 | CON_SMVT_160POS_ASP_122952 | SAMTEC | ASP-122952-01 | | |
| 35 | 4 | JP8 JP13 JP14 JP16 | Jumper_1x3_100_430L | HDR_THVT_1x3_100_M | SAMTEC | HMTSW-103-07-G-S-.230 | (SHUNT 2-3) USE ITEM 111 | |
| 36 | 4 | JP10-JP12 JP15 | Jumper_1x3_100_430L | HDR_THVT_1x3_100_M | SAMTEC | HMTSW-103-07-G-S-.230 | (SHUNT 1-2) USE ITEM 111 | |
| 37 | 1 | JP19 | Jumper_1x2_100_430L | HDR_THVT_1x2_100_M | SAMTEC | HMTSW-102-07-G-S-.230 | | |
| 38 | 0 | L6 L7 | 56nH | IND_0603 | Panasonic | ELJ-RE56NJF3_DNI | DNI | |
| 39 | 4 | L8 L10 L11 L16 | 68nH | 0603 | COILCRAFT | 0603CS-68NXGLU | | |
| 40 | 1 | L9 | 100uH, .88A, 290ml | IND_SM_MSS1048 | COILCRAFT | MSS1048-104MLB | | |
| 41 | 4 | L12-L15 | 250nH | 0603 | COILCRAFT | 0603CS-R25XGL | | |
| 42 | 0 | R1 R2 R4 R5 R12 R14 R17 R19 R3 R7 R13 R21 R26 R80 R82 R90 R93 R96 | 1K | 0402 | Panasonic | ERJ-2RKF1001X_DNI | DNI | |
| 43 | 10 | R6 R15 R20 R27 R35 R118 R159-R164 | 0 | 0603 | Panasonic | ERJ-3GEY0R00V | | |
| 44 | 12 | R8 R22 R44 R49 R62 | 0 | 0402 | Panasonic | ERJ-2GE0R00X | | |
| 45 | 5 | R10 | 93.1 | 0402 | Panasonic | ERJ-2RKF93R1X | | |
| 46 | 1 | R11 R24 R132 R133 | 60.4 | 0603 | Yageo | RC0603FR-0760R4L_DNI | DNI | |
| 47 | 0 | R16 | 100 | 0603 | Panasonic | ERJ-3EKF1000V_DNI | DNI | |

| Item | Qty | Part Reference | Value | PCB Footprint | Mfr_Name | Mfr_Part_Number | Note | TI Supplied |
|------|-----|-------------------------------------|----------------|------------------------------|------------------------|-------------------------|--------------------------|-------------|
| 49 | 1 | R18 | 953 | 0402 | Panasonic | ERJ-2RKF9530X | | |
| 50 | 1 | R25 | 1K | 0402 | Panasonic | ERJ-2RKF1001X | | |
| 51 | 3 | R28-R30 | 750 | 0402 | Panasonic | ERJ-2RKF7500X | | |
| 52 | 2 | R31 R32 | 130 | 0402 | Panasonic | ERJ-2RKF1300X | | |
| 53 | 0 | R33 R34 R42 R43 R48 R54 R66 R67 | 130 | 0402 | Panasonic | ERJ-2RKF1300X_DNI | DNI | |
| 54 | 2 | R36 R37 | 82.5 | 0402 | Panasonic | ERJ-2RKF82R5X | | |
| 55 | 6 | R38 R39 R46 R47 R69 R70 | 150 | 0402 | Panasonic | ERJ-2RKF1500X | | |
| 56 | 0 | R40 R52 R57 R116 | 150 | 0402 | Panasonic | ERJ-2RKF1500X_DNI | DNI | |
| 57 | 0 | R41 R109 R134-R136 | 0 | 0603 | Panasonic | ERJ-3GEY0R00V_DNI | DNI | |
| 58 | 0 | R45 R51 R122 R123 | 0 | 0402 | Panasonic | ERJ-2GEOR00X_DNI | DNI | |
| 59 | 9 | R50 R56 R78 R79 R81 R84 R89 R95 R97 | 22.1 | 0402 | Panasonic | ERJ-2RKF22R1X | | |
| 60 | 0 | R53 R58 | 82.5 | 0402 | Panasonic | ERJ-2RKF82R5X_DNI | DNI | |
| 61 | 0 | R55 | 49.9 | 0402 | Panasonic | ERJ-2RKF49R9X_DNI | DNI | |
| 62 | 8 | R59-R61 R64 R72 R108 R113 R114 | 10K | 0402 | Panasonic | ERJ-2RKF1002X | | |
| 63 | 1 | R63 | 162 | 0402 | Panasonic | ERJ-2RKF1620X | | |
| 64 | 1 | R65 | 4.75K | 0402 | Panasonic | ERJ-2RKF4751X | | |
| 65 | 2 | R68 R110 | 69.8 | 0603 | PANASONIC | ERJ-3EKF69R8V | | |
| 66 | 1 | R71 | 75.0 | 0603 | PANASONIC | ERJ-3EKF75R0V | | |
| 67 | 1 | R73 | 2.87K | 0402 | Panasonic | ERJ-2RKF2871X | | |
| 68 | 3 | R74 R75 R83 | 100K | 0603 | Panasonic | ERJ-3EKF1003V | | |
| 69 | 1 | R76 | 15.8K | 0603 | Panasonic | ERJ-3EKF1582V | | |
| 70 | 1 | R77 | 30.1K | 0603 | Panasonic | ERJ-3EKF3012V | | |
| 71 | 2 | R85 R91 | 249 | 0603 | PANASONIC | ERJ-3EKF2490V | | |
| 72 | 2 | R86 R94 | 499 | 0603 | KOA Speer | RK73H1JTTD4990F | | |
| 73 | 1 | R87 | 174 | 0603 | PANASONIC | ERJ-3EKF1740V | | |
| 74 | 1 | R88 | 187 | 0603 | PANASONIC | ERJ-3EKF1870V | | |
| 75 | 1 | R92 | 100 | 0603 | Panasonic | ERJ-3EKF1000V | | |
| 76 | 1 | R98 | 86.6 | 0603 | PANASONIC | ERJ-3EKF86R6V | | |
| 77 | 0 | R99 R115 | 49.9 | 0603 | KOA Speer | RK73H1JLTD49R9F_DNI | DNI | |
| 78 | 2 | R100 R125 | 130 | 0603 | PANASONIC | ERJ-3EKF1300V | | |
| 79 | 1 | R101 | 143 | 0603 | PANASONIC | ERJ-3EKF1430V | | |
| 80 | 2 | R102 R107 | 750 | 0603 | Panasonic | ERJ-3EKF7500V | | |
| 81 | 2 | R103 R106 | 374 | 0603 | PANASONIC | ERJ-3EKF3740V | | |
| 82 | 1 | R104 | 412 | 0603 | PANASONIC | ERJ-3EKF4120V | | |
| 83 | 1 | R105 | 464 | 0603 | PANASONIC | ERJ-3EKF4640V | | |
| 84 | 1 | R111 | 226 | 0603 | PANASONIC | ERJ-3EKF2260V | | |
| 85 | 1 | R112 | 169 | 0603 | PANASONIC | ERJ-3EKF1690V | | |
| 86 | 1 | R117 | 300 | 0603 | Panasonic | ERJ-3EKF3000V | | |
| 87 | 2 | R119 R120 | 49.9 | 0603 | KOA Speer | RK73H1JLTD49R9F | | |
| 88 | 1 | R121 | 332 | 0603 | YAGEO | RC0603FR-07332RL | | |
| 89 | 1 | R126 | 665 | 0603 | PANASONIC | ERJ-3EKF6650V | | |
| 90 | 1 | R127 | 1.96K | 0603 | PANASONIC | ERJ-3EKF1961V | | |
| 91 | 1 | R288 | 23.2K | 0603 | Panasonic | ERJ-3EKF2322V | | |
| 92 | 1 | SJP4 | Jumper_1x3_SMT | SJP3_JUMPER | | | (SHUNT 1-2) USE ITEM 112 | |
| 93 | 1 | SW1 | SW RESET | SW_SMVT_RESET | C&K | KT11P3JM | | |
| 94 | 2 | T1 T2 | ADT4-6T | TFMR_6_250x340_100 | Mini-Circuits | ADT4-6T | | |
| 95 | 16 | TP1-TP16 | Testloop_Black | TP_THVT_060_RND | Components Corporation | TP-105-01-00 | | |
| 96 | 1 | U1 | DAC5682Z | QFN_64_360x360_0p50mm_pwrpad | Texas Instruments | DAC5682Z | | YES |
| 97 | 1 | U2 | CDCM7005 | QFN_48_281x281_0p50mm_pwrpad | Texas Instruments | CDCM7005RG2T | | YES |
| 98 | 1 | U3 | OSC-VECTRON | OSC_4_SM_460x386 | Vectron | VTD3-J0BC-10M000 | | YES |
| 99 | 1 | U5 | FT245RL | SSOP_28_413x220_26 | FTDI Chip | FT245RL | | |
| 100 | 1 | U6 | 800MHZ | VCXO_6 | VECTRON | VS-705-LFF-GNN_800M0000 | | |
| 101 | 1 | U7 | TPS5430 | PSOP_8P_THERMAL | Texas Instruments | TPS5430DDA | | |
| 102 | 1 | U8 | UCC284-5 | SOIC_8 | Texas Instruments | UCC284DP-5 | | |
| 103 | 1 | U10 | SN74AHC541PW | TSSOP_20_260x177_26 | Texas Instruments | SN74AHC541PW | | YES |
| 104 | 1 | U11 | SN74HC241PW | TSSOP_20_260x177_26 | Texas Instruments | SN74HC241PW | | YES |
| 105 | 1 | U13 | TPS76750QPWP | HTSSOP_20_260x177_26_pwrpad | Texas Instruments | TPS76750QPWP | | |
| 106 | 1 | U14 | TPS76701QPWP | HTSSOP_20_260x177_26_pwrpad | Texas Instruments | TPS76701QPWP | | |

| Item | Qty | Part Reference | Value | PCB Footprint | Mfr_Name | Mfr_Part_Number | Note | TI Supplied |
|------|-----|--|-------------------------------|-----------------------------|--------------------|-----------------|--------------------|-------------|
| 107 | 1 | U15 | TPS76733QPWP | HTSSOP_20_260x177_26_pwrpad | Texas Instruments | TPS76733QPWP | | |
| 108 | 1 | U16 | OPA695IDBVT | PSOP_6P_DBV | Texas Instruments | OPA695IDBVT | | |
| 109 | 1 | U17 | THS3095DDA | PSOP_8P_THERMAL | Texas Instruments | THS3095DDA | | |
| 110 | 4 | Z_SCREW1-Z_SCREW4 | SCREW PANHEAD 4-40 x 3/8 | | Building Fasteners | PMS 440 0038 PH | SCREW FOR STANDOFF | |
| 111 | 8 | Z_SH-H1-Z_SH-H4 Z_SH-H6 Z_SH-H9-Z_SH-H11 | SHUNT-HEADER | | Keltron | MJ-5.97-G | SHUNT FOR HEADER | |
| 112 | 1 | Z_SH-J1 | SHUNT-JUMPER-0603 | | Panasonic | ERJ-3GEY0R00V | SHUNT FOR JUMPER | |
| 113 | 4 | Z_STANDOFF1-Z_STANDOFF4 | STANDOFF ALUM HEX 4-40 x .500 | | Keystone | 2203 | STANDOFF | |

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. **TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design.** TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have **not** been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.