

Bill of Materials

_		Λ.			1 A
ш	יע	ч-		2	14

Item	Qty	Reference	Value	Part Description	Manufacturer	Manufacturer	Alternate Part	Alternate	Package Reference
iteiii	Qty		Value	•	Wallulacturel	Part Number	Alternate Part	Manufacturer	rackage hererence
1	1	!PCB1		Printed Circuit Board	Any	ISE4015	-	-	
2	1	C1	10uF	CAP, CERM, 10uF, 50V, +/-10%, X7R, 1210	MuRata	GRM32ER71H106KA12 L			1210
3	2	C2, C7	1.0μF	CAP CER 1UF 50V 10% X7R 0805	Murata Electronics No	GRM21BR71H105KA12 L			0805 (2012 Metric)
4	2	C3, C8	0.1uF	General Purpose Ceramic Capacitors	Venkel	C0805X7R500-104KNE			0805
5	1	C4	68uF	Low ESR Tantalum Capacitors	Venkel	TA020TCR686KER			
6	1	C5	10µF	CAP TANT 10UF 50V 10% 2917	Kemet	T495X106K050ATE300			2917 (7343 Metric)
7	1	C6	10uF	CAP, CERM, 10uF, 6.3V, +/-20%, X5R, 0603	MuRata	GRM188R60J106ME47			0603
8	1	C11	0.1μF	CAP, CERM, xxxF, xxV, [TempCo], xx%, [PackageReference]	Kemet	C0805C104K5RACTU	-	-	0805 (2012 Metric)
9	1	C14	4700 pF	CAP, CERM, xxxF, xxV, [TempCo], xx%, [PackageReference]	Novacap	1812B472K202NT	-	-	1812 (4532 metric)
10	1	D1		VCC ON	Lite-On Inc	LTST-S220TBKT			2-SMD, No Lead, Exposed Pad
11	1	D2	1V @ 15mA	DIODE SCHOTTKY 70V 0.07A SOD123F	NXP Semiconductors	BAS70H,115			SOD-123F
12	2	D3, D4	24V	Diode, TVS, Bi, 24V, 350W, SOD- 323	Bourns	CDSOD323-T24C-DSL			SOD-323
13	5	J1, J3, J5, J9, J16		Header, TH, 100mil, 3x1, Gold plated, 230 mil above insulator	Samtec	TSW-103-07-G-S			3x1 Header
14	9	J2, J4, J6, J7, J8, J11, J15, J17, J18		Header, TH, 100mil, 4x1, Gold plated, 230 mil above insulator	Samtec	TSW-104-07-G-S			4x1 Header
15	4	J10, J12, J19, J20		Header, TH, 100mil, 2x1, Gold plated, 230 mil above insulator	Samtec	TSW-102-07-G-S			2x1 Header
16	2	J13, J14		Samtec Socket Strip 10 POS 2.54mm Thru-Hole	Samtec Inc	SSW-110-23-F-S			
17	1	L1	4.7uH	Inductor, Shielded, Ferrite, 4.7uH, 1.2A, 0.14 ohm, SMD	Coilcraft	EPL3015-472MLB			Inductor, 3x1.55x3mm
18	1	R1	1.8Meg	RES, 1.8Meg ohm, 5%, 0.063W, 0402	Vishay-Dale	CRCW04021M80JNED			0402
19	1	R2	220	RES, 220 ohm, 5%, 0.125W, 0805	Panasonic	ERJ-6GEYJ221V			0805
20	1	R3	200k	RES, 200k ohm, 5%, 0.063W, 0402	Vishay-Dale	CRCW0402200KJNED			0402
21	3	R4, R9, R13	0.0	RES 0.0 OHM 1/8W JUMP 0805	Yageo	RC0805JR-070RL			0805 (2012 Metric)
22	4	R5, R6, R16, R17	4.7k	RES, xxx ohm, x%, xW,	Yageo	RT0603FRE074K7L	-	-	0603 (1608 Metric)
23	2	R8, R12	10	RES, xxx ohm, x%, xW,	Vishay Dale	CRCW060310R0FKEAH	-	-	0603 (1608 Metric)
24	1	R10	121 Ohm	RES 121 OHM 0.1W 1% 0805	Venkel	CR0805-10W-1210FT			0805 (2012 Metric)
25	1	R18	1M	RES, xxx ohm, x%, xW,	Ohmite	HVC2512T1004JET	-	-	2512 (6432 Metric)
26	5	SH-J1, SH-J10, SH-J12, SH	1x2	Shunt, 100mil, Gold plated, Black	Samtec	SNT-100-BK-G	969102-0000-DA	3M	Shunt

Item	Qty	Reference	Value	Part Description	Manufacturer	Manufacturer Part Number	Alternate Part	Alternate Manufacturer	Package Reference
27	2	TB1, TB2		CONN TERM BLOCK 2.54MM	Phoenix Contact	1725669			
28	1	U1		LOW INPUT VOLTAGE STEP-UP	Texas Instruments	TPS61220DCK		None	DCK0006A
29	1	U2		Extended Common-Mode RS-485	Texas Instruments	SN65HVD24D		None	D0008A
30	0	C9	68uF	Low ESR Tantalum Capacitors	Venkel	TA020TCR686KER			
31	0	C10	10μF	CAP TANT 10UF 50V 10% 2917	Kemet	T495X106K050ATE300			2917 (7343 Metric)
32	0	C12, C13, C15, C16	1.0µF	CAP CER 1UF 50V 10% X7R	Murata Electronics Nort	GRM21BR71H105KA12			0805 (2012 Metric)
33	0	FID1, FID2, FID3, FID4,		Fiducial mark. There is nothing to	N/A	N/A			Fiducial
34	0	R7, R14	0.0	RES 0.0 OHM 1/8W JUMP 0805	Yageo	RC0805JR-070RL			0805 (2012 Metric)
35	0	R11, R19, R21	49.9 Ohm	RES 49.9 OHM 0.1W 1% 0805	Venkel	CR0805-10W-49R9FT	•		0805 (2012 Metric)

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design. TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, Is GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have *not* been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.