

# **Seismic Sensor Demonstration Using an ADS1255 and TMS320VC5510A DSP**

Grant Christiansen

Signal Chain Applications


## **ABSTRACT**

A prototype system for seismic sensing for such applications as oil exploration, earthquake detection, and acoustic monitoring is described. The system uses a delta-sigma converter and low-power DSP. Measured system performance met the requirements for such systems.

Oil exploration, earthquake detection, and acoustic monitoring of drilling operations are all applications that use seismic sensing capabilities. Such applications require signal conditioning of the input of a geophone, hydrophone, or other acoustic sensor, demanding effective amplification, filtering, and digitization of the target acoustic signal.

An ideal seismic sensing system has the characteristics of good signal-to-noise ratio, low power consumption (to allow for remote operation), programmable signal filtering to accommodate several applications, a variable sampling rate, and cost-effectiveness. An additional goal is to make the system easy to prototype for fast evaluation.

The system architecture that was selected is shown in [Figure 1](#) and consists of an excellent front-end processor followed by a programmable, powerful, low-power filter engine.



**Figure 1. Seismic System Architecture**




Figure 2. ADS1255 Modulator Noise

The system input is an acoustic sensor that drives a signal conditioning circuit which in turn drives an A/D converter. The ADS1255 24-bit sigma-delta converter was chosen because it contains a programmable gain front-end stage that can replace the signal conditioning circuit. Further, the sigma-delta ADC's fourth-order oversampling architecture (Figure 2) provides signal-to-noise gain by moving the quantization noise up in frequency, where it is filtered out. This is a performance level that cannot be met by pipeline or successive-approximation architectures.

Seismic sensing applications require a processor that is fast, efficient, requires little logic glue, and is easy to implement. The TMS320VC5510A digital signal processor provides the low-power operation desired. The DSP has a 40-bit accumulator that makes the implementation of the pseudo-floating point operation used for the filtering easy – filter operations could be accumulated in 40 bits of resolution and truncated to 32 bits at the end of the filter. The DSP library provides for an efficient 32-bit x 32-bit multiply, making the filter operations efficient. Finally, the onboard McBSP interface allows interfacing to the ADC with minimal processor intervention.

The filtering architecture combined the fifth-order filter built into the ADS1255 with the flexible filter architecture of the DSP (Figure 3). The filter architecture allowed a variable rate output while providing a flat passband, sharp filter cutoff for noise reduction, >130-dB stopband rejection, and 50-Hz/60-Hz rejection.





Figure 3. Filtering Architecture Block Diagram



**Figure 4. Seismic System Prototype Board**

This solution can be built using evaluation boards that are readily available from Texas Instruments with the exception of the UART board (Figure 4). The system can attach to a host computer for complete system evaluation.

The measured results from the system showed performance that meets the needs of the application as Table 1 shows.

**Table 1. Prototype System Performance**

PARAMETER	MIN	TYP	MAX	UNIT
Sample Rate	0.9375		3750	Hz
SNR (3.75 ksps)		116		dB
SNR (117 sps)		131		dB

**References**

1. *TMS320VC5510/5510A Fixed Point DSP data manual* ([SPRS076](#))
2. *ADS1255/ADS1256 Very Low Noise 24-Bit ADC data sheet* ([SBAS288](#))
3. *TMS320VC5501/5502/5503/5507/5509/5510 DSP (McBSP) Reference Guide* ([SPRU592](#))
4. [TMS320VC5510 DSP Starter Kit](#)
5. [5-6K Interface Evaluation Module](#)
6. [ADS1256 Evaluation Module](#)

## IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

### Products

Amplifiers	<a href="http://amplifier.ti.com">amplifier.ti.com</a>
Data Converters	<a href="http://dataconverter.ti.com">dataconverter.ti.com</a>
DLP® Products	<a href="http://www.dlp.com">www.dlp.com</a>
DSP	<a href="http://dsp.ti.com">dsp.ti.com</a>
Clocks and Timers	<a href="http://www.ti.com/clocks">www.ti.com/clocks</a>
Interface	<a href="http://interface.ti.com">interface.ti.com</a>
Logic	<a href="http://logic.ti.com">logic.ti.com</a>
Power Mgmt	<a href="http://power.ti.com">power.ti.com</a>
Microcontrollers	<a href="http://microcontroller.ti.com">microcontroller.ti.com</a>
RFID	<a href="http://www.ti-rfid.com">www.ti-rfid.com</a>
RF/IF and ZigBee® Solutions	<a href="http://www.ti.com/lprf">www.ti.com/lprf</a>

### Applications

Audio	<a href="http://www.ti.com/audio">www.ti.com/audio</a>
Automotive	<a href="http://www.ti.com/automotive">www.ti.com/automotive</a>
Broadband	<a href="http://www.ti.com/broadband">www.ti.com/broadband</a>
Digital Control	<a href="http://www.ti.com/digitalcontrol">www.ti.com/digitalcontrol</a>
Medical	<a href="http://www.ti.com/medical">www.ti.com/medical</a>
Military	<a href="http://www.ti.com/military">www.ti.com/military</a>
Optical Networking	<a href="http://www.ti.com/opticalnetwork">www.ti.com/opticalnetwork</a>
Security	<a href="http://www.ti.com/security">www.ti.com/security</a>
Telephony	<a href="http://www.ti.com/telephony">www.ti.com/telephony</a>
Video & Imaging	<a href="http://www.ti.com/video">www.ti.com/video</a>
Wireless	<a href="http://www.ti.com/wireless">www.ti.com/wireless</a>

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2009, Texas Instruments Incorporated