

PRU-ICSS Feature Comparison

Catalog Processors

ABSTRACT

This application report documents the feature differences between the PRU subsystems available on different TI processors.

Contents

1	Introduction	2
2	PRU-ICSS Feature Comparison	3
3	PRU_ICSSG Feature Comparison	4
4	References	5

Trademarks

All trademarks are the property of their respective owners.

1 Introduction

TI Sitara devices offer two flavors of PRU subsystems-- PRU-ICSS and PRU_ICSSG. PRU-ICSS is available on AM335x, AM437x, AM57x family, and K2G devices. PRU_ICSSG is available on AM65x.

[Table 1](#) shows a high-level feature comparison of the two PRU subsystems. The subsequent sections show the feature differences between each device that supports the given subsystem flavor. For a more detailed comparison, see the [PRU-ICSS/PRU_ICSSG Migration Guide](#).

Table 1. PRU-ICSS and PRU_ICSSG Feature Comparison

Feature	PRU-ICSS	PRU_ICSSG
PRU cores	Yes	Yes
RTU_PRU (Auxiliary PRU) cores	No	Yes
TX PRU (Transmit PRU) cores	No	Yes
IRAM (per PRU / RTU_PRU / TX_PRU core)	Yes	Yes
DRAM (2 DRAMs per PRU-ICSS/PRU_ICSSG)	Yes	Yes
Shared DRAM	Yes	Yes
INTC	Yes	Yes
General Purpose Inputs		
Direct Input	Yes	Yes
16-bit Parallel Capture	Yes	Yes
28-bit Shift	Yes	Yes
3 Ch. Peripheral Interface (EnDAT)	Device dependent	Yes
9 Ch. Sigma Delta	Device dependent	Yes
General Purpose Outputs		
Direct Output	Yes	Yes
Shift out	Yes	Yes
Accelerators: Data Processing		
MPY/MAC	Yes	Yes
CRC 16/32	Device dependent	Yes
Scratch Pad	Yes	Yes
IPC Scratch Pad	No	Yes
Broadside RAM	No	Yes
BSWAP	No	Yes
SUM32	No	Yes
Task Manager	No	Yes
Spinlock	No	Yes
Filter Data Base (FDB)	No	Yes
Accelerators: Data Movement		
XFR2VBUS	No	Yes
PSI TX & RX	No	Yes
XFR2TR	No	Yes
Peripherals		
UART	Yes	Yes
eCAP	Yes	Yes
IEP	Yes	Yes
MII_RT or MII_G_RT	Yes (MII)	Yes (MII/RGMII)
MDIO	Yes	Yes
SGMII	No	Yes
PWM	No	Yes

2 PRU-ICSS Feature Comparison

Table 2. PRU-ICSS Feature Comparison

Features	AM335x	AM437x		AM570x	AM571x	AM572x	AM574x	K2G
	PRU-ICSS1	PRU-ICSS1	PRU-ICSS0	2x PRU-ICSS ⁽¹⁾	2x PRU-ICSS ⁽¹⁾	2x PRU-ICSS ⁽¹⁾	2x PRU-ICSS ⁽¹⁾	2x PRU-ICSS ⁽¹⁾
Number of PRU cores	2	2	2	2	2	2	2	2
Max Frequency	200 MHz	225 MHz ⁽²⁾	225 MHz ⁽²⁾	200 MHz	200 MHz	200 MHz	200 MHz	200 MHz
IRAM size (per PRU core)	8 KB	12 KB	4 KB	12 KB	12 KB	12 KB	12 KB	16 KB
DRAM size (2 DRAMs per PRU-ICSS)	8 KB	8 KB	4 KB	8 KB	8 KB	8 KB	8 KB	8 KB
Shared DRAM size	12 KB	32 KB	0 KB	32KB	32KB	32KB	32 KB	64KB w/ ECC
General Purpose Input (per PRU core)	Direct; or 16-bit parallel capture; or 28-bit shift	Direct; or 16-bit parallel capture; or 28-bit shift; or 3ch EnDat 2.2; or 9ch Sigma Delta	Direct; or 16-bit parallel capture; or 28-bit shift; or 3ch EnDat 2.2; or 9ch Sigma Delta	Direct; or 16-bit parallel capture; or 28-bit shift; or 3ch EnDat 2.2; or 9ch Sigma Delta	Direct; or 16-bit parallel capture; or 28-bit shift; or 3ch EnDat 2.2; or 9ch Sigma Delta	Direct; or 16-bit parallel capture; or 28-bit shift	Direct; or 16-bit parallel capture; or 28-bit shift; or 3ch EnDat 2.2; or 9ch Sigma Delta	Direct; or 16-bit parallel capture; or 28-bit shift; or 3ch EnDat 2.2; or 9ch Sigma Delta
General Purpose Output (per PRU core)	Direct; or Shift out	Direct; or Shift out	Direct; or Shift out	Direct; or Shift out	Direct; or Shift out	Direct; or Shift out	Direct; or Shift out	Direct; or Shift out
GPI Pins (PRU0, PRU1)	17, 17	13, 0	20, 20	0/21 ⁽³⁾ , 21/17	0/21 ⁽³⁾ , 21/21	21, 21	21, 21	20, 20
GPO Pins (PRU0, PRU1)	16, 16	12, 0	20, 20	0/21 ⁽³⁾ , 21/17	0/21 ⁽³⁾ , 21/21	21, 21	21, 21	20, 20
MPY/MAC	Y	Y	Y	Y	Y	Y	Y	Y
Scratchpad	Y (3 banks)	Y (3 banks)	N	Y (3 banks)	Y (3 banks)	Y (3 banks)	Y (3 banks)	Y (3 banks)
CRC16/32	0	2	2	2	2	2 ⁽⁴⁾	2	2
INTC	1	1	1	1	1	1	1	1
Peripherals								
UART	1	1	1	1 / not pinned out ⁽⁵⁾	1	1	1	1
eCAP	1	1	not pinned out	1 / not pinned out ⁽⁵⁾	1	1	1	1
IEP	1	1	not pinned out	1 / not pinned out ⁽⁵⁾	1	1	1	1
MII_RT	2	2	not pinned out	2	2	2	2	2
MDIO	1	1	not pinned out	1	1	1	1	1

- (1) The name PRU-ICSS and PRUSS are used interchangeably throughout the AM57xx and K2G documentation to describe the Programmable Real-Time Unit (PRU) and Industrial Communication Subsystem.
- (2) The default frequency for AM437x is 200 MHz. However, the max frequency 225 MHz is achievable through display PLL CLKOUT. For DSS limitations when configuring this PLL for frequencies >200 MHz, see the [AM437x Sitara Processors Technical Reference Manual](#).
- (3) AM571x and AM570x PRU-ICSS1 does not pin out the PRU0 core GPIs/GPOs. The other AM571x and AM570x PRU cores (PRU-ICSS1 PRU1, PRU-ICSS2 PRU0, PRU-ICSS2 PRU1) each pin out the number of GPIs/GPOs is listed in [Table 2](#).
- (4) AM572x SR1.1 does not have CRC16/32. Within the AM57x family, this feature is only available in AM572x SR2.0, AM571x, and AM570x.
- (5) AM570x PRU-ICSS2 does not pin out these submodules. However, they are pinned out on the other AM570x subsystem (PRU-ICSS1).

3 PRU_ICSSG Feature Comparison

Table 3. PRU_ICSSG Feature Comparison Across Devices

Feature	AM65x SR1.0	AM65x SR2.0
	3x PRU_ICSSG	
Number of PRU cores	2	
Number of RTU_PRU (Auxiliary PRU) cores	2	
Number of TX_PRU (Transmit PRU) cores	0	2
Max Frequency	250 MHz	
IRAM Size (per PRU / RTU_PRU / TX_PRU core)	12 KB / 8 KB (w/ ECC) / 0 KB	12 KB / 8 KB (w/ ECC) / 6 KB (w/ ECC)
DRAM Size (2 DRAMs per PRU_ICSSG)	8 KB (w/ ECC)	
Shared DRAM Size	64 KB (w/ ECC)	
INTC	Yes	
General Purpose Inputs (per PRU core)	Direct; or 16-bit parallel capture; or 28-bit shift; or 3ch EnDat 2.2; or 9ch Sigma Delta	
General Purpose Outputs (per PRU core)	Direct; or Shift out	
GPI Pins (PRU0, PRU1)	PRU_ICSSG0: 19/19	
	PRU_ICSSG1: 19/19	
	PRU_ICSSG2: 17/17	
GPO Pins (PRU0, PRU1)	PRU_ICSSG0: 19/19	
	PRU_ICSSG1: 19/19	
	PRU_ICSSG2: 17/17	
Accelerators: Data Processing		
MPY/MAC	Yes	
CRC 16/32	Yes	
Scratch Pad	Yes (PRU cores: 4 banks, RTU_PRU cores: 2 banks)	Yes (PRU cores: 3 banks, RTU_PRU cores: 3 banks, TX_PRU0 core: 1 bank, TX_PRU1 core: 1 bank)
IPC Scratch Pad	Yes	
Broadside RAM	4 KB	
BSWAP	Yes	
SUM32	Yes	
Task Manager	Yes	
Spinlock	Yes	
Filter Data Base (FDB)	Yes	
Accelerators: Data Movement		
XFR2VBUS	Yes	
PSI TX & RX	Yes	
XFR2TR	Yes	
Peripherals		
UART	1	
eCAP	1	
IEP	2	
MII_G_RT (MII/RGMII)	2	
MDIO	1	
SGMII	2 (PRU_ICSSG2 instance only)	
PWM	12 primary and 12 complimentary outputs	

4 References

- [AM437x Sitara Processors Technical Reference Manual](#)
- [PRU-ICSS/PRU_ICSSG Migration Guide](#)

Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

Changes from C Revision (December 2018) to D Revision	Page
• Updated PRU-ICSS and PRU_ICSSG Feature Comparison table.	2
• Updated PRU_ICSSG Feature Comparison Across Devices table.	4

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (www.ti.com/legal/termsofsale.html) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2020, Texas Instruments Incorporated