

## **CC1101+CC1190 600 kbps Data Rate, +19 dBm Transmit Power without FHSS in 902-928 MHz Frequency Band**

By Sverre Hellan

---

### **Keywords**

- *FCC Section 15.247*
- *Digital Modulation*
- *FHSS*
- *4-FSK*
- *+19 dBm Output Power*
- *CC1101*
- *CC1100*
- *CC1110*
- *CC1111*
- *CC430*
- *CC1190*

### **1 Introduction**

In the 902-928 MHz ISM band, FCC Section 15.247 specifies requirements that allows for up to 1 W transmit output power.

High output power can be used if the system employs Frequency Hopping Spread Spectrum (FHSS) or use a digital modulation technique that gives a 6 dB bandwidth of minimum 500 kHz [1], [6].

The CC1101 transceiver together with the CC1190 range extender can be set up with 4-FSK modulation. This digital modulation technique allows the combined CC1101 and CC1190 solution to comply with Section 15.247 requirements with a +19 dBm (79 mW) transmit output power without the need frequency hopping.

In this design note the data rate is set to 600 kbps using 4-FSK modulation.

Design Note DN006 [7] shows how CC1101 can be configured for 2-ary modulation formats and meet requirements for digital modulation systems defined under FCC Section 15.247.

The CC1101-CC1190EM 915 MHz reference design [4] is used as an example in this design note, but the results are also applicable if CC1101 is replaced with CC1100, CC1110, CC1111, or CC430 as they use the same radio as the CC1101.

## **Table of Contents**

KEYWORDS.....	1
1 INTRODUCTION.....	1
2 ABBREVIATIONS.....	2
3 FCC 15.247 DIGITAL MODULATION REQUIREMENTS.....	3
4 FCC 15.247 MEASUREMENT SETUP.....	3
5 FCC 15.247 MEASUREMENT RESULTS.....	4
6 CONCLUSION.....	4
7 REFERENCES.....	5
8 GENERAL INFORMATION.....	5
8.1 DOCUMENT HISTORY.....	5
9 APPENDIX.....	6

## **2 Abbreviations**

EM	Evaluation Module
FCC	Federal Communications Commission
FHSS	Frequency hopping Spread Spectrum
ISM	Industrial, Scientific, Medical
PSD	Power Spectral Density
RBW	Resolution Bandwidth
VBW	Video Bandwidth

## 3 FCC 15.247 Digital Modulation Requirements

Table 1 gives the FCC 15.247 digital modulation requirements.

Section	Requirement
15.247a2	The 6 dB bandwidth shall be at least 500 kHz
15.247b3	The maximum conducted power shall not exceed 1 W (+30 dBm)
15.247e	The power spectral density (PSD) shall not be greater than 8 dBm in any 3 kHz band during any time interval during continuous transmission

**Table 1. FCC 15.247 Digital Modulation Requirements [6]**

## 4 FCC 15.247 Measurement Setup

- All measurements were performed at 3V, 25°C
- Measurements were performed on the CC1101-CC1190EM 915 MHz reference design [4]
- Rohde & Schwarz FSEM spectrum analyzer was used in the measurements
- Results presented are the average values of 6 modules
- Register settings used are given in the appendix. It is recommended to increase the CC1101 loop filter BW when operating at 600 kbps, 4-FSK. This is achieved by setting FIFOTHR[7] = 1 and TEST2[1] = 1. (Note: for CC1110 the settings are MCSM0[3] = 1 and TEST2[1] = 1).

Table 2 gives the CC1101 system parameters used in the tests.

System Parameter	Value	Comment
RF Frequency	915 MHz	
Output Power	Up to +20 dBm	Different CC1101 PATABLE settings
Modulation Format	4-FSK	MDMCFG2.MOD_FORMAT = 4 [1]
Data Rate	600 kbps	Corresponds to 300 kBaud
Frequency Deviation	228 kHz	'01' - Deviation '00' - 1/3· Deviation '10' + 1/3· Deviation '11' + Deviation
RX Filter Bandwidth	812 kHz	

**Table 2. CC1101 System Parameters Used in the Tests**

Table 3 gives the spectrum analyzer settings used in the tests.

Requirement	RBW	VBW	Comment
6 dB Bandwidth	100 kHz	1 MHz	
Output Power	3 MHz	3 MHz	
PSD	3 kHz	100 kHz	Span 1.5 MHz Sweep time of 500 s Max hold Peak detector

**Table 3. Spectrum Analyzer Settings Used in the Measurements [6]**

## 5 FCC 15.247 Measurement Results

Table 4 gives the measurement results.

CC1101 PATABLE	6 dB Bandwidth [kHz]	Output Power [dBm]	PSD [dBm/3 kHz]	Sensitivity [dBm]
0x2B	718	18.0	6.6	-95.2
0x2C	717	18.5	7.2	
0x2D	717	18.9	7.7	
0x39	717	19.3	7.9	

**Table 4. Typical CC1101-CC1190 FCC 15.247 Measurement Results**

See Application Note AN096 [5] for more performance figures for the CC1101-CC1190EM 915 MHz reference design.

## 6 Conclusion

The CC1101+CC1190 combination is suited for systems targeting compliance with digital modulation systems defined under FCC Section 15.247. The combined CC1101 and CC1190 solution complies with Section 15.247 requirements with a +19 dBm transmit output power without the need frequency hopping.

The link budget, assuming 0 dB antenna gain, is up to 114 dB when operating the CC1101+CC1190 design at 600 kbps, 4-FSK.

## **7 References**

- [1] FCC rules (www.fcc.gov)
- [2] CC1101 Data Sheet (SWRS061.pdf)
- [3] CC1190 Datasheet (SWRS089.pdf)
- [4] CC1101–CC1190EM 915 MHz Reference Design (SWRR077.zip)
- [5] Using the CC1190 Front End with CC1101 under FCC 15.247 (SWRA361.pdf)
- [6] Measurement of Digital Transmission Systems Operating under Section 15.247
- [7] DN006 CC11xx Settings for FCC 15.247 Solutions (SWRA123.pdf)

## **8 General Information**

### **8.1 Document History**

<b>Revision</b>	<b>Date</b>	<b>Description/Changes</b>
SWRR078	2011.05.11	Initial release.
SWRR078A	2011.11.07	Added information in section 4 on how to increase CC1110 loop filter bandwidth

## 9 Appendix

Register settings used in the test.

IOCFG2	2F	LNA off
IOCFG1	2E	
IOCFG0	6F	PA on
FIFOTHR	87	TX: 0x87. RX: 0x07
SYNC1	D3	
SYNC0	91	
PKTLEN	14	
PKTCTRL1	4	
PKTCTRL0	22	
ADDR	0	
CHANNR	0	
FSCTRL1	D	
FSCTRL0	0	
FREQ2	21	
FREQ1	62	
FREQ0	76	
MDMCFG4	0D	300 kBaud, 812 kHz RX BW
MDMCFG3	7A	
MDMCFG2	43	4FSK
MDMCFG1	22	
MDMCFG0	F8	
DEVIATN	71	228 kHz
MCSM2	7	
MCSM1	30	
MCSM0	18	
FOCCFG	1D	
BSCFG	1C	
AGCCTRL2	C7	
AGCCTRL1	0	
AGCCTRL0	B0	
WOREVT1	87	
WOREVT0	6B	
WORCTRL	FB	
FREND1	B6	
FREND0	10	
FSCAL3	EA	
FSCAL2	2A	
FSCAL1	0	
FSCAL0	1F	
RCCTRL1	41	
RCCTRL0	0	
FSTEST	59	
PTEST	7F	
AGCTEST	3F	
TEST2	8A	TX: 0x8A. RX: 0x88
TEST1	31	
TEST0	9	
# PATABLE	39	

## IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

### Products

Audio	<a href="http://www.ti.com/audio">www.ti.com/audio</a>
Amplifiers	<a href="http://amplifier.ti.com">amplifier.ti.com</a>
Data Converters	<a href="http://dataconverter.ti.com">dataconverter.ti.com</a>
DLP® Products	<a href="http://www.dlp.com">www.dlp.com</a>
DSP	<a href="http://dsp.ti.com">dsp.ti.com</a>
Clocks and Timers	<a href="http://www.ti.com/clocks">www.ti.com/clocks</a>
Interface	<a href="http://interface.ti.com">interface.ti.com</a>
Logic	<a href="http://logic.ti.com">logic.ti.com</a>
Power Mgmt	<a href="http://power.ti.com">power.ti.com</a>
Microcontrollers	<a href="http://microcontroller.ti.com">microcontroller.ti.com</a>
RFID	<a href="http://www.ti-rfid.com">www.ti-rfid.com</a>
OMAP Mobile Processors	<a href="http://www.ti.com/omap">www.ti.com/omap</a>
Wireless Connectivity	<a href="http://www.ti.com/wirelessconnectivity">www.ti.com/wirelessconnectivity</a>

### Applications

Communications and Telecom	<a href="http://www.ti.com/communications">www.ti.com/communications</a>
Computers and Peripherals	<a href="http://www.ti.com/computers">www.ti.com/computers</a>
Consumer Electronics	<a href="http://www.ti.com/consumer-apps">www.ti.com/consumer-apps</a>
Energy and Lighting	<a href="http://www.ti.com/energy">www.ti.com/energy</a>
Industrial	<a href="http://www.ti.com/industrial">www.ti.com/industrial</a>
Medical	<a href="http://www.ti.com/medical">www.ti.com/medical</a>
Security	<a href="http://www.ti.com/security">www.ti.com/security</a>
Space, Avionics and Defense	<a href="http://www.ti.com/space-avionics-defense">www.ti.com/space-avionics-defense</a>
Transportation and Automotive	<a href="http://www.ti.com/automotive">www.ti.com/automotive</a>
Video and Imaging	<a href="http://www.ti.com/video">www.ti.com/video</a>

TI E2E Community Home Page

[e2e.ti.com](http://e2e.ti.com)

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2011, Texas Instruments Incorporated