

### PMP2260\_REVA BOM

COUNT	RefDes	VALUE	Description	Size	Part Number	MFR
1	C1	{Value}	Capacitor, Aluminum, xxV, 20%	0.260 x 0.276 in	EEVFKxyyyD	Panasonic
4	C2	10uF	Capacitor, Ceramic, 10uF, 25V, BJ M	1210	C3225JB1E106	TDK
	C3	10uF	Capacitor, Ceramic, 10uF, 25V, BJ M	1210	C3225JB1E106	TDK
	C4	10uF	Capacitor, Ceramic, 10uF, 25V, BJ M	1210	C3225JB1E106	TDK
	C5	10uF	Capacitor, Ceramic, 10uF, 25V, BJ M	1210	C3225JB1E106	TDK
2	C6	0.1uF	Capacitor, Ceramic, 50V, BJ, 20%	0805	Std	Std
3	C7	330uF	Capacitor, PS, 330-uF, 2.5-V, 15-milliohm, 20%	7343 (D)	2R5TPE330MF	SANYO
	C8	330uF	Capacitor, PS, 330-uF, 2.5-V, 15-milliohm, 20%	7343 (D)	2R5TPE330MF	SANYO
	C9	330uF	Capacitor, PS, 330-uF, 2.5-V, 15-milliohm, 20%	7343 (D)	2R5TPE330MF	SANYO
	C11	0.1uF	Capacitor, Ceramic, 50V, BJ, 20%	0805	Std	Std
3	C13	330uF	Capacitor, PS, 330-uF, 2.5-V, 18-milliohm, 20%	7343 (D)	2R5TPE330MI	SANYO
	C14	330uF	Capacitor, PS, 330-uF, 2.5-V, 18-milliohm, 20%	7343 (D)	2R5TPE330MI	SANYO
1	C15	4.7uF	Capacitor, Ceramic, 6.3V, BJ, 20%	0805	Std	Std
3	C16	1uF	Capacitor, Ceramic, 6.3V, BJ, 20%	0805	Std	Std
	C18	1uF	Capacitor, Ceramic, 6.3V, BJ, 20%	0805	Std	Std
	C19	1uF	Capacitor, Ceramic, 6.3V, BJ, 20%	0805	Std	Std
	C20	330uF	Capacitor, PS, 330-uF, 2.5-V, 18-milliohm, 20%	7343 (D)	2R5TPE330MI	SANYO
2	D1		Diode, Schottky, 0.5A, 30V	SOD-123	Any	Any
	D2		Diode, Schottky, 0.5A, 30V	SOD-123	Any	Any
2	J1	{value}	Terminal Block, 2-pin, 32-A, 9.5mm	0.75 x 0.49 in	ED1981	OST
	J2	{value}	Terminal Block, 2-pin, 32-A, 9.5mm	0.75 x 0.49 in	ED1981	OST
1	J3	ED1515	Terminal Block, 3-pin, 6-A, 3.5mm	0.41 x 0.25 in	ED1515	OST
1	JP1	PTC36DAAN	Header, 2x3-pin, 100mil spacing (36-pin strip)	0.20 inch x 0.30	PTC36DAAN	Sullins
2	L1	0.47uH	Inductor, SMT, 32A, 2milliohm	0.51 x 0.51 in	IHL5050	Vishay
	L2	0.47uH	Inductor, SMT, 32A, 2milliohm	0.51 x 0.51 in	IHL5050	Vishay
6	Q2	Si7392ADP	MOSFET, NChannel, 30V, 17.5A, 7.5milliohm	PWRPAK S0-8	Si7392ADP	Vishay
	Q5	Si7392ADP	MOSFET, NChannel, 30V, 17.5A, 7.5milliohm	PWRPAK S0-8	Si7392ADP	Vishay
	Q6	Si7392ADP	MOSFET, NChannel, 30V, 17.5A, 7.5milliohm	PWRPAK S0-8	Si7392ADP	Vishay
	Q7	Si7392ADP	MOSFET, NChannel, 30V, 17.5A, 7.5milliohm	PWRPAK S0-8	Si7392ADP	Vishay
	Q8	Si7392ADP	MOSFET, NChannel, 30V, 17.5A, 7.5milliohm	PWRPAK S0-8	Si7392ADP	Vishay
	Q9	Si7392ADP	MOSFET, NChannel, 30V, 17.5A, 7.5milliohm	PWRPAK S0-8	Si7392ADP	Vishay
2	R1	100K	Resistor, Chip, 1/10W, 1%	0805	Std	Std
3	R2	3.3	Resistor, Chip, 1/10W, 1%	0805	Std	Std
1	R3	28.7K	Resistor, Chip, 1/10W, 1%	0805	Std	Std
2	R4	75K	Resistor, Chip, 1/10W, 1%	0805	Std	Std
1	R5	73.2K	Resistor, Chip, 1/10W, 1%	0805	Std	Std
	R6	75K	Resistor, Chip, 1/10W, 1%	0805	Std	Std
	R7	100K	Resistor, Chip, 1/10W, 1%	0805	Std	Std
2	R8	10K	Resistor, Chip, 1/10W, 1%	0805	Std	Std
	R9	3.3	Resistor, Chip, 1/10W, 1%	0805	Std	Std
	R10	3.3	Resistor, Chip, 1/10W, 1%	0805	Std	Std
	R11	10K	Resistor, Chip, 1/10W, 1%	0805	Std	Std
2	SW1	G-12AP	Switch, ON-ON Mini Toggle	0.28 x 0.18"	G12AP	Nikkai
	SW2	G-12AP	Switch, ON-ON Mini Toggle	0.28 x 0.18"	G12AP	Nikkai
2	TP1	LC-2-S	Pin, Probe monitor	0.12(D) X 0.4 in	LC-2-S	MAC8
	TP2	LC-2-S	Pin, Probe monitor	0.12(D) X 0.4 in	LC-2-S	MAC8
1	U1	TPS51124RGE	IC, Dual Synchronous Step-Down Controller For Lc	QFN-24	TPS51124RGE	TI
	VIN_GND2	3138-2	Pin, Wiring Terminal	0.09(D) X 0.31 in	3138-2-00-15-00-0	Mill Max
2	VIN2	3138-2	Pin, Wiring Terminal	0.09(D) X 0.31 in	3138-2-00-15-00-0	Mill Max

- Notes:
1. These assemblies are ESD sensitive, ESD precautions shall be observed.
  2. These assemblies must be clean and free from flux and all contaminants.  
Use of no clean flux is not acceptable.
  3. These assemblies must comply with workmanship standards IPC-A-610 Class 2.
  4. Ref designators marked with an asterisk ("\*\*") cannot be substituted.  
All other components can be substituted with equivalent MFG's components.

## IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

### Products

Audio	<a href="http://www.ti.com/audio">www.ti.com/audio</a>
Amplifiers	<a href="http://amplifier.ti.com">amplifier.ti.com</a>
Data Converters	<a href="http://dataconverter.ti.com">dataconverter.ti.com</a>
DLP® Products	<a href="http://www.dlp.com">www.dlp.com</a>
DSP	<a href="http://dsp.ti.com">dsp.ti.com</a>
Clocks and Timers	<a href="http://www.ti.com/clocks">www.ti.com/clocks</a>
Interface	<a href="http://interface.ti.com">interface.ti.com</a>
Logic	<a href="http://logic.ti.com">logic.ti.com</a>
Power Mgmt	<a href="http://power.ti.com">power.ti.com</a>
Microcontrollers	<a href="http://microcontroller.ti.com">microcontroller.ti.com</a>
RFID	<a href="http://www.ti-rfid.com">www.ti-rfid.com</a>
RF/IF and ZigBee® Solutions	<a href="http://www.ti.com/lprf">www.ti.com/lprf</a>

### Applications

Communications and Telecom	<a href="http://www.ti.com/communications">www.ti.com/communications</a>
Computers and Peripherals	<a href="http://www.ti.com/computers">www.ti.com/computers</a>
Consumer Electronics	<a href="http://www.ti.com/consumer-apps">www.ti.com/consumer-apps</a>
Energy and Lighting	<a href="http://www.ti.com/energy">www.ti.com/energy</a>
Industrial	<a href="http://www.ti.com/industrial">www.ti.com/industrial</a>
Medical	<a href="http://www.ti.com/medical">www.ti.com/medical</a>
Security	<a href="http://www.ti.com/security">www.ti.com/security</a>
Space, Avionics and Defense	<a href="http://www.ti.com/space-avionics-defense">www.ti.com/space-avionics-defense</a>
Transportation and Automotive	<a href="http://www.ti.com/automotive">www.ti.com/automotive</a>
Video and Imaging	<a href="http://www.ti.com/video">www.ti.com/video</a>
Wireless	<a href="http://www.ti.com/wireless-apps">www.ti.com/wireless-apps</a>

TI E2E Community Home Page

[e2e.ti.com](http://e2e.ti.com)

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2011, Texas Instruments Incorporated