

PMP22288 REV A Bill of Materials

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
!PCB1	1		PMP22288	Any	Printed Circuit Board	
C1, C2	2	0.022uF	C1206C223KDRACU	Kemet	CAP, CERM, 0.022 μ F, 1000 V, +/- 10%, X7R, AEC-Q200 Grade 1, 1206	1206
C3, C4	2	1uF	GRM188R71E105KA12D	MuRata	CAP, CERM, 1 uF, 25 V, +/- 10%, X7R, 0603	0603
C5, C10	2	10uF	ULV2G100MNL1GS	Nichicon	CAP, AL, 10 uF, 400 V, +/- 20%, SMD	D10xL13.5mm
C6, C7	2	390uF	EEU-FC1V391S	Panasonic	CAP, AL, 390 μ F, 35 V, +/- 20%, AEC-Q200 Grade 2, TH	12.5x15mm
C8	1	0.1uF	C0603C104K5RACAUTO	Kemet	CAP, CERM, 0.1 μ F, 50 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0603	0603
C11	1	10uF	CGA5L1X7R1V106K160AC	TDK	CAP, CERM, 10 uF, 35 V, +/- 10%, X7R, AEC-Q200 Grade 1, 1206_190	1206_190
C12	1	100pF	CGA3E2NP01H101J080AA	TDK	CAP, CERM, 100 pF, 50 V, +/- 5%, C0G/NP0, AEC-Q200 Grade 0, 0603	0603
D1	1	200V	MBRD20200CT-13	Diodes Inc.	Diode, Schottky, 200 V, 10 A, AEC-Q101, DPAK	DPAK
D2	1	200V	1SMB5956BT3G	ON Semiconductor	Diode, Zener, 200 V, 550 mW, SMB	SMB
D3	1	1300V	EGF1T-E3/67A	Vishay-Semiconductor	Diode, Ultrafast, 1300 V, 1 A, AEC-Q101, DO-214BA	DO-214BA
D4, D5	2	100V	B1100B-13-F	Diodes Inc.	Diode, Schottky, 100 V, 1 A, SMB	SMB
D6	1	20V	DDZ20CQ-7	Diodes Inc.	Diode, Zener, 20 V, 500 mW, AEC-Q101, SOD-123	SOD-123
J1, J2	2		ED120/2DS	On-Shore Technology	Terminal Block, 5.08 mm, 2x1, Brass, TH	2x1 5.08 mm Terminal Block
Q1	1		STD3N95K5AG	STMicroelectronics	N-Channel 950V 2A (Tc) 45W (Tc) Surface Mount DPAK	DPAK
R1	1	0	CRCW12060000Z0EA	Vishay-Dale	RES, 0, 5%, 0.25 W, AEC-Q200 Grade 0, 1206	1206
R2, R3, R5, R6	4	1.00Meg	CRCW12061M00FKEA	Vishay-Dale	RES, 1.00 M, 1%, 0.25 W, AEC-Q200 Grade 0, 1206	1206
R7	1	23.2k	CRCW060323K2FKEA	Vishay-Dale	RES, 23.2 k, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603
R8	1	1.69k	CRCW06031K69FKEA	Vishay-Dale	RES, 1.69 k, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603
R9	1	1.02k	CRCW06031K02FKEA	Vishay-Dale	RES, 1.02 k, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603
R10	1	8.66k	CRCW06038K66FKEA	Vishay-Dale	RES, 8.66 k, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603
R11	1	332k	CRCW0402332KFKED	Vishay-Dale	RES, 332 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402
R12	1	1.00	CSR1206FT1R00	Stackpole Electronics Inc	RES, 1.00, 1%, 0.5 W, 1206	1206
T1	1		B78311A2439A003	TDK	Flyback Transformer	SMD_TRANSFORMER_26MM0_22MM8
TP1, TP2	2		5000	Keystone	Test Point, Miniature, Red, TH	Red Miniature Testpoint
TP3	1		5001	Keystone	Test Point, Miniature, Black, TH	Black Miniature Testpoint
TP4	1		5011	Keystone	Test Point, Multipurpose, Black, TH	Black Multipurpose Testpoint
U1	1		UCC28730QDRQ1	Texas Instruments	Zero Standby PSR Flyback Controller with CVCC and Wake-Up Monitoring, Automotive, D0007A (SOIC-7)	D0007A
C9	0	0.01uF	CGA3E2X7R2A103K080AA	TDK	CAP, CERM, 0.01 uF, 100 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0603	0603
L1	0	470nH	784383350047	Würth Elektronik	Inductor, Shielded, Powdered Iron, 470 nH, 4.6 A, 0.023 ohm, AEC-Q200 Grade 1, SMD	SMD, 2-Leads, Body 3x3mm
R4	0	0	CRCW12060000Z0EA	Vishay-Dale	RES, 0, 5%, 0.25 W, AEC-Q200 Grade 0, 1206	1206

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (<https://www.ti.com/legal/termsofsale.html>) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2021, Texas Instruments Incorporated