

PMP10698 REV A Bill of Materials

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
IPCBA	1		PMP10624	Any	PMP10624	N/A
C1, C2, C5	3	0.22uF	C1608X7R1H224K080AB	TDK	CAP, CERM, 0.22uF, 50V, +/-10%, X7R, 0603	0603
C3, C10	2	100pF	GRM1885C1H101JA01D	MuRata	CAP, CERM, 100 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
C4, C15, C19, C20	4	0.1uF	06033C104JAT2A	AVX	CAP, CERM, 0.1 uF, 25 V, +/- 5%, X7R, 0603	0603
C6	1	1uF	GRM188R71C105KA12D	MuRata	CAP, CERM, 1uF, 16V, +/-10%, X7R, 0603	0603
C7	1	10uF	EMK212BB7106MG-T	Taiyo Yuden	CAP, CERM, 10 uF, 16 V, +/- 20%, X7R, 0805	0805
C8, C16	2	0.22uF	C1608X7R1H224K080AB	TDK	CAP, CERM, 0.22 uF, 50 V, +/- 10%, X7R, 0603	0603
C9, R7	2	0	CRCW06030000Z0EA	Vishay-Dale	RES, 0, 5%, 0.1 W, 0603	0603
C11	1	0.047uF	GRM188R71H473KA61D	MuRata	CAP, CERM, 0.047 uF, 50 V, +/- 10%, X7R, 0603	0603
C13	1	0.022uF	GRM188R71H223KA01D	MuRata	CAP, CERM, 0.022 uF, 50 V, +/- 10%, X7R, 0603	0603
C14, C17	2	220pF	GRM1885C1H221JA01D	MuRata	CAP, CERM, 220 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
C101, C102, C103, C104, Cin2, Cin3, Cin4, Co2, Co3, Co4	10	4.7uF	GRM31CR71H475KA12L	MuRata	CAP, CERM, 4.7 uF, 50 V, +/- 10%, X7R, 1206	1206
Cin1, Co1	2	68uF	EEE-FK1J680UP	Panasonic	CAP, AL, 68 uF, 63 V, +/- 20%, 0.65 ohm, SMD	SMT Radial F
D1	1	30V	BAT54HT1G	ON Semiconductor	Diode, Schottky, 30V, 0.2A, SOD-323	SOD-323
D2, D3	2	100V	BAS516,115	NXP Semiconductor	Diode, Switching, 100V, 0.25A, SOD-523	SOD-523
H1, H2, H3, H4	4		NY PMS 440 0025 PH	B&F Fastener Supply	Machine Screw, Round, #4-40 x 1/4, Nylon, Philips panhead	Screw
H5, H6, H7, H8	4		1902C	Keystone	Standoff, Hex, 0.5"L #4-40 Nylon	Standoff
J1, J2, J3, J4	4		575-4	Keystone	Standard Banana Jack, Uninsulated, 5.5mm	Keystone_575-4
J5	1		PEC05DAAN	Sullins Connector Solutions	Header, 100mil, 5x2, Tin, TH	Header, 5x2, 100mil, Tin
J6	1		PEC02SAAN	Sullins Connector Solutions	Header, 100mil, 2x1, Tin, TH	Header, 2 PIN, 100mil, Tin
J7	1		PEC04DAAN	Sullins Connector Solutions	Header, 100mil, 4x2, Tin, TH	Header, 4x2, 100mil, Tin
L1	1	4.7uH	7443320470	Würth Elektronik	Inductor, Shielded Drum Core, Ferrite, 4.7 uH, 15.5 A, 0.0064 ohm, SMD	12.1x9.5x11.4mm
Q1, Q2, Q3, Q4	4	60V	BSZ042N06NS	Infineon Technologies	MOSFET, N-CH, 60 V, 17 A, PG-TSDSON-8	PG-TSDSON-8
Q5	1	60V	2N7002-7-F	Diodes Inc.	MOSFET, N-CH, 60 V, 0.17 A, SOT-23	SOT-23
R1	1	130k	CRCW0603130KJNEA	Vishay-Dale	RES, 130 k, 5%, 0.1 W, 0603	0603
R2, R3, R5, R6	4	10	CRCW060310R0JNEA	Vishay-Dale	RES, 10, 5%, 0.1 W, 0603	0603
R4	1	23.7k	CRCW060323K7FKEA	Vishay-Dale	RES, 23.7 k, 1%, 0.1 W, 0603	0603
R8	1	1.0	CRCW06031R00JNEA	Vishay-Dale	RES, 1.0, 5%, 0.1 W, 0603	0603
R9	1	20k	CRCW060320K0JNEA	Vishay-Dale	RES, 20 k, 5%, 0.1 W, 0603	0603
R10	1	3.3k	CRCW06033K30JNEA	Vishay-Dale	RES, 3.3 k, 5%, 0.1 W, 0603	0603
R11, R21	2	49.9k	CRCW060349K9FKEA	Vishay-Dale	RES, 49.9 k, 1%, 0.1 W, 0603	0603
R12	1	64.9k	CRCW060364K9FKEA	Vishay-Dale	RES, 64.9 k, 1%, 0.1 W, 0603	0603
R13, R15	2	100	CRCW0603100RFKEA	Vishay-Dale	RES, 100, 1%, 0.1 W, 0603	0603
R14	1	100k	CRCW0603100KJNEA	Vishay-Dale	RES, 100 k, 5%, 0.1 W, 0603	0603
R16, R17, RH2, RL1, RL2	5	0	CRCW06030000Z0EA	Vishay-Dale	RES, 0 ohm, 5%, 0.1W, 0603	0603
R18	1	47	CRCW060347R0JNEA	Vishay-Dale	RES, 47, 5%, 0.1 W, 0603	0603
R19	1	2.87k	CRCW06032K87FKEA	Vishay-Dale	RES, 2.87 k, 1%, 0.1 W, 0603	0603
R20	1	2.80k	CRCW06032K80FKEA	Vishay-Dale	RES, 2.80 k, 1%, 0.1 W, 0603	0603
R22, R23	2	2.49k	CRCW06032K49FKEA	Vishay-Dale	RES, 2.49 k, 1%, 0.1 W, 0603	0603
R24	1	9.53k	CRCW06039K53FKEA	Vishay-Dale	RES, 9.53 k, 1%, 0.1 W, 0603	0603

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
RH1	1	3.0	CRCW06033R00JNEA	Vishay-Dale	RES, 3.0, 5%, 0.1 W, 0603	0603
RS1	1	0.008	PMR50HZPFU8L00	Rohm	RES, 0.008, 1%, 1 W, 2010	2010
RS2	1	0.006	ERJ-M1WSF6M0U	Panasonic	RES, 0.006, 1%, 1 W, 2512	2512
TP1, TP2	2	Red	5000	Keystone	Test Point, TH, Miniature, Red	Keystone5000
TP3, TP4	2	Black	5001	Keystone	Test Point, TH, Miniature, Black	Keystone5001
TP5, TP6, TP7, TP8, TP10, TP11	6	White	5002	Keystone	Test Point, Miniature, White, TH	White Miniature Testpoint
TP9, TP12, TP13	3	Triple	1598-2	Keystone	Terminal, Turret, TH, Triple	Keystone1598-2
U1	1		LM5175PWP	Texas Instruments	42V Wide VIN 4-Switch Synchronous Buck-Boost Controller, PWP0028F	PWP0028F
U2	1		LM2936MX-3.3	Texas Instruments	Ultra-Low Quiescent Current LDO Voltage Regulator, 8-pin Narrow SOIC	M08A
C12, C18	0	100pF	GRM1885C1H101JA01D	MuRata	CAP, CERM, 100pF, 50V, +/-5%, C0G/NP0, 0603	0603
FID1, FID2, FID3	0		N/A	N/A	Fiducial mark. There is nothing to buy or mount.	Fiducial

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. **TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design.** TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have **not** been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.