

DDC2256A 256 通道、电流输入模数转换器

1 特性

- 单芯片解决方案，可同时直接测量 256 个低电平电流
- 用户可调的满量程范围
- 可调整速度，积分时间短至 58.8 μ s（每条通道 17KSPS），24 位分辨率
- 每条通道的功耗低至 1.7mW
- 积分线性度： $\pm 0.025\%$ ， ± 1 ppm FSR（所有通道均处于活动状态）
- 低噪声
- 24 位 ADC
- 同时采样且无电荷损失
- 板载温度传感器
- 封装内置旁路电容和基准缓冲器，可减小 PCB 面积并降低设计复杂度
- 串行 LVDS 和 CMOS 输出接口选项

2 应用

- CT 扫描仪数据采集系统
- 发光二极管传感器
- X 射线检测系统
- 光纤功耗监测
- 多通道电流/电压仪表

3 说明

DDC2256A 是一款 24 位、256 通道、电流输入模数 (A/D) 转换器。该器件将电流电压积分和 A/D 转换完美结合，能够直接将 256 个单独的低电平电流输出器件（例如二极管）接至其输入端，从而并行（同时）实施数字化。

对于全部路输入，DDC2256A 都分别提供了一个低噪声/低功耗积分器，专用于捕捉传感器中的全部电荷。积分时间可在 58.8 μ s 到 100ms 范围内调整，从而允许以出色的精度连续测量 fA 到 μ A 级别的电流。积分器的输出通过十六个 24 位低功耗 ADC 进行数字化，生成的所有数据通过单个 LVDS 串行接口对输出，该接口经设计可最大限度减少高通道数应用中的噪声耦合。

DDC2256A 由 ± 2.5 V 模拟电源、1.8V 模拟电源 (AVDD_18) 以及 1.8V 数字电源 (DVDD) 供电运行。该器件的运行温度范围为 0°C 至 70°C，并且采用 14mm x 16mm² 323 焊球 0.8mm 间距 BGA 封装。最后，板载基准缓冲器和旁路电容有助于最大程度降低外部组件需求，从而进一步减小电路板空间。


更多信息，请点击德州仪器 (TI) 网站上 DDC2256A 页面的链接。

器件信息 (1)

部件号	封装	封装尺寸 (标称值)
DDC2256A	NFBGA (323)	16.0mm x 14.0mm

(1) 要了解所有可用封装，请见数据表末尾的可订购产品附录。

方框图



4 修订历史记录

注：之前版本的页码可能与当前版本有所不同。

Changes from Original (March 2016) to Revision A

Page

-
- 已从“产品预览”更改为“量产数据” 1
-

5 器件和文档支持

5.1 文档支持

《1A 超低噪声负电压稳压器》，[SBVS169](#)

5.2 社区资源

The following links connect to TI community resources. Linked contents are provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's [Terms of Use](#).

TI E2E™ Online Community *TI's Engineer-to-Engineer (E2E) Community*. Created to foster collaboration among engineers. At [e2e.ti.com](#), you can ask questions, share knowledge, explore ideas and help solve problems with fellow engineers.

Design Support *TI's Design Support* Quickly find helpful E2E forums along with design support tools and contact information for technical support.

5.3 商标

E2E is a trademark of Texas Instruments.

5.4 静电放电警告



这些装置包含有限的内置 ESD 保护。存储或装卸时，应将导线一起截短或将装置放置于导电泡棉中，以防止 MOS 门极遭受静电损伤。

5.5 Glossary

[SLYZ022](#) — *TI Glossary*.

This glossary lists and explains terms, acronyms, and definitions.


6 机械、封装和可订购信息

以下页中包括机械、封装和可订购信息。这些信息是针对指定器件可提供的最新数据。这些数据会在无通知且不对本文档进行修订的情况下发生改变。欲获得该数据表的浏览器版本，请查阅左侧的导航栏。

ZZF0323A

PACKAGE OUTLINE
NFBGA - 1.66 mm max height

BGA



NOTES:

1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.

PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan (2)	Lead finish/ Ball material (6)	MSL Peak Temp (3)	Op Temp (°C)	Device Marking (4/5)	Samples
DDC2256AZZF	ACTIVE	NFBGA	ZZF	323	84	RoHS & Green	Call TI SNAGCU	Level-3-260C-168 HR	0 to 70	DDC2256A	Samples

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) **RoHS:** TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (Cl) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

(3) MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

(4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

(5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

(6) Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer:The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

重要声明和免责声明

TI“按原样”提供技术和可靠性数据（包括数据表）、设计资源（包括参考设计）、应用或其他设计建议、网络工具、安全信息和其他资源，不保证没有瑕疵且不做任何明示或暗示的担保，包括但不限于对适销性、某特定用途方面的适用性或不侵犯任何第三方知识产权的暗示担保。

这些资源可供使用 TI 产品进行设计的熟练开发人员使用。您将自行承担以下全部责任：(1) 针对您的应用选择合适的 TI 产品，(2) 设计、验证并测试您的应用，(3) 确保您的应用满足相应标准以及任何其他功能安全、信息安全、监管或其他要求。

这些资源如有变更，恕不另行通知。TI 授权您仅可将这些资源用于研发本资源所述的 TI 产品的应用。严禁对这些资源进行其他复制或展示。您无权使用任何其他 TI 知识产权或任何第三方知识产权。您应全额赔偿因在这些资源的使用中对 TI 及其代表造成的任何索赔、损害、成本、损失和债务，TI 对此概不负责。

TI 提供的产品受 [TI 的销售条款](#) 或 [ti.com](#) 上其他适用条款/TI 产品随附的其他适用条款的约束。TI 提供这些资源并不会扩展或以其他方式更改 TI 针对 TI 产品发布的适用的担保或担保免责声明。

TI 反对并拒绝您可能提出的任何其他或不同的条款。

邮寄地址：Texas Instruments, Post Office Box 655303, Dallas, Texas 75265

Copyright © 2023，德州仪器 (TI) 公司