

CSD17381F4 30V N 沟道 FemtoFET™ MOSFET

1 特性


- 超低导通电阻
- 超低 Q_g 和 Q_{gd}
- 低阈值电压
- 超小封装尺寸 (0402 外壳尺寸)
 - 1.0mm × 0.6mm
- 超薄型封装
 - 厚度为 0.36mm
- 集成型 ESD 保护二极管
 - 额定值 > 4kV 人体放电模型 (HBM)
 - 额定值 > 2kV 充电器件模型 (CDM)
- 无铅且无卤素
- 符合 RoHS

2 应用

- 针对负载开关应用进行了优化
- 针对通用开关应用进行了优化
- 单节电池应用
- 手持式和移动类应用

3 说明

此 90mΩ、30V N 沟道 FemtoFET™ MOSFET 技术经过设计和优化，能更大程度减小在许多手持式和移动应用中的空间占用。这项技术能够在替代标准小信号 MOSFET 的同时将封装尺寸减小至少 60%。



典型尺寸

产品概要

$T_A = 25^\circ\text{C}$		典型值		单位
V_{DS}	漏源电压	30		V
Q_g	栅极电荷总量 (4.5V)	1040		pC
Q_{gd}	栅极电荷 (栅漏极)	133		pC
$R_{DS(on)}$	漏源导通电阻	$V_{GS} = 1.8\text{V}$	160	mΩ
		$V_{GS} = 2.5\text{V}$	110	mΩ
		$V_{GS} = 4.5\text{V}$	90	mΩ
$V_{GS(th)}$	阈值电压	0.85		V

订购信息


器件 ⁽¹⁾	数量	介质	封装	配送
CSD17381F4	3000	7 英寸卷带	Femto(0402) 1.0mm × 0.6mm 无引线表面贴装器件 (SMD)	卷带包装
CSD17381F4T	250			

- (1) 如需了解所有可用封装，请参阅数据表末尾的可订购产品附录。

绝对最大额定值

$T_A = 25^\circ\text{C}$ 时测得，除非另外注明		值	单位
V_{DS}	漏源电压	30	V
V_{GS}	栅源电压	12	V
I_D	持续漏极电流， $T_A = 25^\circ\text{C}$ 时测得 ⁽¹⁾	3.1	A
I_{DM}	脉冲漏极电流， $T_A = 25^\circ\text{C}$ ⁽²⁾	12	A
I_G	持续栅极钳位电流	35	mA
	脉冲栅极钳位电流 ⁽²⁾	350	
P_D	功率耗散 ⁽¹⁾	500	mW
ESD 等级	人体放电模型 (HBM)	4	kV
	充电器件模型 (CDM)	2	kV
T_J 、 T_{stg}	运行结温和贮存温度范围	-55 至 150	°C
E_{AS}	雪崩能量，单脉冲 $I_D = 7.4\text{A}$ ， $L = 0.1\text{mH}$ ， $R_G = 25\Omega$	2.7	mJ

- (1) 典型 $R_{\theta JA} = 90^\circ\text{C/W}$ (在 0.06 英寸 (1.52mm) 厚的 FR4 PCB 上安装 1 平方英寸 (6.45cm²)、2oz、0.071mm 厚的铜焊盘时)。
- (2) 脉冲持续时间 $\leq 100\mu\text{s}$ ，占空比 $\leq 1\%$ 。



顶视图



Table of Contents

1 特性	1	6.1 支持资源.....	7
2 应用	1	6.2 Trademarks.....	7
3 说明	1	6.3 Electrostatic Discharge Caution.....	7
4 Revision History	2	6.4 术语表.....	7
5 Specifications	3	7 Mechanical, Packaging, and Orderable Information	8
5.1 Electrical Characteristics.....	3	7.1 Mechanical Dimensions.....	8
5.2 Thermal Information.....	3	7.2 Recommended Minimum PCB Layout.....	9
5.3 Typical MOSFET Characteristics.....	4	7.3 Recommended Stencil Pattern.....	9
6 Device and Documentation Support	7		

4 Revision History

注：以前版本的页码可能与当前版本的页码不同

Changes from Revision F (October 2021) to Revision G (January 2022) Page

• 将特性中的高度尺寸从“0.35mm”更改为“0.36mm”	1
• 将典型尺寸中的高度尺寸从“0.35mm”更改为“0.36mm”	1
• Changed height dimension from "0.35 mm" to "0.36 mm" in <i>Mechanical Dimensions</i>	8

Changes from Revision E (December 2017) to Revision F (October 2021) Page

• 更新了整个文档的表、图和交叉参考的编号格式.....	1
• Changed footnote to refer to correct support document.....	9

Changes from Revision D (August 2014) to Revision E (December 2017) Page

• 将脉冲漏极电流值从 10A 更改为 12A (位于绝对最大额定值表格中)	1
• 将注释 2 从“脉冲持续时间 ≤ 300 μs , 占空比 ≤ 2%”更改为“脉冲持续时间 ≤ 100 μs , 占空比 ≤ 1%”	1
• Updated 图 5-1.	4
• Updated 图 5-10 with newly measured data.	4
• Updated all mechanical drawings, increased the size of the pads in 节 7.3	8

5 Specifications

5.1 Electrical Characteristics

(T_A = 25°C unless otherwise stated)

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT	
STATIC CHARACTERISTICS							
BV _{DSS}	Drain-to-Source Voltage	V _{GS} = 0 V, I _{DS} = 250 μA	30			V	
I _{DSS}	Drain-to-Source Leakage Current	V _{GS} = 0 V, V _{DS} = 24 V	100			nA	
I _{GSS}	Gate-to-Source Leakage Current	V _{DS} = 0 V, V _{GS} = 10 V	50			nA	
V _{GS(th)}	Gate-to-Source Threshold Voltage	V _{DS} = V _{GS} , I _{DS} = 250 μA	0.65	0.85	1.10	V	
R _{DS(on)}	Drain-to-Source On-Resistance	V _{GS} = 1.8 V, I _{DS} =0.5 A	160			250	mΩ
		V _{GS} = 2.5 V, I _{DS} =0.5 A	110			143	mΩ
		V _{GS} = 4.5 V, I _{DS} = 0.5 A	90			117	mΩ
		V _{GS} = 8 V, I _{DS} =0.5 A	84			109	mΩ
g _{fs}	Transconductance	V _{DS} = 15 V, I _{DS} = 0.5 A	4.8			S	
DYNAMIC CHARACTERISTICS							
C _{iss}	Input Capacitance	V _{GS} = 0 V, V _{DS} = 15 V, f = 1 MHz	150			195	pF
C _{oss}	Output Capacitance		44			57	pF
C _{rss}	Reverse Transfer Capacitance		2.2			2.9	pF
R _G	Series Gate Resistance		23				Ω
Q _g	Gate Charge Total (4.5 V)	V _{DS} = 15 V, I _{DS} = 0.5 A	1040			1350	pC
Q _{gd}	Gate Charge Gate-to-Drain		133				pC
Q _{gs}	Gate Charge Gate-to-Source		226				pC
Q _{g(th)}	Gate Charge at V _{th}		150				pC
Q _{oss}	Output Charge	V _{DS} = 15 V, V _{GS} = 0 V	1110				pC
t _{d(on)}	Turn On Delay Time	V _{DS} = 15 V, V _{GS} = 4.5 V, I _{DS} = 0.5 A,R _G = 2 Ω	3.4				ns
t _r	Rise Time		1.4				ns
t _{d(off)}	Turn Off Delay Time		10.8				ns
t _f	Fall Time		3.6				ns
DIODE CHARACTERISTICS							
V _{SD}	Diode Forward Voltage	I _{SD} = 0.5 A, V _{GS} = 0 V	0.73			0.9	V
Q _{rr}	Reverse Recovery Charge	V _{DS} = 15 V, I _F = 0.5 A, di/dt = 300 A/ μs	1500				pC
t _{rr}	Reverse Recovery Time		5.6				ns

5.2 Thermal Information






(T_A = 25°C unless otherwise stated)

THERMAL METRIC		TYPICAL VALUES	UNIT
R _{θJA}	Junction-to-Ambient Thermal Resistance ⁽¹⁾	90	°C/W
	Junction-to-Ambient Thermal Resistance ⁽²⁾	250	

- (1) Device mounted on FR4 material with 1 inch² (6.45 cm²), 2 oz. (0.071 mm thick) Cu.
 (2) Device mounted on FR4 material with minimum Cu mounting area.

5.3 Typical MOSFET Characteristics

($T_A = 25^\circ\text{C}$ unless otherwise stated)






图 5-6. Threshold Voltage vs Temperature




图 5-7. On-State Resistance vs Gate-to-Source Voltage




图 5-8. Normalized On-State Resistance vs Temperature




图 5-9. Typical Diode Forward Voltage




图 5-10. Maximum Safe Operating Area




图 5-11. Single Pulse Unclamped Inductive Switching




图 5-12. Maximum Drain Current vs Temperature

6 Device and Documentation Support

6.1 支持资源

[TI E2E™ 支持论坛](#)是工程师的重要参考资料，可直接从专家获得快速、经过验证的解答和设计帮助。搜索现有解答或提出自己的问题可获得所需的快速设计帮助。

链接的内容由各个贡献者“按原样”提供。这些内容并不构成 TI 技术规范，并且不一定反映 TI 的观点；请参阅 TI 的《使用条款》。

6.2 Trademarks

FemtoFET™ is a trademark of Texas Instruments.

TI E2E™ is a trademark of Texas Instruments.

所有商标均为其各自所有者的财产。

6.3 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.


6.4 术语表

[TI 术语表](#) 本术语表列出并解释了术语、首字母缩略词和定义。

7 Mechanical, Packaging, and Orderable Information


The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

7.1 Mechanical Dimensions




- All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
- This drawing is subject to change without notice.
- This package is a Pb-free bump design. Bump finish may vary. To determine the exact finish, refer to the device data sheet or contact a local TI representative.

7.2 Recommended Minimum PCB Layout



- A. All dimensions are in millimeters.
- B. For more information, see [FemtoFET Surface Mount Guide](#) (SLRA003D).

7.3 Recommended Stencil Pattern



- A. All dimensions are in millimeters.
- B. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.

PACKAGING INFORMATION

Orderable part number	Status (1)	Material type (2)	Package Pins	Package qty Carrier	RoHS (3)	Lead finish/ Ball material (4)	MSL rating/ Peak reflow (5)	Op temp (°C)	Part marking (6)
CSD17381F4	Active	Production	PICOSTAR (YJC) 3	3000 LARGE T&R	Yes	NIAU	Level-1-260C-UNLIM	-55 to 150	CQ
CSD17381F4.B	Active	Production	PICOSTAR (YJC) 3	3000 LARGE T&R	Yes	NIAU	Level-1-260C-UNLIM	-55 to 150	CQ
CSD17381F4T	Active	Production	PICOSTAR (YJC) 3	250 SMALL T&R	Yes	NIAU	Level-1-260C-UNLIM	-55 to 150	CQ
CSD17381F4T.B	Active	Production	PICOSTAR (YJC) 3	250 SMALL T&R	Yes	NIAU	Level-1-260C-UNLIM	-55 to 150	CQ

⁽¹⁾ **Status:** For more details on status, see our [product life cycle](#).

⁽²⁾ **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

⁽³⁾ **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

⁽⁴⁾ **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

⁽⁵⁾ **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.


⁽⁶⁾ **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.


TAPE AND REEL INFORMATION



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
CSD17381F4	PICOSTAR	YJC	3	3000	180.0	8.4	0.7	1.1	0.46	4.0	8.0	Q2
CSD17381F4T	PICOSTAR	YJC	3	250	180.0	8.4	0.7	1.1	0.46	4.0	8.0	Q2

TAPE AND REEL BOX DIMENSIONS



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
CSD17381F4	PICOSTAR	YJC	3	3000	182.0	182.0	20.0
CSD17381F4T	PICOSTAR	YJC	3	250	182.0	182.0	20.0

重要通知和免责声明

TI“按原样”提供技术和可靠性数据（包括数据表）、设计资源（包括参考设计）、应用或其他设计建议、网络工具、安全信息和其他资源，不保证没有瑕疵且不做任何明示或暗示的担保，包括但不限于对适销性、与某特定用途的适用性或不侵犯任何第三方知识产权的暗示担保。

这些资源可供使用 TI 产品进行设计的熟练开发人员使用。您将自行承担以下全部责任：(1) 针对您的应用选择合适的 TI 产品，(2) 设计、验证并测试您的应用，(3) 确保您的应用满足相应标准以及任何其他安全、安保法规或其他要求。

这些资源如有变更，恕不另行通知。TI 授权您仅可将这些资源用于研发本资源所述的 TI 产品的相关应用。严禁以其他方式对这些资源进行复制或展示。您无权使用任何其他 TI 知识产权或任何第三方知识产权。对于因您对这些资源的使用而对 TI 及其代表造成的任何索赔、损害、成本、损失和债务，您将全额赔偿，TI 对此概不负责。

TI 提供的产品受 [TI 销售条款](#)、[TI 通用质量指南](#) 或 [ti.com](#) 上其他适用条款或 TI 产品随附的其他适用条款的约束。TI 提供这些资源并不会扩展或以其他方式更改 TI 针对 TI 产品发布的适用的担保或担保免责声明。除非德州仪器 (TI) 明确将某产品指定为定制产品或客户特定产品，否则其产品均为按确定价格收入目录的标准通用器件。

TI 反对并拒绝您可能提出的任何其他或不同的条款。

版权所有 © 2025，德州仪器 (TI) 公司

最后更新日期：2025 年 10 月