

Four Quadrant Inverse Tangent (Low Precision)

Medical Imaging DSP Applications Team

1 Description

This is a low precision and low complexity implementation of the four quadrant inverse tangent (atan2) function. It operates on input complex vectors, Z = X + jY, where $X = \{x\}$ and $Y = \{y\}$, and computes the result, $\theta = \text{atan2}(y, x)$, for each point, where $-\pi \le \text{atan2} \le \pi$. The resulting output can be 8 bit (in Q7, [-128 (-pi), 127 (pi)]) or 16 bit (in Q15 format, [-32768 (-pi), 32767 (pi)]) vector. It uses the approximation [1] as given below:

$$r = \frac{x - |y|}{x + |y|'} \qquad \theta = \frac{\pi}{4} - \frac{\pi}{4}r, \qquad (x, y) \in Q1, (x, y) \in Q4$$

$$r = \frac{x + |y|}{|y| - x'} \qquad \theta = \frac{3\pi}{4} - \frac{\pi}{4}r, \qquad (x, y) \in Q2, (x, y) \in Q3$$

$$\theta = -\theta \qquad (x, y) \in Q4, (x, y) \in Q3$$
(1)

The Ámaximum Áerror Áusing Áthis Áapproximation Ás Áexpected Áo Áo e Ávithin Áo. 1 Áradians Áof Áthe Átloating Ápoint Áresult.

ProjectÁcollateralÁdiscussedÁnÁthisÁdocumentÁcanÁbeÁdownloadedÁfromÁtheÁfollowingÁJRL: https://www.ti.com/lit/zip/sprs618

2 Kernel Complexity ('C64x+™'CPU cycles, based on CPU cycle accurate Simulator)

- With 8-bit outputs, util_atan2_lp_16b_8b: 4.5 L + 53
- With 16-bit outputs, util_atan2_ lp_16b_16b: 4.5 L + 48

where,

L = Length of input/output vector,

3 Cycles on TMS320C6455 EVM

The performance is given for several example cases on the C6455 EVM in cycles. The test bench for math UTIL can be used to find cycles of interest for any other valid configuration.

API	L	Test Case	EVM Cycles
util_atan2_lp_16b_8b	1024	1	4661
util_atan2_lp_16b_8b	512	2	2357
util_atan2_lp_16b_16b	1024	1	4726
util_atan2_lp_16b_16b	512	2	2388

C64x+ is a trademark of Texas Instruments.

All other trademarks are the property of their respective owners.



Memory www.ti.com

4 Memory

Memory	Size in Bytes	
Data	None	
Program	~1KB (util_atan2_ lp_16b_8b + util_atan2_ lp_16b_16b)	

5 References

 J.M.Shima, FM Demodulation Using Digital Radio and Digital Signal Processing, MS Thesis, University of Florida, 1995.

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2022, Texas Instruments Incorporated