



- Supports ITU-T V.24 Recommendation
- Provides Buffered Byte-Oriented DTE Operation
- Frame Size can be up to 128 Octets
- Allows to Select Frame/Buffer Memory Size According to Available System Resources
- Supports Message Handling Mechanism to Make Integration More Feasible
- Can be Efficiently Integrated Into Multitasking Environment With Separate Low and High Priority Processes

- Supports Traffic Load Control
- Includes Buffered Data Pump Interface as Well as Simple Callback Handlers
- Supports Externally Linked Protocol Monitor
- Easily Interfaces With SPIRIT CORP Modem Data Pumps
- eXpressDSP-Compliant Algorithm. Code is Reentrant, Supports Multithreading and Dynamic Memory Allocation
- Can be Easily Ported to any Platform

description

The SPIRIT V.42/V.42bis conforms to ITU-T V.42 error correction protocol that uses LAP-M and ITU-T V.42bis data compression protocol.

resource requirements

CONFIGURATION	MIPS PEAK / AVERAGE	PROGRAM MEMORY (KWORDS)	CONSTANT MEMORY (KWORDS)	DYNAMIC MEMORY (KWORDS)
V.42/V.42bis Generic	N/A [†] / 4			1370 + (P1‡–259) * 4 + Memory Pool Size§
V.42/V.42bis Pool Size = 1500 Duplex compression, Dictionary size = 512	8†/3	13.1	162	4936
V.42 only Pool Size = 1500	4/3			2308

[†] Peak MIPS of V.42bis depend very much on the content of data to be compressed. For this reason, V.42/V.42bis object supports multiple threads, so that compressions/decompression tasks, which may consume a lot of MIPS in some exceptional cases, would run in a lower priority thread. ‡ P1 is a negotiation parameter that determines the dictionary size (512 ÷ 4096) for V.42bis. MIPS requirements are given for 14400 bps. § Minimum value of Memory Pool SIze is 800.

availability

The SPIRIT V.42/V.42bis is available in the following forms:

- eXpressDSP compliant object code for TMS320C54x
- Fully functional eXpressDSP evaluation object at extremely low price
- DLL for MS Windows
- Portable C code
- Assembly code

The algorithm is supplied with test environment and integration example code.

Detailed product annotation and user guide documents describing testing procedures, interface and integration of this product, as well as PC-based and DSP-based (TI TMS320VC5406 EVM and TMS320VC5402 DSK) demos are available for evaluation upon request. To get additional information on CST software, go to www.spiritdsp.com/CST.



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

CST Software Copyright © 2003, SPIRIT Technologies, Inc.

All trademarks are the property of their respective owners.



IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third—party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Mailing Address:

Texas Instruments Post Office Box 655303 Dallas, Texas 75265

Copyright © 2003, Texas Instruments Incorporated