Filename: BOM_PMP9365

Variant: 001

Generated: 8/12/2014 2:47:00 PM

PMP9365 Bill of Materials

Designator	Description	Manufacturer	PartNumber	Quantity
!PCB1	Printed Circuit Board	Any	PMP9365	1
C1	CAP, CERM, 1uF, 25V, +/-10%, X5R, 0603	MuRata	GRM188R61E105KA12D	1
C2, C3	CAP, AL, 22uF, 16V, +/-20%, 1.8 ohm, SMD	Panasonic	EEE-FC1C220R	2
	CAP, CERM, 47uF, 16V, +/-10%, X5R, 1210	MuRata	GRM32ER61C476KE15L	8
C7, C8, C9,				
C10, C11				
040, 040	OAD TA 000 F 0V +/ 000/ 0 000 -h 0MD	Danasaria	FEE OVODOGAVE	
	CAP, TA, 330uF, 2V, +/-20%, 0.006 ohm, SMD	Panasonic	EEF-SX0D331XE	2
C14, C15,	CAP, CERM, 100uF, 6.3V, +/-20%, X5R, 1210	MuRata	GRM32ER60J107ME20L	8
C16, C17,				
C18, C80, C81, C82				
C19, C22,	CAP, CERM, 0.1uF, 25V, +/-10%, X5R, 0603	MuRata	GRM188R61E104KA01D	4
C19, C22,	CAF, CERIVI, 0.10F, 25V, +7-1070, A5R, 0003	Iviurala	GRW166R61E104RA01D	4
·	CAP, CERM, 100pF, 100V, +/-5%, C0G/NP0, 0603	MuRata	GRM1885C2A101JA01D	2
C23	CAP, CERM, 10uF, 25V, +/-20%, X5R, 0805	MuRata	GRM21BR61E106MA73	1
C24	CAP, CERM, 22uF, 6.3V, +/-20%, X5R, 0805	MuRata	GRM21BR60J226ME39L	1
C28, C29,	CAP, TA, 68uF, 16V, +/-20%, 0.05 ohm, SMD	Panasonic	16TQC68MYF	5
C46, C55,	57 tt , 17 tt, 55 tt , 7 25 75, 5155 51 tt 1, 51112	T directing	101 4000	
C56				
C30, C31,	CAP, CERM, 47uF, 16V, +/-20%, X5R, 1210	MuRata	GRM32ER61C476ME15L	5
C47, C57,				
C58				
C36, C37,	CAP, TA, 220uF, 6.3V, +/-20%, 0.009 ohm, SMD	Kemet	T520D227M006ATE009	5
C50, C63,				
C64				
C38, C39,	CAP, CERM, 47uF, 6.3V, +/-20%, X5R, 1210	MuRata	GRM32ER60J476ME20L	22
C40, C41,				
C42, C43,				
C44, C45,				
C51, C52,				
C53, C54,				
C65, C66,				
C67, C68,				
C69, C70,				
C71, C72,				
C103, C104				
C73	CAP, CERM, 4.7uF, 25V, +/-10%, X7R, 1206	TDK	C3216X7R1E475K	1
C74	CAP, CERM, 4.7ur, 25V, +/-10%, X/R, 1206 CAP, AL, 100uF, 25V, +/-20%, 30 ohm, SMD	Panasonic	EEHZA1E101XP	1
C75	CAP, AL, 220uF, 2.5V, +/-20%, 0.009 ohm, SMD	Panasonic	EEF-UD0E221LR	1
C76, C77	CAP, CERM, 22uF, 25V, +/-10%, X5R, 1210	MuRata	GRM32ER61E226KE15L	2
C83	CAP, CERM, 3300pF, 50V, +/-10%, X7R, 0402	MuRata	GRM155R71H332KA01D	1
C85, C87	CAP, CERM, 2.2uF, 6.3V, +/-10%, X7S, 0603	MuRata	GRM188C70J225KE20D	2
C86, C88,	CAP, CERM, 10uF, 6.3V, +/-20%, X5R, 0603	Kemet	C0603C106M9PACTU	8
C93, C95,	, , , , , , , , , , , , , , , , , , , ,			
C96, C100,				
C101, C102				
,				
C89, C91,	CAP, CERM, 1000pF, 100V, +/-5%, X7R, 0603	AVX	06031C102JAT2A	3
C94	, , , , , , , , , , , , , , , , , , , ,			
C98	CAP, CERM, 0.1uF, 50V, +/-10%, X7R, 0603	MuRata	GCM188R71H104KA57B	1
C99	CAP, CERM, 10pF, 50V, +/-5%, C0G/NP0, 0603	AVX	06035A100JAT2A	1

Designator		Manufacturer	PartNumber	Quantity
	Diode, Zener, 5.1V, 300mW, SOD-523	Diodes Inc.	BZT52C5V1T-7	2
	Fiducial mark. There is nothing to buy or mount.	N/A	N/A	6
FID3, FID4,				
FID5, FID6				
	Bumpon, Hemisphere, 0.44 X 0.20, Clear	3M	SJ-5303 (CLEAR)	4
H4				
	Standard Banana Jack, Uninsulated	Keystone	6095	4
J4	TERMINAL BLOOK FORMAN/ERT ORGO TH		ED 400 (0D 0	
	TERMINAL BLOCK 5.08MM VERT 2POS, TH	On-Shore Technology	ED120/2DS	6
J8, J9, J10 L1	Inductor, Shielded, Composite, 10uH, 3A, 0.084 ohm,	Coilcraft	XAL4040-103MEB	1
LI	SMD	Coliciait	AAL4040-TOSIVIED	ı
LBL1	Thermal Transfer Printable Labels, 0.650" W x 0.200" H	Brady	THT-14-423-10	1
LDL	- 10,000 per roll	ыасу	1111-14-423-10	'
R1, R36	RES, 10.0 ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW060310R0FKEA	2
R4	RES, 0 ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW06030000Z0EA	1
R5	RES, 3.57k ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW06033K57FKEA	1
	RES, 100k ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW0603100KJNEA	7
R15, R39,				-
R44, R45				
	RES, 169k ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW0603169KFKEA	2
	RES, 121k ohm, 1%, 0.1W, 0603	Yageo America	RC0603FR-07121KL	2
R12	RES, 105k ohm, 0.1%, 0.1W, 0603	Yageo America	RT0603BRD07105KL	1
R13	RES, 20.0k ohm, 0.1%, 0.1W, 0603	Susumu Co Ltd	RG1608P-203-B-T5	1
R16, R17,	RES, 49.9 ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW060349R9FKEA	5
R24, R28,				
R29				
	RES, 665 ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW0603665RFKEA	2
R19	RES, 511 ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW0603511RFKEA	1
	RES, 324k ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW0603324KFKEA	3
R33				
R21	RES, 191k ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW0603191KFKEA	1
R25	RES, 5.76k ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW06035K76FKEA	1
R31	RES, 1.13k ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW06031K13FKEA	1
R37	RES, 953 ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW0603953RFKEA	1
R38	RES, 487k ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW0603487KFKEA	1
R40, R41 R42	RES, 10.0k ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW060310K0FKEA	2
R42 R43	RES, 100k ohm, 1%, 0.1W, 0603 RES, 10 ohm, 5%, 0.1W, 0603	Vishay-Dale Vishay-Dale	CRCW0603100KFKEA CRCW060310R0JNEA	1
TP1, TP2,	Test Point, Multipurpose, Red, TH	Keystone	5010	11
TP9, TP10,	1 cot i onit, manaparposo, rea, i i	i to yotorio		
TP15,				
TP21,				
TP22,				
TP26,				
TP29,				
TP30, TP36				
TP3, TP8,	Test Point, Miniature, White, TH	Keystone	5002	10
TP11,				
TP16,				
TP20,				
TP23,				
TP28,				
TP32,				
TP33, TP35				

Designator	Description	Manufacturer	PartNumber	Quantity
TP4, TP5,	Test Point, Multipurpose, Black, TH	Keystone	5011	11
TP12,				
TP13,				
TP17,				
TP24,				
TP25,				
TP27,				
TP31,				
TP34, TP37				
TP6, TP7,	Test Point, Multipurpose, Orange, TH	Keystone	5013	6
TP14,				
TP18,				
TP19, TP38				
U1	20A SIMPLE SWITCHER(R) Power Module with 3.0V-	Texas Instruments	LMZ31520RLG	1
	14.5V Input, RLG0072A			
U2, U14	Power Sequencer, 6-pin SOT-23	National Semiconductor	LM3880MF-1AA	2
U3, U4, U5,	3A SIMPLE SWITCHER Power Module with 4.5V-14.5V	Texas Instruments	LMZ31503RUQ	5
U6, U7	Input in QFN Package, RUQ0047A			
U8	4A SIMPLE SWITCHER Power Module with 2.95V-17V	Texas Instruments	LMZ31704RVQ	1
	Input and Current Sharing in QFN Package, RVQ0042A			
U9, U10	IC, 500mA, Low Quiescent Current, Ultra-Low Noise,	TI	TPS735xxDRB	2
	High PSRR LDO, xx-V			
U11	IC, Sink/Source DDR Termination Regulator	TI	TPS51200DRC	1
U12	IC, Single 2-Input Positive-OR Gate	TI	SN74AHC1G32DCK	1
U13	4.5V to 18V Input, 500mA Synchronous Step Down	Texas Instruments	TPS560200DBV	1
	SWIFT Converter, DBV0005A			
U15	Single 2-Input Positive-AND Gate, DRL0005A	Texas Instruments	SN74AHC1G08DRL	1

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design. TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, Is GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have *not* been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.