Assembly Bill of Materials

Texas Instruments

Enter search term in cell K2 below

Search Findchips.com
Search Digi-Key
Search Mouser
Search Newark
Search RS Components

Project Name:	TIDA-00558
Project File:	SM72295EvalBoard REVC.PrjPcb
Base ID:	<parameter found="" not="" prj_number=""></parameter>
Schematic Rev:	<parameter found="" not="" sch_rev=""></parameter>
Assembly Variant:	001
Build Quantity:	100
Generated:	9/18/2015 2:28:01 PM

Item	Designator	Description	RoHS	Manufacturer	PartNumber	Quantity	Required	Supplier 1	Supplier Part Number 1	Supplier 2	Supplier Part Number 2	Alternate Manufacturer	Alternate PartNumber
1	!PCB1	Printed Circuit Board	0	Anv	PRJ Number	1	100						
2		CAP, CERM, 47 µF, 100 V, +/- 20%, X7R, 1075x300mil	Y	AVX	RT201C476MAJ10	2	200						
3	C2	CAP, CERM, 220 pF, 100 V, +/- 5%, C0G/NP0, 0805	Ÿ	Kemet	C0805C221J1GACTU	1	100	Digi-Key	399-1128-1-ND	Mouser	80-C0805C221J1G		
4		CAP, CERM, 0.015 µF, 100 V, +/- 5%, X7R, 1206	Ÿ	AVX	12061C153JAT2A	4	400	Digi-Key	478-3787-1-ND		581-12061C153JAT2A		
5		CAP, CERM, 0.1 µF, 50 V, +/- 10%, X7R, 0805	·	AVX	08055C104KAT2A	4	400	Digi-Key	478-1395-1-ND	Mouser	581-08055C104K		
6		CAP, CERM, 0.1 µF, 25 V, +/- 10%, X7R, 0805	Ÿ	AVX	08053C104KAT2A	4	400	Digi-Key	478-3755-1-ND	Mouser	581-08053C104K		
7		CAP, CERM, 0.47 µF, 25 V, +/- 10%, X7R, 0805	÷	TDK	C2012X7R1E474K	4	400	Digi-Key	445-1353-1-ND	Farnell	1844282		
8		CAP, CERM, 1 μF, 25 V, +/- 10%, X7R, 0805	,	TDK	C2012X7R1E474R	4	400	Digi-Key	445-1354-1-ND	Farnell	1907348		
9	C8, C24	CAP, CERM, 1 µF, 25 V, +/- 10%, X/K, 0805 CAP, CERM, 220 µF, 25 V, +/- 20%, X/R, 1075x300mil	, T	AVX	RT203C227MAJ10	2	200	Digi-Key	445-1354-1-ND	ramen	1907346		
10	C0, C24	CAP, CERM, 220 pF, 25 V, +/- 20%, A/R, 10/3x300ffff CAP, CERM, 220 pF, 50 V, +/- 5%, C0G/NP0, 0805	, ,	AVX	08055A221JAT2A	1	100	Digi-Key	478-1320-1-ND	Mouser	581-08055A221J		
11	00	CAP, CERM, 0.022 µF, 50 V, +/- 10%, X7R, 0805	Ų	Kemet	C0805C223K5RACTU	2	200	Digi-Key	399-1163-1-ND	Mouser	80-C0805C223K5R		
			Ţ						445-12899-1-ND				
12		CAP, CERM, 0.68 µF, 100 V, +/- 10%, X7R, 1206_190	, Y	TDK TDK	CGA5L2X7R2A684K160AA	2	200	Digi-Key	445-12899-1-ND 445-4464-1-ND		810-CGA5L2X7R2A684KA		
13		CAP, CERM, 0.33 µF, 100 V, +/- 10%, X7R, 1206	Y V		C3216X7R2A334K130AA	2	200	Digi-Key		Mouser	810-C3216X7R2A334K		
14		CAP, CERM, 0.01 µF, 50 V, +/- 5%, X7R, 0805	, Y	AVX	08055C103JAT2A	1	100	Digi-Key	478-3768-1-ND	Mouser	581-08055C103J		
15		CAP, CERM, 10 µF, 25 V, +/- 10%, X7R, 1206	Y	MuRata	GRM31CR71E106KA12L	3	300	Mouser	81-GRM31CR71E106KA12	Farnell	1828837		
16		CAP, CERM, 10 µF, 16 V, +/- 20%, X7R, 0805	Y	Taiyo Yuden	EMK212BB7106MG-T	1	100	Digi-Key	587-3319-1-ND	Mouser	963-EMK212BB7106MG-T		
17		CAP, CERM, 33 pF, 50 V, +/- 5%, C0G/NP0, 0805	Y	AVX	08055A330JAT2A	2	200	Digi-Key	478-1310-1-ND	Mouser	581-08055A330J		
18	C41	CAP, CERM, 100 pF, 50 V, +/- 5%, C0G/NP0, 0805	Y	AVX	08055A101JAT2A	1	100	Digi-Key	478-1316-1-ND	Mouser	581-08055A101J		
19	C42	CAP, AL, 680 µF, 80 V, +/- 20%, 0.041 ohm, TH	Y	Chemi-Con	EGPA800ELL681MM30S	1	100	Digi-Key	565-3420-ND	Mouser	661-EGPA800L681MM30S		
20		Diode, Ultrafast, 100 V, 0.15 A, SOD-123	Y	Diodes Inc.	1N4148W-7-F	3	300	Digi-Key	1N4148W-FDICT-ND	Mouser	621-1N4148W-F		
21	F1, F3	FUSE BOARD MNT 12A 125VAC 86VDC	RoHS	Bel Fuse Inc	SSQ 12	2	200	Digi-Key	507-1058-1-ND			-	-
			Compliant										
22	F2, F4	FUSE BOARD MNT 30A 125VAC 72VDC	RoHS	Littelfuse Inc	0456030.ER	2	200	Digi-Key	F3345CT-ND			-	-
			Compliant										
23	FID1, FID2, FID3,	Fiducial mark. There is nothing to buy or mount.		N/A	N/A	6	600						
	FID4, FID5, FID6	,											
24	H1, H2, H3, H4	Machine Screw, Round, #4-40 x 1/4, Nylon, Philips panhead	Y	B&F Fastener Supply	NY PMS 440 0025 PH	4	400	Digi-Key	H542-ND				
	,,,							57					
25	H5, H6, H7, H8	Standoff, Hex. 0.5"L #4-40 Nylon	Y	Kevstone	1902C	4	400	Digi-Key	1902CK-ND				
26	H9, H10, H11,	Machine Screw Pan PHILLIPS M3, TH	·	APM HEXSEAL	RM3X12MM 2701	24	2400	Digi-Key	335-1157-ND	Mouser	608-RM3X12MM2701		
20	H12, H13, H14,	Waciline Ociew i airi riileen o wo, iiri		AI WITIEXOEAE	TOTAL STATE OF THE	2-7	2400	Digi-10cy	333-1137-14B	Wiousei	000-ITIND/CTZININIZ/OT		
	H15, H16, H17,												
	H18, H19, H20,												
	H21, H22, H23,												
	H24, H25, H26,												
	H27, H28, H65,												
	H66, H67, H68												
27	H29, H30, H31,	PushPIN™ Heat Sink Attachments, 14 mm	Y	Advanced Thermal	ATS-PPS-06	20	2000	Digi-Key	ATS1893-ND				
	H32, H33, H34,			Solutions									
	H35, H36, H37,												
	H38, H40, H41,												
	H42, H43, H44,												
	H45, H46, H47,												
	H48, H49												
28		Ultra Soft Thermal Conductive Pad	v	t-Global Technology	TG6050-150-150-0.5-0	1	100	Digi-Key	1168-1341-ND				
29	H50, H51	HOLE INDUCTOR	·	Used in BOM report	NONE	2	200	DIGIKEY	1.00 1041-110				
30		Fan Leg Kit for 92mm and 120mm Fans, 1.25" elevation		Custom	FNLK-120-01	1	100	DIGINET					-
31		AC/DC Adapter, 12 V, 12 W	V	Triad Magnetics	WSU120-1000	4	100	Digi-Key	237-1455-ND	Mouser	553-WSU120-1000		
		Fan, DC 12 V, 120mm square x 38mm 134 CFM	- '		DFS123812H-3000	1	100	Digi-Rey	237-1400-IND	wodser	333-VV 3U 12U-10UU		
32			V	Scythe	HSS-5.4-1.5-AL-01	4	100						
33	H63	Heat Sink Fan Shroud, 5.4x5.4x1.5 Inch	Y	Custom		1							
34		Heat Sink 5.4 x 5.4 x 1.4 Inch	Y	Custom	HS-5.4-5.4-1.4-01	1	100	Dist Ks	005 4000 ND				
35		MACH SCREW PAN PHILLIPS 1/4-20	Y	APM HEXSEAL	R1/4-20X3/8 2701	2	200	Digi-Key	335-1068-ND				
36		HEX SEAL NUT 7/16" STEEL 1/4-20	Y	APM HEXSEAL	1/4-20 AJ 6	2	200	Digi-Key	335-1050-ND	Mouser	608-1/4-20AJ6		
37		Screw Combination Head 10-32	Y	Keystone	F1283	2	200	Digi-Key	F1283-ND				
38	H75, H76	Machine Screw Nut, Hex, 3/8??', Stn, Steel, 10-32	Y	B&F Fastener Supply	HNSS 102	2	200	Digi-Key	H727-ND				
39	J1	CONN JACK POWER 2.1MM PCB	RoHS	CUI Inc	PJ-102A	1	100	Digi-Key	CP-102A-ND		l		
			Compliant										
40		CONN HEADER 3POS .100 VERT TIN	Y	Molex	22-27-2031	1	100	Digi-Key	WM4112-ND	Mouser	538-22-27-2031		
41	J3, J4	DEV STICK USB PICCOLO F28069 HALF PART	RoHS		SSW-108-01-T-D	2	200	Digi-Key	SAM1212-08-ND				
1			Compliant					1	1		l		
1			By						1				
1			Exemptio					1	1		l		
1			n						1				
42	L1, L2	Inductor, Shielded E Core, Ferrite, 6.8uH, 28A, 0.0026 ohm,	Υ	Coilcraft	SER2918H-682KL	2	200						
I		SMD											
43	LBL1	Thermal Transfer Printable Labels, 0.650" W x 0.200" H -	Υ	Brady	THT-14-423-10	1	100	Farnell	2065596	Newark	97C5133		
I		10.000 per roll		,				1					
44	PCBA1	Printed Circuit Board Assembly		Texas Instruments	TMDX28069USB	1	100	Digi-Key	296-28115-ND	Mouser	595-TMDX28069USB		

45	Q1, Q2, Q3, Q6, Q7, Q8, Q9, Q10, Q13, Q14, Q15, Q17, Q18, Q19, Q20, Q21	MOSFET, N-CH, 80V, 55A, PG-TDSON-8	Y	Infineon Technologies	BSC123N08NS3 G	16	1600	Digi-Key	BSC123N08NS3 GCT-ND	Mouser	726-BSC123N08NS3G	None	
46 47	Q4, Q11	MOSFET, N-CH, 30 V, 0.18 A, SOT-323 Transistor, NPN, 120 V, 0.05 A, SOT-23	Y	NXP Semiconductor Fairchild Semiconductor	NX3020NAKW,115 FJV1845FMTF	2 4	200 400	Digi-Key Digi-Key	568-10508-1-ND FJV1845FMTFCT-ND	Mouser Mouser	771-NX3020NAKW115 512-FJV1845FMTF	None	
	Q22	1141101017, 14114, 120 1, 0.0074, 001 20		Tallorina Connocinadolor		·	100	Digi Noy		····ouooi	012101101011111		
48		RES, 0.012, 1%, 1 W, 2412	Υ	Ohmite	LVK24R012FER	2	200	Mouser	588-LVK24R012FER	Farnell	1462310		
49		RES, 39.2 k, 1%, 0.125 W, 0805	Υ	Vishay-Dale	CRCW080539K2FKEA	1	100	Digi-Key	541-39.2KCCT-ND	Mouser	71-CRCW0805-39.2K-E3		
50		RES, 2.00 k, 1%, 0.125 W, 0805	Y	Vishay-Dale	CRCW08052K00FKEA	2	200	Digi-Key	541-2.00KCCT-ND	Mouser	71-CRCW0805-2.0K-E3		
51	R4, R5, R6, R21, R22, R23, R24, R25, R37, R38, R41, R47, R48, R49, R51	RES, 3.01, 1%, 0.125 W, 0805	Y	Vishay-Dale	CRCW08053R01FKEA	15	1500	Digi-Key	541-3.01CCCT-ND	Mouser	71-CRCW08053R01FKEA		
52	R63, R64, R65, R66	RES, 105, 1%, 0.125 W, 0805	Y	Vishay-Dale	CRCW0805105RFKEA	8	800	Digi-Key	541-105CCT-ND	Mouser	71-CRCW0805105RFKEA		
53 54		RES, 10.0 k, 1%, 0.125 W, 0805 RES, 9.76 k, 1%, 0.125 W, 0805	Y	Vishay-Dale Vishay-Dale	CRCW080510K0FKEA CRCW08059K76FKEA	4	400 400	Digi-Key Digi-Key	541-10.0KCCT-ND 541-9.76KCCT-ND	Mouser Mouser	71-CRCW0805-10K-E3 71-CRCW0805-9.76K-E3		
55	R12, R15, R20, R26, R30, R43, R45, R46, R52	RES, 1.00, 1%, 0.125 W, 0805	Y	Vishay-Dale	CRCW08051R00FKEA	9	900	Mouser	71-CRCW0805-1-E3	Farnell	1563923		
56	R13, R44	RES, 0.002, 1%, 3 W, 6.6x3x6.9mm	RoHS Compliant	Vishay Dale	WSL27262L000FEB	2	200	Digi-Key	WSLQ002CT-ND	Mouser	71-WSL27262L000FEB		
57	R14	RES, 8.25 k, 1%, 0.125 W, 0805	Y	Vishay-Dale	CRCW08058K25FKEA	1	100	Digi-Key	541-8.25KCCT-ND	Mouser	71-CRCW0805-8.25K-E3		
58 59	R16 R27, R31, R34,	RES, 499, 1%, 0.25 W, 1206 RES, 4.99 k, 1%, 0.125 W, 0805	Y	Vishay-Dale Vishay-Dale	CRCW1206499RFKEA CRCW08054K99FKEA	1 4	100 400	Digi-Key Digi-Key	541-499FCT-ND 541-4.99KCCT-ND	Mouser Mouser	71-CRCW1206-499-E3 71-CRCW0805-4.99K-E3		
	R35			*		-							
60	R28, R29, R54, R55	RES, 196, 1%, 0.125 W, 0805	Y	Vishay-Dale	CRCW0805196RFKEA	4	400	Digi-Key	541-196CCT-ND	Mouser	71-CRCW0805-196-E3		
61	R32, R57	RES, 392, 1%, 0.125 W, 0805	Υ	Vishay-Dale	CRCW0805392RFKEA	2	200	Digi-Key	541-392CCT-ND	Mouser	71-CRCW0805-392-E3		
62		RES, 3.0, 5%, 0.125 W, 0805	Y	Vishay-Dale	CRCW08053R00JNEA	1	100	Digi-Key	541-3.0ACT-ND	Mouser	71-CRCW08053R00JNEA		
63		RES, 100 k, 1%, 0.125 W, 0805	Y	Vishay-Dale	CRCW0805100KFKEA	1	100	Digi-Key	541-100KCCT-ND	Mouser	71-CRCW0805-100K-E3		
64 65		RES, 1.00 k, 1%, 0.125 W, 0805 Terminal 50A Lug	Y	Vishay-Dale Panduit	CRCW08051K00FKEA CB35-36-CY	1 2	100 200	Digi-Key Digi-Key	541-1.00KCCT-ND CB35-36-CY-ND	Mouser	71-CRCW0805-1.0K-E3		
66		Terminal 90A Lug	Y	Panduit	CB70-14-CY	2	200	Digi-Key Digi-Key	CB70-14-CY-ND				
67	TP1, TP2, TP3,	Test Point, Miniature, SMT	v	Keystone	5015	56	5600	Digi-Key Digi-Key	5015KCT-ND				
	TP4, TP5, TP6, TP7, TP8, TP9, TP10, TP11, TP12, TP13, TP14, TP15, TP16, TP17, TP18, TP19, TP20, TP21, TP22, TP23, TP24, TP25, TP26, TP27, TP28, TP29, TP30, TP31, TP32, TP33, TP40, TP41, TP42, TP43, TP44, TP45, TP46, TP47, TP48, TP49, TP50, TP51, TP52, TP56, TP56, TP55, TP56	Co Changachtain Full Didge Diving			SMESSENA		200						
68 69	U2	IC, Photovoltaic Full Bridge Driver Low-Power, Digital Temperature Sensor with Two-Wire Interface in WCSP, YFF0004AAAA	Y	TI Texas Instruments	SM72295MA TMP103AYFF	1	200 100					None Texas Instruments	
70		Low-Power, Digital Temperature Sensor with Two-Wire Interface in WCSP, YFF0004AAAA	Y	Texas Instruments	TMP103BYFF	1	100					Texas Instruments	
71	U5	Single Output Low Noise LDO, 150 mA, Fixed 10 V Output, 2.2 to 16 V Input, with Low IQ, 5-pin SOT-23 (DBV), -40 to 125 degC, Green (RoHS & no Sb/Br)		Texas Instruments	LP2985-10DBVT	1	100	Digi-Key	296-32147-2-ND	Digi-Key	296-32147-1-ND	None	Equivalent
72	U6	Single Output Fast Transient Response LDO, 1.5 A, Fixed 3.3 V Output, 2.1 to 20 V Input, 6-pin SOT-223 (DCQ), -40 to 125 degC, Green (RoHS & no Sb/Br)		Texas Instruments	TPS7A4533DCQT	1	100	Digi-Key	296-32587-2-ND	Digi-Key	296-32587-1-ND	None	Equivalent

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design. TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have *not* been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.