## TIDA-00774E2(001)\_TI-BOM.xls 001 11/12/2016 2:06:27 PM TIDA-00774



## TIDA-00774 REV E2 Bill of Materials

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
!PCB1	1		TIDA-00774	Any	Printed Circuit Board	
C1, C2, C4, C18,	10	2.2uF	GRM32ER72A225KA35L	MuRata	CAP, CERM, 2.2 μF, 100 V, +/- 10%, X7R, 1210	1210
C19, C20, C21,						
C22, C41, C42						
C3	1	0.01uF	GRM155R71E103KA01D	MuRata	CAP, CERM, 0.01 μF, 25 V, +/- 10%, X7R, 0402	0402
C5	1	22uF	CC1210MKX5R8BB226	Yageo	ion 22µF 25V Ceramic Capacitor X5R 1210	1210
C6	1	2.2uF	GRM32ER72A225KA35L	MuRata	CAP, CERM, 2.2uF, 100V, +/-10%, X7R, 1210	1210
C7	1	820pF	GRM155R71H821KA01D	MuRata	CAP, CERM, 820 pF, 50 V, +/- 10%, X7R, 0402	0402
C8	1	15pF	CC0402JRNPO9BN150	Yageo America	CAP, CERM, 15 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
C9	1	0.1uF	06035C104KAT2A	AVX	CAP, CERM, 0.1 μF, 50 V, +/- 10%, X7R, 0603	0603
C10	1	4.7uF	GRM31CR71H475KA12L	MuRata	CAP 4.7µF ±10% 50V Ceramic X7R 1206	1206
C11, C13	2	1uF	C1608X7R1C105K080AC	TDK	CAP, CERM, 1 µF, 16 V, +/- 10%, X7R, 0603	0603
C12	1	0.022uF	C0603C223K3RACTU	Kemet	CAP, CERM, 0.022 μF, 25 V, +/- 10%, X7R, 0603	0603
C14, C15, C16	3	470uF	35ZLG470MEFC10X20	Rubycon	470μF 35V CAP ALUM CAN 4000 Hrs @ 105 ℃	10x20
C17	1	0.1uF	08055C104KAT2A	AVX Corporation	CAP, CERM, 0.1 μF, 50 V, +/- 10%, X7R, 0805	0805
C23, C24, C33,	6	0.1uF	885012105016	Wurth Elektronik	CAP, CERM, 0.1 μF, 16 V, +/- 20%, X5R, 0402	0402
C34, C35, C36						
C26	1	0.47uF	C0805C474K4RACTU	Kemet	CAP, CERM, 0.47 μF, 16 V, +/- 10%, X7R, 0805	0805
C27, C29, C31	3	10uF	0805YD106MAT2A	AVX	CAP, CERM, 10uF, 16V, +/-20%, X5R, 0805	0805
C28, C30, C32	3	0.1uF	0603YC104JAT2A	AVX	CAP, CERM, 0.1 μF, 16 V, +/- 5%, X7R, 0603	0603
C37	1	2200pF	GRM155R71H222KA01D	MuRata	CAP, CERM, 2200 pF, 50 V, +/- 10%, X7R, 0402	0402
C38, C39, C40	3	1000pF	885012205061	Wurth Elektronik	CAP, CERM, 1000 pF, 50 V, +/- 10%, X7R, 0402	0402
C43, C44, C45	3	3300pF	CGA2B2X7R1H332K050BA	TDK	CAP, CERM, 3300 pF, 50 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0402	0402
D1	1	30V	SMAJ30CA-E3/61	Vishay Semiconductor Diodes	s TVS DIODE 30VWM 48.4VC DO214AC	SMA
D2	1	RED	150060RS75000	Wurth Elektronics Inc	LED RED CLEAR 0603 SMD	LED_0603
D3	1	YELLOW	150060YS75000	Wurth Elektronics Inc	LED YELLOW CLEAR 0603 SMD	LED_0603
D4	1	GREEN	150060GS75000	Wurth Elektronics Inc	LED, Green, SMD	LED_0603
J1	1		800-10-003-10-001000	Mill-Max	Header, 100mil, 3x1, TH	Header, 3x1, 100mil, TH
J2, J6	2		800-10-002-10-001000	Mill-Max	Header, 100mil, 2x1, TH	Header, 2x1, 100mil, TH
J3	1	PEC04SAA N	PEC04SAAN	Sullins	Header, Male 4-pin, 100mil spacing,	0.100 inch x 4
J4	1		800-10-005-10-001000	Mill-Max	Header, 100mil, 5x1, TH	Header, 5x1, 100mil, TH
J5	1		PEC07DAAN	Sullins Connector Solutions	Header, 100mil, 7x2, Tin, TH	Header, 7x2, 100mil, Tin
L1	1	120uH	SDR0302-121KL	Bourns	Inductor, Drum Core, Ferrite, 120uH, 0.22A, 3.2 ohm, SMD	3x2.5x2.8mm
R1, R2, R3, R4, R5, R6, R7, R8, R9, R10, R11, R12, R37		3.3	CRCW06033R30JNEA	Vishay-Dale	RES, 3.3, 5%, 0.1 W, 0603	0603
R13, R15	2	0.001	CSS2H-2512R-1L00F	Bourns Inc.	RES SMD 0.001 OHM 1% 5W 2512	2512
	2	0.001		Dourno ino.		2012

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
R14	1	30.9k	CRCW040230K9FKED	Vishay-Dale	RES, 30.9k ohm, 1%, 0.063W, 0402	0402
R16	1	196k	CRCW0402196KFKED	Vishay-Dale	RES, 196 k, 1%, 0.063 W, 0402	0402
R19	1	53.6k	CRCW040253K6FKED	Vishay-Dale	RES, 53.6 k, 1%, 0.063 W, 0402	0402
R20	1	10.0k	CRCW040210K0FKED	Vishay-Dale	RES, 10.0k ohm, 1%, 0.063W, 0402	0402
R21	1	49.9k	CRCW040249K9FKED	Vishay-Dale	RES, 49.9 k, 1%, 0.063 W, 0402	0402
R22	1	97.6k	CRCW040297K6FKED	Vishay-Dale	RES, 97.6k ohm, 1%, 0.063W, 0402	0402
R23	1	2M	RC0603FR-072ML	Yageo	RES SMD 2M OHM 1% 1/10W 0603	0603
R24, R26, R56, R57	4	0	CRCW04020000Z0ED	Vishay-Dale	RES, 0, 5%, 0.063 W, 0402	0402
R27, R29, R32, R34, R35, R50, R51, R52, R53, R54, R55	11	100	ERJ-2RKF1000X	Panasonic	RES, 100, 1%, 0.1 W, 0402	0402
R31	1	300k	RC0402FR-07300KL	Yageo	RES SMD 300K OHM 1% 1/16W 0402	0402
R33, R36, R42, R45	4	10.0k	CRCW040210K0FKED	Vishay-Dale	RES, 10.0 k, 1%, 0.063 W, 0402	0402
R38, R40, R41	3	1.0k	CRCW06031K00JNEA	Vishay-Dale	RES, 1.0 k, 5%, 0.1 W, 0603	0603
R43, R46	2	1.00Meg	ERJ-2RKF1004X	Panasonic	RES, 1.00 M, 1%, 0.1 W, 0402	0402
R44	1	47.5k	CRCW040247K5FKED	Vishay-Dale	RES, 47.5 k, 1%, 0.063 W, 0402	0402
R47, R48, R49	3	3.3k	CRCW04023K30JNED	Vishay-Dale	RES, 3.3 k, 5%, 0.063 W, 0402	0402
S1	1		434121025816	Wurth Elektronik	Switch, Tactile, SPST, 12 V, SMD	SMD, 6x3.9mm
U1, U2, U3, U4, U6, U7	6		CSD88584Q5DC	Texas Instruments	40 V Half-Bridge NexFE Power Block, DMM0022A	DMM0022A
U5	1	TPS54061D RBR	TPS54061DRBR	Texas Instruments	IC, 60V/0.2A Synchronous Buck Regulator	QFN
U8	1		DRV8323SRTAR	Texas Instruments	60-V Three-Phase Smart Gate Driver, RHA0040B	WQFN
U9	1		MSP430F5132IDA	Texas Instruments	25 MHz Mixed Signal Microcontroller with 8 KB Flash, 1024 B SRAM and 29 GPIOs, -40 to 85 degC, 38-pin SOP (DA), Green (RoHS & no Sb/Br)	DA0038A
U10	1		LMT87DCKR	Texas Instruments	SC70 Analog Temperature Sensor with Class-AB Output, DCK0005A	DCK0005A
C25, C46, C47, C48	0	1000pF	885012205061	Wurth Elektronik	CAP, CERM, 1000 pF, 50 V, +/- 10%, X7R, 0402	0402
R17, R18, R25, R28, R30	0	100	ERJ-2RKF1000X	Panasonic	RES, 100, 1%, 0.1 W, 0402	0402

## IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ('TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your noncompliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products <a href="http://www.ti.com/sc/docs/stdterms.htm">http://www.ti.com/sc/docs/stdterms.htm</a>), evaluation modules, and samples (<a href="http://www.ti.com/sc/docs/stdterms.htm">http://www.ti.com/sc/docs/stdterms.htm</a>), evaluation

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2017, Texas Instruments Incorporated