

Symbol	Quantity	Finished Hole Size	Plated	Hole Type	Drill Layer Pair	Hole Tolerance
✕	2	62.99mil (1.600mm)	NPTH	Round	Top Layer - Bottom Layer	±1.97mil
⚙	2	86.61mil (2.200mm)	NPTH	Round	Top Layer - Bottom Layer	
C	2	124.02mil (3.150mm)	NPTH	Round	Top Layer - Bottom Layer	
B	400	7.87mil (0.200mm)	PTH	Round	Top Layer - Bottom Layer	
⚙	2	27.56mil (0.700mm)	PTH	Round	Top Layer - Bottom Layer	
⚙	12	35.43mil (0.900mm)	PTH	Round	Top Layer - Bottom Layer	
✕	2	39.37mil (1.000mm)	PTH	Round	Top Layer - Bottom Layer	
□	29	40.00mil (1.016mm)	PTH	Round	Top Layer - Bottom Layer	
⊠	4	40.16mil (1.020mm)	PTH	Round	Top Layer - Bottom Layer	
○	2	45.28mil (1.150mm)	PTH	Round	Top Layer - Bottom Layer	
■	2	59.06mil (1.500mm)	PTH	Round	Top Layer - Bottom Layer	±1.97mil
D	2	62.99mil (1.600mm)	PTH	Round	Top Layer - Bottom Layer	
E	4	63.78mil (1.620mm)	PTH	Round	Top Layer - Bottom Layer	
◇	8	66.93mil (1.700mm)	PTH	Round	Top Layer - Bottom Layer	
●	2	98.43mil (2.500mm)	PTH	Round	Top Layer - Bottom Layer	
▼	4	125.98mil (3.200mm)	PTH	Round	Top Layer - Bottom Layer	
⌵	2	23.62mil (0.600mm)	PTH	Slot	Top Layer - Bottom Layer	
⚙	2	27.56mil (0.700mm)	PTH	Slot	Top Layer - Bottom Layer	
▽	3	31.50mil (0.800mm)	PTH	Slot	Top Layer - Bottom Layer	
A	2	39.37mil (1.000mm)	PTH	Slot	Top Layer - Bottom Layer	
G	2	39.37mil (1.000mm)	PTH	Slot	Top Layer - Bottom Layer	
H	2	39.37mil (1.000mm)	PTH	Slot	Top Layer - Bottom Layer	
492 Total						
Slot definitions : Routed Path Length = Calculated from tool start centre position to tool end centre position. Hole Length = Routed Path Length + Tool Size = Slot length as defined in the PCB layout						

1	2	3	4	5	6

