## BILL OF MATERIALS for DRV2605EVM-CT\_RevA-BOM

DESIGN LEAD:

## Brian Burk

Page 1 of 3

April 27 2012

SEMICONDUCTORS									
TEM	MANU PARTNUM	QTY	<b>REF DESIGNATORS</b>	VENDOR PARTNUM	DESCRIPTION	VENDOR	MANUFACTURER		
						TEXAS			
					HAPTIC DRIVER AUTO DETECT FOR LRA AND ERM	INSTRUMEN			
	DRV2605YZF	1	U1	DRV2605YZF	WCSP9-YZF ROHS	TS	TEXAS INSTRUMENTS		
	TXS0102DCTR	1	U4	296-21978-1	2-BIT BIDIR LEVEL TRANSLATOR SSOP8-DCT ROHS	DIGI-KEY	TEXAS INSTRUMENTS		
				595-	MIXED SIGNAL MICRO 16KB FLASH 512B RAM				
	MSP430G2553IRHB32T	1	U2	P430G2553IRHB32T	QFN32-RHB ROHS	MOUSER	TEXAS INSTRUMENTS		
					VOLT REG 3.3V 400MA LDO CAP FREE NMOS				
Ļ	TPS73633MDBVREP	1	U3	296-21283-1	SOT23-DBV5 ROHS	DIGI-KEY	TEXAS INSTRUMENTS		
					IEC LEVEL 4 ESD-PROTECTED 0.75-OHM ANALOG				
	TS5A12301EYFPR	1	U5	296-23757-1-ND	SWITCH WCSP6-YFP ROHS	DIGI-KEY	TEXAS INSTRUMENTS		
i	LTST-C190KGKT	2	5V,ACTIVE	160-1435-1-ND	LED,GREEN,2.0V,SMD0603,ROHS	DIGI-KEY	LITE-ON INC.		
	LNJ037X8ARA	5	M0,M1,M2,M3,M4	LNJ037X8ARACT-ND	LED, WHITE 2.9V SMD0805 ROHS	DIGI-KEY	PANASONIC		
6	SML-LXT0805SRW-TR	1	B1	67-1555-1	LED, RED 2.0V SMD0805 ROHS	DIGI-KEY	LUMEX OPTO		
)	SML-LXT0805GW-TR	1	B2	67-1553-1	LED, GREEN 2.0V SMD0805 ROHS	DIGI-KEY	LUMEX OPTO		
0	SML-LXT0805YW-TR	1	B3	67-1554-1	LED, YELLOW 2.0V SMD0805 ROHS	DIGI-KEY	LUMEX OPTO		
1	LTST-C171TBKT	1	B4	160-1645-1-ND	LED, BLUE 3.3V SMD0805 ROHS	DIGI-KEY	LITE-ON INC.		

	CAPACITORS									
ITEM	MANU PARTNUM	QTY	REF DESIGNA	TORS VENDOR PARTNUM	DESCRIPTION	VENDOR	MANUFACTURER			
12	GRM155R71C104KA88D	3	C1,C2,C12	490-3261-1-ND	CAP SMD0402 CERM 0.1UFD 16V X7R 10% ROHS	DIGI-KEY	MURATA			
13	C1005X5R0J104K	3	C8,C9,C10	445-1266-1	CAP SMD0402 CERM 0.1UFD 6.3V 10% X5R ROHS	DIGI-KEY	TDK CORP			
4	0805YD106KAT2A	1	C6	478-5165-1	CAP SMD0805 CERM 10UFD 16V X5R 10% ROHS	DIGI-KEY	AVX			
5	GRM155R60J105KE19D	1	C7	490-1320-1	CAP SMD0402 CERM 1.0UFD 6.3V X5R 10% ROHS	DIGI-KEY	MURATA			
6	C1005X5R0J104K	1	C11	445-1266-1	CAP SMD0402 CERM 0.1UFD 6.3V 10% X5R ROHS	DIGI-KEY	TDK CORP			
17	C0402C471K5RACTU	2	C14,C15	399-1025-1	CAP SMD0402 CERM 470PFD 50V 10% X7R ROHS	DIGI-KEY	КЕМЕТ			
8	TCTAL0J107M8R	1	C5	511-1498-1-ND	CAP TANT1206 100UFD 6.3V 20% TCT SERIES ROH	S DIGI-KEY	ROHM			

## BILL OF MATERIALS for DRV2605EVM-CT\_RevA-BOM

DESIGN LEAD:

Page 2 of 3

April 27 2012

RESISTORS									
ITEM	MANU PARTNUM	QTY	<b>REF DESIGNATORS</b>	VENDOR PARTNUM	DESCRIPTION	VENDOR	MANUFACTURER		
40		4	D7	Do JOKI OT ND	RESISTOR SMD0402 THICK FILM 9.76K OHMS 1/10W		DANACONIC		
19	ERJ-2RKF9761X	1	R7	P9.76KLCT-ND	1% ROHS ZERO OHM JUMPER SMT 0402 0 OHM 1/16W,5%	DIGI-KEY	PANASONIC STACKPOLE		
20	RMCF0402ZT0R00	5	R8,R32,R33,R34,R36	RMCF0402ZT0R00CT	ROHS RESISTOR SMD0402 THICK FILM 511 OHMS 1%	DIGI-KEY	ELECTRONICS		
21	RC0402FR-07511RL	5	R9,R11,R12,R13,R14	311-511LRCT-ND	1/16W ROHS	DIGI-KEY	YAGEO		
22	ERJ-2GEJ152	1	R26	RMCF0603ZT0R00CT-	RESISTOR,SMT,0402,THICK FILM,5%,1/16W,1.5K		Panasonic STACKPOLE		
23	RMCF0603ZT0R00	1	R5	ND	RESISTOR SMD0603 ZERO OHMS 1/10W ROHS	DIGI-KEY	ELECTRONICS		
24	ERJ-2RKF2490X	5	R15,R16,R17,R18,R19	P249LTR-ND	RESISTOR,SMT,0402,249 OHM,1%,1/16W ZERO OHM JUMPER SMT 0402 0 OHM 1/16W,5%	DIGI-KEY	Panasonic		
25	CRCW04020000Z0ED	2	R40,R43	541-0.0JCT	ROHS RESISTOR SMD0402 THICK FILM 100K OHMS 1/16W	DIGI-KEY	VISHAY		
26	ERJ-2GEJ104	2	R50,R51	P100KJCT	5% ROHS	DIGI-KEY	PANASONIC		

	FERRITE BEADS									
ITEM	MANU PARTNUM	QTY	REF DESIGNATORS	VENDOR PARTNUM	DESCRIPTION	VENDOR	MANUFACTURER			
27	MPZ2012S601A	2	FB1,FB2	445-2206-1	FERRITE BEAD SMD0805 600 Ohms 2A ROHS	DIGI-KEY	TDK			

	HEADERS, JACKS, AND SHUNTS									
ITEM	MANU PARTNUM	QTY	REF DESIGNATORS	VENDOR PARTNUM	DESCRIPTION	VENDOR	MANUFACTURER			
28	LPPB061NGCN-RC	1	SBW	S9010E-06	HEADER THRU FEMALE 1X6-RA 50LS GOLD ROHS	DIGI-KEY	SULLINS			
29	PBC03SAAN	3	DRV,I2C,MSP	S1011E-03-ND	HEADER THRU MALE 3 PIN 100LS GOLD ROHS	DIGI-KEY	SULLINS			
30	PBC02SAAN	1	JP2	S1011E-02	HEADER THRU MALE 2 PIN 100LS GOLD ROHS	DIGI-KEY	SULLINS			
31	PBC02SAAN	3	JP1,JP3,JP4		HEADER THRU MALE 2 PIN 100LS GOLD ROHS	DIGI-KEY	SULLINS			
32	UX60-MB-5ST	1	USB	H2959CT	JACK USB MINIB SMT-RA 5PIN ROHS JACK AUDIO-STEREO MINI(3.5MM ,3-COND SMT-RA	DIGI-KEY	HIROSE			
33	SJ-3523-SMT	1	Audio	CP-3523SJCT-ND	ROHS	DIGI-KEY	CUI STACK			
34	SPC02SYAN	6	MSP (2-3), DRV (2-3), JP1, JP2, JP3, JP4	S9001-ND	SHUNT BLACK AU FLASH 0.100LS CLOSED TOP ROHS TERMINAL BLOCK MPT COMBICON 2PIN 6A/125V	DIGI-KEY	SULLINS			
35	1725656	2	OUT,VBAT	277-1273	GREEN 100LS ROHS	DIGI-KEY	PHOENIX CONTACT			

	DESIGN LEAD		Brian E	Burk	Page 3 of 3	A	opril 27 2012				
	TESTPOINTS AND SWITCHES										
TEN	1 MANU PARTNUM	QTY	<b>REF DESIGNATORS</b>	VENDOR PARTNUM	DESCRIPTION	VENDOR	MANUFACTURER				
36	5011	2	GND,TP1 ((Solder so that color ring is secured)	5011K	PC TESTPOINT BLACK 063 HOLE ROHS	DIGI-KEY					
7	5003	4	PWM,ENIN,OUT+,OUT- ((Solder so that color ring is secured)	5003K	PC TESTPOINT, ORANGE, ROHS	DIGI-KEY	KEYSTONE ELECTRON				
EN	1 MANU PARTNUM	QTY	REF DESIGNATORS	VENDOR PARTNUM	DESCRIPTION	VENDOR	MANUFACTURER				
					ACUTATOR VIBRATION MOTOR 1,3V 9000 RPM	•					
8	NRS-2574	1	AVM1	NRS-2574	ROHS	SANYO	SANYO				
9	ELV1036A	1	-	-	ACTUATOR - LINEAR VIBRATOR, 2VRMS Metal Block (Custom Block, Heavy Metal, See metal	AAC	AAC				
0	-	1	-	-	block spec)	Heavy Metal	Heavy Metal				
1	3-5-468MP	1	-	3M9724-ND	TAPE TRANSFER ADHESIVE 3" X 5YD	DIGI-KEY	3M				
2	2-5-4466W	1	-	3M9962-ND	TAPE POLY FOAM 2" x 5YD	DIGI-KEY	3M				

	COMPONENTS NOT ASSEMBLED										
	TestPoint_SMD-										
43	Square_2.0mm	2	LRA_OUT+,LRA_OUT-		TESTPOINT SMD SQUARE 2.0mm						
			R20,R21,R22,R23,R24,								
44	R0402_DNP	9	R25,R30,R31,R35		R0402_DNP						
				RMCF0603ZT0R00CT-			STACKPOLE				
45	R0603_DNP	1	R4	ND	R0603_DNP	DIGI-KEY	ELECTRONICS				
46	R0402_DNP	1	R41	P4.99KLCT-ND	R0402_DNP	DIGI-KEY	PANASONIC				
47	R0402_DNP	1	R42	541-0.0JCT	R0402_DNP	DIGI-KEY	VISHAY				

## **IMPORTANT NOTICE FOR TI REFERENCE DESIGNS**

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. **TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design.** TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have **not** been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2013, Texas Instruments Incorporated