

Design of Differential Filters for High-Speed Signal Chains

Ken Chan

High Speed - Wireless Infrastructure

ABSTRACT

Differential filters have many desirable attributes. The task of designing differential filters can seem daunting at first. Single-ended filters designed in any filter design package can be converted to a differential implementation. This application report explores simple conversion techniques for low-pass, high-pass, and band-pass LC filters.

1 Introduction

Differential signals have many desirable attributes in high-speed signal chains: namely, common-mode rejection from a balanced signal path and matched filter response, immunity from single-ended component parasitic effects, decoupling the signal from requiring a ground reference, and rejection of even-order harmonics. However, most LC filter design information, techniques, and software are for single-ended systems. This application report highlights some simple translations that can be made to convert the single-ended designs to fully differential designs. Some examples are used to demonstrate these translations.

The design of single-ended passive analog LC filters has been simplified greatly by various pieces of software that can be obtained freely on the Internet. An Internet search for *LC filter design* yields many results, any of which can be used for this tutorial.

This application report uses ELSIE (i.e., *LC*) which is freely available for download from the following link as a trial version with some limitations on filter order and usage. For commercial applications, the full version should be purchased. For purposes of this application report, the free version is sufficient.

http://www.tonnesoftware.com/elsiedownload.html

The SPICE simulator used in this tutorial is the TINA-TI SPICE simulator which can be downloaded from the Texas Instruments Web site at the following link.

http://focus.ti.com/docs/toolsw/folders/print/tina-ti.html

The full TINA version can be purchased from its vendor for access to its full feature set.

2 Single-Ended to Differential-Ended Filter Translation:

2.1 Low-Pass, High-Pass, and Band-Pass Filter Implementations

The process of designing a differential filter requires the design of a single-ended filter that meets the filter requirements. Freely available tools may be used to generate a single-ended filter with the desirable frequency response. The low-pass, high-pass and band-pass differential filter implementations are discussed in the following sections.

The single-ended LC low-pass filter can be converted to a differential filter by repeating and folding the design around GND to create the Vin+ and Vin-. The GND is removed and the center capacitor values are recalculated: the C is half-value (sum of two series C). The L in the horizontal parallel series paths are kept the same and the load resistor is doubled (sum of two series R). The process is illustrated in Figure 1.






Figure 1. Conversion Process From Single-Ended to a Differential Filter




Figure 2. Shunt Capacitor Input Low-Pass Filter




Figure 3. Series Inductor Low-Pass Filter

All four of these produce the same response as shown in Figure 4.






Figure 4. Low-Pass Filter Response for All Four Low-Pass Filters.

Similar circuits can be translated for a simple LC high-pass filter. The circuit is folded along the GND point, the vertical series elements are added and the horizontal elements remain the same. This results in doubling the vertical inductors and load, similar to the approach used for the low-pass filters.




Figure 5. Series Capacitor Input High-Pass Filter






Figure 6. Shunt Inductor High-Pass Filter

All four high-pass filters have the same frequency response as shown in Figure 7.




Figure 7. Frequency Response for All Four High-Pass Filters

This same principle holds for more complex BPF architectures. The single-ended filter is reflected around the GND point, the GND is removed, and the middle elements are added together. Figure 8 provides an example of a third-order Butterworth BPF.






Figure 8. Example of Third-Order Butterworth Band-Pass Filter




Figure 9. Frequency Response of the Third-Order Butterworth Band-Pass Filter

Figure 10 provides an example of a third-order Cauer BPF with some parallel horizontal elements. Performing the translation results in the network on the right. Both these filters have the same frequency response.






Figure 10. Example of Third-Order Cauer Band-Pass Filter




Figure 11. Frequency Response of Third-Order Cauer Band-Pass Filter

3 Implementation and Simulation Notes

Note that all of the networks should show a 6-dB loss due to the voltage divider created by the $100-\Omega$ source impedance and the $100-\Omega$ termination impedance. In the voltage source simulation, the transfer function response is determined with the voltage signal source at the input to the source impedance, in effect grouping the response of the source-to-termination resistor divider into the response of the filter. A 2x VCVS was used at the output of the voltage source to account for this fixed 6-dB loss in the resistor divider and to highlight the actual response of the LC network.



www.ti.com Summary

4 Summary

The task of designing differential LC filters can seem daunting at first. But by using some basic single-ended filter design tools and applying some simple translations, it is possible to design differential LC filters to have the same response as the single-ended filter. The examples in this document have shown that this method can be applied to any singled-ended LC filter network to produce a passive equivalent differential filter.

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products		Applications	
Amplifiers	amplifier.ti.com	Audio	www.ti.com/audio
Data Converters	dataconverter.ti.com	Automotive	www.ti.com/automotive
DLP® Products	www.dlp.com	Communications and Telecom	www.ti.com/communications
DSP	<u>dsp.ti.com</u>	Computers and Peripherals	www.ti.com/computers
Clocks and Timers	www.ti.com/clocks	Consumer Electronics	www.ti.com/consumer-apps
Interface	interface.ti.com	Energy	www.ti.com/energy
Logic	logic.ti.com	Industrial	www.ti.com/industrial
Power Mgmt	power.ti.com	Medical	www.ti.com/medical
Microcontrollers	microcontroller.ti.com	Security	www.ti.com/security
RFID	www.ti-rfid.com	Space, Avionics & Defense	www.ti.com/space-avionics-defense
RF/IF and ZigBee® Solutions	www.ti.com/lprf	Video and Imaging	www.ti.com/video
		Wireless	www.ti.com/wireless-apps