


Delta Threshold 10.00%


ELDRS Report
UC1843

ELDRS Report
UC1843

OUTPUT FREQ; VCC9.5V						
Test Site	MMT		MTF			
Tester	LTX		LTX			
Test Number	XPM01302		XPM01302			
Unit	khz		khz			
Max Limit	57		57			
Min Limit	47		47			
Krads	Serial #	Pre_Rad_25c	Post_Rad_50K	Delta	Delta %	% of Limit Range
50	409	52.566	52.952	-0.386	-0.73%	3.86%
50	410	52.879	53.245	-0.366	-0.69%	3.66%
50	411	52.907	53.273	-0.366	-0.69%	3.66%
50	412	52.626	53.029	-0.403	-0.77%	4.03%
50	413	52.444	52.807	-0.363	-0.69%	3.63%
50	414	52.172	52.543	-0.372	-0.71%	3.72%
50	418	52.651	53.001	-0.351	-0.67%	3.51%
50	421	52.107	52.433	-0.326	-0.63%	3.26%
50	422	52.514	52.844	-0.330	-0.63%	3.30%
50	423	52.914	53.227	-0.313	-0.59%	3.13%
50	424	52.416	52.812	-0.396	-0.76%	3.96%
50	427	52.611	53.035	-0.424	-0.81%	4.24%
50	429	52.578	53.012	-0.434	-0.82%	4.34%
50	431	52.671	53.066	-0.395	-0.75%	3.95%
50	432	52.399	52.833	-0.434	-0.83%	4.34%
50	433	52.609	53.052	-0.443	-0.84%	4.43%
50	434	52.473	52.879	-0.406	-0.77%	4.06%
50	435	52.718	53.165	-0.447	-0.85%	4.47%
50	436	52.758	53.181	-0.423	-0.80%	4.23%
50	437	52.134	52.588	-0.454	-0.87%	4.54%
0	442	52.852	52.978	-0.126	-0.24%	1.26%
Max		52.914	53.273	-0.126	-0.24%	4.54%
Average		52.571	52.950	-0.379	-0.72%	3.79%
Min		52.107	52.433	-0.454	-0.87%	1.26%
Std Dev		0.238	0.229	0.071	0.14%	0.71%




OUTPUT FREQ; VCC9.5V		
Test Site	MMT	
Tester	LTX	
Test Number	XPM01302	
Max Limit	57	khz
Min Limit	47	khz
Krads	0	50
LL	47.000	47.000
Min	52.978	52.433
Average	52.978	52.949
Max	52.978	53.273
UL	57.000	57.000




ELDRS Report
UC1843

OUTPUT HIGH LEVEL; VCC9.5V						
Test Site	MMT		MTF			
Tester	LTX		LTX			
Test Number	XPM01302		XPM01302			
Unit	v		v			
Max Limit	9.5		9.5			
Min Limit	7		7			
Krads	Serial #	Pre_Rad_25c	Post_Rad_50K	Delta	Delta %	% of Limit Range
50	409	8.079	8.072	0.007	0.09%	0.30%
50	410	8.083	8.076	0.008	0.10%	0.31%
50	411	8.081	8.070	0.011	0.13%	0.43%
50	412	8.081	8.071	0.011	0.13%	0.42%
50	413	8.081	8.068	0.012	0.15%	0.49%
50	414	8.083	8.073	0.009	0.12%	0.38%
50	418	8.080	8.071	0.010	0.12%	0.38%
50	421	8.084	8.077	0.007	0.09%	0.30%
50	422	8.081	8.071	0.010	0.13%	0.42%
50	423	8.084	8.080	0.005	0.06%	0.18%
50	424	8.083	8.073	0.010	0.13%	0.41%
50	427	8.084	8.077	0.007	0.09%	0.28%
50	429	8.081	8.071	0.010	0.12%	0.38%
50	431	8.083	8.076	0.008	0.10%	0.31%
50	432	8.080	8.074	0.006	0.07%	0.24%
50	433	8.080	8.071	0.010	0.12%	0.38%
50	434	8.083	8.073	0.010	0.12%	0.40%
50	435	8.082	8.073	0.009	0.11%	0.35%
50	436	8.079	8.070	0.009	0.12%	0.37%
50	437	8.081	8.071	0.010	0.12%	0.40%
0	442	8.080	8.079	0.000	0.00%	0.01%
Max		8.084	8.080	0.012	0.15%	0.49%
Average		8.082	8.073	0.009	0.11%	0.34%
Min		8.079	8.068	0.000	0.00%	0.01%
Std Dev		0.002	0.003	0.003	0.03%	0.10%




OUTPUT HIGH LEVEL; VCC9.5V		
Test Site	MMT	
Tester	LTX	
Test Number	XPM01302	
Max Limit	9.5	v
Min Limit	7	v
Krads	0	50
LL	7.000	7.000
Min	8.079	8.068
Average	8.079	8.073
Max	8.079	8.080
UL	9.500	9.500




ELDRS Report
UC1843

OUTPUT LOW LEVEL; VCC9.5V						
Test Site	MMT		MTF			
Tester	LTX		LTX			
Test Number	XPM01302		XPM01302			
Unit	v		v			
Max Limit	0.4		0.4			
Min Limit	0		0			
Krads	Serial #	Pre_Rad_25c	Post_Rad_50K	Delta	Delta %	% of Limit Range
50	409	0.006	0.005	0.000	5.36%	0.07%
50	410	0.005	0.006	0.000	-7.69%	0.10%
50	411	0.005	0.005	0.000	-1.92%	0.02%
50	412	0.006	0.005	0.001	15.52%	0.22%
50	413	0.005	0.005	0.000	5.77%	0.07%
50	414	0.006	0.006	0.000	-3.57%	0.05%
50	418	0.005	0.005	0.001	9.62%	0.13%
50	421	0.006	0.005	0.001	8.62%	0.13%
50	422	0.005	0.006	-0.001	-11.54%	0.15%
50	423	0.006	0.006	0.000	0.00%	0.00%
50	424	0.006	0.006	0.000	1.75%	0.03%
50	427	0.006	0.005	0.000	5.36%	0.07%
50	429	0.006	0.005	0.001	8.77%	0.13%
50	431	0.006	0.006	0.000	0.00%	0.00%
50	432	0.005	0.005	0.000	5.77%	0.07%
50	433	0.006	0.005	0.001	8.62%	0.13%
50	434	0.006	0.006	0.000	-5.36%	0.08%
50	435	0.005	0.005	0.000	-8.16%	0.10%
50	436	0.006	0.006	0.000	0.00%	0.00%
50	437	0.005	0.005	0.000	5.77%	0.07%
0	442	0.005	0.005	0.000	5.77%	0.07%
Max		0.006	0.006	0.001	15.52%	0.22%
Average		0.005	0.005	0.000	2.31%	0.08%
Min		0.005	0.005	-0.001	-11.54%	0.00%
Std Dev		0.000	0.000	0.000	6.87%	0.06%




OUTPUT LOW LEVEL; VCC9.5V		
Test Site	MMT	
Tester	LTX	
Test Number	XPM01302	
Max Limit	0.4	v
Min Limit	0	v
Krads	0	50
LL	0.000	0.000
Min	0.005	0.005
Average	0.005	0.005
Max	0.005	0.006
UL	0.400	0.400




ELDRS Report
UC1843

PWR GND CHECK OK						
Test Site	MMT		MTF			
Tester	LTX		LTX			
Test Number	XPM01302		XPM01302			
Unit	v		v			
Max Limit	1.5		1.5			
Min Limit	0.5		0.5			
Krads	Serial #	Pre_Rad_25c	Post_Rad_50K	Delta	Delta %	% of Limit Range
50	409	1.000	1.000	0.000	-0.04%	0.04%
50	410	1.000	1.000	-0.001	-0.08%	0.08%
50	411	1.000	1.001	-0.001	-0.08%	0.08%
50	412	1.000	1.000	-0.001	-0.06%	0.06%
50	413	1.000	1.000	0.000	-0.01%	0.01%
50	414	1.000	1.001	-0.001	-0.08%	0.08%
50	418	1.000	1.000	-0.001	-0.05%	0.05%
50	421	1.000	1.000	-0.001	-0.07%	0.07%
50	422	1.000	1.000	0.000	-0.02%	0.02%
50	423	1.000	1.000	0.000	-0.04%	0.04%
50	424	1.000	1.000	0.000	-0.03%	0.03%
50	427	1.000	1.000	0.000	-0.04%	0.04%
50	429	1.000	1.000	0.000	-0.04%	0.04%
50	431	1.000	1.000	-0.001	-0.06%	0.06%
50	432	1.000	1.000	-0.001	-0.05%	0.05%
50	433	0.999	1.000	-0.001	-0.11%	0.11%
50	434	0.999	1.001	-0.001	-0.11%	0.11%
50	435	1.000	1.000	0.000	-0.03%	0.03%
50	436	1.000	1.001	-0.001	-0.07%	0.07%
50	437	1.000	1.001	0.000	-0.05%	0.05%
0	442	1.000	1.000	-0.001	-0.08%	0.08%
Max		1.000	1.001	0.000	-0.01%	0.11%
Average		1.000	1.000	-0.001	-0.06%	0.06%
Min		0.999	1.000	-0.001	-0.11%	0.01%
Std Dev		0.000	0.000	0.000	0.03%	0.03%




PWR GND CHECK OK		
Test Site	MMT	
Tester	LTX	
Test Number	XPM01302	
Max Limit	1.5	v
Min Limit	0.5	v
Krads	0	50
LL	0.500	0.500
Min	1.001	1.000
Average	1.001	1.000
Max	1.001	1.001
UL	1.500	1.500




ELDRS Report
UC1843

Icc Standby/ Start-up Current; Vin7v						
Test Site	MMT		MTF			
Tester	LTX		LTX			
Test Number	XPM01302		XPM01302			
Unit	ma		ma			
Max Limit	0.97		0.97			
Min Limit	0.1		0.1			
Krads	Serial #	Pre_Rad_25c	Post_Rad_50K	Delta	Delta %	% of Limit Range
50	409	0.387	0.384	0.002	0.65%	0.29%
50	410	0.388	0.386	0.003	0.64%	0.29%
50	411	0.382	0.384	-0.002	-0.47%	0.21%
50	412	0.387	0.382	0.005	1.24%	0.55%
50	413	0.387	0.388	-0.002	-0.39%	0.17%
50	414	0.382	0.378	0.003	0.87%	0.38%
50	418	0.386	0.380	0.006	1.60%	0.71%
50	421	0.386	0.384	0.002	0.62%	0.28%
50	422	0.394	0.394	-0.001	-0.15%	0.07%
50	423	0.387	0.382	0.005	1.39%	0.62%
50	424	0.380	0.382	-0.002	-0.45%	0.20%
50	427	0.384	0.383	0.001	0.31%	0.14%
50	429	0.384	0.382	0.002	0.47%	0.21%
50	431	0.387	0.385	0.002	0.59%	0.26%
50	432	0.384	0.380	0.004	1.01%	0.45%
50	433	0.386	0.383	0.003	0.80%	0.36%
50	434	0.387	0.389	-0.001	-0.31%	0.14%
50	435	0.389	0.394	-0.005	-1.29%	0.57%
50	436	0.385	0.389	-0.003	-0.91%	0.40%
50	437	0.397	0.394	0.003	0.78%	0.36%
0	442	0.386	0.387	-0.001	-0.31%	0.14%
Max		0.397	0.394	0.006	1.60%	0.71%
Average		0.386	0.385	0.001	0.32%	0.32%
Min		0.380	0.378	-0.005	-1.29%	0.07%
Std Dev		0.004	0.005	0.003	0.78%	0.18%




Icc Standby/ Start-up Current;		
Test Site	MMT	
Tester	LTX	
Test Number	XPM01302	
Max Limit	0.97	ma
Min Limit	0.1	ma
Krads	0	50
LL	0.100	0.100
Min	0.387	0.378
Average	0.387	0.385
Max	0.387	0.394
UL	0.970	0.970




ELDRS Report
UC1843

*PWM UVLO Saturation; II1ma, Vin5v						
Test Site	MMT		MTF			
Tester	LTX		LTX			
Test Number	XPM01302		XPM01302			
Unit	v		v			
Max Limit	1		1			
Min Limit	0.005		0.005			
Krads	Serial #	Pre_Rad_25c	Post_Rad_50K	Delta	Delta %	% of Limit Range
50	409	0.068	0.069	-0.001	-1.02%	0.07%
50	410	0.068	0.069	-0.001	-1.63%	0.11%
50	411	0.069	0.070	-0.001	-1.46%	0.10%
50	412	0.069	0.070	-0.001	-1.31%	0.09%
50	413	0.068	0.068	-0.001	-0.88%	0.06%
50	414	0.068	0.071	-0.002	-3.07%	0.21%
50	418	0.069	0.069	-0.001	-1.02%	0.07%
50	421	0.066	0.067	-0.001	-1.67%	0.11%
50	422	0.067	0.068	-0.001	-1.34%	0.09%
50	423	0.068	0.069	-0.001	-1.48%	0.10%
50	424	0.068	0.070	-0.002	-2.35%	0.16%
50	427	0.068	0.069	-0.002	-2.52%	0.17%
50	429	0.069	0.071	-0.002	-2.45%	0.17%
50	431	0.067	0.069	-0.002	-2.53%	0.17%
50	432	0.070	0.072	-0.002	-2.73%	0.19%
50	433	0.069	0.072	-0.003	-4.32%	0.30%
50	434	0.067	0.070	-0.003	-4.01%	0.27%
50	435	0.067	0.069	-0.002	-3.15%	0.21%
50	436	0.068	0.071	-0.003	-4.25%	0.29%
50	437	0.067	0.069	-0.002	-3.00%	0.20%
0	442	0.068	0.067	0.001	1.91%	0.13%
Max		0.070	0.072	0.001	1.91%	0.30%
Average		0.068	0.069	-0.001	-2.11%	0.16%
Min		0.066	0.067	-0.003	-4.32%	0.06%
Std Dev		0.001	0.001	0.001	1.40%	0.07%




*PWM UVLO Saturation; II1ma, Vin5v		
Test Site	MMT	
Tester	LTX	
Test Number	XPM01302	
Max Limit	1	v
Min Limit	0.005	v
Krads	0	50
LL	0.005	0.005
Min	0.067	0.067
Average	0.067	0.070
Max	0.067	0.073
UL	1.000	1.000




ELDRS Report
UC1843

Icc Operating Current; Vin15v						
Test Site	MMT		MTF			
Tester	LTX		LTX			
Test Number	XPM01302		XPM01302			
Unit	ma		ma			
Max Limit	16.6		16.6			
Min Limit	2		2			
Krads	Serial #	Pre_Rad_25c	Post_Rad_50K	Delta	Delta %	% of Limit Range
50	409	13.270	13.099	0.172	1.29%	1.17%
50	410	13.008	12.853	0.155	1.19%	1.06%
50	411	13.172	12.999	0.173	1.32%	1.19%
50	412	13.040	12.877	0.163	1.25%	1.12%
50	413	13.253	13.086	0.167	1.26%	1.14%
50	414	13.121	12.942	0.179	1.36%	1.22%
50	418	13.173	13.005	0.168	1.27%	1.15%
50	421	13.333	13.158	0.175	1.31%	1.20%
50	422	13.210	13.038	0.172	1.30%	1.18%
50	423	13.074	12.896	0.178	1.36%	1.22%
50	424	13.159	13.018	0.141	1.07%	0.96%
50	427	13.204	13.056	0.148	1.12%	1.02%
50	429	13.207	13.051	0.156	1.18%	1.07%
50	431	13.139	12.991	0.148	1.12%	1.01%
50	432	13.126	12.978	0.148	1.13%	1.02%
50	433	13.197	13.052	0.146	1.10%	1.00%
50	434	13.143	13.006	0.137	1.04%	0.93%
50	435	13.372	13.218	0.154	1.15%	1.05%
50	436	13.325	13.170	0.155	1.16%	1.06%
50	437	13.349	13.195	0.154	1.15%	1.05%
0	442	13.132	13.129	0.003	0.03%	0.02%
Max		13.372	13.218	0.179	1.36%	1.22%
Average		13.191	13.039	0.152	1.15%	1.04%
Min		13.008	12.853	0.003	0.03%	0.02%
Std Dev		0.099	0.101	0.036	0.28%	0.25%




Icc Operating Current; Vin15v		
Test Site	MMT	
Tester	LTX	
Test Number	XPM01302	
Max Limit	16.6	ma
Min Limit	2	ma
Krads	0	50
LL	2.000	2.000
Min	13.129	12.853
Average	13.129	13.034
Max	13.129	13.218
UL	16.600	16.600




ELDRS Report
UC1843

Icc Operating Current; Vin30v						
Test Site	MMT		MTF			
Tester	LTX		LTX			
Test Number	XPM01302		XPM01302			
Unit	ma		ma			
Max Limit	17.9		17.9			
Min Limit	2		2			
Krads	Serial #	Pre_Rad_25c	Post_Rad_50K	Delta	Delta %	% of Limit Range
50	409	14.109	13.939	0.170	1.21%	1.07%
50	410	13.828	13.665	0.163	1.18%	1.02%
50	411	13.990	13.831	0.159	1.13%	1.00%
50	412	13.865	13.698	0.167	1.20%	1.05%
50	413	14.086	13.916	0.170	1.21%	1.07%
50	414	13.938	13.756	0.182	1.31%	1.14%
50	418	13.984	13.825	0.159	1.14%	1.00%
50	421	14.150	13.974	0.175	1.24%	1.10%
50	422	14.043	13.876	0.167	1.19%	1.05%
50	423	13.902	13.718	0.184	1.32%	1.16%
50	424	13.969	13.835	0.135	0.96%	0.85%
50	427	14.018	13.881	0.137	0.98%	0.86%
50	429	14.044	13.891	0.153	1.09%	0.96%
50	431	13.958	13.816	0.142	1.02%	0.89%
50	432	13.942	13.795	0.147	1.06%	0.93%
50	433	14.025	13.883	0.142	1.01%	0.89%
50	434	13.958	13.825	0.133	0.95%	0.84%
50	435	14.211	14.057	0.154	1.08%	0.97%
50	436	14.164	13.995	0.169	1.19%	1.06%
50	437	14.201	14.040	0.161	1.13%	1.01%
0	442	13.956	13.959	-0.003	-0.02%	0.02%
Max		14.211	14.057	0.184	1.32%	1.16%
Average		14.016	13.865	0.151	1.08%	0.95%
Min		13.828	13.665	-0.003	-0.02%	0.02%
Std Dev		0.106	0.107	0.038	0.27%	0.23%




Icc Operating Current; Vin30v		
Test Site	MMT	
Tester	LTX	
Test Number	XPM01302	
Max Limit	17.9	ma
Min Limit	2	ma
Krads	0	50
LL	2.000	2.000
Min	13.959	13.665
Average	13.959	13.861
Max	13.959	14.057
UL	17.900	17.900




ELDRS Report
UC1843

Reference Output Voltage; II1ma						
Test Site	MMT		MTF			
Tester	LTX		LTX			
Test Number	XPM01302		XPM01302			
Unit	v		v			
Max Limit	5.048		5.048			
Min Limit	4.954		4.954			
Krads	Serial #	Pre_Rad_25c	Post_Rad_50K	Delta	Delta %	% of Limit Range
50	409	5.017	5.004	0.012	0.25%	13.30%
50	410	4.963	4.950	0.012	0.25%	13.30%
50	411	5.017	5.002	0.015	0.30%	16.17%
50	412	4.978	4.965	0.013	0.26%	13.51%
50	413	5.019	5.004	0.015	0.30%	15.96%
50	414	4.982	4.967	0.016	0.31%	16.49%
50	418	5.005	4.991	0.013	0.27%	14.26%
50	421	5.028	5.014	0.014	0.28%	14.79%
50	422	4.960	4.947	0.014	0.28%	14.68%
50	423	4.955	4.941	0.014	0.29%	15.32%
50	424	4.993	4.983	0.010	0.21%	11.17%
50	427	5.023	5.010	0.013	0.25%	13.51%
50	429	5.002	4.989	0.014	0.27%	14.36%
50	431	4.976	4.963	0.013	0.26%	13.94%
50	432	5.002	4.989	0.014	0.27%	14.36%
50	433	5.011	4.998	0.013	0.25%	13.40%
50	434	4.979	4.967	0.012	0.24%	12.87%
50	435	5.016	5.001	0.015	0.30%	15.96%
50	436	4.992	4.976	0.016	0.31%	16.49%
50	437	4.999	4.981	0.018	0.35%	18.83%
0	442	4.976	4.978	-0.002	-0.04%	2.13%
Max		5.028	5.014	0.018	0.35%	18.83%
Average		4.995	4.982	0.013	0.26%	14.04%
Min		4.955	4.941	-0.002	-0.04%	2.13%
Std Dev		0.022	0.021	0.004	0.08%	3.19%




Reference Output Voltage; II1ma		
Test Site	MMT	
Tester	LTX	
Test Number	XPM01302	
Max Limit	5.048	v
Min Limit	4.954	v
Krads	0	50
LL	4.954	4.954
Min	4.978	4.941
Average	4.978	4.982
Max	4.978	5.014
UL	5.048	5.048




ELDRS Report
UC1843

*Reference Output Voltage; Vin3						
Test Site	MMT		MTF			
Tester	LTX		LTX			
Test Number	XPM01302		XPM01302			
Unit	v		v			
Max Limit	5.065		5.065			
Min Limit	4.942		4.942			
Krads	Serial #	Pre_Rad_25c	Post_Rad_50K	Delta	Delta %	% of Limit Range
50	409	5.015	5.002	0.013	0.25%	10.33%
50	410	4.961	4.949	0.012	0.25%	10.16%
50	411	5.015	5.001	0.015	0.30%	12.11%
50	412	4.976	4.963	0.013	0.26%	10.49%
50	413	5.017	5.002	0.015	0.30%	12.36%
50	414	4.981	4.966	0.015	0.31%	12.36%
50	418	5.003	4.989	0.014	0.27%	11.06%
50	421	5.025	5.012	0.014	0.27%	11.06%
50	422	4.958	4.945	0.013	0.27%	10.73%
50	423	4.953	4.939	0.014	0.29%	11.71%
50	424	4.991	4.981	0.010	0.21%	8.37%
50	427	5.021	5.008	0.012	0.25%	10.08%
50	429	5.000	4.987	0.013	0.27%	10.89%
50	431	4.974	4.961	0.013	0.26%	10.57%
50	432	5.000	4.987	0.013	0.27%	10.81%
50	433	5.009	4.997	0.012	0.25%	10.00%
50	434	4.977	4.966	0.012	0.24%	9.59%
50	435	5.015	5.000	0.015	0.30%	12.03%
50	436	4.990	4.975	0.015	0.30%	12.36%
50	437	4.997	4.979	0.017	0.34%	13.98%
0	442	4.974	4.976	-0.002	-0.04%	1.79%
Max		5.025	5.012	0.017	0.34%	13.98%
Average		4.993	4.980	0.013	0.26%	10.61%
Min		4.953	4.939	-0.002	-0.04%	1.79%
Std Dev		0.022	0.021	0.004	0.08%	2.36%




*Reference Output Voltage; Vin		
Test Site	MMT	
Tester	LTX	
Test Number	XPM01302	
Max Limit	5.065	v
Min Limit	4.942	v
Krads	0	50
LL	4.942	4.942
Min	4.976	4.939
Average	4.976	4.980
Max	4.976	5.012
UL	5.065	5.065




ELDRS Report UC1843

*Startup Test; Ref Load20ma						
Test Site	MMT		MTF			
Tester	LTX		LTX			
Test Number	XPM01302		XPM01302			
Unit	v		v			
Max Limit	5.18		5.18			
Min Limit	4.82		4.82			
Krads	Serial #	Pre_Rad_25c	Post_Rad_50K	Delta	Delta %	% of Limit Range
50	409	5.007	4.994	0.013	0.25%	3.53%
50	410	4.952	4.939	0.014	0.27%	3.78%
50	411	5.007	4.991	0.016	0.32%	4.42%
50	412	4.967	4.954	0.013	0.27%	3.69%
50	413	5.009	4.992	0.016	0.32%	4.44%
50	414	4.972	4.956	0.016	0.32%	4.42%
50	418	4.994	4.980	0.014	0.28%	3.86%
50	421	5.016	5.002	0.014	0.29%	4.00%
50	422	4.950	4.935	0.015	0.30%	4.14%
50	423	4.944	4.930	0.014	0.29%	4.00%
50	424	4.983	4.972	0.010	0.21%	2.89%
50	427	5.013	4.999	0.014	0.28%	3.83%
50	429	4.991	4.978	0.014	0.28%	3.86%
50	431	4.965	4.952	0.013	0.27%	3.72%
50	432	4.991	4.978	0.013	0.27%	3.72%
50	433	5.000	4.987	0.013	0.26%	3.58%
50	434	4.968	4.956	0.012	0.24%	3.33%
50	435	5.006	4.991	0.015	0.30%	4.19%
50	436	4.982	4.965	0.017	0.35%	4.78%
50	437	4.989	4.970	0.018	0.37%	5.11%
0	442	4.965	4.967	-0.002	-0.05%	0.64%
Max		5.016	5.002	0.018	0.37%	5.11%
Average		4.984	4.971	0.013	0.27%	3.81%
Min		4.944	4.930	-0.002	-0.05%	0.64%
Std Dev		0.022	0.021	0.004	0.08%	0.88%




*Startup Test; Ref Load20ma		
Test Site	MMT	
Tester	LTX	
Test Number	XPM01302	
Max Limit	5.18	v
Min Limit	4.82	v
Krads	0	50
LL	4.820	4.820
Min	4.967	4.930
Average	4.967	4.971
Max	4.967	5.002
UL	5.180	5.180




ELDRS Report
UC1843

Reference Line Regulation; Vin12-25v						
Test Site		MMT	MTF			
Tester		LTX	LTX			
Test Number		XPM01302	XPM01302			
Unit		mv	mv			
Max Limit		18.9	18.9			
Min Limit		-18.9	-18.9			
Krads	Serial #	Pre_Rad_25c	Post_Rad_50K	Delta	Delta %	% of Limit Range
50	409	-1.087	-1.148	0.061	-5.64%	0.16%
50	410	-0.992	-1.045	0.054	-5.42%	0.14%
50	411	-0.961	-1.324	0.363	-37.74%	0.96%
50	412	-1.236	-1.408	0.172	-13.92%	0.46%
50	413	-1.350	-1.377	0.027	-2.01%	0.07%
50	414	-0.797	-0.896	0.099	-12.47%	0.26%
50	418	-1.304	-1.343	0.038	-2.95%	0.10%
50	421	-1.106	-1.545	0.439	-39.70%	1.16%
50	422	-1.159	-0.893	-0.267	23.01%	0.71%
50	423	-1.213	-1.179	-0.034	2.80%	0.09%
50	424	-1.331	-1.343	0.012	-0.89%	0.03%
50	427	-1.018	-1.061	0.042	-4.15%	0.11%
50	429	-1.178	-1.343	0.164	-13.94%	0.43%
50	431	-1.068	-1.011	-0.057	5.33%	0.15%
50	432	-1.354	-1.591	0.237	-17.50%	0.63%
50	433	-1.175	-0.999	-0.175	14.92%	0.46%
50	434	-1.190	-1.186	-0.003	0.29%	0.01%
50	435	-1.102	-0.809	-0.293	26.62%	0.78%
50	436	-1.011	-0.786	-0.225	22.24%	0.59%
50	437	-1.197	-1.419	0.222	-18.50%	0.59%
0	442	-1.030	-1.079	0.050	-4.84%	0.13%
Max		-0.797	-0.786	0.439	26.62%	1.16%
Average		-1.136	-1.180	0.044	-4.02%	0.38%
Min		-1.354	-1.591	-0.293	-39.70%	0.01%
Std Dev		0.142	0.236	0.189	17.26%	0.33%




Reference Line Regulation; Vin		
Test Site		MMT
Tester		LTX
Test Number		XPM01302
Max Limit		18.9 mv
Min Limit		-18.9 mv
Krads		0 50
LL		-18.900 -18.900
Min		-1.080 -1.591
Average		-1.080 -1.185
Max		-1.080 -0.786
UL		18.900 18.900




ELDRS Report
UC1843

>Reference Load Regulation; II1						
Test Site	MMT		MTF			
Tester	LTX		LTX			
Test Number	XPM01302		XPM01302			
Unit	mv		mv			
Max Limit	23.6		23.6			
Min Limit	-23.6		-23.6			
Krads	Serial #	Pre_Rad_25c	Post_Rad_50K	Delta	Delta %	% of Limit Range
50	409	-8.276	-8.392	0.117	-1.41%	0.25%
50	410	-8.619	-9.613	0.994	-11.53%	2.11%
50	411	-8.542	-8.850	0.307	-3.60%	0.65%
50	412	-8.847	-9.308	0.460	-5.20%	0.97%
50	413	-8.542	-9.041	0.498	-5.83%	1.06%
50	414	-8.352	-8.888	0.536	-6.42%	1.14%
50	418	-8.847	-9.308	0.460	-5.20%	0.97%
50	421	-8.314	-9.918	1.604	-19.30%	3.40%
50	422	-8.542	-10.223	1.681	-19.67%	3.56%
50	423	-8.237	-8.278	0.040	-0.49%	0.09%
50	424	-8.771	-8.583	-0.188	2.15%	0.40%
50	427	-8.428	-9.308	0.880	-10.44%	1.86%
50	429	-8.199	-9.308	1.108	-13.52%	2.35%
50	431	-8.657	-8.659	0.002	-0.03%	0.01%
50	432	-8.352	-9.422	1.070	-12.82%	2.27%
50	433	-8.276	-9.155	0.880	-10.63%	1.86%
50	434	-8.542	-8.964	0.422	-4.94%	0.89%
50	435	-8.847	-9.079	0.231	-2.61%	0.49%
50	436	-7.780	-9.804	2.024	-26.01%	4.29%
50	437	-7.970	-8.964	0.994	-12.47%	2.11%
0	442	-8.847	-8.354	-0.493	5.58%	1.05%
Max		-7.780	-8.278	2.024	5.58%	4.29%
Average		-8.466	-9.115	0.649	-7.83%	1.51%
Min		-8.847	-10.223	-0.493	-26.01%	0.01%
Std Dev		0.293	0.515	0.637	7.80%	1.19%




>Reference Load Regulation; II1		
Test Site	MMT	
Tester	LTX	
Test Number	XPM01302	
Max Limit	23.6	mv
Min Limit	-23.6	mv
Krads	0	50
LL	-23.600	-23.600
Min	-8.354	-10.223
Average	-8.354	-9.153
Max	-8.354	-8.278
UL	23.600	23.600




ELDRS Report

UC1843

>Reference Short Circuit Current						
Test Site	MMT		MTF			
Tester	LTX		LTX			
Test Number	XPM01302		XPM01302			
Unit	ma		ma			
Max Limit	-36		-36			
Min Limit	-174		-174			
Krads	Serial #	Pre_Rad_25c	Post_Rad_50K	Delta	Delta %	% of Limit Range
50	409	-109.873	-110.028	0.155	-0.14%	0.11%
50	410	-112.192	-112.220	0.027	-0.02%	0.02%
50	411	-110.706	-111.177	0.471	-0.43%	0.34%
50	412	-109.460	-109.944	0.485	-0.44%	0.35%
50	413	-110.331	-110.929	0.598	-0.54%	0.43%
50	414	-109.631	-109.831	0.200	-0.18%	0.14%
50	418	-110.040	-110.376	0.337	-0.31%	0.24%
50	421	-111.592	-111.693	0.101	-0.09%	0.07%
50	422	-110.960	-111.371	0.411	-0.37%	0.30%
50	423	-111.613	-111.365	-0.248	0.22%	0.18%
50	424	-109.492	-109.899	0.407	-0.37%	0.29%
50	427	-111.265	-111.371	0.106	-0.10%	0.08%
50	429	-109.762	-109.994	0.232	-0.21%	0.17%
50	431	-110.388	-110.527	0.139	-0.13%	0.10%
50	432	-109.028	-109.059	0.031	-0.03%	0.02%
50	433	-109.972	-110.300	0.328	-0.30%	0.24%
50	434	-110.307	-110.796	0.489	-0.44%	0.35%
50	435	-111.536	-111.723	0.187	-0.17%	0.14%
50	436	-109.592	-109.875	0.283	-0.26%	0.21%
50	437	-110.783	-111.244	0.462	-0.42%	0.33%
0	442	-108.837	-108.500	-0.338	0.31%	0.24%
Max		-108.837	-108.500	0.598	0.31%	0.43%
Average		-110.350	-110.582	0.232	-0.21%	0.21%
Min		-112.192	-112.220	-0.338	-0.54%	0.02%
Std Dev		0.920	0.933	0.240	0.22%	0.12%




>Reference Short Circuit Current		
Test Site	MMT	
Tester	LTX	
Test Number	XPM01302	
Max Limit	-36	ma
Min Limit	-174	ma
Krads	0	50
LL	-174.000	-174.000
Min	-108.500	-112.220
Average	-108.500	-110.686
Max	-108.500	-109.059
UL	-36.000	-36.000




ELDRS Report

UC1843

*Ct Discharge Current; Pin 42v						
Test Site	MMT		MTF			
Tester	LTX		LTX			
Test Number	XPM01302		XPM01302			
Unit	ma		ma			
Max Limit	20		20			
Min Limit	1		1			
Krads	Serial #	Pre_Rad_25c	Post_Rad_50K	Delta	Delta %	% of Limit Range
50	409	11.148	10.842	0.306	2.74%	1.61%
50	410	10.949	10.667	0.282	2.57%	1.48%
50	411	11.286	10.979	0.307	2.72%	1.62%
50	412	11.214	10.898	0.316	2.82%	1.66%
50	413	11.188	10.877	0.310	2.77%	1.63%
50	414	11.285	10.986	0.300	2.65%	1.58%
50	418	11.247	10.935	0.312	2.77%	1.64%
50	421	11.694	11.394	0.299	2.56%	1.58%
50	422	11.262	10.952	0.310	2.75%	1.63%
50	423	10.932	10.652	0.279	2.56%	1.47%
50	424	11.464	11.149	0.316	2.75%	1.66%
50	427	11.190	10.873	0.316	2.83%	1.67%
50	429	11.093	10.761	0.332	2.99%	1.75%
50	431	11.282	10.957	0.325	2.88%	1.71%
50	432	11.049	10.711	0.338	3.06%	1.78%
50	433	11.193	10.835	0.357	3.19%	1.88%
50	434	11.389	11.073	0.316	2.78%	1.66%
50	435	11.477	11.139	0.337	2.94%	1.78%
50	436	11.407	11.077	0.330	2.89%	1.74%
50	437	11.172	10.829	0.342	3.07%	1.80%
0	442	11.249	11.257	-0.008	-0.07%	0.04%
Max		11.694	11.394	0.357	3.19%	1.88%
Average		11.246	10.945	0.301	2.68%	1.59%
Min		10.932	10.652	-0.008	-0.07%	0.04%
Std Dev		0.177	0.189	0.073	0.65%	0.37%




*Ct Discharge Current; Pin 42v		
Test Site	MMT	
Tester	LTX	
Test Number	XPM01302	
Max Limit	20	ma
Min Limit	1	ma
Krads	0	50
LL	1.000	1.000
Min	11.257	10.652
Average	11.257	10.929
Max	11.257	11.394
UL	20.000	20.000




ELDRS Report
UC1843

OSC Initial Accuracy (50KHz)						
Test Site	MMT		MTF			
Tester	LTX		LTX			
Test Number	XPM01302		XPM01302			
Unit	khz		khz			
Max Limit	56.7		56.7			
Min Limit	47.3		47.3			
Krads	Serial #	Pre_Rad_25c	Post_Rad_50K	Delta	Delta %	% of Limit Range
50	409	52.665	53.146	-0.481	-0.91%	5.12%
50	410	52.919	53.431	-0.513	-0.97%	5.45%
50	411	52.950	53.451	-0.501	-0.95%	5.33%
50	412	52.682	53.206	-0.524	-0.99%	5.57%
50	413	52.540	53.021	-0.480	-0.91%	5.11%
50	414	52.221	52.716	-0.495	-0.95%	5.27%
50	418	52.697	53.195	-0.498	-0.94%	5.29%
50	421	52.136	52.644	-0.508	-0.97%	5.40%
50	422	52.552	53.084	-0.532	-1.01%	5.66%
50	423	52.994	53.494	-0.500	-0.94%	5.31%
50	424	52.445	52.994	-0.549	-1.05%	5.84%
50	427	52.677	53.220	-0.543	-1.03%	5.78%
50	429	52.663	53.199	-0.536	-1.02%	5.70%
50	431	52.715	53.250	-0.535	-1.02%	5.69%
50	432	52.476	53.008	-0.532	-1.01%	5.66%
50	433	52.680	53.243	-0.563	-1.07%	5.99%
50	434	52.499	53.064	-0.566	-1.08%	6.02%
50	435	52.737	53.367	-0.630	-1.19%	6.70%
50	436	52.800	53.373	-0.572	-1.08%	6.09%
50	437	52.202	52.797	-0.594	-1.14%	6.32%
0	442	52.896	53.197	-0.301	-0.57%	3.20%
Max		52.994	53.494	-0.301	-0.57%	6.70%
Average		52.626	53.148	-0.521	-0.99%	5.55%
Min		52.136	52.644	-0.630	-1.19%	3.20%
Std Dev		0.238	0.230	0.063	0.12%	0.67%




OSC Initial Accuracy (50KHz)		
Test Site	MMT	
Tester	LTX	
Test Number	XPM01302	
Max Limit	56.7	khz
Min Limit	47.3	khz
Krads	0	50
LL	47.300	47.300
Min	53.197	52.644
Average	53.197	53.145
Max	53.197	53.494
UL	56.700	56.700




ELDRS Report
UC1843

OSC Voltage Stability; Vcc12-25v						
Test Site	MMT		MTF			
Tester	LTX		LTX			
Test Number	XPM01302		XPM01302			
Unit	%		%			
Max Limit	0.91		0.91			
Min Limit	-0.001		-0.001			
Krads	Serial #	Pre_Rad_25c	Post_Rad_50K	Delta	Delta %	% of Limit Range
50	409	0.036	0.056	-0.020	-56.08%	2.23%
50	410	0.050	0.027	0.023	46.17%	2.51%
50	411	0.053	0.013	0.040	74.67%	4.34%
50	412	0.049	0.017	0.033	66.40%	3.60%
50	413	0.039	0.046	-0.007	-17.77%	0.77%
50	414	0.039	0.026	0.013	32.65%	1.41%
50	418	0.053	0.013	0.039	74.76%	4.32%
50	421	0.033	0.026	0.006	19.33%	0.69%
50	422	0.033	0.017	0.016	49.39%	1.78%
50	423	0.046	0.020	0.026	56.68%	2.89%
50	424	0.030	0.010	0.020	66.44%	2.15%
50	427	0.049	0.017	0.033	66.40%	3.60%
50	429	0.049	0.020	0.030	59.72%	3.24%
50	431	0.036	0.050	-0.014	-37.85%	1.50%
50	432	0.033	0.003	0.030	89.94%	3.24%
50	433	0.043	0.043	0.000	-0.93%	0.04%
50	434	0.030	0.013	0.016	54.92%	1.78%
50	435	0.040	0.003	0.036	91.67%	3.98%
50	436	0.030	0.047	-0.017	-57.24%	1.87%
50	437	0.033	0.030	0.003	8.90%	0.32%
0	442	0.036	0.040	-0.003	-9.62%	0.38%
Max		0.053	0.056	0.040	91.67%	4.34%
Average		0.040	0.026	0.014	32.31%	2.22%
Min		0.030	0.003	-0.020	-57.24%	0.04%
Std Dev		0.008	0.016	0.019	46.43%	1.35%




OSC Voltage Stability; Vcc12-25v		
Test Site	MMT	
Tester	LTX	
Test Number	XPM01302	
Max Limit	0.91	%
Min Limit	-0.001	%
Krads	0	50
LL	-0.001	-0.001
Min	0.040	0.003
Average	0.040	0.025
Max	0.040	0.057
UL	0.910	0.910




ELDRS Report
UC1843

*S/R Latch Check For Hold							
Test Site		MMT		MTF			
Tester		LTX		LTX			
Test Number		XPM01302		XPM01302			
Unit		%		%			
Max Limit		19.8		19.8			
Min Limit		-0.001		-0.001			
Krads	Serial #	Pre_Rad_25c	Post_Rad_50K	Delta	Delta %	% of Limit Range	
50	409	0.156	0.216	-0.060	-38.77%	0.31%	
50	410	0.234	0.255	-0.021	-8.96%	0.11%	
50	411	0.134	0.248	-0.114	-84.82%	0.58%	
50	412	0.244	0.254	-0.010	-4.19%	0.05%	
50	413	0.166	0.244	-0.078	-47.19%	0.39%	
50	414	0.207	0.243	-0.036	-17.46%	0.18%	
50	418	0.182	0.235	-0.054	-29.53%	0.27%	
50	421	0.335	0.231	0.103	30.81%	0.52%	
50	422	0.235	0.244	-0.009	-3.79%	0.04%	
50	423	0.111	0.254	-0.143	-129.04%	0.72%	
50	424	0.327	0.244	0.083	25.28%	0.42%	
50	427	0.128	0.248	-0.120	-93.67%	0.61%	
50	429	0.092	0.239	-0.147	-160.52%	0.74%	
50	431	0.283	0.245	0.038	13.26%	0.19%	
50	432	0.169	0.259	-0.090	-53.46%	0.46%	
50	433	0.060	0.233	-0.173	-290.60%	0.87%	
50	434	0.375	0.234	0.141	37.63%	0.71%	
50	435	0.334	0.212	0.122	36.51%	0.62%	
50	436	0.329	0.215	0.114	34.71%	0.58%	
50	437	0.210	0.228	-0.018	-8.37%	0.09%	
0	442	0.130	0.250	-0.121	-93.06%	0.61%	
Max		0.375	0.259	0.141	37.63%	0.87%	
Average		0.211	0.240	-0.028	-42.15%	0.43%	
Min		0.060	0.212	-0.173	-290.60%	0.04%	
Std Dev		0.091	0.013	0.097	79.95%	0.25%	




*S/R Latch Check For Hold			
Test Site		MMT	
Tester		LTX	
Test Number		XPM01302	
Max Limit		19.8	%
Min Limit		-0.001	%
Krads		0	50
LL		-0.001	-0.001
Min		0.250	0.212
Average		0.250	0.239
Max		0.250	0.259
UL		19.800	19.800




ELDRS Report
UC1843

E/A Input Voltage; Pin12.5v						
Test Site	MMT		MTF			
Tester	LTX		LTX			
Test Number	XPM01302		XPM01302			
Unit	v		v			
Max Limit	2.55		2.55			
Min Limit	2.45		2.45			
Krads	Serial #	Pre_Rad_25c	Post_Rad_50K	Delta	Delta %	% of Limit Range
50	409	2.506	2.503	0.003	0.14%	3.40%
50	410	2.491	2.487	0.003	0.14%	3.50%
50	411	2.511	2.507	0.005	0.18%	4.60%
50	412	2.494	2.491	0.003	0.12%	3.00%
50	413	2.511	2.507	0.005	0.19%	4.80%
50	414	2.512	2.507	0.005	0.20%	5.00%
50	418	2.506	2.501	0.004	0.16%	4.00%
50	421	2.519	2.515	0.004	0.17%	4.30%
50	422	2.490	2.486	0.004	0.16%	4.00%
50	423	2.504	2.499	0.005	0.18%	4.60%
50	424	2.504	2.500	0.004	0.14%	3.60%
50	427	2.530	2.525	0.005	0.22%	5.50%
50	429	2.507	2.502	0.005	0.21%	5.20%
50	431	2.497	2.492	0.005	0.20%	5.10%
50	432	2.514	2.509	0.005	0.20%	5.00%
50	433	2.515	2.510	0.005	0.21%	5.20%
50	434	2.497	2.492	0.004	0.17%	4.30%
50	435	2.528	2.522	0.006	0.25%	6.30%
50	436	2.508	2.501	0.006	0.25%	6.20%
50	437	2.506	2.499	0.007	0.28%	7.00%
0	442	2.500	2.502	-0.002	-0.07%	1.70%
Max		2.530	2.525	0.007	0.28%	7.00%
Average		2.507	2.503	0.004	0.18%	4.59%
Min		2.490	2.486	-0.002	-0.07%	1.70%
Std Dev		0.011	0.010	0.002	0.07%	1.20%




E/A Input Voltage; Pin12.5v		
Test Site	MMT	
Tester	LTX	
Test Number	XPM01302	
Max Limit	2.55	v
Min Limit	2.45	v
Krads	0	50
LL	2.450	2.450
Min	2.502	2.486
Average	2.502	2.503
Max	2.502	2.525
UL	2.550	2.550




ELDRS Report
UC1843

E/A PSRR; Vcc12-25v						
Test Site	MMT		MTF			
Tester	LTX		LTX			
Test Number	XPM01302		XPM01302			
Unit	db		db			
Max Limit	130		130			
Min Limit	60.65		60.65			
Krads	Serial #	Pre_Rad_25c	Post_Rad_50K	Delta	Delta %	% of Limit Range
50	409	91.609	93.303	-1.694	-1.85%	2.44%
50	410	88.511	90.167	-1.656	-1.87%	2.39%
50	411	87.683	90.434	-2.751	-3.14%	3.97%
50	412	86.067	91.594	-5.527	-6.42%	7.97%
50	413	92.948	98.258	-5.310	-5.71%	7.66%
50	414	90.182	85.890	4.293	4.76%	6.19%
50	418	92.948	101.452	-8.504	-9.15%	12.26%
50	421	87.297	87.095	0.202	0.23%	0.29%
50	422	91.925	88.496	3.429	3.73%	4.94%
50	423	99.725	100.537	-0.813	-0.82%	1.17%
50	424	93.704	108.496	-14.792	-15.79%	21.33%
50	427	99.725	104.974	-5.250	-5.26%	7.57%
50	429	92.253	94.962	-2.709	-2.94%	3.91%
50	431	87.883	87.668	0.215	0.24%	0.31%
50	432	90.449	95.432	-4.982	-5.51%	7.18%
50	433	92.253	87.473	4.780	5.18%	6.89%
50	434	86.928	84.831	2.097	2.41%	3.02%
50	435	93.318	86.052	7.266	7.79%	10.48%
50	436	90.449	87.868	2.581	2.85%	3.72%
50	437	93.704	92.238	1.466	1.56%	2.11%
0	442	88.511	86.558	1.953	2.21%	2.82%
Max		99.725	108.496	7.266	7.79%	21.33%
Average		91.337	92.561	-1.224	-1.31%	5.65%
Min		86.067	84.831	-14.792	-15.79%	0.29%
Std Dev		3.680	6.745	5.074	5.48%	4.83%




E/A PSRR; Vcc12-25v		
Test Site	MMT	
Tester	LTX	
Test Number	XPM01302	
Max Limit	130	db
Min Limit	60.65	db
Krads	0	50
LL	60.650	60.650
Min	86.558	84.831
Average	86.558	92.861
Max	86.558	108.496
UL	130.000	130.000




ELDRS Report
UC1843

E/A Input Bias Current						
Test Site	MMT		MTF			
Tester	LTX		LTX			
Test Number	XPM01302		XPM01302			
Unit	ua		ua			
Max Limit	-0.001		-0.001			
Min Limit	-0.975		-0.975			
Krads	Serial #	Pre_Rad_25c	Post_Rad_50K	Delta	Delta %	% of Limit Range
50	409	-0.109	-0.176	0.067	-61.31%	6.85%
50	410	-0.110	-0.172	0.062	-55.94%	6.33%
50	411	-0.108	-0.175	0.068	-62.67%	6.93%
50	412	-0.111	-0.177	0.066	-59.23%	6.76%
50	413	-0.108	-0.178	0.070	-65.43%	7.23%
50	414	-0.112	-0.175	0.063	-56.72%	6.50%
50	418	-0.112	-0.180	0.067	-59.91%	6.92%
50	421	-0.117	-0.182	0.065	-55.60%	6.67%
50	422	-0.106	-0.172	0.066	-61.90%	6.76%
50	423	-0.112	-0.178	0.066	-59.21%	6.80%
50	424	-0.112	-0.164	0.052	-46.38%	5.33%
50	427	-0.110	-0.162	0.052	-46.96%	5.32%
50	429	-0.112	-0.167	0.055	-49.15%	5.65%
50	431	-0.114	-0.162	0.047	-41.56%	4.88%
50	432	-0.112	-0.166	0.055	-48.97%	5.61%
50	433	-0.110	-0.163	0.052	-47.42%	5.37%
50	434	-0.115	-0.164	0.049	-43.07%	5.07%
50	435	-0.108	-0.158	0.049	-45.39%	5.05%
50	436	-0.111	-0.159	0.048	-43.17%	4.93%
50	437	-0.106	-0.159	0.053	-50.52%	5.48%
0	442	-0.109	-0.097	-0.013	11.63%	1.30%
Max		-0.106	-0.097	0.070	11.63%	7.23%
Average		-0.111	-0.166	0.055	-49.95%	5.80%
Min		-0.117	-0.182	-0.013	-65.43%	1.30%
Std Dev		0.003	0.018	0.017	15.91%	1.30%




E/A Input Bias Current		
Test Site	MMT	
Tester	LTX	
Test Number	XPM01302	
Max Limit	-0.001	ua
Min Limit	-0.975	ua
Krads	0	50
LL	-0.975	-0.975
Min	-0.097	-0.182
Average	-0.097	-0.169
Max	-0.097	-0.158
UL	-0.001	-0.001




ELDRS Report
UC1843

E/A Avol; Vout2-4v						
Test Site	MMT		MTF			
Tester	LTX		LTX			
Test Number	XPM01302		XPM01302			
Unit	db		db			
Max Limit	127.5		127.5			
Min Limit	67.5		67.5			
Krads	Serial #	Pre_Rad_25c	Post_Rad_50K	Delta	Delta %	% of Limit Range
50	409	90.852	85.255	5.597	6.16%	9.33%
50	410	80.084	85.822	-5.738	-7.16%	9.56%
50	411	88.021	85.426	2.595	2.95%	4.32%
50	412	86.950	85.189	1.761	2.03%	2.94%
50	413	94.628	85.157	9.471	10.01%	15.79%
50	414	86.779	85.370	1.409	1.62%	2.35%
50	418	93.035	86.784	6.251	6.72%	10.42%
50	421	88.515	85.282	3.234	3.65%	5.39%
50	422	92.907	83.960	8.947	9.63%	14.91%
50	423	85.760	83.013	2.748	3.20%	4.58%
50	424	102.421	86.376	16.045	15.67%	26.74%
50	427	88.344	86.189	2.155	2.44%	3.59%
50	429	83.625	84.882	-1.258	-1.50%	2.10%
50	431	91.583	86.876	4.706	5.14%	7.84%
50	432	95.077	84.631	10.446	10.99%	17.41%
50	433	93.969	85.972	7.997	8.51%	13.33%
50	434	122.663	84.897	37.766	30.79%	62.94%
50	435	95.634	87.787	7.846	8.20%	13.08%
50	436	107.916	85.736	22.180	20.55%	36.97%
50	437	96.782	85.715	11.067	11.43%	18.44%
0	442	88.783	86.586	2.198	2.48%	3.66%
Max		122.663	87.787	37.766	30.79%	62.94%
Average		93.063	85.567	7.496	7.31%	13.60%
Min		80.084	83.013	-5.738	-7.16%	2.10%
Std Dev		9.202	1.047	9.189	8.04%	14.29%




E/A Avol; Vout2-4v		
Test Site	MMT	
Tester	LTX	
Test Number	XPM01302	
Max Limit	127.5	db
Min Limit	67.5	db
Krads	0	50
LL	67.500	67.500
Min	86.586	83.013
Average	86.586	85.516
Max	86.586	87.787
UL	127.500	127.500




ELDRS Report
UC1843

E/A Output Isink; Pin22.7v,pin11.1v						
Test Site	MMT		MTF			
Tester	LTX		LTX			
Test Number	XPM01302		XPM01302			
Unit	ma		ma			
Max Limit	20		20			
Min Limit	2.2		2.2			
Krads	Serial #	Pre_Rad_25c	Post_Rad_50K	Delta	Delta %	% of Limit Range
50	409	6.606	6.581	0.025	0.38%	0.14%
50	410	6.481	6.451	0.030	0.46%	0.17%
50	411	6.418	6.378	0.040	0.62%	0.22%
50	412	6.314	6.287	0.027	0.43%	0.15%
50	413	6.670	6.611	0.059	0.88%	0.33%
50	414	6.385	6.353	0.032	0.50%	0.18%
50	418	6.353	6.325	0.028	0.44%	0.16%
50	421	6.501	6.479	0.022	0.34%	0.12%
50	422	6.700	6.643	0.056	0.84%	0.32%
50	423	6.391	6.372	0.019	0.30%	0.11%
50	424	6.426	6.366	0.060	0.94%	0.34%
50	427	6.464	6.427	0.037	0.57%	0.21%
50	429	6.316	6.273	0.043	0.68%	0.24%
50	431	6.462	6.425	0.036	0.56%	0.20%
50	432	6.427	6.383	0.043	0.68%	0.24%
50	433	6.329	6.275	0.053	0.84%	0.30%
50	434	6.545	6.492	0.053	0.81%	0.30%
50	435	6.734	6.679	0.055	0.82%	0.31%
50	436	6.571	6.519	0.052	0.79%	0.29%
50	437	6.754	6.696	0.058	0.86%	0.33%
0	442	6.537	6.596	-0.059	-0.91%	0.33%
Max		6.754	6.696	0.060	0.94%	0.34%
Average		6.494	6.458	0.037	0.56%	0.24%
Min		6.314	6.273	-0.059	-0.91%	0.11%
Std Dev		0.136	0.134	0.026	0.39%	0.08%




E/A Output Isink; Pin22.7v,pin11.1v		
Test Site	MMT	
Tester	LTX	
Test Number	XPM01302	
Max Limit	20	ma
Min Limit	2.2	ma
Krads	0	50
LL	2.200	2.200
Min	6.597	6.274
Average	6.597	6.451
Max	6.597	6.696
UL	20.000	20.000




ELDRS Report
UC1843

E/A Output Isource; Pin22.3v, pin15v						
Test Site	MMT		MTF			
Tester	LTX		LTX			
Test Number	XPM01302		XPM01302			
Unit	ma		ma			
Max Limit	-0.515		-0.515			
Min Limit	-5		-5			
Krads	Serial #	Pre_Rad_25c	Post_Rad_50K	Delta	Delta %	% of Limit Range
50	409	-0.955	-0.942	-0.013	1.34%	0.29%
50	410	-0.936	-0.927	-0.008	0.89%	0.19%
50	411	-0.938	-0.926	-0.013	1.34%	0.28%
50	412	-0.964	-0.951	-0.012	1.30%	0.28%
50	413	-0.935	-0.923	-0.012	1.27%	0.27%
50	414	-0.975	-0.962	-0.012	1.28%	0.28%
50	418	-0.981	-0.966	-0.015	1.54%	0.34%
50	421	-0.983	-0.971	-0.012	1.21%	0.27%
50	422	-0.950	-0.936	-0.015	1.54%	0.33%
50	423	-0.987	-0.971	-0.016	1.58%	0.35%
50	424	-0.983	-0.967	-0.016	1.65%	0.36%
50	427	-0.983	-0.968	-0.015	1.54%	0.34%
50	429	-0.989	-0.977	-0.012	1.22%	0.27%
50	431	-0.951	-0.934	-0.017	1.75%	0.37%
50	432	-0.980	-0.964	-0.015	1.57%	0.34%
50	433	-0.977	-0.965	-0.012	1.23%	0.27%
50	434	-0.956	-0.946	-0.011	1.15%	0.25%
50	435	-0.952	-0.939	-0.014	1.44%	0.31%
50	436	-1.014	-0.998	-0.015	1.50%	0.34%
50	437	-0.952	-0.938	-0.014	1.47%	0.31%
0	442	-0.939	-0.947	0.009	-0.92%	0.19%
Max		-0.935	-0.923	0.009	1.75%	0.37%
Average		-0.966	-0.953	-0.012	1.28%	0.29%
Min		-1.014	-0.998	-0.017	-0.92%	0.19%
Std Dev		0.021	0.020	0.005	0.54%	0.05%




E/A Output Isource; Pin22.3v, pin15v		
Test Site	MMT	
Tester	LTX	
Test Number	XPM01302	
Max Limit	-0.515	ma
Min Limit	-5	ma
Krads	0	50
LL	-5.000	-5.000
Min	-0.947	-0.999
Average	-0.947	-0.954
Max	-0.947	-0.923
UL	-0.515	-0.515




ELDRS Report
UC1843

E/A Vout High; Pin22.3v,RI15k To Gnd						
Test Site	MMT		MTF			
Tester	LTX		LTX			
Test Number	XPM01302		XPM01302			
Unit	v		v			
Max Limit	8		8			
Min Limit	5.024		5.024			
Krads	Serial #	Pre_Rad_25c	Post_Rad_50K	Delta	Delta %	% of Limit Range
50	409	5.694	5.686	0.008	0.14%	0.27%
50	410	5.640	5.631	0.009	0.16%	0.31%
50	411	5.693	5.683	0.010	0.17%	0.33%
50	412	5.658	5.652	0.006	0.11%	0.21%
50	413	5.693	5.684	0.009	0.15%	0.29%
50	414	5.663	5.653	0.010	0.17%	0.33%
50	418	5.685	5.677	0.007	0.13%	0.25%
50	421	5.709	5.699	0.010	0.17%	0.32%
50	422	5.636	5.629	0.007	0.13%	0.24%
50	423	5.635	5.625	0.010	0.18%	0.34%
50	424	5.675	5.669	0.006	0.10%	0.18%
50	427	5.701	5.692	0.009	0.16%	0.32%
50	429	5.683	5.675	0.009	0.15%	0.29%
50	431	5.655	5.646	0.010	0.17%	0.32%
50	432	5.683	5.673	0.010	0.17%	0.33%
50	433	5.690	5.683	0.007	0.12%	0.23%
50	434	5.657	5.651	0.007	0.11%	0.22%
50	435	5.692	5.681	0.011	0.19%	0.36%
50	436	5.675	5.665	0.010	0.18%	0.34%
50	437	5.675	5.662	0.012	0.22%	0.42%
0	442	5.653	5.655	-0.002	-0.03%	0.06%
Max		5.709	5.699	0.012	0.22%	0.42%
Average		5.673	5.665	0.008	0.15%	0.28%
Min		5.635	5.625	-0.002	-0.03%	0.06%
Std Dev		0.022	0.021	0.003	0.05%	0.08%




E/A Vout High; Pin22.3v,RI15k To Gnd		
Test Site	MMT	
Tester	LTX	
Test Number	XPM01302	
Max Limit	8	v
Min Limit	5.024	v
Krads	0	50
LL	5.024	5.024
Min	5.655	5.625
Average	5.655	5.666
Max	5.655	5.699
UL	8.000	8.000




ELDRS Report
UC1843

E/A Vout Low; Pin22.7v,RI15k To						
Test Site	MMT		MTF			
Tester	LTX		LTX			
Test Number	XPM01302		XPM01302			
Unit	v		v			
Max Limit	1.084		1.084			
Min Limit	0.1		0.1			
Krads	Serial #	Pre_Rad_25c	Post_Rad_50K	Delta	Delta %	% of Limit Range
50	409	0.826	0.829	-0.003	-0.34%	0.28%
50	410	0.823	0.826	-0.003	-0.38%	0.32%
50	411	0.824	0.828	-0.004	-0.51%	0.43%
50	412	0.828	0.832	-0.004	-0.46%	0.39%
50	413	0.825	0.829	-0.004	-0.50%	0.42%
50	414	0.826	0.830	-0.003	-0.40%	0.34%
50	418	0.828	0.831	-0.003	-0.40%	0.34%
50	421	0.824	0.827	-0.003	-0.34%	0.28%
50	422	0.826	0.830	-0.004	-0.47%	0.40%
50	423	0.825	0.827	-0.002	-0.18%	0.15%
50	424	0.826	0.831	-0.004	-0.52%	0.44%
50	427	0.824	0.827	-0.003	-0.34%	0.28%
50	429	0.829	0.832	-0.003	-0.42%	0.36%
50	431	0.823	0.827	-0.004	-0.47%	0.40%
50	432	0.828	0.831	-0.003	-0.34%	0.28%
50	433	0.828	0.832	-0.004	-0.53%	0.45%
50	434	0.824	0.828	-0.004	-0.52%	0.44%
50	435	0.823	0.827	-0.004	-0.44%	0.37%
50	436	0.828	0.833	-0.004	-0.49%	0.42%
50	437	0.825	0.829	-0.005	-0.59%	0.50%
0	442	0.827	0.826	0.000	0.05%	0.04%
Max		0.829	0.833	0.000	0.05%	0.50%
Average		0.826	0.829	-0.003	-0.41%	0.35%
Min		0.823	0.826	-0.005	-0.59%	0.04%
Std Dev		0.002	0.002	0.001	0.14%	0.11%




E/A Vout Low; Pin22.7v,RI15k To		
Test Site	MMT	
Tester	LTX	
Test Number	XPM01302	
Max Limit	1.084	v
Min Limit	0.1	v
Krads	0	50
LL	0.100	0.100
Min	0.826	0.826
Average	0.826	0.829
Max	0.826	0.833
UL	1.084	1.084




ELDRS Report
UC1843

C/S Amplifier Gain						
Test Site		MMT		MTF		
Tester		LTX		LTX		
Test Number		XPM01302		XPM01302		
Unit		v/v		v/v		
Max Limit		3.145		3.145		
Min Limit		2.855		2.855		
Krads	Serial #	Pre_Rad_25c	Post_Rad_50K	Delta	Delta %	% of Limit Range
50	409	3.035	3.059	-0.023	-0.76%	8.00%
50	410	3.022	3.027	-0.005	-0.18%	1.86%
50	411	3.019	3.035	-0.016	-0.53%	5.52%
50	412	3.026	3.035	-0.009	-0.29%	3.00%
50	413	3.038	3.068	-0.029	-0.96%	10.10%
50	414	3.026	3.042	-0.016	-0.53%	5.48%
50	418	3.027	3.034	-0.007	-0.23%	2.38%
50	421	3.023	3.049	-0.026	-0.86%	8.93%
50	422	3.017	3.036	-0.019	-0.62%	6.45%
50	423	3.019	3.045	-0.026	-0.86%	8.97%
50	424	3.018	3.046	-0.027	-0.90%	9.34%
50	427	3.020	3.050	-0.030	-1.00%	10.38%
50	429	3.017	3.039	-0.022	-0.74%	7.72%
50	431	3.022	3.056	-0.034	-1.14%	11.83%
50	432	3.025	3.055	-0.029	-0.97%	10.14%
50	433	3.025	3.053	-0.028	-0.93%	9.66%
50	434	3.021	3.050	-0.029	-0.96%	9.97%
50	435	3.043	3.058	-0.015	-0.51%	5.31%
50	436	3.035	3.068	-0.033	-1.09%	11.45%
50	437	3.017	3.034	-0.017	-0.56%	5.79%
0	442	3.017	3.050	-0.033	-1.09%	11.34%
Max		3.043	3.068	-0.005	-0.18%	11.83%
Average		3.024	3.047	-0.023	-0.75%	7.79%
Min		3.017	3.027	-0.034	-1.14%	1.86%
Std Dev		0.008	0.011	0.009	0.29%	3.03%




C/S Amplifier Gain		
Test Site		MMT
Tester		LTX
Test Number		XPM01302
Max Limit		3.145 v/v
Min Limit		2.855 v/v
Krads	0	50
LL	2.855	2.855
Min	3.050	3.027
Average	3.050	3.047
Max	3.050	3.068
UL	3.145	3.145




ELDRS Report
UC1843

C/S Maximum Input Signal; Pin1						
Test Site	MMT		MTF			
Tester	LTX		LTX			
Test Number	XPM01302		XPM01302			
Unit	v		v			
Max Limit	1.085		1.085			
Min Limit	0.915		0.915			
Krads	Serial #	Pre_Rad_25c	Post_Rad_50K	Delta	Delta %	% of Limit Range
50	409	0.990	0.980	0.010	1.01%	5.88%
50	410	0.990	0.980	0.010	1.01%	5.88%
50	411	1.000	0.990	0.010	1.00%	5.88%
50	412	0.990	0.990	0.000	0.00%	0.00%
50	413	0.990	0.980	0.010	1.01%	5.88%
50	414	0.990	0.990	0.000	0.00%	0.00%
50	418	0.980	0.980	0.000	0.00%	0.00%
50	421	0.990	0.990	0.000	0.00%	0.00%
50	422	0.980	0.970	0.010	1.02%	5.88%
50	423	0.980	0.970	0.010	1.02%	5.88%
50	424	0.990	0.990	0.000	0.00%	0.00%
50	427	1.000	1.000	0.000	0.00%	0.00%
50	429	1.000	0.990	0.010	1.00%	5.88%
50	431	0.990	0.980	0.010	1.01%	5.88%
50	432	0.990	0.990	0.000	0.00%	0.00%
50	433	0.990	0.990	0.000	0.00%	0.00%
50	434	0.990	0.980	0.010	1.01%	5.88%
50	435	1.000	0.990	0.010	1.00%	5.88%
50	436	0.980	0.980	0.000	0.00%	0.00%
50	437	0.990	0.980	0.010	1.01%	5.88%
0	442	0.990	0.990	0.000	0.00%	0.00%
Max		1.000	1.000	0.010	1.02%	5.88%
Average		0.990	0.985	0.005	0.53%	3.08%
Min		0.980	0.970	0.000	0.00%	0.00%
Std Dev		0.006	0.007	0.005	0.52%	3.01%




C/S Maximum Input Signal; Pin15v		
Test Site	MMT	
Tester	LTX	
Test Number	XPM01302	
Max Limit	1.085	v
Min Limit	0.915	v
Krads	0	50
LL	0.915	0.915
Min	0.990	0.970
Average	0.990	0.985
Max	0.990	1.000
UL	1.085	1.085




ELDRS Report
UC1843

C/S Input Bias Current						
Test Site	MMT		MTF			
Tester	LTX		LTX			
Test Number	XPM01302		XPM01302			
Unit	ua		ua			
Max Limit	-0.1		-0.1			
Min Limit	-9.8		-9.8			
Krads	Serial #	Pre_Rad_25c	Post_Rad_50K	Delta	Delta %	% of Limit Range
50	409	-0.565	-0.886	0.321	-56.77%	3.31%
50	410	-0.608	-0.931	0.322	-52.98%	3.32%
50	411	-0.613	-0.959	0.346	-56.46%	3.57%
50	412	-0.598	-0.933	0.335	-56.10%	3.46%
50	413	-0.594	-0.930	0.336	-56.58%	3.46%
50	414	-0.600	-0.925	0.325	-54.09%	3.35%
50	418	-0.629	-0.957	0.328	-52.23%	3.39%
50	421	-0.656	-0.984	0.328	-50.02%	3.38%
50	422	-0.602	-0.939	0.337	-56.02%	3.47%
50	423	-0.604	-0.936	0.332	-54.91%	3.42%
50	424	-0.650	-0.956	0.307	-47.22%	3.16%
50	427	-0.604	-0.891	0.287	-47.58%	2.96%
50	429	-0.630	-0.935	0.305	-48.39%	3.14%
50	431	-0.635	-0.915	0.281	-44.22%	2.89%
50	432	-0.624	-0.934	0.310	-49.76%	3.20%
50	433	-0.625	-0.941	0.315	-50.43%	3.25%
50	434	-0.613	-0.891	0.278	-45.29%	2.86%
50	435	-0.589	-0.874	0.286	-48.56%	2.95%
50	436	-0.627	-0.924	0.297	-47.45%	3.07%
50	437	-0.575	-0.877	0.303	-52.64%	3.12%
0	442	-0.588	-0.596	0.007	-1.24%	0.08%
Max		-0.565	-0.596	0.346	-1.24%	3.57%
Average		-0.611	-0.910	0.299	-49.00%	3.09%
Min		-0.656	-0.984	0.007	-56.77%	0.08%
Std Dev		0.023	0.078	0.070	11.62%	0.72%




C/S Input Bias Current		
Test Site	MMT	
Tester	LTX	
Test Number	XPM01302	
Max Limit	-0.1	ua
Min Limit	-9.8	ua
Krads	0	50
LL	-9.800	-9.800
Min	-0.596	-0.984
Average	-0.596	-0.926
Max	-0.596	-0.874
UL	-0.100	-0.100




ELDRS Report
UC1843

PWM Maximum Duty Cycle						
Test Site	MMT		MTF			
Tester	LTX		LTX			
Test Number	XPM01302		XPM01302			
Unit	%		%			
Max Limit	100		100			
Min Limit	95.2		95.2			
Krads	Serial #	Pre_Rad_25c	Post_Rad_50K	Delta	Delta %	% of Limit Range
50	409	97.115	97.044	0.071	0.07%	1.48%
50	410	97.223	97.051	0.172	0.18%	3.59%
50	411	97.146	96.936	0.211	0.22%	4.39%
50	412	97.140	97.097	0.043	0.04%	0.90%
50	413	97.086	96.876	0.210	0.22%	4.37%
50	414	97.218	97.133	0.085	0.09%	1.77%
50	418	97.075	97.078	-0.003	0.00%	0.06%
50	421	97.242	97.085	0.157	0.16%	3.27%
50	422	97.271	97.133	0.138	0.14%	2.88%
50	423	97.074	96.994	0.080	0.08%	1.66%
50	424	97.183	97.192	-0.009	-0.01%	0.19%
50	427	97.073	97.067	0.007	0.01%	0.14%
50	429	97.099	96.981	0.118	0.12%	2.46%
50	431	97.155	97.004	0.151	0.16%	3.15%
50	432	97.086	96.952	0.134	0.14%	2.79%
50	433	97.072	97.026	0.046	0.05%	0.95%
50	434	97.310	97.065	0.246	0.25%	5.12%
50	435	97.217	97.185	0.032	0.03%	0.67%
50	436	97.261	97.201	0.059	0.06%	1.24%
50	437	97.161	97.058	0.104	0.11%	2.16%
0	442	97.152	97.068	0.084	0.09%	1.75%
Max		97.310	97.201	0.246	0.25%	5.12%
Average		97.160	97.058	0.102	0.10%	2.14%
Min		97.072	96.876	-0.009	-0.01%	0.06%
Std Dev		0.074	0.084	0.072	0.07%	1.47%




PWM Maximum Duty Cycle		
Test Site	MMT	
Tester	LTX	
Test Number	XPM01302	
Max Limit	100	%
Min Limit	95.2	%
Krads	0	50
LL	95.200	95.200
Min	97.068	96.876
Average	97.068	97.058
Max	97.068	97.202
UL	100.000	100.000




ELDRS Report
UC1843

OUTPUT Low Level Sinking 20ma						
Test Site	MMT		MTF			
Tester	LTX		LTX			
Test Number	XPM01302		XPM01302			
Unit	v		v			
Max Limit	0.39		0.39			
Min Limit	0.01		0.01			
Krads	Serial #	Pre_Rad_25c	Post_Rad_50K	Delta	Delta %	% of Limit Range
50	409	0.123	0.121	0.001	1.14%	0.37%
50	410	0.128	0.127	0.001	0.63%	0.21%
50	411	0.128	0.127	0.001	0.55%	0.18%
50	412	0.128	0.128	0.000	0.23%	0.08%
50	413	0.122	0.121	0.001	1.06%	0.34%
50	414	0.127	0.127	0.000	0.24%	0.08%
50	418	0.128	0.127	0.001	0.78%	0.26%
50	421	0.126	0.125	0.001	0.95%	0.32%
50	422	0.120	0.120	0.000	0.00%	0.00%
50	423	0.128	0.128	0.000	0.00%	0.00%
50	424	0.126	0.127	0.000	-0.32%	0.11%
50	427	0.127	0.127	0.000	0.16%	0.05%
50	429	0.128	0.127	0.001	0.78%	0.26%
50	431	0.127	0.127	0.000	0.24%	0.08%
50	432	0.127	0.127	0.000	0.08%	0.03%
50	433	0.128	0.128	0.000	0.39%	0.13%
50	434	0.126	0.125	0.001	0.72%	0.24%
50	435	0.119	0.120	0.000	-0.25%	0.08%
50	436	0.122	0.122	0.000	-0.25%	0.08%
50	437	0.119	0.118	0.001	0.84%	0.26%
0	442	0.124	0.120	0.004	3.06%	1.00%
Max		0.128	0.128	0.004	3.06%	1.00%
Average		0.125	0.125	0.001	0.53%	0.20%
Min		0.119	0.118	0.000	-0.32%	0.00%
Std Dev		0.003	0.003	0.001	0.73%	0.22%




OUTPUT Low Level Sinking 20ma		
Test Site	MMT	
Tester	LTX	
Test Number	XPM01302	
Max Limit	0.39	v
Min Limit	0.01	v
Krads	0	50
LL	0.010	0.010
Min	0.120	0.118
Average	0.120	0.125
Max	0.120	0.128
UL	0.390	0.390




ELDRS Report
UC1843

>OUTPUT Low Level Sinking 200						
Test Site	MMT		MTF			
Tester	LTX		LTX			
Test Number	XPM01302		XPM01302			
Unit	v		v			
Max Limit	2.17		2.17			
Min Limit	0.5		0.5			
Krads	Serial #	Pre_Rad_25c	Post_Rad_50K	Delta	Delta %	% of Limit Range
50	409	1.707	1.681	0.026	1.54%	1.57%
50	410	1.719	1.699	0.020	1.19%	1.22%
50	411	1.722	1.704	0.019	1.08%	1.11%
50	412	1.726	1.709	0.018	1.01%	1.05%
50	413	1.699	1.679	0.020	1.17%	1.19%
50	414	1.718	1.704	0.013	0.76%	0.78%
50	418	1.726	1.707	0.020	1.13%	1.17%
50	421	1.714	1.693	0.021	1.21%	1.25%
50	422	1.690	1.671	0.019	1.11%	1.12%
50	423	1.718	1.696	0.021	1.25%	1.28%
50	424	1.715	1.702	0.013	0.75%	0.77%
50	427	1.717	1.697	0.020	1.14%	1.17%
50	429	1.725	1.706	0.019	1.12%	1.16%
50	431	1.715	1.696	0.019	1.11%	1.14%
50	432	1.719	1.697	0.022	1.27%	1.31%
50	433	1.723	1.706	0.018	1.02%	1.05%
50	434	1.712	1.692	0.020	1.16%	1.19%
50	435	1.687	1.673	0.014	0.85%	0.86%
50	436	1.698	1.682	0.017	0.98%	0.99%
50	437	1.685	1.668	0.017	1.01%	1.02%
0	442	1.710	1.675	0.036	2.09%	2.14%
Max		1.726	1.709	0.036	2.09%	2.14%
Average		1.712	1.692	0.020	1.14%	1.17%
Min		1.685	1.668	0.013	0.75%	0.77%
Std Dev		0.013	0.013	0.005	0.28%	0.29%




>OUTPUT Low Level Sinking 200		
Test Site	MMT	
Tester	LTX	
Test Number	XPM01302	
Max Limit	2.17	v
Min Limit	0.5	v
Krads	0	50
LL	0.500	0.500
Min	1.675	1.668
Average	1.675	1.693
Max	1.675	1.709
UL	2.170	2.170




ELDRS Report
UC1843

OUTPUT High Level Sourcing 20ma						
Test Site	MMT		MTF			
Tester	LTX		LTX			
Test Number	XPM01302		XPM01302			
Unit	v		v			
Max Limit	15		15			
Min Limit	13.03		13.03			
Krads	Serial #	Pre_Rad_25c	Post_Rad_50K	Delta	Delta %	% of Limit Range
50	409	13.507	13.505	0.002	0.02%	0.12%
50	410	13.511	13.510	0.001	0.01%	0.06%
50	411	13.509	13.505	0.004	0.03%	0.21%
50	412	13.509	13.504	0.005	0.04%	0.24%
50	413	13.509	13.503	0.006	0.05%	0.31%
50	414	13.511	13.508	0.003	0.02%	0.17%
50	418	13.509	13.504	0.004	0.03%	0.22%
50	421	13.513	13.510	0.003	0.02%	0.14%
50	422	13.509	13.503	0.006	0.04%	0.29%
50	423	13.513	13.513	0.000	0.00%	0.02%
50	424	13.511	13.507	0.004	0.03%	0.22%
50	427	13.512	13.511	0.002	0.01%	0.09%
50	429	13.509	13.506	0.004	0.03%	0.18%
50	431	13.512	13.510	0.003	0.02%	0.13%
50	432	13.507	13.507	0.000	0.00%	0.01%
50	433	13.509	13.506	0.004	0.03%	0.18%
50	434	13.512	13.508	0.004	0.03%	0.20%
50	435	13.511	13.508	0.003	0.02%	0.14%
50	436	13.507	13.505	0.003	0.02%	0.13%
50	437	13.509	13.504	0.005	0.04%	0.27%
0	442	13.508	13.514	-0.005	-0.04%	0.27%
Max		13.513	13.514	0.006	0.05%	0.31%
Average		13.510	13.507	0.003	0.02%	0.17%
Min		13.507	13.503	-0.005	-0.04%	0.01%
Std Dev		0.002	0.003	0.002	0.02%	0.08%




OUTPUT High Level Sourcing 20ma		
Test Site	MMT	
Tester	LTX	
Test Number	XPM01302	
Max Limit	15	v
Min Limit	13.03	v
Krads	0	50
LL	13.030	13.030
Min	13.514	13.503
Average	13.514	13.507
Max	13.514	13.513
UL	15.000	15.000




ELDRS Report
UC1843

>OUTPUT High Level Sourcing 200ma						
Test Site	MMT		MTF			
Tester	LTX		LTX			
Test Number	XPM01302		XPM01302			
Unit	v		v			
Max Limit	15		15			
Min Limit	12.04		12.04			
Krads	Serial #	Pre_Rad_25c	Post_Rad_50K	Delta	Delta %	% of Limit Range
50	409	13.286	13.313	-0.027	-0.20%	0.91%
50	410	13.285	13.311	-0.026	-0.19%	0.86%
50	411	13.278	13.306	-0.028	-0.21%	0.94%
50	412	13.281	13.306	-0.025	-0.19%	0.84%
50	413	13.291	13.315	-0.024	-0.18%	0.80%
50	414	13.287	13.308	-0.021	-0.16%	0.72%
50	418	13.280	13.306	-0.027	-0.20%	0.91%
50	421	13.286	13.309	-0.023	-0.18%	0.79%
50	422	13.292	13.318	-0.026	-0.19%	0.87%
50	423	13.286	13.313	-0.027	-0.20%	0.90%
50	424	13.288	13.310	-0.022	-0.16%	0.74%
50	427	13.283	13.312	-0.028	-0.21%	0.96%
50	429	13.283	13.308	-0.025	-0.19%	0.84%
50	431	13.286	13.313	-0.027	-0.21%	0.93%
50	432	13.278	13.314	-0.035	-0.27%	1.20%
50	433	13.283	13.309	-0.026	-0.19%	0.86%
50	434	13.286	13.315	-0.029	-0.22%	0.99%
50	435	13.296	13.318	-0.022	-0.17%	0.75%
50	436	13.289	13.314	-0.025	-0.19%	0.85%
50	437	13.295	13.319	-0.024	-0.18%	0.80%
0	442	13.286	13.320	-0.034	-0.25%	1.14%
Max		13.296	13.320	-0.021	-0.16%	1.20%
Average		13.286	13.312	-0.026	-0.20%	0.89%
Min		13.278	13.306	-0.035	-0.27%	0.72%
Std Dev		0.005	0.004	0.004	0.03%	0.12%




>OUTPUT High Level Sourcing		
Test Site	MMT	
Tester	LTX	
Test Number	XPM01302	
Max Limit	15	v
Min Limit	12.04	v
Krads	0	50
LL	12.040	12.040
Min	13.320	13.306
Average	13.320	13.312
Max	13.320	13.319
UL	15.000	15.000




ELDRS Report
UC1843

*OUTPUT High Level; I120mA,Vcc						
Test Site	MMT		MTF			
Tester	LTX		LTX			
Test Number	XPM01302		XPM01302			
Unit	v		v			
Max Limit	31		31			
Min Limit	25.04		25.04			
Krads	Serial #	Pre_Rad_25c	Post_Rad_50K	Delta	Delta %	% of Limit Range
50	409	26.521	26.508	0.012	0.05%	0.21%
50	410	26.525	26.514	0.011	0.04%	0.19%
50	411	26.522	26.507	0.015	0.06%	0.25%
50	412	26.524	26.509	0.015	0.06%	0.25%
50	413	26.525	26.505	0.020	0.07%	0.33%
50	414	26.525	26.512	0.013	0.05%	0.22%
50	418	26.525	26.507	0.017	0.07%	0.29%
50	421	26.527	26.513	0.014	0.05%	0.23%
50	422	26.520	26.505	0.015	0.06%	0.24%
50	423	26.525	26.517	0.008	0.03%	0.14%
50	424	26.525	26.510	0.014	0.05%	0.24%
50	427	26.527	26.514	0.013	0.05%	0.22%
50	429	26.524	26.509	0.015	0.06%	0.26%
50	431	26.525	26.512	0.014	0.05%	0.23%
50	432	26.522	26.513	0.009	0.03%	0.15%
50	433	26.524	26.509	0.015	0.06%	0.24%
50	434	26.525	26.511	0.014	0.05%	0.23%
50	435	26.525	26.513	0.012	0.04%	0.19%
50	436	26.522	26.505	0.016	0.06%	0.28%
50	437	26.522	26.505	0.016	0.06%	0.28%
0	442	26.521	26.517	0.004	0.01%	0.06%
Max		26.527	26.517	0.020	0.07%	0.33%
Average		26.524	26.510	0.013	0.05%	0.23%
Min		26.520	26.505	0.004	0.01%	0.06%
Std Dev		0.002	0.004	0.003	0.01%	0.06%




*OUTPUT High Level; I120mA,V		
Test Site	MMT	
Tester	LTX	
Test Number	XPM01302	
Max Limit	31	v
Min Limit	25.04	v
Krads	0	50
LL	25.040	25.040
Min	26.517	26.505
Average	26.517	26.510
Max	26.517	26.517
UL	31.000	31.000




ELDRS Report
UC1843

UVLO Start Threshold						
Test Site	MMT		MTF			
Tester	LTX		LTX			
Test Number	XPM01302		XPM01302			
Unit	v		v			
Max Limit	8.98		8.98			
Min Limit	7.82		7.82			
Krads	Serial #	Pre_Rad_25c	Post_Rad_50K	Delta	Delta %	% of Limit Range
50	409	8.500	8.450	0.050	0.59%	4.31%
50	410	8.350	8.300	0.050	0.60%	4.31%
50	411	8.500	8.400	0.100	1.18%	8.62%
50	412	8.400	8.300	0.100	1.19%	8.62%
50	413	8.500	8.400	0.100	1.18%	8.62%
50	414	8.500	8.450	0.050	0.59%	4.31%
50	418	8.450	8.400	0.050	0.59%	4.31%
50	421	8.550	8.450	0.100	1.17%	8.62%
50	422	8.400	8.300	0.100	1.19%	8.62%
50	423	8.350	8.300	0.050	0.60%	4.31%
50	424	8.500	8.500	0.000	0.00%	0.00%
50	427	8.400	8.400	0.000	0.00%	0.00%
50	429	8.500	8.450	0.050	0.59%	4.31%
50	431	8.550	8.550	0.000	0.00%	0.00%
50	432	8.450	8.450	0.000	0.00%	0.00%
50	433	8.500	8.500	0.000	0.00%	0.00%
50	434	8.500	8.500	0.000	0.00%	0.00%
50	435	8.500	8.500	0.000	0.00%	0.00%
50	436	8.450	8.450	0.000	0.00%	0.00%
50	437	8.400	8.400	0.000	0.00%	0.00%
0	442	8.500	8.500	0.000	0.00%	0.00%
Max		8.550	8.550	0.100	1.19%	8.62%
Average		8.464	8.426	0.038	0.45%	3.28%
Min		8.350	8.300	0.000	0.00%	0.00%
Std Dev		0.059	0.075	0.042	0.49%	3.58%




UVLO Start Threshold		
Test Site	MMT	
Tester	LTX	
Test Number	XPM01302	
Max Limit	8.98	v
Min Limit	7.82	v
Krads	0	50
LL	7.820	7.820
Min	8.500	8.300
Average	8.500	8.423
Max	8.500	8.550
UL	8.980	8.980




ELDRS Report
UC1843

UVLO Minimum Operating Voltage						
Test Site	MMT		MTF			
Tester	LTX		LTX			
Test Number	XPM01302		XPM01302			
Unit	v		v			
Max Limit	8.175		8.175			
Min Limit	7.025		7.025			
Krads	Serial #	Pre_Rad_25c	Post_Rad_50K	Delta	Delta %	% of Limit Range
50	409	7.700	7.700	0.000	0.00%	0.00%
50	410	7.550	7.550	0.000	0.00%	0.00%
50	411	7.700	7.700	0.000	0.00%	0.00%
50	412	7.600	7.600	0.000	0.00%	0.00%
50	413	7.700	7.700	0.000	0.00%	0.00%
50	414	7.700	7.700	0.000	0.00%	0.00%
50	418	7.700	7.700	0.000	0.00%	0.00%
50	421	7.750	7.750	0.000	0.00%	0.00%
50	422	7.650	7.600	0.050	0.65%	4.35%
50	423	7.600	7.550	0.050	0.66%	4.35%
50	424	7.700	7.750	-0.050	-0.65%	4.35%
50	427	7.600	7.650	-0.050	-0.66%	4.35%
50	429	7.700	7.750	-0.050	-0.65%	4.35%
50	431	7.750	7.800	-0.050	-0.65%	4.35%
50	432	7.650	7.700	-0.050	-0.65%	4.35%
50	433	7.700	7.750	-0.050	-0.65%	4.35%
50	434	7.700	7.750	-0.050	-0.65%	4.35%
50	435	7.700	7.750	-0.050	-0.65%	4.35%
50	436	7.650	7.700	-0.050	-0.65%	4.35%
50	437	7.600	7.650	-0.050	-0.66%	4.35%
0	442	7.700	7.700	0.000	0.00%	0.00%
Max		7.750	7.800	0.050	0.66%	4.35%
Average		7.671	7.690	-0.019	-0.25%	2.48%
Min		7.550	7.550	-0.050	-0.66%	0.00%
Std Dev		0.054	0.068	0.033	0.44%	2.20%




UVLO Minimum Operating Voltage		
Test Site	MMT	
Tester	LTX	
Test Number	XPM01302	
Max Limit	8.175	v
Min Limit	7.025	v
Krads	0	50
LL	7.025	7.025
Min	7.700	7.550
Average	7.700	7.690
Max	7.700	7.800
UL	8.175	8.175




ELDRS Report
UC1843

*UVLO Input Voltage Hysteresis						
Test Site	MMT		MTF			
Tester	LTX		LTX			
Test Number	XPM01302		XPM01302			
Unit	v		v			
Max Limit	2.55		2.55			
Min Limit	0.25		0.25			
Krads	Serial #	Pre_Rad_25c	Post_Rad_50K	Delta	Delta %	% of Limit Range
50	409	0.800	0.750	0.050	6.25%	2.17%
50	410	0.800	0.750	0.050	6.25%	2.17%
50	411	0.800	0.700	0.100	12.50%	4.35%
50	412	0.800	0.700	0.100	12.50%	4.35%
50	413	0.800	0.700	0.100	12.50%	4.35%
50	414	0.800	0.750	0.050	6.25%	2.17%
50	418	0.750	0.700	0.050	6.67%	2.17%
50	421	0.800	0.700	0.100	12.50%	4.35%
50	422	0.750	0.700	0.050	6.67%	2.17%
50	423	0.750	0.750	0.000	0.00%	0.00%
50	424	0.800	0.750	0.050	6.25%	2.17%
50	427	0.800	0.750	0.050	6.25%	2.17%
50	429	0.800	0.700	0.100	12.50%	4.35%
50	431	0.800	0.750	0.050	6.25%	2.17%
50	432	0.800	0.750	0.050	6.25%	2.17%
50	433	0.800	0.750	0.050	6.25%	2.17%
50	434	0.800	0.750	0.050	6.25%	2.17%
50	435	0.800	0.750	0.050	6.25%	2.17%
50	436	0.800	0.750	0.050	6.25%	2.17%
50	437	0.800	0.750	0.050	6.25%	2.17%
0	442	0.800	0.800	0.000	0.00%	0.00%
Max		0.800	0.800	0.100	12.50%	4.35%
Average		0.793	0.736	0.057	7.18%	2.48%
Min		0.750	0.700	0.000	0.00%	0.00%
Std Dev		0.018	0.028	0.029	3.57%	1.25%




*UVLO Input Voltage Hysteresis		
Test Site	MMT	
Tester	LTX	
Test Number	XPM01302	
Max Limit	2.55	v
Min Limit	0.25	v
Krads	0	50
LL	0.250	0.250
Min	0.800	0.700
Average	0.800	0.733
Max	0.800	0.750
UL	2.550	2.550




ELDRS Report
UC1843

Vcc Zener Clamp Voltage; Icc25ma						
Test Site	MMT		MTF			
Tester	LTX		LTX			
Test Number	XPM01302		XPM01302			
Unit	v		v			
Max Limit	44.9		44.9			
Min Limit	30.1		30.1			
Krads	Serial #	Pre_Rad_25c	Post_Rad_50K	Delta	Delta %	% of Limit Range
50	409	32.668	32.776	-0.108	-0.33%	0.73%
50	410	32.680	32.793	-0.112	-0.34%	0.76%
50	411	32.672	32.776	-0.104	-0.32%	0.70%
50	412	32.692	32.795	-0.103	-0.31%	0.69%
50	413	32.668	32.771	-0.103	-0.31%	0.69%
50	414	32.678	32.788	-0.110	-0.34%	0.74%
50	418	32.677	32.778	-0.101	-0.31%	0.68%
50	421	32.662	32.912	-0.250	-0.77%	1.69%
50	422	32.668	32.773	-0.105	-0.32%	0.71%
50	423	32.675	32.799	-0.124	-0.38%	0.84%
50	424	32.675	32.738	-0.062	-0.19%	0.42%
50	427	32.678	32.749	-0.071	-0.22%	0.48%
50	429	32.678	32.746	-0.068	-0.21%	0.46%
50	431	32.669	32.739	-0.070	-0.21%	0.47%
50	432	32.680	32.754	-0.073	-0.22%	0.50%
50	433	32.684	32.751	-0.067	-0.21%	0.45%
50	434	32.671	32.734	-0.064	-0.19%	0.43%
50	435	32.658	32.731	-0.074	-0.23%	0.50%
50	436	32.663	32.731	-0.068	-0.21%	0.46%
50	437	32.662	32.721	-0.059	-0.18%	0.40%
0	442	32.678	32.705	-0.027	-0.08%	0.18%
Max		32.692	32.912	-0.027	-0.08%	1.69%
Average		32.673	32.765	-0.092	-0.28%	0.62%
Min		32.658	32.705	-0.250	-0.77%	0.18%
Std Dev		0.008	0.043	0.044	0.13%	0.29%




Vcc Zener Clamp Voltage; Icc25ma		
Test Site	MMT	
Tester	LTX	
Test Number	XPM01302	
Max Limit	44.9	v
Min Limit	30.1	v
Krads	0	50
LL	30.100	30.100
Min	32.705	32.721
Average	32.705	32.768
Max	32.705	32.912
UL	44.900	44.900




ELDRS Report
UC1843

*Icc Standby; Vin Vstart-300mv						
Test Site	MMT		MTF			
Tester	LTX		LTX			
Test Number	XPM01302		XPM01302			
Unit	ma		ma			
Max Limit	0.97		0.97			
Min Limit	0.1		0.1			
Krads	Serial #	Pre_Rad_25c	Post_Rad_50K	Delta	Delta %	% of Limit Range
50	409	0.469	0.434	0.034	7.30%	3.93%
50	410	0.469	0.424	0.045	9.58%	5.16%
50	411	0.469	0.420	0.049	10.35%	5.57%
50	412	0.453	0.430	0.023	5.16%	2.69%
50	413	0.469	0.431	0.038	8.07%	4.34%
50	414	0.464	0.448	0.016	3.47%	1.85%
50	418	0.470	0.421	0.049	10.32%	5.57%
50	421	0.470	0.457	0.013	2.68%	1.45%
50	422	0.458	0.454	0.004	0.92%	0.48%
50	423	0.469	0.435	0.034	7.26%	3.91%
50	424	0.466	0.438	0.028	6.01%	3.22%
50	427	0.472	0.409	0.063	13.30%	7.22%
50	429	0.458	0.424	0.034	7.43%	3.91%
50	431	0.458	0.435	0.023	5.09%	2.68%
50	432	0.469	0.447	0.021	4.50%	2.43%
50	433	0.458	0.456	0.002	0.44%	0.23%
50	434	0.470	0.456	0.014	2.96%	1.60%
50	435	0.478	0.440	0.038	7.86%	4.32%
50	436	0.486	0.456	0.031	6.29%	3.52%
50	437	0.470	0.443	0.027	5.75%	3.10%
0	442	0.469	0.438	0.030	6.49%	3.49%
Max		0.486	0.457	0.063	13.30%	7.22%
Average		0.467	0.438	0.029	6.25%	3.37%
Min		0.453	0.409	0.002	0.44%	0.23%
Std Dev		0.007	0.014	0.015	3.19%	1.73%



*Icc Standby; Vin Vstart-300m		
Test Site	MMT	
Tester	LTX	
Test Number	XPM01302	
Max Limit	0.97	ma
Min Limit	0.1	ma
Krads	0	50
LL	0.100	0.100
Min	0.438	0.409
Average	0.438	0.438
Max	0.438	0.457
UL	0.970	0.970



IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have **not** been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Products

Audio	www.ti.com/audio
Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DLP® Products	www.dlp.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
OMAP Applications Processors	www.ti.com/omap
Wireless Connectivity	www.ti.com/wirelessconnectivity

Applications

Automotive and Transportation	www.ti.com/automotive
Communications and Telecom	www.ti.com/communications
Computers and Peripherals	www.ti.com/computers
Consumer Electronics	www.ti.com/consumer-apps
Energy and Lighting	www.ti.com/energy
Industrial	www.ti.com/industrial
Medical	www.ti.com/medical
Security	www.ti.com/security
Space, Avionics and Defense	www.ti.com/space-avionics-defense
Video and Imaging	www.ti.com/video

TI E2E Community

e2e.ti.com