

**DS25CP104A,LMH0302,LMH0340,LMH0341,  
LMH0344,LMH0356**



Literature Number: SNOA827

# Evaluating the performance of DS25CP104 in 3G SDI router applications

National Semiconductor  
Lab Report  
Keith Spaulding  
August 20, 2008



## Purpose:

The DS25CP104 is an excellent candidate for crosspoint switch functions in 3G SDI router applications. To ensure the DS25CP104 will function optimally in these applications the device was tested using pathological video patterns in a full 3G SDI router configuration. Jitter measurements and eye diagrams were taken with various cable lengths before the cable equalizer and with FR4 before and after the DS25CP104.

## Procedure:

Data was taken in numerous configurations. For each setup a block diagram is shown with the jitter data and eye diagram that follows. The following equipment was used in these setups:

- **Smart SerDes (LMH0340/LMH0341) EVK** - Contains ALP100 with Xilinx Spartan-3E FPGA, LMH0340 EVK (serializer), LMH0341 (deserializer); ALP GUI provides a serial data signal (Matrix Pathological patterns, 3G S274 M 1080 p50) for jitter and eye diagrams and PRBS 11 for jitter and BERT (5.0V)
- **SD344EVK:** LMH0344 3 Gbps SDI adaptive cable equalizer evaluation kit
- **SD302EVK:** LMH0302 3 Gbps SDI cable driver evaluation kit
- **SD356EVK:** LMH0356 3 Gbps SDI reclocker evaluation kit
- **DS25CP104EVK** – 3.125 Gbps 4x4 LVDS Crosspoint Switch with Transmit Pre Emphasis and Receive Equalization (3.3V)
- **Belden 1694A Cable**
- **TDS6154C** (Digital Storage Oscilloscope) with jitter measurement provided from **TDSJIT3** software module. For the 75 ohm input, a 75 ohm BNC adaptor is plugged into the scope; for the 50 ohm input, a 50 ohm SMA adaptor is used.

Coupling arrangements:

LMH0340 op/LMH0344 ip – AC coupled, single ended 75 ohm  
LMH0344 op/DS25CP104 ip – DC coupled, differential 50 ohm  
DS25CP104 op/LMH0356 op – DC coupled, differential 50 ohm  
LMH0356 op/LMH0302 ip – AC coupled, differential 50 ohm  
LMH0302 op/ Scope ip – AC coupled, single ended 75 ohm

BERT testing was performed feeding back the output to the internal BERT engine FPGA and ALP software; for each test, 100k bits was transferred using a PRBS 9 pattern.




Figure 1: Final setup

### Setup/ Results:

Jitter and eye diagram data was taken at each step, to show the amount each steps adds to the total jitter of the system.

For reference for  $f = 2.97\text{Gbps}$ ,  $1 \text{ UI} = 336 \text{ ps}$

1. **Setup 1:** Source (ALP Smart SerDes) with adaptive equalizer (LMH0344)




Figure 2.1 - Block diagram Setup 1



Figure 2.2 – Eye Diagram of Setup 1

Video source pattern	Rj (ps)	Dj (ps)	Tj (ps)
Matrix Pathological	3.5	24.1	64.7

Table 1 – Jitter results of Setup 1

**BERT:** 0 errors for 100k bits sent

2. **Setup 2:** Source (ALP Smart SerDes) with adaptive equalizer (LMH0344) and crosspoint switch (DS25CP104, no PE, no EQ)




Figure 3.1 - Block diagram Setup 2




Figure 3.2 – Eye Diagram of Setup 2

Video source pattern	Rj (ps)	Dj (ps)	Tj (ps)
Matrix Pathological	4.2	28.3	74.8

Table 2 – Jitter results of Setup 2

**BERT:** 0 errors for 100k bits sent

For Setup 2 only, jitter is compared for each crosspoint configuration

		<b>Rj (ps)</b>	<b>Dj (ps)</b>	<b>Tj (ps)</b>
<b>IN0</b>	<b>OUT0</b>	3.4	20.8	61.9
<b>IN0</b>	<b>OUT1</b>	3.5	27.6	69.4
<b>IN0</b>	<b>OUT2</b>	3.4	28.7	70.7
<b>IN0</b>	<b>OUT3</b>	3.4	29.5	71.5
<b>IN1</b>	<b>OUT0</b>	3.3	26.5	65.3
<b>IN1</b>	<b>OUT1</b>	3.0	23.0	59.0
<b>IN1</b>	<b>OUT2</b>	3.4	22.9	65.0
<b>IN1</b>	<b>OUT3</b>	3.3	22.9	60.8
<b>IN2</b>	<b>OUT0</b>	3.5	30.0	71.8
<b>IN2</b>	<b>OUT1</b>	3.4	26.7	67.5
<b>IN2</b>	<b>OUT2</b>	3.3	18.7	58.7
<b>IN2</b>	<b>OUT3</b>	3.3	22.1	61.5
<b>IN3</b>	<b>OUT0</b>	3.3	24.4	64.8
<b>IN3</b>	<b>OUT1</b>	3.4	28.6	70.0
<b>IN3</b>	<b>OUT2</b>	3.5	27.3	69.3
<b>IN3</b>	<b>OUT3</b>	3.3	24.0	63.5

**Table 2.1 – Comparing jitter results for various DS25CP104 crosspoint configurations**

3. **Setup 3:** Source (ALP Smart SerDes) with adaptive equalizer (LMH0344) and crosspoint switch (DS25CP104, no PE, no EQ) and cable driver (LMH0302).




Figure 4.1 - Block diagram Setup 3




Figure 4.2 – Eye Diagram of Setup 3

Video source pattern	Rj (ps)	Dj (ps)	Tj (ps)
Matrix Pathological	5.1	36.9	96.3
PRBS11	5.7	31.2	101.5

Table 3 – Jitter results of Setup 3

BERT: 0 errors for 100k bits sent

4. **Setup 4:** Source (ALP Smart SerDes) with adaptive equalizer (LMH0344), 50 m cable (Belden 1694), crosspoint switch (DS25CP104, no PE, no EQ) and cable driver (LMH0302).




Figure 5.1 - Block diagram Setup 4




Figure 5.2 – Eye Diagram of Setup 4

Video source pattern	Rj (ps)	Dj (ps)	Tj (ps)
Matrix Pathological	7.2	54.9	143.8
PRBS11	7.5	54.7	144.9

Table 4 – Jitter results of Setup 4

**BERT:** 0 errors for 100k bits sent

5. **Setup 5:** Source (ALP Smart SerDes) with adaptive equalizer (LMH0344), 50 m cable (Belden 1694), 15 " FR4 before and after crosspoint switch (DS25CP104, PE - Hi, EQ - H) and cable driver (LMH0302).




Figure 6.1 - Block diagram Setup 5




Figure 6.2 – Eye Diagram of Setup 5

Video source pattern	Rj (ps)	Dj (ps)	Tj (ps)
Matrix Pathological	6.6	63.8	140.6
PRBS11	6.9	57.1	141

Table 5 – Jitter results of Setup 5

BERT: 0 errors for 100k bits sent



6. **Setup 6:** Source (ALP Smart SerDes) with adaptive equalizer (LMH0344), 100 m cable (Belden 1694), 15 " FR4 before and after crosspoint switch (DS25CP104, PE - Hi, EQ - H) and cable driver (LMH0302).




Figure 7.1 - Block diagram Setup 6





Figure 7.2 – Eye Diagram of Setup 6

Video source pattern	Rj (ps)	Dj (ps)	Tj (ps)
Matrix Pathological	8.4	70.9	169.6
PRBS11	9.0	63.4	174.2


Table 6 – Jitter results of Setup 6

**BERT:** 0 errors for 100k bits sent (with PE and EQ Hi),  $8.5 \times 10^{-9}$  BER (PE and EQ off)

**Setup 7:** Source (ALP Smart SerDes) with adaptive equalizer (LMH0344), 100 m cable (Belden 1694), 15 " FR4 before and after crosspoint switch (DS25CP104, PE - Hi, EQ - H), reclocker (LMH0356) and cable driver (LMH0302).



**Figure 8.1 - Block diagram Setup 7**



**Figure 8.2 – Eye Diagram of Setup 7**


Video source pattern	Rj (ps)	Dj (ps)	Tj (ps)
Matrix Pathological	2.23	21.45	47.0
PRBS11	4.3	23.9	74.6

**Table 7 – Jitter results of Setup 7**

**BERT:** 0 errors for 100k bits sent (with PE and EQ Hi)

### Cascading the DS25CP104

If a larger crosspoint switch is desired, cascading DS25CP104s can be effective; data was taken cascading three DS25CP104 channels (Setup 8):  
 PE, EQ off  
 Channels cascaded on one EVK board



**Figure 9.1 - Block diagram Setup 8**

Test Point	Rj (ps)	Dj (ps)	Tj(ps)
A	3.5	24.1	64.7
B	4.2	28.3	74.8
C	4.5	37.7	88.8
D	5.6	39.5	103.9

**Table 8 – Jitter results at each step**

### Comments

Considering the above data, the DS25CP104, with full signal conditioning, is well suited for small crosspoint switch requirements or cascaded for larger crosspoint switch configurations in 3G SDI applications.

National's ALP platform has a higher noise floor compared to dedicated pattern generators making it a more realistic source for video application testing purposes. Table 2.1 shows that using pathological patterns, the DS25CP104 outputs, with any crosspoint configuration, will not vary more than 14ps (Tj) and 10ps (Dj); a condition that is within its specification for jitter output variation.

Looking at Setup 4 and Setup 5, you see that the signal conditioning of the DS25CP104 completely compensates for 15in. of FR4 before and after the device; both yield a result of about 140ps. Also there were no errors on the BERT. Even though 140ps is 0.4UI, there are not errors and it may fit within the jitter budget of the system as a cost effective solution; if the jitter is two high then the reclocker can be used (decreasing total jitter to 40ps).

## IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

### Products

Audio	<a href="http://www.ti.com/audio">www.ti.com/audio</a>
Amplifiers	<a href="http://amplifier.ti.com">amplifier.ti.com</a>
Data Converters	<a href="http://dataconverter.ti.com">dataconverter.ti.com</a>
DLP® Products	<a href="http://www.dlp.com">www.dlp.com</a>
DSP	<a href="http://dsp.ti.com">dsp.ti.com</a>
Clocks and Timers	<a href="http://www.ti.com/clocks">www.ti.com/clocks</a>
Interface	<a href="http://interface.ti.com">interface.ti.com</a>
Logic	<a href="http://logic.ti.com">logic.ti.com</a>
Power Mgmt	<a href="http://power.ti.com">power.ti.com</a>
Microcontrollers	<a href="http://microcontroller.ti.com">microcontroller.ti.com</a>
RFID	<a href="http://www.ti-rfid.com">www.ti-rfid.com</a>
OMAP Mobile Processors	<a href="http://www.ti.com/omap">www.ti.com/omap</a>
Wireless Connectivity	<a href="http://www.ti.com/wirelessconnectivity">www.ti.com/wirelessconnectivity</a>

### Applications

Communications and Telecom	<a href="http://www.ti.com/communications">www.ti.com/communications</a>
Computers and Peripherals	<a href="http://www.ti.com/computers">www.ti.com/computers</a>
Consumer Electronics	<a href="http://www.ti.com/consumer-apps">www.ti.com/consumer-apps</a>
Energy and Lighting	<a href="http://www.ti.com/energy">www.ti.com/energy</a>
Industrial	<a href="http://www.ti.com/industrial">www.ti.com/industrial</a>
Medical	<a href="http://www.ti.com/medical">www.ti.com/medical</a>
Security	<a href="http://www.ti.com/security">www.ti.com/security</a>
Space, Avionics and Defense	<a href="http://www.ti.com/space-avionics-defense">www.ti.com/space-avionics-defense</a>
Transportation and Automotive	<a href="http://www.ti.com/automotive">www.ti.com/automotive</a>
Video and Imaging	<a href="http://www.ti.com/video">www.ti.com/video</a>

TI E2E Community Home Page

[e2e.ti.com](http://e2e.ti.com)

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2011, Texas Instruments Incorporated