

Bill of Materials

TI DESIGNS TIDA - 00222

Qty	Reference	Part Description	Manufacturer	Manufacturer Part Number	PCB Footprint	DNIe
1	!PCB1	Printed Circuit Board	Any	TIDA-00222		
		CAP, CERM, 1uF, 16V, +/-10%,				
2	C1, C7	X7R, 0603	TDK	C1608X7R1C105K	0603	
		CAP, CERM, 0.1uF, 50V, +/-10%,				
2	C2, C13	X7R, 0603	Kemet	C0603C104K5RACTU	0603	
	C3, C4, C10, C12, C14, C39,	,				
	C45, C48, C51, C52, C53,	CAP, CERM, 0.1uF, 25V, +/-5%,				
13	C54, C57	X7R, 0603	AVX	06033C104JAT2A	0603	
- 13	C3 1, C3 7	CAP, CERM, 0.01uF, 25V, +/-5%,	/\\\	00033010 13/112/1	0003	
2	C5, C6	COG/NPO, 0603	TDK	C1608C0G1E103J	0603	
	C3, C0	CAP, CERM, 100pF, 50V, +/-1%,	TDK	C1000C0G1L1033	0003	
2	C9 C0 C16	l ' ' ' ' ' ' ' ' ' ' ' ' ' ' ' ' ' ' '	A) ()/	06025410154724	0603	
3	C8, C9, C16	COG/NPO, 0603	AVX	06035A101FAT2A	0603	
2	C14 C15	CAP, CERM, 12pF, 50V, +/-5%,	4.07	00005442014724	0.000	
	C11, C15	COG/NPO, 0603	AVX	06035A120JAT2A	0603	
		CAP, TA, 4.7uF, 35V, +/-10%, 1.9				
1	C17	ohm, SMD	Vishay-Sprague	293D475X9035C2TE3	6032-28	
	C18, C19, C20, C21, C22,	CAP, CERM, 0.015uF, 50V, +/-10%,				
7	C23, C24	X7R, 0805	AVX	08055C153KAT2A	0805_HV	
	C25, C26, C27, C28, C29,					
	C30, C31, C32, C33, C34,	CAP, CERM, 47pF, 500V, +/-5%,				
14	C35, C36, C37, C38	COG/NP0, 0805	MuRata	GRM21A5C2E470JW01D	0805_HV	
		CAP, CERM, 0.1uF, 25V, +/-5%,				
0	C40, C43	X7R, 0603	AVX	06033C104JAT2A	0603	DNI
		RES 0.0 OHM 1/10W JUMP 0603				
3	C41, C42, R66	SMD	Vishay-Dale	CRCW06030000Z0EA	0603	
		CAP, CERM, 4.7uF, 10V, +/-10%,				
5	C44, C49, C50, C55, C56	X5R, 0603	AVX	0603ZD475KAT2A	0603	
		CAP, CERM, 0.47uF, 25V, +/-10%,				
2	C46, C47	X7R, 0603	MuRata	GRM188R71E474KA12J	0603	
2	D1, D2	LED, 5MM, RED, TH	VISHAY	TLHR6405	LED 5MM	
1	D3	LED SmartLED Green 570NM	OSRAM	LG L29K-G2J1-24-Z	LED0603AA	
		Diode, Switching, 200V, 0.2A, SOT-				
1	D4	23	Diodes Inc.	BAS21-7-F	SOT-23	
		DIODE ZENER 3.9V 500MW	2.0000	5,1021 / 1	50. 25	
1	D5	SOD123	Diodes Incorporated	MMSZ5228B-7-F	sod-123	
		FERRITE BEAD, 42 OHM, 4 A,	Diodes incorporated	WWW.DESEEGD 7 T	300 123	
2	FB1, FB3	DCR0.008 OHM, SMT-0805	TAIYO YUDEN	FBMJ2125HS420-T	0805 hv	
	. 51,155	FERRITE CHIP 1000 OHM 300MA	., and roblin	. 517132123113720-1	5505_11V	
1	FB2	0603	TDK Corporation	MMZ1608B102C	0603	
1	104	Header, Male 5-pin, 100mil	TER COLPOTATION	INIINITTOODTOTC	0003	
1	J1		TE Connectivity	826926-5	HEADER 5P	
1)T	spacing,	TE CONNECTIVITY	020320-3	HICADEN_SP	
4	12	Header, TH, 100mil, 12x2, Gold	FCI	67007 424445	TCW 112 07 C D	
1	J2	plated, 230 mil above insulator	FCI	67997-424HLF	TSW-112-07-G-D	
	12	Handar 8v2 100 mil TU	FCI	C7007 44 CU 5	TCM 100 07 0 5	
1	J3	Header, 8x2, 100mil, TH	FCI	67997-416HLF	TSW-108-07-G-D	
_		Header, Male 2x5-pin, 100mil				
1	J4	spacing	FCI	67997-410HLF	HDR2X5	
1	J5	3 pin berger	FCI	68001-403HLF	HDR1X3	
1	J6	Header, 2x2-pin, 100mil spacing	FCI	67997-404HLF	HDR_2X2	
	J7, J9, J10, J11, J12, J13, J14,	TERMINAL BLOCK 5.08MM VERT			CONN_ED120-	
9	J15, J16	2POS, TH	On-Shore Technology	ED120/2DS	2DS	
					3M_N2514-6002-	
1	18	Header, 7x2, 100mil, SMT	Molex	N2514-6002-RB	RB	1

Qty	Reference	Part Description	Manufacturer	Manufacturer Part Number	PCB Footprint	DNIe
		MOSFET, N-CH, 30V, 22A, SON			SON_CSD17571	
2	Q1, Q2	2X2 MM	TEXAS INSTRUMENTS	CSD17571Q2	Q2	
6	R1, R2, R62, R63, R68, R69	RES, 2.2k ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW06032K20JNEA	0603	
3	R3, R4, R16	RES, 300 ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW0603300RJNEA	0603	
		RES 10K OHM 1/10W 5% 0603				
6	R5, R8, R13, R17, R23, R24	SMD	Vishay-Dale	CRCW060310K0JNEA	0603	
4	R6, R7, R22, R29	RES, 100 ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW0603100RFKEA	0603	
2	R9, R92	RES 390K OHM 1/10W 1% 0603 SMD	Vishay Dale	CRCW0603390KFKEA	0603	
2	R10, R91	RES, 200k ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW0603200KFKEA	0603	
		RES 2.40K OHM 1/8W 1% 0805				
0	R11	SMD	Vishay-Dale	CRCW08052K40FKEA	0805_hv	DNI
1	R12	RES 2.40K OHM 1/8W 1% 0805 SMD	Vishay-Dale	CRCW08052K40FKEA	0805_hv	
4	R14, R15, R18, R19	RES, 100k ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW0603100KFKEA	0603	
· ·	,,	,,,,,	Tionay Date			
4	R20, R25, R27, R28	RES, 332k ohm, 1%, 0.125W, 0805	Vishay-Dale	CRCW0805332KFKEA	0805 HV	
1	R21	RES, 47k ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW060347K0JNEA	0603	
1	R26	RES, 30k ohm, 5%, 0.1W, 0603	Vishay-Dale Vishay-Dale	CRCW060330K0JNEA	0603	
1	R30	RES, 470 ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW0603470RJNEA	0603	
1	R31	RES, 10.0k ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW060310K0FKEA	0603	
1	R32	RES 1.00M OHM 1/10W 1% 0603 SMD	Vishay-Dale	CRCW06031M00FKEA	0603	
	R33, R34, R35, R36, R37, R38, R39, R40, R42, R43,	SIVID	Visitay-Date	CRCW00031VIOOTREA	0003	
14	R44, R45, R46, R47	RES, 1.0k ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW06031K00JNEA	0603	
0	R41	RES, 0 ohm, 5%, 0.125W, 0805	Vishay-Dale	CRCW08050000Z0EA	0805 HV	DNI
	R48, R49, R50, R51, R52,		,		_	
0	R53, R55	RES, 13.0 ohm, 1%, 0.125W, 0805	Vishay-Dale	CRCW080513R0FKEA	0805_HV	DNI
7	R54, R56, R57, R58, R59, R60, R61	RES, 13.0 ohm, 1%, 0.125W, 0805	Vichay Dala	CRCW080513R0FKEA	000E HV	
	100, 101	RES 560K OHM 1/10W 1% 0603	Vishay-Dale	CICCV080313NOI KLA	0805_HV	
0	R64, R65, R67	SMD	Vishay-Dale	CRCW0603560KFKEA	0603	DNI
	R70, R71, R73, R74, R75, R76, R77, R78, R79, R80, R81, R82, R83, R84, R85,					
20	R86, R87, R88, R89, R90	RES, 0 ohm, 5%, 0.125W, 0805	Vishay-Dale	CRCW08050000Z0EA	0805_HV	
1	R72	RES, 10 ohm, 5%, 0.125W, 0805	Vishay-Dale	CRCW080510R0JNEA	0805_HV	
		Switch, Tactile, SPST-NO, 0.1A,			SW_7914G-1-	
1	S1	16V, SMT	Bourns	7914G-1-000E	000E	
		IC, 300-mA 40-V LOW-DROPOUT REGULATOR WITH 25-uA				
1	U1	QUIESCENT CURRENT	TI	TPS7A6533QKVURQ1	KVU_1	
		LOW-VOLTAGE RAIL-TO-RAIL		577.0333QRVORQI		
1	U2	OUTPUT OPERATIONAL AMPLIFIERS, PW0014A	Texas Instruments	OPA4314AIPW	PW0014A_N	
-	- =	IC, MCU 16BIT 512KB FLASH, LQFP		- · · · · = · · · · ·	QFP50P1600X22	
1	U3	128		MSP430F6779IPEU	00X160-128N	
		IC, Micropower Shunt Voltage				
		Reference 100 ppm/°C, 45μA-				
1	U4	12mA, Adjustable	TI	LM4041BIDBZ	SOT-23	
1	Y1	CRYSTAL, 32.768KHz, 6PF, +/- 20PPM, SMD-3P	CITIZEN	CMR200T-32.768KDZBT	XTAL_CMR200T	

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design. TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, Is GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have *not* been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.