

## **TIDA-00746 REV A Bill of Materials**

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
PCB1	1		TIDA-00746	Any	Printed Circuit Board	
BIAS1, RESET1	2		5002	Keystone	Test Point, Miniature, White, TH	White Miniature Testpoint
C1, C2, C5	3	1000pF	06031C102KAT2A	AVX	CAP, CERM, 1000 pF, 100 V, +/- 10%, X7R, 0603	0603
C3, C4, C8, C10	4	10uF	GRM32ER71H106KA12L	MuRata	CAP, CERM, 10 μF, 50 V, +/- 10%, X7R, 1210	1210
C6, C7	2	4.7uF	GRM31CR71H475KA12L	MuRata	CAP, CERM, 4.7 μF, 50 V, +/- 10%, X7R, 1206	1206
C9, C11	2	4700pF	C2012X7R2A472K	TDK	CAP, CERM, 4700 pF, 100 V, +/- 10%, X7R, 0805	0805
C12	1	2.2uF	C2012X5R1H225K125AB	TDK	CAP, CERM, 2.2 μF, 50 V, +/- 10%, X5R, 0805	0805
C13, C14	2	10uF	GRM31CR61H106KA12L	MuRata	CAP, CERM, 10 µF, 50 V, +/- 10%, X5R, 1206	1206
C15, C16	2	10uF	GRM31CR71A106KA01L	MuRata	CAP, CERM, 10 μF, 10 V, +/- 10%, X7R, 1206	1206
C17, C27, C37, C52	4	2200pF	C0603C222K5RACTU	Kemet	CAP, CERM, 2200pF, 50V, +/-10%, X7R, 0603	0603
C18	1	0.47uF	GRM188R71A474KA61D	MuRata	CAP, CERM, 0.47uF, 10V, +/-10%, X7R, 0603	0603
C19, C24, C43	3	4.7uF	GRM188R61C475KAAJ	MuRata	CAP, CERM, 4.7 μF, 16 V, +/- 10%, X5R, 0603	0603
C20, C23, C42	3	0.1uF	0603YC104JAT2A	AVX	CAP, CERM, 0.1 μF, 16 V, +/- 5%, X7R, 0603	0603
C21, C25	2	47uF	GRM31CR60J476ME19L	MuRata	CAP, CERM, 47 µF, 6.3 V, +/- 20%, X5R, 1206	1206
C22, C26, Co2, Co3	4	22uF	GRM31CR71A226KE15L	MuRata	CAP, CERM, 22 μF, 10 V, +/- 10%, X7R, 1206	1206
C28, C31, C41, C46	4	0.1uF	06035C104KAT2A	AVX	CAP, CERM, 0.1uF, 50V, +/-10%, X7R, 0603	0603
C29, C30, C44, C45	4	10uF	GRM21BR71A106KE51L	MuRata	CAP, CERM, 10uF, 10V, +/-10%, X7R, 0805	0805
C32, C33, C34, C35, C47, C48, C49, C50	8	47uF	C3225X5R0J476M	TDK	CAP, CERM, 47uF, 6.3V, +/-20%, X5R, 1210	1210
C36, C51	2	0.01uF	GRM188R71H103KA01D	MuRata	CAP, CERM, 0.01uF, 50V, +/-10%, X7R, 0603	0603
C38, C53	2	DNP	06035A100JAT2A	AVX	CAP, CERM, 10pF, 50V, +/-5%, C0G/NP0, 0603	0603
C39, C54	2	47pF	08051A470JAT2A	AVX	CAP, CERM, 47 pF, 100 V, +/- 5%, C0G/NP0, 0805	0805
C40	1	2400pF	GRM1885C1H242JA01D	MuRata	CAP, CERM, 2400 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
C55	1	6800pF	06031C682KAT2A	AVX	CAP, CERM, 6800 pF, 100 V, +/- 10%, X7R, 0603	0603
Cb1	1	0.47uF	GRM188R61E474KA12D	MuRata	CAP, CERM, 0.47 μF, 25 V, +/- 10%, X5R, 0603	0603
Cbias1, Co1	2	0.1uF	GCM188R71C104KA37J	MuRata	CAP, CERM, 0.1 µF, 16 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0603	0603
CFF1	1	91pF	GRM1555C1H910JA01D	MuRata	CAP, CERM, 91 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
Cin_hf1, Cin_hf2	2	0.047uF	GRM188R71H473KA61D	MuRata	CAP, CERM, 0.047 μF, 50 V, +/- 10%, X7R, 0603	0603
Co4	1	47uF	GRM32ER71A476KE15L	MuRata	CAP, CERM, 47 μF, 10 V, +/- 10%, X7R, 1210	1210
Cvcc1	1	4.7uF	GCM21BR71C475KA73L	MuRata	CAP, CERM, 4.7 μF, 16 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0805	0805
01	1	15V	MMSZ5245B-7-F	Diodes Inc.	Diode, Zener, 15 V, 500 mW, SOD-123	SOD-123
02	1	28V	SMBJ28A-13-F	Diodes Inc.	Diode, TVS, Uni, 28 V, 600 W, SMB	SMB
03	1	14V	SMBJ14A-13-F	Diodes Inc.	Diode, TVS, Uni, 14 V, 600 W, SMB	SMB
FID4, FID5, FID6	3		N/A	N/A	Fiducial mark. There is nothing to buy or mount.	Fiducial
GND2, VOUT2	2	Double	1502-2	Keystone	Terminal, Turret, TH, Double	Keystone1502-2
GND3	1	Black	5001	Keystone	Test Point, Miniature, Black, TH	Black Miniature Testpoint
H1, H2, H3, H4	4		NY PMS 440 0025 PH	B&F Fastener Supply	Machine Screw, Round, #4-40 x 1/4, Nylon, Philips panhead	Screw
H5, H6, H7, H8	4		1902C	Keystone	Standoff, Hex, 0.5"L #4-40 Nylon	Standoff
J1	1		6091	Keystone	Standard Banana Jack, Insulated, Red	6091
J2	1		6092	Keystone	Standard Banana Jack, Insulated, Black	6092

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
J3	1		HTSW-102-07-G-S	Samtec	Header, 100mil, 2x1, Gold, TH	Header, 100mil, 2x1,
						TH
L1	1		ACM1211-102-2PL-TL01	TDK	Coupled inductor, 6 A, 0.014 ohm, SMD	SMD, 12x11mm
L2	1	2.2uH	IHLP3232DZER2R2M11	Vishay-Dale	Inductor, Shielded, Powdered Iron, 2.2 µH, 10.2 A, 0.00941 ohm, SMD	322x158x322mil
L3, L5	2	3.3uH	MOS6020-332MLB	Coilcraft	Inductor, Shielded Drum Core, Ferrite, 3.3 µH, 2.48 A, 0.05 ohm, SMD	MOS6020
L4, L6, L9	3	500 ohm	MI1206L501R-10		Ferrite Bead, 500 ohm @ 100 MHz, 2 A, 1206	1206
17	1	1uH	XFL4020-102MEB	Coilcraft	Inductor, Shielded, Composite, 1 µH, 5.4 A, 0.01 ohm, SMD	4x2x4mm
L8	1	2.2uH	SRN8040-2R2Y	Bourns	Inductor, Drum Core, Ferrite, 2.2 µH, 6.3 A, 0.013 ohm, SMD	Inductor, 8x4x8mm
LBL1	1	2.2011	THT-14-423-10	Brady	Thermal Transfer Printable Labels, 0.650" W x 0.200" H - 10,000 per roll	PCB Label 0.650"H x
			1	2.33,	1. 1. 1. 1. 1. 1. 1. 1. 1. 1. 1. 1. 1. 1	0.200"W
LF1	1	2.2uH	IHLP2020CZER2R2M11	Vishay-Dale	Inductor, Shielded Drum Core, Powdered Iron, 2.2 µH, 5.5 A, 0.025 ohm,	5.18x3x5.5mm
				1.0.1.2, 2.3.0	SMD	
Q1	1	40V	SQJ422EP-T1-GE3	Vishay-Siliconix	MOSFET, N-CH, 40 V, 75 A, PowerPAK_SO-8L	PowerPAK_SO-8L
Q2	1	-60V	SQJ461EP	Vishay-Siliconix	MOSFET, P-CH, -60 V, 30 A, PowerPAK_SO-8L	PowerPAK_SO-8L
Q3	1	60V	SQ2360EES-T1-GE3	Vishay-Siliconix	MOSFET, N/P-CH, 60 V, 4.4 A, SOT-23	SOT-23
R1, R5	2	100k	CPF0603B100KE	TE Connectivity	RES, 100 k, 0.1%, 0.063 W, 0603	0603
R2	1	20k	CRCW060320K0JNEA	Vishay-Dale	RES, 20 k, 5%, 0.1 W, 0603	0603
R3, R30	2	30.1k	CRCW060330K1FKEA	Vishay-Dale	RES, 30.1 k, 1%, 0.1 W, 0603	0603
R4	1	20.0k	CRCW060320K0FKEA	Vishay-Dale	RES, 20.0 k, 1%, 0.1 W, 0603	0603
R6	1	2.00k	CRCW06032K00FKEA	Vishay-Dale	RES, 2.00 k, 1%, 0.1 W, 0603	0603
R7, R8, R9	3	100k	CRCW0603100KJNEA	Vishay-Dale	RES, 100 k, 5%, 0.1 W, 0603	0603
R10	1	4.99	RC0805FR-074R99L	Yageo America	RES, 4.99 ohm, 1%, 0.125W, 0805	0805
R11, R17, R20,	4	4.7	CRCW08054R70JNEA	Vishay-Dale	RES, 4.7 ohm, 5%, 0.125W, 0805	0805
R29	_	7.7	CICOVOCCS4IC/OSINEA	Visitay-Date	11123, 4.7 01111, 370, 0.12377, 0003	0003
R12, R14	2	49.9k	CRCW060349K9FKEA	Vishay-Dale	RES, 49.9k ohm, 1%, 0.1W, 0603	0603
R13	1	5.10k	RG1608P-512-B-T5	Susumu Co Ltd	RES, 5.10 k, 0.1%, 0.1 W, 0603	0603
R15	1	3.83k	RG1608P-3831-B-T5	Susumu Co Ltd	RES, 3.83 k, 0.1%, 0.1 W, 0603	0603
R16, R18	2	10.2k	RG1608P-1022-B-T5	Susumu Co Ltd	RES, 10.2 k, 0.1%, 0.1 W, 0603	0603
R19, R28	2	100k	CRCW0603100KFKEA	Vishay-Dale	RES, 100k ohm, 1%, 0.1W, 0603	0603
R21	1	249k	RG1608P-2493-B-T5	Susumu Co Ltd	RES, 249 k, 0.1%, 0.1 W, 0603	0603
R22, R31		82.5k	CRCW060382K5FKEA	Vishay-Dale	RES, 82.5 k, 1%, 0.1 W, 0603	0603
R23, R32	2	80.6k	CRCW060380K6FKEA	Vishay-Dale Vishay-Dale	RES, 80.6 k, 1%, 0.1 W, 0603	0603
R26	1	4.75k	CRCW06034K75FKEA	Vishay-Dale Vishay-Dale	RES, 4.75 k, 1%, 0.1 W, 0603	0603
R33	1	2.61k	CRCW06034K75FKEA	Vishay-Dale Vishay-Dale	RES, 2.61 k, 1%, 0.1 W, 0603	0603
Rbias1	1	3.0	CRCW06032R011REA	Vishay-Dale Vishay-Dale	RES, 3.0, 5%, 0.1 W, 0603	0603
RFBB1	1	20.0k	CRCW040220K0FKED	Vishay-Dale Vishay-Dale	RES, 20.0 k, 1%, 0.063 W, 0402	0402
RFBT1	1	80.6k	CRCW040280K6FKED	Vishay-Dale Vishay-Dale	RES, 80.6 k, 1%, 0.063 W, 0402	0402
TP1, TP2, TP3,	9	Double	1503-2	Keystone	Terminal, Turret, TH, Double	Keystone1503-2
	9	Double	1505-2	Reystorie		Reystone 1505-2
TP4, TP5, TP6, TP7, TP8, TP9						
	1		LM74610	Toyon Instruments		MCOD 0
U1 U2	1		LM74610	Texas Instruments	Automotive Catalog Law Valtage Adjustable Presision Churt Pagulatar 90	MSOP-8
02	1		TLVH431AQDBVRQ1	Texas Instruments	Automotive Catalog Low-Voltage Adjustable Precision Shunt Regulator, 80	DBA0002A
					mA, -40 to 125 degC, 5-pin SOT-23 (DBV), Green (RoHS & no Sb/Br)	
110	4		LMEGGGENOPH DO4	Tavas la atmuni i i i	O S/O SA Complementaria Disabili Describeto (Co. A. Co. C. C. A. C. C. C.	DNII 0000A
U3	1		LM53635MQRNLRQ1	Texas Instruments	2.5/3.5A Synchronous Buck Regulator for Automotive Applications,	RNL0022A
114			L MOCACOVOC /NICED	National Comittee Later	RNL0022A	000464
U4	1		LM26420XSQ/NOPB	National Semiconductor	Dual 2.0A, High Frequency Synchronous Step-Down DC-DC Regulator, 16	SQB16A
			TD0574440DT5D04	T	pin LLP, Pb-Free	DTECOACE
U5	1		TPS57114QRTERQ1	Texas Instruments	2.95 V to 6 V Input, 4-A Output, 2MHz, Synchronous Step Down Switcher,	K1E0016F
110			TD0574400DT5004	To an Institute of	RTE0016F	DTECOACE
U6	1		TPS57112QRTERQ1	Texas Instruments	2.95 V to 6 V Input, 2-A Output, 2MHz, Synchronous Step Down Switcher,	K1E0016F
					RTE0016F	

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
VINs1	1		5000	Keystone	Test Point, Miniature, Red, TH	Red Miniature
						Testpoint
FID1, FID2, FID3	0		N/A	N/A	Fiducial mark. There is nothing to buy or mount.	Fiducial

## IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ('TI") reference designs are solely intended to assist designers ("Designer(s)") who are developing systems that incorporate TI products. TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design.

Tl's provision of reference designs and any other technical, applications or design advice, quality characterization, reliability data or other information or services does not expand or otherwise alter Tl's applicable published warranties or warranty disclaimers for Tl products, and no additional obligations or liabilities arise from Tl providing such reference designs or other items.

TI reserves the right to make corrections, enhancements, improvements and other changes to its reference designs and other items.

Designer understands and agrees that Designer remains responsible for using its independent analysis, evaluation and judgment in designing Designer's systems and products, and has full and exclusive responsibility to assure the safety of its products and compliance of its products (and of all TI products used in or for such Designer's products) with all applicable regulations, laws and other applicable requirements. Designer represents that, with respect to its applications, it has all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. Designer agrees that prior to using or distributing any systems that include TI products, Designer will thoroughly test such systems and the functionality of such TI products as used in such systems. Designer may not use any TI products in life-critical medical equipment unless authorized officers of the parties have executed a special contract specifically governing such use. Life-critical medical equipment is medical equipment where failure of such equipment would cause serious bodily injury or death (e.g., life support, pacemakers, defibrillators, heart pumps, neurostimulators, and implantables). Such equipment includes, without limitation, all medical devices identified by the U.S. Food and Drug Administration as Class III devices and equivalent classifications outside the U.S.

Designers are authorized to use, copy and modify any individual TI reference design only in connection with the development of end products that include the TI product(s) identified in that reference design. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of the reference design or other items described above may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS AND OTHER ITEMS DESCRIBED ABOVE ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY DESIGNERS AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS AS DESCRIBED IN A TI REFERENCE DESIGN OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

Tl's standard terms of sale for semiconductor products (<a href="http://www.ti.com/sc/docs/stdterms.htm">http://www.ti.com/sc/docs/stdterms.htm</a>) apply to the sale of packaged integrated circuit products. Additional terms may apply to the use or sale of other types of TI products and services.

Designer will fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of Designer's non-compliance with the terms and provisions of this Notice.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2016, Texas Instruments Incorporated