Filename: Pro9B18.tmp Variant: 001 Generated: 12/8/2016 10:50:46 AM TID #: N/A

PMP20080 REV A Bill of Materials



item #	Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageRefe
1	C1, C20, C27,	6	0.1uF	GRM155R61E104KA87D	MuRata	CAP, CERM, 0.1uF, 25V, +/-10%, X5R, 0402	0402
2	C29, C56, C57 C2, C3, C4, C5,	6	22uF	C3216X5R0J226K	TDK	CAP, CERM, 22 µF, 6.3 V, +/- 20%, X5R, 1206	1206
2	C2, C3, C4, C5, C6, C7	0	ZZUF	C3210A3R03220R	IDK	CAP, CERM, 22 µF, 0.3 V, +/- 20%, ASR, 1206	1200
3	C8, C10, C22,	4	1uF	C1608X7R1E105K080AB	TDK	CAP, CERM, 1 µF, 25 V, +/- 10%, X7R, 0603	0603
	C51						
4	C9	1	4700pF	C3216C0G1H472J	TDK	CAP, CERM, 4700 pF, 50 V, +/- 5%, C0G/NP0, 1206	1206
5	C12	1	560uF	20SVPF560M	Panasonic	CAP, Aluminum Polymer, 560 μF, 20 V, +/- 20%, 0.012 ohm, F12,	F12, SMD, 2-L Body 10.5x10.
						SMD, 2-Leads, Body 10.5x10.5mm, Height 12.7mm SMD	Height 12.7mn
6	C13, C14, C15,	9	100uF	GRM32ER60J107ME20L	MuRata	CAP, CERM, 100uF, 6.3V, +/-20%, X5R, 1210	1210
	C16, C17, C59,						
7	C60, C61, C62	4	47.5	005040405000	Musth Electronic		0.400
7 8	C18 C19, C28, C43	1 3	4.7uF 0.01uF	885012105008 885012205031	Wurth Elektronik Wurth Elektronik	CAP, CERM, 4.7 µF, 6.3 V, +/- 20%, X5R, 0402 CAP, CERM, 0.01 µF, 16 V, +/- 10%, X7R, 0402	0402 0402
9	C21, C39, C58,	4	330pF	C1005C0G1H331J	TDK	CAP, CERM, 330 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
	C66						
10	C23, C44, C52	3	10uF	885012208069	Wurth Elektronik	CAP, CERM, 10 μF, 25 V, +/- 10%, X7R, 1206	1206
11	C24, C25, C26, C68	4	22uF	CL32A226KAJNNNE	Samsung Electro-Mechanics	CAP, CERM, 22 µF, 25 V, +/- 10%, X5R, 1210	1210
12	C30	1	33pF	GRM1555C1H330JA01D	MuRata	CAP, CERM, 33 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
13	C31	1	680pF	GRM1555C1H681JA01D	MuRata	CAP, CERM, 680 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
14	C32, C33, C34,	6	100uF	C3216X5R1A107M160AC	TDK	CAP, CERM, 100 µF, 10 V, +/- 20%, X5R, 1206_190	1206_190
45	C35, C36, C37	4	4000-E	0000055504100000000	MuData		0.400
15 16	C38 C40, C41, C65,	1 4	1000pF 1uF	GRM1555C1H102JA01D GRM155R61A105KE15D	MuRata MuRata	CAP, CERM, 1000 pF, 50 V, +/- 5%, C0G/NP0, 0402 CAP, CERM, 1uF, 10V, +/-10%, X5R, 0402	0402 0402
10	C40, C41, C65, C67	4	i di	GRANI JORG TA TUDICE TOD	mullala	0/1, 0ENW, 101, 107, 7/10/0, AJK, 0402	0402
17	C42	1		885012205029	Wurth Elektronik	DNP, 0402	0402
18	C45, C46, C47	3	10uF	GRM21BR70J106KE76L	MuRata	CAP, CERM, 10 μF, 6.3 V, +/- 10%, X7R, 0805	0805
19	C48	1	22pF	C1005C0G1H220J050BA	TDK	CAP, CERM, 22 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
20 21	C49 C50	1	4.7uF 4.7uF	GRM319R61E475KA12D C1608X5R0J475M	MuRata TDK	CAP, CERM, 4.7 µF, 25 V, +/- 10%, X5R, 1206 CAP, CERM, 4.7 µF, 6.3 V, +/- 20%, X5R, 0603	1206 0603
21	C50 C54	1	4.7uF 10pF	GRM1555C1H100JA01D	MuRata	CAP, CERM, 4.7 µP, 6.3 V, +/- 20%, XSR, 0603 CAP, CERM, 10 pF, 50 V, +/- 5%, C0G/NP0, 0402	0603
23	C55, C63	2	1500pF	GRM155R71H152KA01D	MuRata	CAP, CERM, 1500 pF, 50 V, +/- 10%, X7R, 0402	0402
24	C64	1	220pF	GRM155R71H221KA01D	MuRata	CAP, CERM, 220 pF, 50 V, +/- 10%, X7R, 0402	0402
25	C100	1	680uF	UUD0J681MNL1GS	Nichicon	CAP, AL, 680 µF, 6.3 V, +/- 20%, 0.17 ohm, SMD	8x10
26 27	J1, J5, J6, J7 J2, J4	4		ED555/2DS OSTTA024163	On-Shore Technology On-Shore Technology	Terminal Block, 6A, 3.5mm Pitch, 2-Pos, TH Terminal Block, 2x1, 5.08mm, TH	7.0x8.2x6.5mr 2x1 Terminal E
28	J3	1		5103308-1	TE Connectivity	Header (shrouded), 100mil, 5x2, Gold, TH	5x2 Shrouded
					-		
29	L1, L2	2	470nH	IHLP2525CZEBR47M01	Vishay-Dale	Inductor, Shielded, Ferrite, 470 nH, 17.5 A, 0.0042 ohm, SMD	6.47x3x6.86
30	L3	1	2.2uH	BRC2012T2R2MD	Taiyo Yuden	Inductor, Wirewound, 2.2 µH, 1 A, 0.143 ohm, SMD	0805_140
31 32	L4 L5	1	22uH 3.3uH	LQH3NPN220MG0 IHLP2020CZER3R3M11	MuRata Vishay-Dale	Inductor, Wirewound, Ferrite, 22 µH, 0.34 A, 1.1 ohm, SMD Inductor, Shielded Drum Core, Powdered Iron, 3.3 µH, 5.5 A, 0.0404	3.0x0.9x3.0mr 5.18x3x5.5mm
52			0.0011	IN LA ZOZOOZE NONOWITI	tionay Date	ohm, SMD	0.10x0x0.01111
33	Q1	1	0.2V	MMBT3904	Fairchild Semiconductor	Transistor, NPN, 40V, 0.2A, SOT-23	SOT-23
34	Q2	1		CSD87588N	Texas Instruments	Synchronous Buck NexFET Power Block II, MPA0005A	MPA0005A
35 36	Q3	1	20V	CSD85301Q2 CRCW04020000Z0ED	Texas Instruments	MOSFET, N-CH, 20 V, 6.7 A, RES, 0 ohm, 5%, 0.063W, 0402	0402
30	R1, R12, R13, R14, R38, R47, R51	<i>'</i>	0	GING W 0402000020ED	Vishay-Dale	INES, 0 01111, 376, 0.00399, 0402	0402
37	R2, R3	2	10	CRCW040210R0JNED	Vishay-Dale	RES, 10, 5%, 0.063 W, 0402	0402
38	R4, R11, R20, R26, R46, R48,	7	49.9	CRCW040249R9FKED	Vishay-Dale	RES, 49.9 ohm, 1%, 0.063W, 0402	0402
39	R49 R5	1	10.0k	CRCW060310K0FKEA	Vishay-Dale	RES, 10.0 k, 1%, 0.1 W, 0603	0603
39 40	R5 R6	1	10.0k 2.94k	CRCW060310K0FKEA	Vishay-Dale	RES, 10.0 k, 1%, 0.1 W, 0603 RES, 2.94 k, 1%, 0.1 W, 0603	0603
41	R7	1	38.3k	CRCW040238K3FKED	Vishay-Dale	RES, 38.3 k, 1%, 0.063 W, 0402	0402
42	R8, R9	2	54.9k	CRCW040254K9FKED	Vishay-Dale	RES, 54.9 k, 1%, 0.063 W, 0402	0402
43	R10	1	20.0k	CRCW060320K0FKEA	Vishay-Dale	RES, 20.0 k, 1%, 0.1 W, 0603	0603
44	R15, R19, R23, R25, R35, R39, R44, R50	8	10.0k	CRCW040210K0DHEDP	Vishay-Dale	RES, 10.0 k, 0.5%, 0.063 W, 0402	0402
45	R16	1	1.13k	CRCW04021K13FKED	Vishay-Dale	RES, 1.13 k, 1%, 0.063 W, 0402	0402
46	R17	1	17.8k	CRCW040217K8FKED	Vishay-Dale	RES, 17.8 k, 1%, 0.063 W, 0402	0402
17 18	R21, R22	2	84.5k	CRCW040284K5FKED CRCW0402499RFKED	Vishay-Dale	RES, 84.5 k, 1%, 0.063 W, 0402	0402 0402
48 49	R24 R27, R52	1	499 100k	CRCW0402499RFKED CRCW0402100KFKED	Vishay-Dale Vishay-Dale	RES, 499, 1%, 0.063 W, 0402 RES, 100k ohm, 1%, 0.063W, 0402	0402
50	R28	1	392k	CRCW0402392KFKED	Vishay-Dale	RES, 392 k, 1%, 0.063 W, 0402	0402
51	R29	1	178k	CRCW0402178KFKED	Vishay-Dale	RES, 178 k, 1%, 0.063 W, 0402	0402
52	R30	1	205k	CRCW0402205KFKED	Vishay-Dale	RES, 205 k, 1%, 0.063 W, 0402	0402
53 54	R31	1	232k	CRCW0402232KFKED CRCW04021K50FKED	Vishay-Dale	RES, 232 k, 1%, 0.063 W, 0402	0402
54 55	R33 R34, R36	1	1.50k 36.5k	CRCW04021K50FKED CRCW040236K5FKED	Vishay-Dale Vishay-Dale	RES, 1.50 k, 1%, 0.063 W, 0402 RES, 36.5k ohm, 1%, 0.063W, 0402	0402 0402
56	R37	1	20.0k	CRCW040220K0FKED	Vishay-Dale	RES, 20.0 k, 1%, 0.063 W, 0402	0402
57	R40	1	2.49k	CRCW04022K49FKED	Vishay-Dale	RES, 2.49 k, 1%, 0.063 W, 0402	0402
58	R41	1	6.8	CRCW04026R80JNED	Vishay-Dale	RES, 6.8, 5%, 0.063 W, 0402	0402
59 60	R42 R43, R45	1	249 100	CRCW0402249RFKED CRCW0402100RFKED	Vishay-Dale Vishay-Dale	RES, 249, 1%, 0.063 W, 0402 RES, 100 ohm, 1%, 0.063W, 0402	0402 0402
61	R43, R45 U1	2	100	TPS544B20RVFR	Texas Instruments	TPS544B20 18V, 20A PMBUS SYNCHRONOUS BUCK CONVERTERS,	0402 RVF0040A
62	U2, U5	2		TPS40400RHLR	Texas Instruments	3.0-V TO 20-V PMBus SYNCHRONOUS BUCK CONTROLLER,	RHL0024A
63	U3	1		TPS62170DSGR	Texas Instruments	RHL0024A Buck Step Down Regulator with 3 to 17 V Input and 0.9 to 6 V Output, -	DSG0008A
				TR0000400800/		40 to 85 degC, 8-Pin WSON (DSG), Green (RoHS & no Sb/Br)	DOUGS
64	U4	1	FEOUE	TPS62120DCNR	Texas Instruments	15-V, 75-mA Highly Efficient Buck Converter, DCN0008A	DCN0008A
65	C11	0	560uF	20SVPF560M	Panasonic	CAP, Aluminum Polymer, 560 μF, 20 V, +/- 20%, 0.012 ohm, F12, SMD, 2-Leads, Body 10.5x10.5mm, Height 12.7mm SMD	F12, SMD, 2-L Body 10.5x10.
							Height 12.7n

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ('TI') reference designs are solely intended to assist designers ("Designer(s)") who are developing systems that incorporate TI products. TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design.

TI's provision of reference designs and any other technical, applications or design advice, quality characterization, reliability data or other information or services does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such reference designs or other items.

TI reserves the right to make corrections, enhancements, improvements and other changes to its reference designs and other items.

Designer understands and agrees that Designer remains responsible for using its independent analysis, evaluation and judgment in designing Designer's systems and products, and has full and exclusive responsibility to assure the safety of its products and compliance of its products (and of all TI products used in or for such Designer's products) with all applicable regulations, laws and other applicable requirements. Designer represents that, with respect to its applications, it has all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. Designer agrees that prior to using or distributing any systems that include TI products, Designer will thoroughly test such systems and the functionality of such TI products as used in such systems. Designer may not use any TI products in life-critical medical equipment unless authorized officers of the parties have executed a special contract specifically governing such use. Life-critical medical equipment is medical equipment where failure of such equipment would cause serious bodily injury or death (e.g., life support, pacemakers, defibrillators, heart pumps, neurostimulators, and implantables). Such equivalent classifications outside the U.S.

Designers are authorized to use, copy and modify any individual TI reference design only in connection with the development of end products that include the TI product(s) identified in that reference design. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of the reference design or other items described above may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS AND OTHER ITEMS DESCRIBED ABOVE ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY DESIGNERS AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS AS DESCRIBED IN A TI REFERENCE DESIGN OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

TI's standard terms of sale for semiconductor products (<u>http://www.ti.com/sc/docs/stdterms.htm</u>) apply to the sale of packaged integrated circuit products. Additional terms may apply to the use or sale of other types of TI products and services.

Designer will fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of Designer's noncompliance with the terms and provisions of this Notice.

> Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2016, Texas Instruments Incorporated